

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912466

Luminaire Tested: DFN2DIP-TR2F0-030D020US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912466
REPORT IS A COMBINATION OF REPORTS P900224 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-030D020US850-RLLFLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4790.9 lumens
Efficiency: N/A
Efficacy: 118.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 40.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912466
CATALOG NUMBER: DFN2DIP-TR2F0-030D020US850-RLLFLL

Luminous Intensity Polar Plot



41% Up

59% Dn



TEST NUMBER: P912466
 CATALOG NUMBER: DFN2DIP-TR2F0-030D020US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59			59
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51			51
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48	44			44
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41	38			38
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36	33			33
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	34	32	29			29
6	66	54	46	40	61	51	44	39	45	39	35	40	35	32	35	31	28	26			26
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23			23
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21			21
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	24	21	19			19
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19	17			17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3067	3067	3067
5°	3067	3011	3032
10°	3032	2946	2929
15°	2986	2841	2771
20°	2926	2701	2580
25°	2865	2545	2395
30°	2785	2385	2163
35°	2705	2214	1959
40°	2624	2038	1726
45°	2531	1844	1515
50°	2433	1648	1310
55°	2331	1439	1113
60°	2213	1223	911
65°	2077	1004	814
70°	1912	799	730
75°	1703	692	653
80°	1404	561	551
85°	923	348	387

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2531 cd/sqm



TEST NUMBER: P912466

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US850-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.9	2.7
10°-20°	353.8	7.4
20°-30°	496.7	10.4
30°-40°	541.4	11.3
40°-50°	497.6	10.4
50°-60°	390.8	8.2
60°-70°	254.4	5.3
70°-80°	130.9	2.7
80°-90°	35.4	0.7
90°-100°	43.4	0.9
100°-110°	137.9	2.9
110°-120°	236.0	4.9
120°-130°	310.4	6.5
130°-140°	348.4	7.3
140°-150°	341.7	7.1
150°-160°	286.6	6.0
160°-170°	190.1	4.0
170°-180°	66.4	1.4
0°-30°	979.3	20.4
0°-40°	1520.7	31.7
0°-60°	2409.2	50.3
0°-90°	2829.9	59.1
90°-120°	417.3	8.7
90°-150°	1417.8	29.6
90°-180°	1961.0	40.9
0°-180°	4790.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1375	1375	1375	1375	1375	
5°	1375	1369	1353	1364	1360	130
15°	1308	1294	1252	1228	1216	369
25°	1187	1147	1065	1014	995	546
35°	1023	959	850	772	744	640
45°	836	753	622	534	504	646
55°	636	539	404	330	306	568
65°	429	328	216	174	170	426
75°	229	142	100	91	90	242
85°	54	27	24	24	24	61
90°	1	8	21	19	20	5
95°	31	37	38	38	37	34
105°	127	129	130	131	131	134
115°	237	240	239	238	237	234
125°	344	350	348	346	346	308
135°	446	452	453	453	451	344
145°	541	545	549	549	547	338
155°	619	620	622	625	623	285
165°	673	672	672	676	674	190
175°	700	699	697	701	698	67
180°	701	701	701	701	701	



TEST NUMBER: P912466

CATALOG NUMBER: DFN2DIP-TR2FO-030D020US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1375.0	1375.0	1375.0	1375.0	1375.0
2.5°	1381.3	1375.0	1361.3	1373.8	1371.4
5°	1375.0	1368.8	1352.6	1363.8	1360.1
7.5°	1363.8	1356.4	1339.0	1343.9	1337.7
10°	1348.9	1340.2	1315.4	1311.5	1304.2
12.5°	1330.2	1319.0	1285.4	1278.0	1264.3
15°	1307.8	1294.1	1251.8	1228.2	1215.8
17.5°	1281.7	1261.8	1209.5	1182.2	1162.2
20°	1251.8	1226.9	1164.7	1133.7	1106.2
22.5°	1219.6	1190.8	1118.6	1076.4	1057.8
25°	1187.2	1147.3	1065.2	1014.2	995.4
27.5°	1148.6	1106.2	1015.4	957.0	928.2
30°	1107.6	1060.2	960.6	897.3	863.6
32.5°	1067.6	1010.4	908.5	833.7	802.6
35°	1022.9	959.4	849.9	771.5	744.1
37.5°	979.4	910.8	795.2	709.2	678.3
40°	933.3	858.7	737.9	649.5	617.3
42.5°	886.0	806.5	680.7	588.5	557.5
45°	836.3	752.8	622.3	533.8	503.9
47.5°	788.9	700.7	566.3	477.8	450.5
50°	736.7	648.3	511.5	425.5	399.5
52.5°	685.6	592.3	459.2	377.1	353.4
55°	635.8	538.8	404.3	329.8	306.2
57.5°	584.9	485.3	356.0	286.2	266.3
60°	532.5	433.1	304.9	241.4	221.6
62.5°	481.6	382.1	261.3	201.6	191.7
65°	429.3	328.5	216.5	174.2	170.5
67.5°	379.6	278.7	174.2	153.0	149.3
70°	327.3	230.2	144.3	131.9	126.9
72.5°	277.5	185.3	120.7	110.8	108.2
75°	228.9	141.8	99.6	90.8	89.6
77.5°	180.4	100.7	78.4	73.4	70.9
80°	135.6	72.2	59.7	54.8	54.8
82.5°	94.5	48.6	41.0	38.6	38.6
85°	53.5	27.3	23.6	23.6	23.6
87.5°	20.0	9.9	9.9	8.8	8.8
90°	0.7	7.7	20.7	19.4	20.1
92.5°	13.1	17.7	18.4	19.1	19.1
95°	30.8	36.8	37.8	37.8	36.8
97.5°	51.3	56.9	59.2	59.2	59.2
100°	75.1	80.0	81.6	81.6	81.0
102.5°	100.0	103.6	105.9	106.6	105.9
105°	127.3	129.0	130.3	131.3	131.3
107.5°	154.4	156.9	156.9	157.4	154.4
110°	180.7	184.0	184.0	184.0	182.3



TEST NUMBER: P912466

CATALOG NUMBER: DFN2DIP-TR2F0-030D020US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	208.9	212.5	211.9	210.2	208.9
115°	236.9	240.2	239.2	238.5	236.9
117.5°	264.6	269.3	266.3	264.6	262.8
120°	292.4	297.1	292.4	292.4	290.6
122.5°	317.8	323.7	320.8	319.2	317.8
125°	344.5	349.8	348.1	346.2	345.6
127.5°	370.5	377.1	374.7	372.2	370.5
130°	394.8	402.5	401.3	400.1	397.8
132.5°	422.1	428.1	428.4	425.5	423.7
135°	445.6	452.1	453.4	452.8	451.0
137.5°	471.8	477.1	478.2	477.8	475.2
140°	494.8	500.2	503.2	503.2	500.8
142.5°	518.6	523.8	525.6	526.1	523.8
145°	541.0	545.2	548.6	549.2	546.8
147.5°	561.0	566.4	568.9	569.9	567.6
150°	581.8	585.3	587.7	589.5	587.7
152.5°	600.2	603.7	606.7	609.1	606.7
155°	618.6	620.3	622.1	625.1	623.3
157.5°	634.5	635.7	636.8	641.0	638.0
160°	648.7	649.9	650.5	654.1	651.5
162.5°	661.7	661.7	662.3	666.4	663.4
165°	672.9	672.3	672.3	676.5	673.6
167.5°	683.0	681.1	681.1	685.4	682.5
170°	690.7	689.0	688.4	692.6	689.0
172.5°	696.0	694.2	693.7	697.9	694.2
175°	700.2	698.6	697.2	701.4	697.9
177.5°	702.6	700.9	699.6	703.1	699.6
180°	701.4	701.4	701.4	701.4	701.4



TEST NUMBER: P912466
 CATALOG NUMBER: DFN2DIP-TR2F0-030D020US850-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.72	12.63	12.60	13.53	14.66	7.70	8.61	8.58	9.51	10.65
	3H	13.38	14.19	14.27	15.10	16.26	8.88	9.69	9.77	10.60	11.76
	4H	13.97	14.74	14.88	15.66	16.83	9.32	10.09	10.23	11.00	12.18
	6H	14.38	15.09	15.30	16.01	17.19	9.63	10.34	10.55	11.26	12.45
	8H	14.50	15.17	15.43	16.11	17.29	9.72	10.39	10.65	11.33	12.51
	12H	14.55	15.19	15.49	16.12	17.33	9.76	10.40	10.69	11.33	12.54
4H	2H	11.74	12.51	12.66	13.42	14.60	8.29	9.06	9.21	9.97	11.15
	3H	13.55	14.19	14.48	15.13	16.32	9.63	10.27	10.56	11.21	12.40
	4H	14.23	14.81	15.16	15.75	16.96	10.17	10.75	11.10	11.69	12.90
	6H	14.73	15.23	15.67	16.19	17.40	10.57	11.08	11.52	12.04	13.25
	8H	14.89	15.36	15.84	16.31	17.54	10.70	11.16	11.65	12.12	13.35
	12H	14.97	15.40	15.94	16.37	17.60	10.76	11.18	11.73	12.15	13.38
8H	4H	14.20	14.67	15.15	15.62	16.85	10.44	10.91	11.39	11.86	13.09
	6H	14.74	15.13	15.72	16.13	17.35	10.94	11.33	11.92	12.32	13.55
	8H	14.94	15.28	15.93	16.27	17.52	11.12	11.46	12.10	12.45	13.69
	12H	15.07	15.37	16.06	16.35	17.64	11.23	11.53	12.22	12.51	13.80
12H	4H	14.15	14.57	15.12	15.55	16.78	10.44	10.87	11.41	11.84	13.07
	6H	14.72	15.06	15.70	16.04	17.29	10.98	11.32	11.97	12.31	13.56
	8H	14.92	15.22	15.91	16.20	17.50	11.18	11.48	12.17	12.46	13.76