

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904405

Luminaire Tested: DFN2DIP-TR3F0-040D070US830-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904405
REPORT IS A COMBINATION OF REPORTS P901850 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-040D070US830-RLLONL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9736.4 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904405
CATALOG NUMBER: DFN2DIP-TR3F0-040D070US830-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P904405
 CATALOG NUMBER: DFN2DIP-TR3F0-040D070US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	40	40	40	33
1	94	90	87	83	85	81	78	76	65	63	61	50	49	48	36	35	35	35	35	35	28
2	86	79	73	68	77	72	67	62	57	54	51	44	42	40	32	31	30	30	30	30	24
3	79	70	63	57	71	63	57	53	51	47	43	39	37	34	29	27	26	26	26	26	21
4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	22	22	22	22	18
5	66	55	47	42	59	50	43	38	41	36	32	32	28	26	24	21	20	20	20	20	16
6	61	49	42	36	55	45	38	33	37	32	28	29	25	23	21	19	17	17	17	17	14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	17	16	16	16	16	13
8	52	41	33	28	47	37	31	26	30	25	22	24	21	18	18	16	14	14	14	14	12
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13	13	13	13	10
10	45	34	27	22	41	31	25	21	26	21	18	20	17	15	16	13	12	12	12	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1942	1942	1942
5°	1944	1909	1922
10°	1923	1870	1858
15°	1896	1807	1760
20°	1860	1720	1641
25°	1823	1623	1525
30°	1774	1524	1379
35°	1725	1417	1251
40°	1676	1307	1104
45°	1619	1185	971
50°	1559	1063	841
55°	1498	931	716
60°	1426	794	589
65°	1343	655	528
70°	1243	526	476
75°	1117	460	430
80°	934	381	369
85°	636	247	270

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1619 cd/sqm



TEST NUMBER: P904405

CATALOG NUMBER: DFN2DIP-TR3F0-040D070US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.0	1.5
10°-20°	400.9	4.1
20°-30°	562.8	5.8
30°-40°	613.5	6.3
40°-50°	563.9	5.8
50°-60°	442.9	4.5
60°-70°	288.3	3.0
70°-80°	148.4	1.5
80°-90°	41.8	0.4
90°-100°	73.4	0.8
100°-110°	273.7	2.8
110°-120°	725.9	7.5
120°-130°	1204.0	12.4
130°-140°	1278.9	13.1
140°-150°	1188.6	12.2
150°-160°	955.6	9.8
160°-170°	615.8	6.3
170°-180°	211.9	2.2
0°-30°	1109.8	11.4
0°-40°	1723.3	17.7
0°-60°	2730.1	28.0
0°-90°	3208.5	33.0
90°-120°	1073.0	11.0
90°-150°	4744.6	48.7
90°-180°	6528.0	67.0
0°-180°	9736.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1558	1558	1558	1558	1558	
5°	1558	1551	1533	1546	1541	148
15°	1482	1466	1419	1392	1378	418
25°	1345	1300	1207	1149	1128	619
35°	1159	1087	963	874	843	726
45°	948	853	705	605	571	732
55°	721	611	458	374	347	644
65°	486	372	245	198	193	482
75°	259	161	113	103	102	274
85°	61	31	27	27	27	70
90°	2	19	32	40	44	9
95°	105	52	63	71	69	124
105°	490	538	98	116	122	523
115°	926	954	994	248	132	912
125°	1310	1331	1362	1373	1378	1168
135°	1621	1647	1661	1677	1674	1252
145°	1880	1879	1906	1917	1909	1176
155°	2070	2056	2075	2085	2072	954
165°	2182	2172	2177	2188	2177	616
175°	2232	2220	2224	2235	2219	212
180°	2227	2227	2227	2227	2227	



TEST NUMBER: P904405

CATALOG NUMBER: DFN2DIP-TR3F0-040D070US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1558.2	1558.2	1558.2	1558.2	1558.2
2.5°	1565.3	1558.2	1542.7	1556.9	1554.0
5°	1558.2	1551.1	1532.8	1545.5	1541.3
7.5°	1545.5	1537.1	1517.4	1522.9	1515.9
10°	1528.6	1518.7	1490.5	1486.2	1477.9
12.5°	1507.5	1494.8	1456.6	1448.2	1432.7
15°	1482.1	1466.5	1418.6	1391.9	1377.8
17.5°	1452.5	1429.8	1370.6	1339.6	1317.0
20°	1418.6	1390.3	1319.8	1284.7	1253.6
22.5°	1382.0	1349.5	1267.6	1219.7	1198.7
25°	1345.3	1300.1	1207.0	1149.3	1128.0
27.5°	1301.7	1253.6	1150.7	1084.4	1051.9
30°	1255.1	1201.4	1088.5	1016.7	978.6
32.5°	1209.9	1145.0	1029.4	944.8	909.5
35°	1159.2	1087.2	963.2	874.3	843.2
37.5°	1109.8	1032.2	901.1	803.7	768.5
40°	1057.6	973.1	836.2	736.1	699.5
42.5°	1004.0	913.8	771.4	666.9	631.8
45°	947.6	853.1	705.1	604.9	571.1
47.5°	894.1	794.0	641.7	541.5	510.5
50°	834.8	734.7	579.6	482.2	452.7
52.5°	776.9	671.2	520.4	427.3	400.5
55°	720.6	610.6	458.3	373.7	346.9
57.5°	662.8	550.0	403.3	324.3	301.8
60°	603.5	490.7	345.4	273.6	251.1
62.5°	545.8	433.0	296.1	228.5	217.3
65°	486.5	372.2	245.3	197.5	193.1
67.5°	430.2	315.8	197.5	173.4	169.2
70°	370.9	260.9	163.5	149.5	143.7
72.5°	314.5	210.1	136.8	125.5	122.7
75°	259.4	160.7	112.8	102.9	101.6
77.5°	204.5	114.1	88.9	83.2	80.3
80°	153.6	81.8	67.6	62.1	62.1
82.5°	107.2	55.0	46.6	43.6	43.6
85°	60.6	31.0	26.8	26.8	26.8
87.5°	22.6	11.2	11.2	9.9	9.9
90°	1.5	19.3	32.1	40.3	43.5
92.5°	40.3	33.8	38.6	41.9	43.5
95°	104.6	51.5	62.8	71.0	69.3
97.5°	188.4	56.5	82.1	87.1	88.6
100°	285.3	64.5	91.8	104.6	107.9
102.5°	391.4	388.4	95.1	112.7	117.6
105°	489.8	538.2	98.3	115.9	122.4
107.5°	604.2	644.4	101.6	119.2	125.7
110°	713.9	747.5	282.0	120.9	127.2



TEST NUMBER: P904405

CATALOG NUMBER: DFN2DIP-TR3F0-040D070US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	817.0	845.8	818.5	123.9	128.9
115°	926.4	953.8	994.1	248.2	132.2
117.5°	1021.5	1053.7	1081.2	850.6	428.6
120°	1127.8	1152.0	1181.1	1200.4	982.9
122.5°	1218.0	1243.8	1276.2	1285.7	1287.4
125°	1309.9	1330.9	1361.5	1372.8	1377.5
127.5°	1393.6	1416.2	1440.5	1456.6	1458.1
130°	1472.6	1498.5	1516.1	1533.9	1532.4
132.5°	1553.2	1574.2	1591.9	1606.4	1604.9
135°	1620.9	1646.7	1661.1	1677.3	1674.1
137.5°	1691.7	1711.1	1727.3	1743.4	1738.6
140°	1761.0	1774.0	1791.6	1806.1	1798.1
142.5°	1819.1	1830.4	1851.2	1864.1	1856.1
145°	1880.4	1878.7	1906.0	1917.3	1909.3
147.5°	1933.3	1928.6	1956.0	1964.0	1957.7
150°	1985.0	1973.8	1999.6	2009.1	2001.1
152.5°	2028.4	2015.6	2039.8	2049.5	2038.2
155°	2070.4	2056.0	2075.3	2084.9	2072.1
157.5°	2104.2	2091.4	2105.9	2117.2	2104.2
160°	2133.4	2123.5	2133.4	2142.9	2131.6
162.5°	2159.0	2149.4	2157.4	2168.7	2154.2
165°	2181.5	2172.0	2176.7	2188.0	2176.7
167.5°	2199.3	2189.5	2194.5	2205.8	2191.3
170°	2213.8	2204.1	2207.3	2218.7	2204.1
172.5°	2223.5	2213.8	2217.1	2228.4	2213.8
175°	2231.5	2220.2	2223.5	2234.7	2218.7
177.5°	2234.7	2223.5	2225.2	2236.5	2221.9
180°	2226.7	2226.7	2226.7	2226.7	2226.7



TEST NUMBER: P904405
 CATALOG NUMBER: DFN2DIP-TR3F0-040D070US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.56	8.27	8.66	9.36	10.86	3.54	4.24	4.63	5.33	6.83
	3H	9.22	9.85	10.32	10.95	12.46	4.71	5.34	5.81	6.44	7.96
	4H	9.81	10.42	10.93	11.51	13.04	5.15	5.75	6.27	6.85	8.37
	6H	10.22	10.77	11.35	11.88	13.41	5.46	6.01	6.58	7.11	8.65
	8H	10.34	10.87	11.47	11.98	13.51	5.54	6.07	6.67	7.19	8.71
	12H	10.39	10.89	11.53	12.00	13.55	5.58	6.08	6.71	7.19	8.74
4H	2H	7.56	8.16	8.68	9.26	10.78	4.11	4.71	5.23	5.81	7.33
	3H	9.37	9.87	10.50	10.99	12.53	5.44	5.94	6.57	7.07	8.60
	4H	10.05	10.51	11.18	11.62	13.18	5.98	6.44	7.11	7.56	9.11
	6H	10.55	10.94	11.69	12.08	13.62	6.39	6.78	7.53	7.92	9.46
	8H	10.72	11.08	11.85	12.21	13.77	6.51	6.88	7.65	8.01	9.57
	12H	10.80	11.13	11.95	12.27	13.84	6.57	6.90	7.72	8.04	9.61
8H	4H	10.01	10.37	11.14	11.50	13.06	6.25	6.61	7.38	7.74	9.30
	6H	10.56	10.86	11.72	12.03	13.59	6.75	7.05	7.91	8.23	9.79
	8H	10.77	11.03	11.93	12.18	13.76	6.94	7.20	8.10	8.35	9.93
	12H	10.89	11.13	12.06	12.27	13.89	7.05	7.28	8.21	8.43	10.04
12H	4H	9.95	10.28	11.11	11.43	12.99	6.24	6.58	7.40	7.72	9.28
	6H	10.53	10.80	11.70	11.95	13.53	6.80	7.06	7.96	8.22	9.79
	8H	10.74	10.97	11.91	12.12	13.73	7.00	7.23	8.17	8.38	9.99