

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915179

Luminaire Tested: DFN2DIP-TR2F0-020D030US927-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915179
REPORT IS A COMBINATION OF REPORTS P901752 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-020D030US927-RLLONL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3450.0 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 37
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915179
CATALOG NUMBER: DFN2DIP-TR2F0-020D030US927-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P915179

CATALOG NUMBER: DFN2DIP-TR2F0-020D030US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39				39
1	96	92	88	85	87	83	80	78	68	66	64	54	53	51	41	40	40	34				34
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34	29				29
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29	25				25
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	26	22				22
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	24	22	19				19
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	25	22	20	17				17
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18	15				15
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16	14				14
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15	12				12
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11				11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1460	1460	1460
5°	1461	1434	1444
10°	1444	1403	1395
15°	1422	1353	1320
20°	1393	1286	1229
25°	1365	1212	1141
30°	1326	1136	1030
35°	1288	1055	933
40°	1250	971	822
45°	1205	878	722
50°	1159	785	624
55°	1110	686	530
60°	1054	583	434
65°	989	478	388
70°	910	381	347
75°	811	329	311
80°	669	267	262
85°	438	165	184

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1205 cd/sqm



TEST NUMBER: P915179

CATALOG NUMBER: DFN2DIP-TR2F0-020D030US927-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.4	1.8
10°-20°	168.5	4.9
20°-30°	236.5	6.9
30°-40°	257.8	7.5
40°-50°	237.0	6.9
50°-60°	186.1	5.4
60°-70°	121.2	3.5
70°-80°	62.3	1.8
80°-90°	18.1	0.5
90°-100°	46.5	1.3
100°-110°	147.8	4.3
110°-120°	252.9	7.3
120°-130°	332.6	9.6
130°-140°	373.3	10.8
140°-150°	366.1	10.6
150°-160°	307.1	8.9
160°-170°	203.7	5.9
170°-180°	71.2	2.1
0°-30°	466.4	13.5
0°-40°	724.2	21.0
0°-60°	1147.3	33.3
0°-90°	1348.8	39.1
90°-120°	447.2	13.0
90°-150°	1519.2	44.0
90°-180°	2101.0	60.9
0°-180°	3450.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	655	655	655	655	655	
5°	655	652	644	650	648	62
15°	623	616	596	585	579	176
25°	565	546	507	483	474	260
35°	487	457	405	367	354	305
45°	398	358	296	254	240	308
55°	303	257	193	157	146	271
65°	204	156	103	83	81	203
75°	109	68	47	43	43	115
85°	25	13	11	11	11	29
90°	1	8	22	21	22	3
95°	33	40	41	41	40	37
105°	136	138	140	141	141	144
115°	254	257	256	256	254	251
125°	369	375	373	371	370	330
135°	477	484	486	485	483	369
145°	580	584	588	588	586	362
155°	663	665	667	670	668	305
165°	721	720	720	725	722	203
175°	750	748	747	752	748	71
180°	752	752	752	752	752	



TEST NUMBER: P915179

CATALOG NUMBER: DFN2DIP-TR2F0-020D030US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	654.8	654.8	654.8	654.8	654.8
2.5°	657.7	654.8	648.2	654.3	653.1
5°	654.8	651.9	644.1	649.5	647.7
7.5°	649.5	645.9	637.6	640.0	637.0
10°	642.4	638.2	626.4	624.6	621.1
12.5°	633.5	628.1	612.1	608.6	602.1
15°	622.8	616.2	596.1	584.9	579.0
17.5°	610.4	600.9	576.0	562.9	553.5
20°	596.1	584.2	554.7	539.9	526.8
22.5°	580.7	567.1	532.7	512.6	503.7
25°	565.4	546.4	507.2	483.0	474.0
27.5°	547.0	526.8	483.5	455.7	442.0
30°	527.4	504.9	457.5	427.3	411.2
32.5°	508.4	481.2	432.6	397.0	382.2
35°	487.1	456.9	404.8	367.4	354.3
37.5°	466.4	433.7	378.7	337.8	323.0
40°	444.4	408.9	351.4	309.3	293.9
42.5°	421.9	384.0	324.2	280.3	265.5
45°	398.2	358.5	296.4	254.2	240.0
47.5°	375.7	333.7	269.7	227.5	214.5
50°	350.9	308.8	243.6	202.6	190.3
52.5°	326.5	282.0	218.6	179.6	168.3
55°	302.8	256.6	192.6	157.1	145.8
57.5°	278.5	231.1	169.5	136.3	126.8
60°	253.7	206.2	145.2	115.0	105.5
62.5°	229.3	182.0	124.5	96.0	91.3
65°	204.5	156.5	103.1	83.0	81.2
67.5°	180.8	132.7	83.0	72.9	71.1
70°	155.8	109.6	68.7	62.8	60.4
72.5°	132.1	88.2	57.4	52.8	51.6
75°	109.0	67.5	47.4	43.3	42.7
77.5°	86.0	48.0	37.3	34.9	33.7
80°	64.6	34.4	28.4	26.1	26.1
82.5°	45.0	23.1	19.6	18.4	18.4
85°	25.4	13.0	11.2	11.2	11.2
87.5°	9.5	4.8	4.8	4.1	4.1
90°	0.7	8.2	22.2	20.8	21.5
92.5°	14.0	19.0	19.7	20.4	20.4
95°	33.1	39.5	40.6	40.6	39.5
97.5°	55.1	60.9	63.5	63.5	63.5
100°	80.4	85.6	87.5	87.5	86.8
102.5°	107.2	111.1	113.5	114.2	113.5
105°	136.4	138.2	139.6	140.7	140.7
107.5°	165.4	168.1	168.1	168.6	165.4
110°	193.5	197.2	197.2	197.2	195.4



TEST NUMBER: P915179

CATALOG NUMBER: DFN2DIP-TR2F0-020D030US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	223.9	227.8	227.0	225.2	223.9
115°	253.8	257.4	256.3	255.6	253.8
117.5°	283.4	288.4	285.3	283.4	281.6
120°	313.4	318.4	313.4	313.4	311.3
122.5°	340.6	346.9	343.7	341.9	340.6
125°	369.2	374.8	373.0	370.9	370.3
127.5°	397.0	404.0	401.6	398.8	397.0
130°	423.0	431.2	430.1	428.7	426.2
132.5°	452.3	458.6	459.1	455.9	454.1
135°	477.4	484.4	485.8	485.1	483.3
137.5°	505.5	511.2	512.3	511.9	509.1
140°	530.2	535.9	539.1	539.1	536.5
142.5°	555.6	561.3	563.1	563.8	561.3
145°	579.6	584.2	587.8	588.4	586.0
147.5°	601.2	606.8	609.5	610.7	608.2
150°	623.4	627.2	629.7	631.8	629.7
152.5°	643.1	646.9	650.1	652.6	650.1
155°	662.8	664.6	666.6	669.8	667.8
157.5°	679.8	681.1	682.3	686.8	683.7
160°	695.0	696.3	697.0	700.8	698.1
162.5°	709.0	709.0	709.7	714.0	710.8
165°	721.0	720.3	720.3	724.8	721.7
167.5°	731.9	729.8	729.8	734.4	731.2
170°	740.1	738.2	737.6	742.1	738.2
172.5°	745.7	743.9	743.2	747.7	743.9
175°	750.3	748.5	747.1	751.6	747.7
177.5°	752.7	750.9	749.6	753.4	749.6
180°	751.6	751.6	751.6	751.6	751.6



TEST NUMBER: P915179
 CATALOG NUMBER: DFN2DIP-TR2F0-020D030US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.22	7.97	8.27	9.02	10.44	3.20	3.95	4.25	5.00	6.42
	3H	8.87	9.54	9.93	10.60	12.04	4.37	5.04	5.43	6.10	7.54
	4H	9.46	10.09	10.53	11.15	12.60	4.81	5.44	5.88	6.50	7.95
	6H	9.86	10.44	10.94	11.50	12.96	5.11	5.69	6.19	6.76	8.22
	8H	9.97	10.52	11.06	11.61	13.06	5.19	5.74	6.28	6.83	8.28
	12H	10.02	10.55	11.11	11.62	13.10	5.22	5.75	6.31	6.83	8.30
4H	2H	7.23	7.86	8.30	8.92	10.37	3.78	4.41	4.85	5.47	6.92
	3H	9.02	9.55	10.11	10.64	12.10	5.10	5.63	6.19	6.72	8.18
	4H	9.69	10.17	10.78	11.25	12.73	5.63	6.11	6.72	7.20	8.68
	6H	10.18	10.59	11.28	11.70	13.17	6.03	6.44	7.13	7.55	9.02
	8H	10.34	10.73	11.44	11.82	13.31	6.15	6.53	7.25	7.63	9.12
	12H	10.42	10.77	11.53	11.88	13.37	6.20	6.55	7.31	7.66	9.15
8H	4H	9.65	10.03	10.75	11.13	12.62	5.89	6.28	6.99	7.37	8.86
	6H	10.19	10.51	11.31	11.64	13.13	6.38	6.70	7.50	7.84	9.33
	8H	10.39	10.67	11.51	11.79	13.29	6.56	6.84	7.69	7.96	9.47
	12H	10.50	10.75	11.64	11.87	13.41	6.66	6.91	7.79	8.03	9.57
12H	4H	9.60	9.94	10.71	11.05	12.55	5.89	6.24	7.00	7.35	8.84
	6H	10.16	10.44	11.29	11.56	13.07	6.43	6.71	7.55	7.83	9.33
	8H	10.36	10.61	11.49	11.72	13.27	6.62	6.87	7.75	7.98	9.52