

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915222

Luminaire Tested: DFN2DIP-TR2F0-040D040US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915222
REPORT IS A COMBINATION OF REPORTS P900246 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-040D040US927-RLLFLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5497.7 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 65.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915222
CATALOG NUMBER: DFN2DIP-TR2F0-040D040US927-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P915222
 CATALOG NUMBER: DFN2DIP-TR2F0-040D040US927-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49			49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42			42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36			36
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35	31			31
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31	27			27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24			24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24	21			21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19			19
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17			17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	16			16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14			14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2921	2921	2921
5°	2921	2868	2888
10°	2888	2805	2789
15°	2844	2706	2639
20°	2787	2573	2457
25°	2729	2424	2281
30°	2652	2272	2060
35°	2576	2109	1866
40°	2499	1941	1644
45°	2410	1756	1443
50°	2318	1569	1248
55°	2221	1371	1060
60°	2108	1165	868
65°	1978	956	775
70°	1821	761	694
75°	1622	658	622
80°	1337	534	525
85°	878	331	369

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2410 cd/sqm



TEST NUMBER: P915222

CATALOG NUMBER: DFN2DIP-TR2F0-040D040US927-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.7	2.2
10°-20°	336.9	6.1
20°-30°	473.1	8.6
30°-40°	515.7	9.4
40°-50°	473.9	8.6
50°-60°	372.2	6.8
60°-70°	242.3	4.4
70°-80°	124.7	2.3
80°-90°	34.7	0.6
90°-100°	62.0	1.1
100°-110°	197.0	3.6
110°-120°	337.2	6.1
120°-130°	443.5	8.1
130°-140°	497.8	9.1
140°-150°	488.1	8.9
150°-160°	409.5	7.4
160°-170°	271.5	4.9
170°-180°	94.9	1.7
0°-30°	932.7	17.0
0°-40°	1448.4	26.3
0°-60°	2294.6	41.7
0°-90°	2696.2	49.0
90°-120°	596.2	10.8
90°-150°	2025.6	36.8
90°-180°	2801.0	50.9
0°-180°	5497.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1310	1310	1310	1310	1310	
5°	1310	1304	1288	1299	1296	124
15°	1246	1233	1192	1170	1158	351
25°	1131	1093	1014	966	948	520
35°	974	914	810	735	709	610
45°	796	717	593	508	480	615
55°	606	513	385	314	292	541
65°	409	313	206	166	162	405
75°	218	135	95	86	85	231
85°	51	26	22	22	22	58
90°	1	11	30	28	29	5
95°	44	53	54	54	53	49
105°	182	184	186	188	188	192
115°	338	343	342	341	338	335
125°	492	500	497	495	494	440
135°	637	646	648	647	644	492
145°	773	779	784	785	781	483
155°	884	886	889	893	890	407
165°	961	960	960	966	962	271
175°	1000	998	996	1002	997	95
180°	1002	1002	1002	1002	1002	



TEST NUMBER: P915222

CATALOG NUMBER: DFN2DIP-TR2FO-040D040US927-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1309.6	1309.6	1309.6	1309.6	1309.6
2.5°	1315.6	1309.6	1296.6	1308.5	1306.1
5°	1309.6	1303.7	1288.2	1298.9	1295.5
7.5°	1298.9	1291.9	1275.3	1279.9	1274.1
10°	1284.8	1276.4	1252.8	1249.1	1242.1
12.5°	1267.0	1256.3	1224.2	1217.2	1204.1
15°	1245.6	1232.6	1192.3	1169.8	1158.0
17.5°	1220.8	1201.7	1151.9	1125.9	1106.9
20°	1192.3	1168.5	1109.3	1079.7	1053.6
22.5°	1161.5	1134.2	1065.4	1025.2	1007.5
25°	1130.7	1092.7	1014.5	966.0	948.1
27.5°	1094.0	1053.6	967.1	911.4	884.1
30°	1054.9	1009.7	914.9	854.5	822.5
32.5°	1016.9	962.3	865.2	794.1	764.4
35°	974.3	913.8	809.5	734.8	708.7
37.5°	932.8	867.5	757.3	675.5	645.9
40°	888.9	817.8	702.8	618.7	587.9
42.5°	843.8	768.0	648.3	560.5	531.0
45°	796.5	717.0	592.6	508.4	480.0
47.5°	751.5	667.3	539.3	455.1	429.0
50°	701.6	617.5	487.1	405.3	380.5
52.5°	653.0	564.1	437.4	359.1	336.6
55°	605.6	513.2	385.2	314.1	291.6
57.5°	557.1	462.2	339.0	272.6	253.7
60°	507.2	412.4	290.3	230.0	211.0
62.5°	458.8	363.9	248.8	192.0	182.6
65°	408.9	312.8	206.2	166.0	162.3
67.5°	361.6	265.5	166.0	145.8	142.2
70°	311.7	219.3	137.4	125.6	120.8
72.5°	264.4	176.6	114.9	105.5	103.1
75°	218.0	135.1	94.8	86.5	85.4
77.5°	171.9	95.9	74.7	69.9	67.5
80°	129.1	68.8	56.8	52.2	52.2
82.5°	90.1	46.3	39.1	36.7	36.7
85°	50.9	26.1	22.5	22.5	22.5
87.5°	19.0	9.4	9.4	8.3	8.3
90°	0.9	10.9	29.6	27.8	28.7
92.5°	18.7	25.3	26.3	27.2	27.2
95°	44.1	52.6	54.1	54.1	52.6
97.5°	73.4	81.3	84.6	84.6	84.6
100°	107.3	114.2	116.6	116.6	115.7
102.5°	142.9	148.1	151.4	152.3	151.4
105°	181.9	184.3	186.1	187.6	187.6
107.5°	220.5	224.2	224.2	224.7	220.5
110°	258.0	262.8	262.8	262.8	260.5



TEST NUMBER: P915222

CATALOG NUMBER: DFN2DIP-TR2F0-040D040US927-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	298.5	303.6	302.7	300.3	298.5
115°	338.3	343.3	341.7	340.8	338.3
117.5°	377.9	384.6	380.4	377.9	375.6
120°	417.9	424.5	417.9	417.9	415.1
122.5°	454.1	462.6	458.4	455.9	454.1
125°	492.2	499.7	497.3	494.6	493.7
127.5°	529.3	538.7	535.4	531.7	529.3
130°	564.0	575.0	573.5	571.6	568.3
132.5°	603.0	611.5	612.1	607.8	605.5
135°	636.6	645.9	647.8	646.8	644.4
137.5°	674.1	681.6	683.1	682.5	678.9
140°	706.9	714.5	718.7	718.7	715.4
142.5°	740.8	748.4	750.8	751.7	748.4
145°	772.9	778.9	783.7	784.7	781.3
147.5°	801.5	809.1	812.7	814.2	810.9
150°	831.2	836.3	839.6	842.3	839.6
152.5°	857.5	862.5	866.8	870.1	866.8
155°	883.7	886.1	888.8	893.1	890.3
157.5°	906.4	908.2	909.7	915.8	911.5
160°	926.6	928.4	929.3	934.5	930.8
162.5°	945.3	945.3	946.3	952.0	947.8
165°	961.4	960.4	960.4	966.5	962.3
167.5°	975.9	973.1	973.1	979.2	974.9
170°	986.7	984.3	983.4	989.4	984.3
172.5°	994.3	991.9	990.9	997.0	991.9
175°	1000.4	997.9	996.1	1002.1	997.0
177.5°	1003.7	1001.2	999.4	1004.6	999.4
180°	1002.1	1002.1	1002.1	1002.1	1002.1



TEST NUMBER: P915222
 CATALOG NUMBER: DFN2DIP-TR2F0-040D040US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.65	11.47	11.62	12.45	13.74	6.63	7.46	7.60	8.44	9.72
	3H	12.30	13.04	13.29	14.03	15.34	7.81	8.54	8.79	9.53	10.84
	4H	12.90	13.59	13.89	14.59	15.90	8.24	8.94	9.24	9.93	11.25
	6H	13.30	13.94	14.31	14.94	16.27	8.55	9.19	9.56	10.19	11.52
	8H	13.41	14.02	14.43	15.04	16.36	8.63	9.24	9.65	10.26	11.58
	12H	13.47	14.04	14.48	15.05	16.40	8.67	9.25	9.69	10.26	11.61
4H	2H	10.66	11.36	11.67	12.35	13.67	7.21	7.91	8.22	8.90	10.22
	3H	12.47	13.04	13.48	14.07	15.40	8.54	9.12	9.56	10.15	11.48
	4H	13.14	13.67	14.16	14.68	16.04	9.08	9.61	10.10	10.62	11.98
	6H	13.63	14.09	14.66	15.12	16.48	9.48	9.93	10.51	10.97	12.33
	8H	13.79	14.22	14.82	15.25	16.62	9.60	10.02	10.63	11.06	12.42
	12H	13.88	14.26	14.92	15.30	16.68	9.66	10.04	10.70	11.09	12.46
8H	4H	13.10	13.53	14.13	14.56	15.92	9.34	9.77	10.38	10.80	12.17
	6H	13.64	13.99	14.70	15.07	16.43	9.84	10.19	10.89	11.26	12.63
	8H	13.84	14.15	14.91	15.21	16.59	10.02	10.33	11.08	11.39	12.77
	12H	13.97	14.24	15.03	15.29	16.72	10.12	10.40	11.19	11.45	12.87
12H	4H	13.05	13.44	14.10	14.48	15.85	9.35	9.73	10.39	10.77	12.15
	6H	13.62	13.92	14.68	14.98	16.37	9.88	10.19	10.95	11.25	12.63
	8H	13.82	14.09	14.89	15.14	16.57	10.08	10.35	11.14	11.40	12.83