

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915239

Luminaire Tested: DFN2DIP-TR2F0-050D030US927-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915239
REPORT IS A COMBINATION OF REPORTS P901758 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-050D030US927-RLLONL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5470.0 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 69.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915239
CATALOG NUMBER: DFN2DIP-TR2F0-050D030US927-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P915239

CATALOG NUMBER: DFN2DIP-TR2F0-050D030US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	67	67	67	62
1	101	97	93	90	94	91	88	85	80	77	75	69	68	66	60	59	58	60	59	58	53
2	92	85	79	74	86	80	75	70	71	67	63	62	59	56	53	51	49	53	51	49	45
3	85	75	68	63	79	71	65	60	63	58	54	55	51	48	48	45	43	48	45	43	39
4	78	67	60	54	73	63	57	51	56	51	46	49	45	42	43	40	37	43	40	37	34
5	72	60	52	46	67	57	50	44	51	45	41	45	40	37	39	36	33	39	36	33	30
6	66	54	46	41	62	51	44	39	46	40	36	41	36	32	36	32	29	36	32	29	27
7	62	49	42	36	58	47	40	35	42	36	32	37	33	29	33	29	26	33	29	26	24
8	57	45	37	32	54	43	36	31	38	33	28	34	30	26	30	27	24	30	27	24	22
9	53	41	34	29	50	39	32	28	35	30	26	32	27	24	28	24	22	28	24	22	20
10	50	38	31	26	47	36	30	25	33	27	23	29	25	22	26	22	20	26	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3651	3651	3651
5°	3652	3585	3610
10°	3610	3507	3486
15°	3555	3383	3299
20°	3484	3216	3071
25°	3411	3030	2851
30°	3315	2840	2575
35°	3220	2636	2332
40°	3124	2426	2055
45°	3013	2195	1804
50°	2897	1962	1559
55°	2776	1714	1325
60°	2635	1456	1084
65°	2473	1195	970
70°	2276	952	869
75°	2029	823	778
80°	1672	669	656
85°	1098	414	461

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3013 cd/sqm



TEST NUMBER: P915239

CATALOG NUMBER: DFN2DIP-TR2F0-050D030US927-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.4	2.8
10°-20°	421.2	7.7
20°-30°	591.3	10.8
30°-40°	644.6	11.8
40°-50°	592.4	10.8
50°-60°	465.3	8.5
60°-70°	302.9	5.5
70°-80°	155.9	2.8
80°-90°	41.9	0.8
90°-100°	46.5	0.9
100°-110°	147.8	2.7
110°-120°	252.9	4.6
120°-130°	332.6	6.1
130°-140°	373.3	6.8
140°-150°	366.1	6.7
150°-160°	307.1	5.6
160°-170°	203.7	3.7
170°-180°	71.2	1.3
0°-30°	1165.9	21.3
0°-40°	1810.5	33.1
0°-60°	2868.2	52.4
0°-90°	3368.9	61.6
90°-120°	447.2	8.2
90°-150°	1519.2	27.8
90°-180°	2101.0	38.4
0°-180°	5470.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1637	1637	1637	1637	1637	
5°	1637	1630	1610	1624	1619	155
15°	1557	1541	1490	1462	1448	439
25°	1413	1366	1268	1207	1185	650
35°	1218	1142	1012	918	886	762
45°	996	896	741	636	600	769
55°	757	641	481	393	364	676
65°	511	391	258	208	203	507
75°	273	169	118	108	107	288
85°	64	33	28	28	28	73
90°	1	8	22	21	22	5
95°	33	40	41	41	40	37
105°	136	138	140	141	141	144
115°	254	257	256	256	254	251
125°	369	375	373	371	370	330
135°	477	484	486	485	483	369
145°	580	584	588	588	586	362
155°	663	665	667	670	668	305
165°	721	720	720	725	722	203
175°	750	748	747	752	748	71
180°	752	752	752	752	752	



TEST NUMBER: P915239

CATALOG NUMBER: DFN2DIP-TR2F0-050D030US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1637.0	1637.0	1637.0	1637.0	1637.0
2.5°	1644.4	1637.0	1620.7	1635.6	1632.6
5°	1637.0	1629.7	1610.3	1623.7	1619.3
7.5°	1623.7	1614.9	1594.1	1600.0	1592.5
10°	1605.9	1595.5	1566.0	1561.5	1552.6
12.5°	1583.7	1570.4	1530.3	1521.5	1505.1
15°	1557.0	1540.7	1490.4	1462.3	1447.5
17.5°	1525.9	1502.2	1439.9	1407.4	1383.6
20°	1490.4	1460.7	1386.6	1349.7	1317.0
22.5°	1451.9	1417.8	1331.8	1281.5	1259.3
25°	1413.3	1365.9	1268.1	1207.4	1185.1
27.5°	1367.5	1317.0	1208.9	1139.2	1105.2
30°	1318.6	1262.2	1143.7	1068.2	1028.1
32.5°	1271.1	1202.9	1081.6	992.6	955.5
35°	1217.8	1142.2	1011.9	918.5	885.9
37.5°	1165.9	1084.4	946.7	844.4	807.5
40°	1111.1	1022.3	878.4	773.3	734.8
42.5°	1054.9	960.0	810.4	700.7	663.8
45°	995.6	896.3	740.8	635.5	599.9
47.5°	939.3	834.2	674.1	568.9	536.3
50°	877.1	771.9	608.9	506.6	475.6
52.5°	816.3	705.1	546.7	448.9	420.8
55°	757.0	641.4	481.4	392.6	364.5
57.5°	696.3	577.8	423.7	340.8	317.0
60°	634.1	515.6	362.9	287.5	263.7
62.5°	573.4	454.9	311.1	240.0	228.2
65°	511.1	391.1	257.8	207.5	203.0
67.5°	451.9	331.8	207.5	182.2	177.8
70°	389.7	274.1	171.8	157.0	151.1
72.5°	330.4	220.7	143.7	131.9	128.9
75°	272.6	168.8	118.5	108.1	106.7
77.5°	214.8	119.9	93.4	87.4	84.4
80°	161.4	86.0	71.1	65.2	65.2
82.5°	112.6	57.8	48.9	45.9	45.9
85°	63.7	32.6	28.1	28.1	28.1
87.5°	23.8	11.8	11.8	10.4	10.4
90°	0.7	8.2	22.2	20.8	21.5
92.5°	14.0	19.0	19.7	20.4	20.4
95°	33.1	39.5	40.6	40.6	39.5
97.5°	55.1	60.9	63.5	63.5	63.5
100°	80.4	85.6	87.5	87.5	86.8
102.5°	107.2	111.1	113.5	114.2	113.5
105°	136.4	138.2	139.6	140.7	140.7
107.5°	165.4	168.1	168.1	168.6	165.4
110°	193.5	197.2	197.2	197.2	195.4



TEST NUMBER: P915239

CATALOG NUMBER: DFN2DIP-TR2F0-050D030US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	223.9	227.8	227.0	225.2	223.9
115°	253.8	257.4	256.3	255.6	253.8
117.5°	283.4	288.4	285.3	283.4	281.6
120°	313.4	318.4	313.4	313.4	311.3
122.5°	340.6	346.9	343.7	341.9	340.6
125°	369.2	374.8	373.0	370.9	370.3
127.5°	397.0	404.0	401.6	398.8	397.0
130°	423.0	431.2	430.1	428.7	426.2
132.5°	452.3	458.6	459.1	455.9	454.1
135°	477.4	484.4	485.8	485.1	483.3
137.5°	505.5	511.2	512.3	511.9	509.1
140°	530.2	535.9	539.1	539.1	536.5
142.5°	555.6	561.3	563.1	563.8	561.3
145°	579.6	584.2	587.8	588.4	586.0
147.5°	601.2	606.8	609.5	610.7	608.2
150°	623.4	627.2	629.7	631.8	629.7
152.5°	643.1	646.9	650.1	652.6	650.1
155°	662.8	664.6	666.6	669.8	667.8
157.5°	679.8	681.1	682.3	686.8	683.7
160°	695.0	696.3	697.0	700.8	698.1
162.5°	709.0	709.0	709.7	714.0	710.8
165°	721.0	720.3	720.3	724.8	721.7
167.5°	731.9	729.8	729.8	734.4	731.2
170°	740.1	738.2	737.6	742.1	738.2
172.5°	745.7	743.9	743.2	747.7	743.9
175°	750.3	748.5	747.1	751.6	747.7
177.5°	752.7	750.9	749.6	753.4	749.6
180°	751.6	751.6	751.6	751.6	751.6



TEST NUMBER: P915239
 CATALOG NUMBER: DFN2DIP-TR2F0-050D030US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.54	13.47	13.39	14.34	15.44	8.52	9.45	9.38	10.33	11.43
	3H	14.20	15.03	15.07	15.92	17.04	9.70	10.53	10.57	11.42	12.54
	4H	14.79	15.58	15.68	16.47	17.61	10.14	10.93	11.03	11.82	12.96
	6H	15.20	15.93	16.10	16.83	17.97	10.46	11.18	11.35	12.08	13.23
	8H	15.32	16.01	16.23	16.93	18.07	10.54	11.23	11.45	12.15	13.29
	12H	15.38	16.03	16.29	16.94	18.11	10.58	11.24	11.49	12.15	13.32
4H	2H	12.56	13.35	13.45	14.24	15.38	9.11	9.90	10.00	10.79	11.93
	3H	14.37	15.03	15.28	15.95	17.10	10.45	11.11	11.36	12.03	13.18
	4H	15.05	15.65	15.97	16.57	17.74	10.99	11.59	11.91	12.51	13.68
	6H	15.55	16.06	16.48	17.01	18.18	11.40	11.91	12.33	12.86	14.03
	8H	15.71	16.19	16.64	17.13	18.32	11.52	12.00	12.45	12.94	14.13
	12H	15.80	16.23	16.75	17.19	18.38	11.58	12.01	12.53	12.97	14.16
8H	4H	15.02	15.50	15.95	16.44	17.63	11.27	11.75	12.20	12.68	13.87
	6H	15.57	15.96	16.52	16.94	18.13	11.77	12.16	12.72	13.14	14.33
	8H	15.77	16.12	16.73	17.09	18.30	11.94	12.29	12.91	13.26	14.47
	12H	15.90	16.21	16.86	17.17	18.42	12.05	12.36	13.02	13.32	14.58
12H	4H	14.98	15.41	15.93	16.37	17.56	11.27	11.70	12.22	12.66	13.85
	6H	15.54	15.89	16.51	16.86	18.07	11.81	12.16	12.77	13.13	14.34
	8H	15.75	16.06	16.72	17.02	18.28	12.01	12.32	12.98	13.28	14.54