

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904536

Luminaire Tested: DFN2DIP-TR3F0-090D080US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904536
REPORT IS A COMBINATION OF REPORTS P900353 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-090D080US830-FLLFLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15071.3 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 156
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904536

CATALOG NUMBER: DFN2DIP-TR3F0-090D080US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904536

CATALOG NUMBER: DFN2DIP-TR3F0-090D080US830-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		73	73	73		61	61	61
1	99	95	91	87		92	88	85	82		76	73	71		65	63	61		54	53	52
2	90	83	77	71		84	77	72	67		67	62	59		57	54	51		48	46	44
3	82	73	65	59		76	68	61	56		59	54	50		50	46	43		42	40	37
4	75	64	56	50		70	60	53	48		52	47	42		45	41	37		38	35	32
5	69	57	49	43		64	54	46	41		47	41	36		40	36	32		34	31	28
6	64	52	43	37		59	48	41	36		42	36	32		36	32	28		31	27	25
7	59	47	39	33		55	44	36	31		38	32	28		33	28	25		28	25	22
8	55	42	35	29		51	40	33	28		35	29	25		30	26	22		26	22	20
9	51	39	31	26		47	36	30	25		32	26	22		28	23	20		24	20	18
10	48	36	28	23		44	33	27	22		30	24	20		26	21	18		22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4113	4113	4113
5°	4117	4052	4080
10°	4082	3994	4022
15°	4020	3925	3933
20°	3936	3830	3842
25°	3853	3718	3738
30°	3750	3612	3605
35°	3651	3489	3465
40°	3531	3364	3331
45°	3410	3239	3195
50°	3279	3107	3037
55°	3141	2955	2890
60°	2984	2774	2723
65°	2814	2587	2526
70°	2596	2358	2312
75°	2295	2084	2111
80°	1932	1734	1736
85°	1365	1142	1120

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3410 cd/sqm

TEST NUMBER: P904536

CATALOG NUMBER: DFN2DIP-TR3F0-090D080US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	310.7	2.1
10°-20°	874.1	5.8
20°-30°	1284.6	8.5
30°-40°	1492.0	9.9
40°-50°	1490.1	9.9
50°-60°	1299.3	8.6
60°-70°	960.5	6.4
70°-80°	543.4	3.6
80°-90°	150.2	1.0
90°-100°	147.6	1.0
100°-110°	468.9	3.1
110°-120°	802.4	5.3
120°-130°	1055.3	7.0
130°-140°	1184.5	7.9
140°-150°	1161.5	7.7
150°-160°	974.4	6.5
160°-170°	646.2	4.3
170°-180°	225.9	1.5
0°-30°	2469.3	16.4
0°-40°	3961.3	26.3
0°-60°	6750.7	44.8
0°-90°	8404.8	55.8
90°-120°	1418.8	9.4
90°-150°	4820.1	32.0
90°-180°	6666.0	44.2
0°-180°	15071.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3301	3301	3301	3301	3301	
5°	3301	3288	3253	3278	3272	313
15°	3142	3123	3082	3095	3079	885
25°	2844	2818	2765	2771	2765	1309
35°	2454	2422	2371	2352	2336	1532
45°	1996	1974	1926	1892	1879	1541
55°	1511	1492	1454	1416	1400	1351
65°	1019	1000	968	940	924	1007
75°	533	527	511	492	498	569
85°	130	127	124	114	111	145
90°	2	26	70	66	68	15
95°	105	125	129	129	125	117
105°	433	439	443	446	446	457
115°	805	817	813	811	805	796
125°	1171	1189	1183	1177	1175	1047
135°	1515	1537	1541	1539	1534	1171
145°	1839	1853	1865	1867	1859	1149
155°	2103	2109	2115	2125	2119	968
165°	2288	2286	2286	2300	2290	645
175°	2380	2375	2370	2385	2372	226
180°	2385	2385	2385	2385	2385	

TEST NUMBER: P904536

CATALOG NUMBER: DFN2DIP-TR3F0-090D080US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3300.7	3300.7	3300.7	3300.7	3300.7
2.5°	3319.9	3304.1	3269.1	3300.7	3294.7
5°	3300.7	3288.2	3253.3	3278.5	3272.4
7.5°	3278.5	3259.7	3224.6	3250.3	3243.9
10°	3243.9	3221.6	3183.5	3208.8	3199.4
12.5°	3196.0	3177.1	3139.1	3154.9	3148.6
15°	3142.2	3123.3	3081.8	3094.6	3078.8
17.5°	3075.4	3056.6	3015.2	3031.0	3015.2
20°	3002.4	2983.5	2939.0	2948.5	2936.0
22.5°	2929.6	2901.1	2859.6	2859.6	2853.2
25°	2843.7	2818.5	2764.7	2770.7	2764.7
27.5°	2748.5	2726.2	2685.2	2675.8	2659.9
30°	2653.5	2627.9	2580.4	2571.0	2558.2
32.5°	2551.8	2533.0	2482.1	2463.0	2450.1
35°	2453.5	2421.9	2371.0	2351.8	2336.0
37.5°	2342.4	2313.8	2262.9	2240.7	2224.9
40°	2228.2	2202.6	2151.7	2123.5	2110.7
42.5°	2117.0	2091.5	2041.0	2009.0	1990.2
45°	1996.5	1974.3	1926.5	1891.8	1879.1
47.5°	1879.1	1856.8	1805.9	1770.9	1752.1
50°	1755.1	1739.3	1694.8	1650.4	1634.6
52.5°	1634.6	1612.3	1571.2	1536.2	1514.0
55°	1511.0	1491.8	1453.7	1415.7	1399.9
57.5°	1387.0	1371.2	1329.8	1291.8	1278.9
60°	1263.1	1250.7	1206.2	1171.2	1161.8
62.5°	1142.5	1120.3	1088.6	1057.1	1044.2
65°	1019.0	999.8	968.1	939.5	923.7
67.5°	892.0	875.9	847.5	825.4	812.6
70°	774.5	761.7	733.1	710.9	698.4
72.5°	653.9	641.1	625.3	603.1	593.7
75°	533.1	527.0	510.9	492.0	498.4
77.5°	425.3	412.6	406.1	396.7	387.3
80°	317.5	314.1	307.7	298.3	292.0
82.5°	215.8	215.8	212.8	200.0	200.0
85°	130.0	127.0	123.9	114.1	111.1
87.5°	57.2	50.8	44.5	35.1	31.7
90°	2.2	25.9	70.5	66.2	68.3
92.5°	44.6	60.4	62.6	64.7	64.7
95°	105.0	125.1	128.7	128.7	125.1
97.5°	174.7	193.4	201.3	201.3	201.3
100°	255.2	271.7	277.5	277.5	275.3
102.5°	340.1	352.3	360.1	362.3	360.1
105°	432.8	438.6	442.9	446.5	446.5
107.5°	524.8	533.5	533.5	534.9	524.8
110°	614.0	625.5	625.5	625.5	619.7



TEST NUMBER: P904536

CATALOG NUMBER: DFN2DIP-TR3F0-090D080US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	710.3	722.6	720.4	714.6	710.3
115°	805.2	816.7	813.1	811.0	805.2
117.5°	899.4	915.2	905.1	899.4	893.6
120°	994.3	1010.1	994.3	994.3	987.8
122.5°	1080.5	1100.7	1090.6	1084.9	1080.5
125°	1171.1	1189.1	1183.4	1176.9	1174.8
127.5°	1259.6	1281.9	1273.9	1265.4	1259.6
130°	1342.3	1368.1	1364.5	1360.3	1352.4
132.5°	1435.0	1455.1	1456.6	1446.5	1440.8
135°	1514.8	1537.1	1541.4	1539.3	1533.5
137.5°	1603.9	1621.9	1625.5	1624.1	1615.4
140°	1682.3	1700.3	1710.3	1710.3	1702.4
142.5°	1762.8	1780.8	1786.6	1788.8	1780.8
145°	1839.1	1853.4	1864.9	1867.1	1859.2
147.5°	1907.3	1925.3	1933.9	1937.6	1929.7
150°	1977.8	1990.0	1997.9	2004.4	1997.9
152.5°	2040.3	2052.6	2062.7	2070.6	2062.7
155°	2102.9	2108.7	2115.2	2125.2	2118.7
157.5°	2156.8	2161.2	2164.7	2179.1	2169.1
160°	2205.0	2209.3	2211.5	2223.6	2215.1
162.5°	2249.6	2249.6	2251.7	2265.4	2255.3
165°	2287.6	2285.5	2285.5	2299.9	2289.8
167.5°	2322.1	2315.7	2315.7	2330.1	2320.0
170°	2348.1	2342.3	2340.1	2354.6	2342.3
172.5°	2366.1	2360.3	2358.1	2372.5	2360.3
175°	2380.4	2374.6	2370.3	2384.7	2372.5
177.5°	2388.3	2382.6	2378.2	2390.5	2378.2
180°	2384.7	2384.7	2384.7	2384.7	2384.7

TEST NUMBER: P904536

CATALOG NUMBER: DFN2DIP-TR3F0-090D080US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.65	13.56	13.55	14.49	15.68	12.22	13.14	13.13	14.06	15.25
	3H	14.30	15.13	15.22	16.06	17.27	13.84	14.66	14.75	15.59	16.80
	4H	14.89	15.66	15.82	16.60	17.82	14.42	15.20	15.35	16.14	17.36
	6H	15.28	16.00	16.23	16.95	18.18	14.81	15.53	15.76	16.48	17.71
	8H	15.39	16.07	16.34	17.03	18.26	14.92	15.60	15.87	16.56	17.79
	12H	15.43	16.08	16.39	17.04	18.29	14.96	15.61	15.92	16.57	17.82
4H	2H	13.11	13.89	14.05	14.83	16.05	12.77	13.55	13.71	14.49	15.71
	3H	14.97	15.62	15.92	16.59	17.83	14.58	15.23	15.53	16.20	17.44
	4H	15.68	16.28	16.64	17.24	18.50	15.28	15.87	16.24	16.84	18.10
	6H	16.19	16.70	17.16	17.69	18.95	15.79	16.30	16.76	17.29	18.55
	8H	16.34	16.82	17.31	17.80	19.07	15.93	16.41	16.91	17.39	18.66
	12H	16.41	16.84	17.40	17.84	19.12	15.99	16.43	16.99	17.42	18.70
8H	4H	15.88	16.36	16.85	17.34	18.61	15.52	16.00	16.50	16.98	18.25
	6H	16.50	16.90	17.50	17.92	19.19	16.14	16.54	17.14	17.56	18.83
	8H	16.72	17.07	17.72	18.08	19.37	16.35	16.70	17.36	17.71	19.00
	12H	16.84	17.15	17.86	18.16	19.49	16.47	16.77	17.48	17.78	19.11
12H	4H	15.87	16.30	16.86	17.30	18.57	15.52	15.95	16.51	16.95	18.23
	6H	16.53	16.88	17.54	17.89	19.18	16.18	16.53	17.19	17.54	18.83
	8H	16.77	17.08	17.78	18.08	19.42	16.42	16.72	17.43	17.73	19.06