

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907099

Luminaire Tested: DFN2DIP-TR3F0-030D050US835-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907099
REPORT IS A COMBINATION OF REPORTS P901820 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-030D050US835-RLLONL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7500.0 lumens
Efficiency: N/A
Efficacy: 122.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 61.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907099
CATALOG NUMBER: DFN2DIP-TR3F0-030D050US835-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P907099

CATALOG NUMBER: DFN2DIP-TR3F0-030D050US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				34
1	95	90	87	83	85	82	79	76	66	64	62	51	49	48	37	36	36	29				29
2	86	79	74	69	78	72	67	63	58	54	52	45	43	41	33	32	30	25				25
3	79	70	63	58	71	63	58	53	51	47	44	40	37	35	30	28	26	22				22
4	72	62	55	49	65	56	50	45	46	41	37	36	33	30	27	25	23	19				19
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	17				17
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	20	18	15				15
7	57	45	37	32	51	41	34	30	34	29	25	27	23	20	20	18	16	13				13
8	52	41	33	28	47	37	31	26	31	26	22	24	21	18	19	16	14	12				12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11				11
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10				10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1545	1545	1545
5°	1547	1519	1529
10°	1530	1488	1478
15°	1509	1438	1401
20°	1480	1369	1305
25°	1450	1292	1213
30°	1411	1213	1097
35°	1373	1128	995
40°	1334	1040	878
45°	1288	943	773
50°	1241	845	669
55°	1192	741	570
60°	1135	632	468
65°	1069	522	420
70°	989	419	379
75°	889	366	342
80°	744	303	294
85°	506	196	215

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1288 cd/sqm



TEST NUMBER: P907099

CATALOG NUMBER: DFN2DIP-TR3F0-030D050US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.2	1.5
10°-20°	319.0	4.3
20°-30°	447.9	6.0
30°-40°	488.2	6.5
40°-50°	448.7	6.0
50°-60°	352.4	4.7
60°-70°	229.4	3.1
70°-80°	118.1	1.6
80°-90°	33.1	0.4
90°-100°	55.7	0.7
100°-110°	207.4	2.8
110°-120°	550.1	7.3
120°-130°	912.4	12.2
130°-140°	969.2	12.9
140°-150°	900.8	12.0
150°-160°	724.2	9.7
160°-170°	466.6	6.2
170°-180°	160.6	2.1
0°-30°	883.1	11.8
0°-40°	1371.3	18.3
0°-60°	2172.4	29.0
0°-90°	2552.9	34.0
90°-120°	813.2	10.8
90°-150°	3595.6	47.9
90°-180°	4947.0	66.0
0°-180°	7500.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1240	1240	1240	1240	1240	
5°	1240	1234	1220	1230	1226	118
15°	1179	1167	1129	1108	1096	332
25°	1070	1034	960	914	898	492
35°	922	865	766	696	671	577
45°	754	679	561	481	454	582
55°	573	486	365	297	276	512
65°	387	296	195	157	154	384
75°	206	128	90	82	81	218
85°	48	25	21	21	21	55
90°	1	15	24	31	33	7
95°	79	39	48	54	52	94
105°	371	408	74	88	93	397
115°	702	723	753	188	100	691
125°	993	1009	1032	1040	1044	885
135°	1228	1248	1259	1271	1269	949
145°	1425	1424	1444	1453	1447	891
155°	1569	1558	1573	1580	1570	723
165°	1653	1646	1650	1658	1650	467
175°	1691	1682	1685	1694	1681	161
180°	1687	1687	1687	1687	1687	



TEST NUMBER: P907099

CATALOG NUMBER: DFN2DIP-TR3F0-030D050US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1239.9	1239.9	1239.9	1239.9	1239.9
2.5°	1245.5	1239.9	1227.5	1238.8	1236.6
5°	1239.9	1234.3	1219.7	1229.8	1226.4
7.5°	1229.8	1223.1	1207.4	1211.8	1206.2
10°	1216.3	1208.5	1186.1	1182.6	1176.0
12.5°	1199.5	1189.4	1159.1	1152.4	1140.0
15°	1179.3	1166.9	1128.8	1107.5	1096.3
17.5°	1155.7	1137.8	1090.6	1066.0	1048.0
20°	1128.8	1106.3	1050.2	1022.3	997.5
22.5°	1099.7	1073.8	1008.7	970.6	953.8
25°	1070.5	1034.5	960.5	914.5	897.6
27.5°	1035.7	997.5	915.6	862.9	837.0
30°	998.7	956.0	866.2	809.1	778.7
32.5°	962.7	911.1	819.2	751.8	723.7
35°	922.4	865.1	766.4	695.7	671.0
37.5°	883.1	821.3	717.0	639.5	611.6
40°	841.6	774.3	665.4	585.7	556.6
42.5°	798.9	727.2	613.8	530.7	502.7
45°	754.1	678.8	561.1	481.3	454.4
47.5°	711.4	631.8	510.6	430.8	406.2
50°	664.3	584.6	461.2	383.7	360.2
52.5°	618.2	534.1	414.1	340.0	318.7
55°	573.3	485.8	364.6	297.4	276.1
57.5°	527.4	437.6	321.0	258.1	240.1
60°	480.2	390.5	274.9	217.7	199.8
62.5°	434.3	344.5	235.6	181.8	172.9
65°	387.1	296.2	195.2	157.1	153.7
67.5°	342.3	251.3	157.1	138.0	134.6
70°	295.1	207.6	130.1	118.9	114.4
72.5°	250.2	167.1	108.8	99.9	97.6
75°	206.4	127.9	89.8	81.9	80.8
77.5°	162.7	90.8	70.7	66.2	63.9
80°	122.3	65.1	53.8	49.4	49.4
82.5°	85.2	43.8	37.0	34.8	34.8
85°	48.2	24.6	21.3	21.3	21.3
87.5°	18.0	8.9	8.9	7.9	7.9
90°	1.2	14.6	24.4	30.6	32.9
92.5°	30.6	25.7	29.3	31.8	32.9
95°	79.3	39.0	47.6	53.8	52.5
97.5°	142.8	42.8	62.2	66.0	67.1
100°	216.2	48.9	69.6	79.3	81.8
102.5°	296.7	294.3	72.1	85.4	89.2
105°	371.2	407.9	74.5	87.9	92.8
107.5°	457.9	488.3	77.0	90.3	95.3
110°	541.0	566.5	213.7	91.6	96.4



TEST NUMBER: P907099

CATALOG NUMBER: DFN2DIP-TR3F0-030D050US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	619.1	641.0	620.3	94.0	97.7
115°	702.1	722.8	753.4	188.1	100.2
117.5°	774.1	798.5	819.4	644.6	324.8
120°	854.7	873.0	895.0	909.7	744.8
122.5°	923.0	942.6	967.1	974.4	975.7
125°	992.6	1008.6	1031.8	1040.3	1044.0
127.5°	1056.1	1073.2	1091.7	1103.8	1105.0
130°	1116.0	1135.6	1148.9	1162.4	1161.3
132.5°	1177.1	1193.0	1206.3	1217.4	1216.2
135°	1228.4	1248.0	1258.8	1271.2	1268.7
137.5°	1282.0	1296.7	1309.0	1321.2	1317.6
140°	1334.5	1344.4	1357.7	1368.7	1362.7
142.5°	1378.6	1387.2	1403.0	1412.7	1406.6
145°	1425.0	1423.7	1444.4	1453.0	1446.9
147.5°	1465.2	1461.5	1482.3	1488.4	1483.6
150°	1504.3	1495.8	1515.3	1522.6	1516.5
152.5°	1537.2	1527.5	1545.8	1553.2	1544.6
155°	1569.0	1558.1	1572.7	1580.0	1570.3
157.5°	1594.6	1584.9	1595.9	1604.5	1594.6
160°	1616.7	1609.3	1616.7	1623.9	1615.4
162.5°	1636.1	1628.9	1634.9	1643.5	1632.5
165°	1653.2	1646.0	1649.6	1658.1	1649.6
167.5°	1666.7	1659.3	1663.1	1671.6	1660.6
170°	1677.7	1670.3	1672.8	1681.3	1670.3
172.5°	1685.0	1677.7	1680.2	1688.7	1677.7
175°	1691.1	1682.5	1685.0	1693.5	1681.3
177.5°	1693.5	1685.0	1686.3	1694.8	1683.8
180°	1687.4	1687.4	1687.4	1687.4	1687.4



TEST NUMBER: P907099
 CATALOG NUMBER: DFN2DIP-TR3F0-030D050US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.90	7.62	7.99	8.70	10.18	2.88	3.59	3.97	4.68	6.16
	3H	8.56	9.20	9.66	10.29	11.79	4.05	4.69	5.15	5.78	7.29
	4H	9.16	9.76	10.27	10.86	12.37	4.49	5.10	5.60	6.19	7.70
	6H	9.57	10.12	10.68	11.22	12.74	4.80	5.36	5.92	6.46	7.98
	8H	9.68	10.21	10.80	11.33	12.84	4.89	5.42	6.01	6.53	8.04
	12H	9.74	10.24	10.86	11.35	12.88	4.93	5.43	6.05	6.53	8.07
4H	2H	6.90	7.51	8.02	8.60	10.11	3.45	4.06	4.57	5.15	6.66
	3H	8.71	9.22	9.83	10.34	11.86	4.79	5.29	5.91	6.41	7.93
	4H	9.39	9.86	10.52	10.97	12.51	5.33	5.79	6.45	6.90	8.44
	6H	9.89	10.29	11.02	11.42	12.95	5.73	6.13	6.86	7.26	8.79
	8H	10.06	10.43	11.19	11.55	13.10	5.86	6.23	6.99	7.35	8.90
	12H	10.14	10.48	11.29	11.62	13.17	5.91	6.25	7.06	7.38	8.94
8H	4H	9.35	9.72	10.48	10.84	12.39	5.59	5.96	6.72	7.09	8.63
	6H	9.90	10.21	11.05	11.37	12.92	6.10	6.40	7.25	7.57	9.11
	8H	10.11	10.38	11.27	11.52	13.09	6.28	6.55	7.44	7.70	9.26
	12H	10.24	10.47	11.40	11.62	13.22	6.39	6.63	7.55	7.77	9.37
12H	4H	9.30	9.63	10.44	10.77	12.32	5.59	5.92	6.74	7.06	8.61
	6H	9.88	10.14	11.03	11.29	12.86	6.14	6.41	7.30	7.56	9.12
	8H	10.09	10.32	11.25	11.46	13.06	6.34	6.58	7.51	7.72	9.32