

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907109

Luminaire Tested: DFN2DIP-TR3F0-030D080US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907109
REPORT IS A COMBINATION OF REPORTS P901861 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-030D080US835-FLLONL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10890.0 lumens
Efficiency: N/A
Efficacy: 128.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 85.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907109

CATALOG NUMBER: DFN2DIP-TR3F0-030D080US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P907109

CATALOG NUMBER: DFN2DIP-TR3F0-030D080US835-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35
1	93	89	85	81	83	79	76	73	62	60	58	46	45	43	31	30	30
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	55	68	61	55	50	48	44	40	36	33	31	24	23	21
4	70	60	52	47	63	54	47	42	42	38	34	32	29	26	22	20	18
5	64	53	45	40	57	48	41	36	38	33	29	28	25	23	19	18	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	14	12	10
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1455	1455	1455
5°	1456	1433	1443
10°	1444	1413	1423
15°	1421	1388	1391
20°	1392	1355	1359
25°	1363	1315	1322
30°	1326	1278	1275
35°	1291	1234	1225
40°	1249	1190	1178
45°	1206	1145	1130
50°	1160	1099	1074
55°	1111	1045	1022
60°	1055	981	963
65°	995	915	893
70°	918	834	818
75°	812	737	747
80°	683	613	614
85°	483	404	396

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1796 cd/sqm

TEST NUMBER: P907109

CATALOG NUMBER: DFN2DIP-TR3F0-030D080US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.9	1.0
10°-20°	309.1	2.8
20°-30°	454.3	4.2
30°-40°	527.6	4.8
40°-50°	527.0	4.8
50°-60°	459.5	4.2
60°-70°	339.7	3.1
70°-80°	192.2	1.8
80°-90°	55.5	0.5
90°-100°	89.0	0.8
100°-110°	331.9	3.0
110°-120°	880.2	8.1
120°-130°	1459.9	13.4
130°-140°	1550.7	14.2
140°-150°	1441.2	13.2
150°-160°	1158.7	10.6
160°-170°	746.6	6.9
170°-180°	257.0	2.4
0°-30°	873.3	8.0
0°-40°	1400.9	12.9
0°-60°	2387.4	21.9
0°-90°	2974.8	27.3
90°-120°	1301.1	11.9
90°-150°	5752.9	52.8
90°-180°	7915.0	72.7
0°-180°	10890.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1167	1167	1167	1167	1167	
5°	1167	1163	1150	1160	1157	111
15°	1111	1105	1090	1094	1089	313
25°	1006	997	978	980	978	463
35°	868	856	838	832	826	542
45°	706	698	681	669	664	545
55°	534	528	514	501	495	478
65°	360	354	342	332	327	356
75°	188	186	181	174	176	201
85°	46	45	44	40	39	51
90°	2	23	39	49	53	10
95°	127	62	76	86	84	150
105°	594	653	119	141	148	635
115°	1123	1156	1205	301	160	1106
125°	1588	1614	1651	1664	1670	1416
135°	1965	1997	2014	2034	2030	1518
145°	2280	2278	2311	2325	2315	1426
155°	2510	2493	2516	2528	2512	1157
165°	2645	2634	2639	2653	2639	747
175°	2706	2692	2696	2710	2690	258
180°	2700	2700	2700	2700	2700	

TEST NUMBER: P907109

CATALOG NUMBER: DFN2DIP-TR3F0-030D080US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1167.3	1167.3	1167.3	1167.3	1167.3
2.5°	1174.1	1168.5	1156.1	1167.3	1165.2
5°	1167.3	1162.9	1150.5	1159.5	1157.3
7.5°	1159.5	1152.8	1140.4	1149.5	1147.2
10°	1147.2	1139.3	1125.9	1134.8	1131.5
12.5°	1130.3	1123.6	1110.2	1115.7	1113.5
15°	1111.2	1104.6	1089.9	1094.4	1088.8
17.5°	1087.6	1081.0	1066.3	1071.9	1066.3
20°	1061.8	1055.1	1039.4	1042.7	1038.3
22.5°	1036.1	1026.0	1011.3	1011.3	1009.0
25°	1005.7	996.8	977.7	979.9	977.7
27.5°	972.0	964.1	949.6	946.3	940.7
30°	938.4	929.4	912.6	909.2	904.7
32.5°	902.5	895.8	877.8	871.0	866.5
35°	867.7	856.5	838.5	831.7	826.1
37.5°	828.4	818.3	800.3	792.4	786.8
40°	788.0	779.0	761.0	751.0	746.5
42.5°	748.7	739.7	721.8	710.5	703.8
45°	706.1	698.2	681.3	669.0	664.5
47.5°	664.5	656.7	638.7	626.3	619.6
50°	620.7	615.1	599.4	583.7	578.1
52.5°	578.1	570.2	555.7	543.3	535.4
55°	534.4	527.6	514.1	500.7	495.1
57.5°	490.5	484.9	470.3	456.8	452.3
60°	446.7	442.3	426.6	414.2	410.9
62.5°	404.1	396.2	385.0	373.8	369.3
65°	360.4	353.6	342.4	332.3	326.7
67.5°	315.5	309.8	299.7	291.9	287.4
70°	273.9	269.4	259.3	251.4	247.0
72.5°	231.3	226.7	221.1	213.3	210.0
75°	188.5	186.4	180.7	174.0	176.3
77.5°	150.4	145.9	143.6	140.3	137.0
80°	112.3	111.1	108.8	105.5	103.3
82.5°	76.3	76.3	75.3	70.7	70.7
85°	46.0	44.9	43.8	40.4	39.3
87.5°	20.2	18.0	15.7	12.4	11.2
90°	1.9	23.4	39.0	48.9	52.7
92.5°	48.9	41.1	46.9	50.8	52.7
95°	126.9	62.4	76.1	86.1	84.0
97.5°	228.5	68.4	99.5	105.6	107.4
100°	345.9	78.2	111.4	126.9	130.8
102.5°	474.7	470.9	115.3	136.6	142.7
105°	593.9	652.6	119.2	140.6	148.5
107.5°	732.6	781.3	123.2	144.5	152.4
110°	865.6	906.4	342.0	146.6	154.3

TEST NUMBER: P907109

CATALOG NUMBER: DFN2DIP-TR3F0-030D080US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	990.6	1025.6	992.5	150.3	156.4
115°	1123.3	1156.5	1205.4	300.9	160.3
117.5°	1238.6	1277.6	1311.0	1031.4	519.7
120°	1367.6	1396.8	1432.1	1455.5	1191.7
122.5°	1476.8	1508.2	1547.4	1559.0	1561.1
125°	1588.2	1613.7	1650.8	1664.5	1670.3
127.5°	1689.8	1717.2	1746.7	1766.1	1768.0
130°	1785.6	1816.9	1838.3	1859.9	1858.0
132.5°	1883.3	1908.8	1930.2	1947.8	1945.9
135°	1965.4	1996.7	2014.1	2033.9	2029.9
137.5°	2051.3	2074.7	2094.4	2113.9	2108.1
140°	2135.2	2151.0	2172.4	2190.0	2180.2
142.5°	2205.8	2219.4	2244.7	2260.3	2250.5
145°	2280.0	2277.9	2311.1	2324.8	2315.0
147.5°	2344.3	2338.5	2371.6	2381.4	2373.7
150°	2406.9	2393.2	2424.5	2436.1	2426.4
152.5°	2459.6	2444.0	2473.2	2485.1	2471.4
155°	2510.4	2493.0	2516.4	2528.0	2512.5
157.5°	2551.4	2535.9	2553.5	2567.2	2551.4
160°	2586.7	2574.9	2586.7	2598.3	2584.6
162.5°	2617.8	2606.2	2615.9	2629.6	2612.0
165°	2645.2	2633.6	2639.4	2653.0	2639.4
167.5°	2666.7	2654.9	2660.9	2674.6	2657.0
170°	2684.4	2672.5	2676.5	2690.2	2672.5
172.5°	2696.0	2684.4	2688.3	2702.0	2684.4
175°	2705.7	2692.0	2696.0	2709.6	2690.2
177.5°	2709.6	2696.0	2698.0	2711.7	2694.1
180°	2699.9	2699.9	2699.9	2699.9	2699.9

TEST NUMBER: P907109

CATALOG NUMBER: DFN2DIP-TR3F0-030D080US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.93	6.62	7.06	7.74	9.30	5.50	6.19	6.63	7.31	8.87
	3H	7.57	8.18	8.70	9.31	10.89	7.10	7.71	8.24	8.84	10.42
	4H	8.14	8.72	9.29	9.86	11.44	7.67	8.26	8.82	9.39	10.97
	6H	8.52	9.06	9.68	10.19	11.79	8.05	8.59	9.21	9.73	11.32
	8H	8.62	9.13	9.78	10.28	11.87	8.15	8.66	9.31	9.81	11.40
	12H	8.66	9.14	9.82	10.29	11.90	8.18	8.67	9.35	9.81	11.42
4H	2H	6.36	6.95	7.52	8.08	9.66	6.02	6.61	7.18	7.74	9.32
	3H	8.20	8.69	9.36	9.85	11.44	7.81	8.30	8.97	9.46	11.05
	4H	8.90	9.35	10.07	10.50	12.11	8.50	8.95	9.67	10.10	11.71
	6H	9.40	9.79	10.57	10.95	12.56	9.00	9.38	10.16	10.55	12.15
	8H	9.54	9.90	10.71	11.06	12.68	9.13	9.49	10.30	10.65	12.28
	12H	9.60	9.93	10.78	11.10	12.72	9.19	9.51	10.37	10.68	12.31
8H	4H	9.08	9.44	10.25	10.60	12.22	8.73	9.08	9.89	10.24	11.87
	6H	9.69	9.99	10.88	11.19	12.81	9.34	9.63	10.52	10.84	12.45
	8H	9.91	10.17	11.10	11.35	12.98	9.54	9.80	10.74	10.98	12.62
	12H	10.02	10.25	11.22	11.43	13.10	9.65	9.87	10.84	11.05	12.72
12H	4H	9.06	9.38	10.24	10.56	12.18	8.71	9.04	9.89	10.21	11.83
	6H	9.72	9.98	10.91	11.16	12.80	9.37	9.63	10.57	10.81	12.45
	8H	9.95	10.18	11.14	11.35	13.02	9.60	9.82	10.79	11.00	12.67

END OF REPORT