

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907111

Luminaire Tested: DFN2DIP-TR3F0-030D080US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907111
REPORT IS A COMBINATION OF REPORTS P901862 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-030D080US835-RLLONL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10470.0 lumens
Efficiency: N/A
Efficacy: 123.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 85.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907111

CATALOG NUMBER: DFN2DIP-TR3F0-030D080US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P907111

CATALOG NUMBER: DFN2DIP-TR3F0-030D080US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	26	25	24
3	77	68	61	56	68	61	55	50	47	43	40	35	32	30	23	22	21
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	17	16
6	59	48	40	35	53	43	37	32	34	29	26	25	22	20	17	15	14
7	55	43	36	30	49	39	32	28	31	26	23	23	20	17	16	14	12
8	51	39	32	27	45	35	29	25	28	23	20	21	18	16	14	13	11
9	47	36	29	24	42	32	26	22	25	21	18	19	16	14	13	11	10
10	44	33	26	21	39	29	23	19	23	19	16	18	15	13	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1545	1545	1545
5°	1547	1519	1529
10°	1530	1488	1478
15°	1509	1438	1401
20°	1480	1369	1305
25°	1450	1292	1213
30°	1411	1213	1097
35°	1373	1128	995
40°	1334	1040	878
45°	1288	943	773
50°	1241	845	669
55°	1192	741	570
60°	1135	632	468
65°	1069	522	420
70°	989	419	379
75°	889	366	342
80°	744	303	294
85°	506	196	215

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1796 cd/sqm

TEST NUMBER: P907111

CATALOG NUMBER: DFN2DIP-TR3F0-030D080US835-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.2	1.1
10°-20°	319.0	3.0
20°-30°	447.9	4.3
30°-40°	488.2	4.7
40°-50°	448.7	4.3
50°-60°	352.4	3.4
60°-70°	229.4	2.2
70°-80°	118.1	1.1
80°-90°	34.9	0.3
90°-100°	89.0	0.9
100°-110°	331.9	3.2
110°-120°	880.2	8.4
120°-130°	1459.9	13.9
130°-140°	1550.7	14.8
140°-150°	1441.2	13.8
150°-160°	1158.7	11.1
160°-170°	746.6	7.1
170°-180°	257.0	2.5
0°-30°	883.1	8.4
0°-40°	1371.3	13.1
0°-60°	2172.4	20.7
0°-90°	2554.7	24.4
90°-120°	1301.1	12.4
90°-150°	5752.9	54.9
90°-180°	7915.0	75.6
0°-180°	10470.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1240	1240	1240	1240	1240	
5°	1240	1234	1220	1230	1226	118
15°	1179	1167	1129	1108	1096	332
25°	1070	1034	960	914	898	492
35°	922	865	766	696	671	577
45°	754	679	561	481	454	582
55°	573	486	365	297	276	512
65°	387	296	195	157	154	384
75°	206	128	90	82	81	218
85°	48	25	21	21	21	55
90°	2	23	39	49	53	10
95°	127	62	76	86	84	150
105°	594	653	119	141	148	635
115°	1123	1156	1205	301	160	1106
125°	1588	1614	1651	1664	1670	1416
135°	1965	1997	2014	2034	2030	1518
145°	2280	2278	2311	2325	2315	1426
155°	2510	2493	2516	2528	2512	1157
165°	2645	2634	2639	2653	2639	747
175°	2706	2692	2696	2710	2690	258
180°	2700	2700	2700	2700	2700	

TEST NUMBER: P907111

CATALOG NUMBER: DFN2DIP-TR3F0-030D080US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1239.9	1239.9	1239.9	1239.9	1239.9
2.5°	1245.5	1239.9	1227.5	1238.8	1236.6
5°	1239.9	1234.3	1219.7	1229.8	1226.4
7.5°	1229.8	1223.1	1207.4	1211.8	1206.2
10°	1216.3	1208.5	1186.1	1182.6	1176.0
12.5°	1199.5	1189.4	1159.1	1152.4	1140.0
15°	1179.3	1166.9	1128.8	1107.5	1096.3
17.5°	1155.7	1137.8	1090.6	1066.0	1048.0
20°	1128.8	1106.3	1050.2	1022.3	997.5
22.5°	1099.7	1073.8	1008.7	970.6	953.8
25°	1070.5	1034.5	960.5	914.5	897.6
27.5°	1035.7	997.5	915.6	862.9	837.0
30°	998.7	956.0	866.2	809.1	778.7
32.5°	962.7	911.1	819.2	751.8	723.7
35°	922.4	865.1	766.4	695.7	671.0
37.5°	883.1	821.3	717.0	639.5	611.6
40°	841.6	774.3	665.4	585.7	556.6
42.5°	798.9	727.2	613.8	530.7	502.7
45°	754.1	678.8	561.1	481.3	454.4
47.5°	711.4	631.8	510.6	430.8	406.2
50°	664.3	584.6	461.2	383.7	360.2
52.5°	618.2	534.1	414.1	340.0	318.7
55°	573.3	485.8	364.6	297.4	276.1
57.5°	527.4	437.6	321.0	258.1	240.1
60°	480.2	390.5	274.9	217.7	199.8
62.5°	434.3	344.5	235.6	181.8	172.9
65°	387.1	296.2	195.2	157.1	153.7
67.5°	342.3	251.3	157.1	138.0	134.6
70°	295.1	207.6	130.1	118.9	114.4
72.5°	250.2	167.1	108.8	99.9	97.6
75°	206.4	127.9	89.8	81.9	80.8
77.5°	162.7	90.8	70.7	66.2	63.9
80°	122.3	65.1	53.8	49.4	49.4
82.5°	85.2	43.8	37.0	34.8	34.8
85°	48.2	24.6	21.3	21.3	21.3
87.5°	18.0	8.9	8.9	7.9	7.9
90°	1.9	23.4	39.0	48.9	52.7
92.5°	48.9	41.1	46.9	50.8	52.7
95°	126.9	62.4	76.1	86.1	84.0
97.5°	228.5	68.4	99.5	105.6	107.4
100°	345.9	78.2	111.4	126.9	130.8
102.5°	474.7	470.9	115.3	136.6	142.7
105°	593.9	652.6	119.2	140.6	148.5
107.5°	732.6	781.3	123.2	144.5	152.4
110°	865.6	906.4	342.0	146.6	154.3

TEST NUMBER: P907111

CATALOG NUMBER: DFN2DIP-TR3F0-030D080US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	990.6	1025.6	992.5	150.3	156.4
115°	1123.3	1156.5	1205.4	300.9	160.3
117.5°	1238.6	1277.6	1311.0	1031.4	519.7
120°	1367.6	1396.8	1432.1	1455.5	1191.7
122.5°	1476.8	1508.2	1547.4	1559.0	1561.1
125°	1588.2	1613.7	1650.8	1664.5	1670.3
127.5°	1689.8	1717.2	1746.7	1766.1	1768.0
130°	1785.6	1816.9	1838.3	1859.9	1858.0
132.5°	1883.3	1908.8	1930.2	1947.8	1945.9
135°	1965.4	1996.7	2014.1	2033.9	2029.9
137.5°	2051.3	2074.7	2094.4	2113.9	2108.1
140°	2135.2	2151.0	2172.4	2190.0	2180.2
142.5°	2205.8	2219.4	2244.7	2260.3	2250.5
145°	2280.0	2277.9	2311.1	2324.8	2315.0
147.5°	2344.3	2338.5	2371.6	2381.4	2373.7
150°	2406.9	2393.2	2424.5	2436.1	2426.4
152.5°	2459.6	2444.0	2473.2	2485.1	2471.4
155°	2510.4	2493.0	2516.4	2528.0	2512.5
157.5°	2551.4	2535.9	2553.5	2567.2	2551.4
160°	2586.7	2574.9	2586.7	2598.3	2584.6
162.5°	2617.8	2606.2	2615.9	2629.6	2612.0
165°	2645.2	2633.6	2639.4	2653.0	2639.4
167.5°	2666.7	2654.9	2660.9	2674.6	2657.0
170°	2684.4	2672.5	2676.5	2690.2	2672.5
172.5°	2696.0	2684.4	2688.3	2702.0	2684.4
175°	2705.7	2692.0	2696.0	2709.6	2690.2
177.5°	2709.6	2696.0	2698.0	2711.7	2694.1
180°	2699.9	2699.9	2699.9	2699.9	2699.9

TEST NUMBER: P907111

CATALOG NUMBER: DFN2DIP-TR3F0-030D080US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.54	6.20	6.69	7.33	8.93	1.52	2.17	2.67	3.31	4.91
	3H	7.19	7.78	8.35	8.93	10.54	2.68	3.27	3.85	4.42	6.03
	4H	7.79	8.35	8.96	9.49	11.11	3.12	3.68	4.29	4.83	6.44
	6H	8.19	8.71	9.37	9.85	11.48	3.43	3.94	4.61	5.09	6.72
	8H	8.31	8.80	9.49	9.96	11.58	3.51	4.00	4.69	5.16	6.78
	12H	8.36	8.82	9.54	9.98	11.62	3.55	4.01	4.73	5.17	6.81
4H	2H	5.53	6.09	6.71	7.24	8.85	2.08	2.64	3.26	3.79	5.41
	3H	7.34	7.80	8.52	8.97	10.60	3.41	3.88	4.59	5.05	6.68
	4H	8.01	8.44	9.20	9.60	11.25	3.95	4.38	5.13	5.54	7.18
	6H	8.51	8.88	9.70	10.06	11.70	4.35	4.72	5.54	5.90	7.54
	8H	8.68	9.02	9.86	10.19	11.85	4.47	4.81	5.66	5.99	7.64
	12H	8.76	9.07	9.96	10.25	11.91	4.53	4.84	5.73	6.02	7.68
8H	4H	7.97	8.31	9.15	9.48	11.14	4.21	4.55	5.40	5.72	7.38
	6H	8.52	8.80	9.72	10.02	11.67	4.71	4.99	5.92	6.21	7.86
	8H	8.73	8.97	9.94	10.17	11.84	4.90	5.14	6.11	6.34	8.01
	12H	8.85	9.07	10.06	10.26	11.96	5.01	5.22	6.22	6.41	8.11
12H	4H	7.91	8.22	9.11	9.41	11.06	4.20	4.51	5.41	5.70	7.36
	6H	8.49	8.74	9.70	9.93	11.60	4.76	5.00	5.97	6.20	7.87
	8H	8.70	8.91	9.91	10.10	11.81	4.96	5.17	6.17	6.36	8.07

END OF REPORT