

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917955

Luminaire Tested: DFN2DIP-TR2F0-040D050US930-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917955
REPORT IS A COMBINATION OF REPORTS P901776 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-040D050US930-RLLONL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6379.7 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 74.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917955
CATALOG NUMBER: DFN2DIP-TR2F0-040D050US930-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P917955
 CATALOG NUMBER: DFN2DIP-TR2F0-040D050US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44			44
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43	37			37
2	88	81	75	71	81	75	70	65	62	59	55	51	48	46	40	38	37	32			32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28			28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28	24			24
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	29	27	25	21			21
6	63	51	43	38	57	47	41	35	40	35	31	33	29	26	27	24	22	19			19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17			17
8	54	42	35	30	50	39	32	28	33	28	24	28	24	21	23	20	18	15			15
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14			14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3006	3006	3006
5°	3007	2952	2972
10°	2973	2887	2871
15°	2927	2785	2716
20°	2868	2648	2529
25°	2808	2494	2348
30°	2729	2338	2120
35°	2652	2171	1920
40°	2572	1998	1692
45°	2481	1807	1486
50°	2385	1615	1284
55°	2286	1411	1091
60°	2169	1199	893
65°	2036	984	798
70°	1874	784	715
75°	1670	678	641
80°	1376	550	540
85°	904	342	381

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2481 cd/sqm



TEST NUMBER: P917955
 CATALOG NUMBER: DFN2DIP-TR2F0-040D050US930-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	2.0
10°-20°	346.8	5.4
20°-30°	486.9	7.6
30°-40°	530.7	8.3
40°-50°	487.8	7.6
50°-60°	383.1	6.0
60°-70°	249.3	3.9
70°-80°	128.4	2.0
80°-90°	36.4	0.6
90°-100°	79.8	1.3
100°-110°	253.5	4.0
110°-120°	433.8	6.8
120°-130°	570.5	8.9
130°-140°	640.4	10.0
140°-150°	627.9	9.8
150°-160°	526.8	8.3
160°-170°	349.3	5.5
170°-180°	122.1	1.9
0°-30°	960.0	15.0
0°-40°	1490.7	23.4
0°-60°	2361.5	37.0
0°-90°	2775.7	43.5
90°-120°	767.0	12.0
90°-150°	2605.8	40.8
90°-180°	3604.0	56.5
0°-180°	6379.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1348	1348	1348	1348	1348	
5°	1348	1342	1326	1337	1333	128
15°	1282	1268	1227	1204	1192	361
25°	1164	1125	1044	994	976	535
35°	1003	940	833	756	729	628
45°	820	738	610	523	494	633
55°	623	528	396	323	300	557
65°	421	322	212	171	167	417
75°	224	139	98	89	88	237
85°	52	27	23	23	23	60
90°	1	14	38	36	37	6
95°	57	68	70	70	68	63
105°	234	237	240	241	241	247
115°	435	442	440	438	435	431
125°	633	643	640	636	635	566
135°	819	831	833	832	829	633
145°	994	1002	1008	1009	1005	621
155°	1137	1140	1144	1149	1145	523
165°	1237	1236	1236	1243	1238	349
175°	1287	1284	1282	1289	1283	122
180°	1289	1289	1289	1289	1289	



TEST NUMBER: P917955

CATALOG NUMBER: DFN2DIP-TR2F0-040D050US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1347.9	1347.9	1347.9	1347.9	1347.9
2.5°	1354.0	1347.9	1334.4	1346.7	1344.2
5°	1347.9	1341.7	1325.8	1336.8	1333.3
7.5°	1336.8	1329.6	1312.5	1317.3	1311.2
10°	1322.3	1313.7	1289.3	1285.6	1278.4
12.5°	1304.0	1293.0	1260.0	1252.7	1239.3
15°	1282.0	1268.5	1227.1	1204.0	1191.8
17.5°	1256.4	1236.8	1185.5	1158.8	1139.2
20°	1227.1	1202.6	1141.7	1111.3	1084.3
22.5°	1195.4	1167.3	1096.5	1055.1	1036.9
25°	1163.7	1124.6	1044.1	994.2	975.7
27.5°	1125.9	1084.3	995.3	938.0	909.9
30°	1085.7	1039.2	941.6	879.5	846.5
32.5°	1046.6	990.4	890.5	817.3	786.7
35°	1002.7	940.4	833.2	756.3	729.4
37.5°	960.0	892.8	779.4	695.2	664.8
40°	914.8	841.7	723.3	636.7	605.0
42.5°	868.5	790.4	667.2	576.9	546.5
45°	819.7	737.9	609.9	523.3	494.0
47.5°	773.4	686.8	555.1	468.4	441.6
50°	722.1	635.5	501.3	417.1	391.6
52.5°	672.1	580.6	450.1	369.6	346.4
55°	623.3	528.2	396.4	323.3	300.1
57.5°	573.3	475.7	348.9	280.5	261.1
60°	522.0	424.4	298.8	236.7	217.2
62.5°	472.1	374.5	256.1	197.6	187.9
65°	420.9	322.0	212.2	170.8	167.1
67.5°	372.1	273.2	170.8	150.0	146.3
70°	320.8	225.7	141.5	129.3	124.3
72.5°	272.1	181.7	118.3	108.6	106.2
75°	224.4	139.0	97.6	89.0	87.9
77.5°	176.9	98.7	76.9	72.0	69.5
80°	132.9	70.8	58.5	53.7	53.7
82.5°	92.7	47.6	40.3	37.7	37.7
85°	52.4	26.8	23.2	23.2	23.2
87.5°	19.6	9.7	9.7	8.6	8.6
90°	1.1	14.0	38.1	35.8	36.9
92.5°	24.1	32.6	33.8	35.0	35.0
95°	56.7	67.7	69.5	69.5	67.7
97.5°	94.4	104.5	108.8	108.8	108.8
100°	137.9	146.9	150.0	150.0	148.9
102.5°	183.8	190.5	194.7	195.9	194.7
105°	234.0	237.1	239.5	241.3	241.3
107.5°	283.7	288.4	288.4	289.2	283.7
110°	331.9	338.2	338.2	338.2	335.0



TEST NUMBER: P917955

CATALOG NUMBER: DFN2DIP-TR2F0-040D050US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	384.0	390.6	389.5	386.4	384.0
115°	435.3	441.6	439.6	438.5	435.3
117.5°	486.2	494.8	489.3	486.2	483.1
120°	537.5	546.1	537.5	537.5	534.0
122.5°	584.2	595.1	589.6	586.5	584.2
125°	633.2	642.9	639.8	636.3	635.1
127.5°	680.9	693.0	688.8	684.0	680.9
130°	725.7	739.6	737.7	735.4	731.1
132.5°	775.8	786.7	787.5	782.0	778.9
135°	819.0	831.0	833.3	832.2	829.1
137.5°	867.2	876.9	878.8	878.0	873.3
140°	909.5	919.2	924.6	924.6	920.4
142.5°	953.0	962.8	965.9	967.0	962.8
145°	994.3	1002.0	1008.2	1009.4	1005.1
147.5°	1031.2	1040.9	1045.5	1047.5	1043.2
150°	1069.3	1075.9	1080.1	1083.6	1080.1
152.5°	1103.1	1109.7	1115.1	1119.4	1115.1
155°	1136.9	1140.0	1143.5	1148.9	1145.4
157.5°	1166.0	1168.3	1170.3	1178.1	1172.6
160°	1192.0	1194.4	1195.6	1202.2	1197.5
162.5°	1216.2	1216.2	1217.3	1224.7	1219.3
165°	1236.8	1235.6	1235.6	1243.4	1237.9
167.5°	1255.4	1251.9	1251.9	1259.7	1254.3
170°	1269.4	1266.3	1265.2	1272.9	1266.3
172.5°	1279.1	1276.0	1274.9	1282.6	1276.0
175°	1286.9	1283.8	1281.5	1289.2	1282.6
177.5°	1291.2	1288.1	1285.7	1292.3	1285.7
180°	1289.2	1289.2	1289.2	1289.2	1289.2



TEST NUMBER: P917955
 CATALOG NUMBER: DFN2DIP-TR2F0-040D050US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.20	10.98	11.22	12.00	13.37	6.18	6.96	7.20	7.99	9.35
	3H	11.85	12.55	12.88	13.58	14.96	7.35	8.05	8.38	9.08	10.46
	4H	12.44	13.10	13.48	14.14	15.53	7.79	8.45	8.83	9.48	10.88
	6H	12.84	13.45	13.89	14.49	15.89	8.10	8.70	9.14	9.74	11.14
	8H	12.96	13.53	14.01	14.59	15.99	8.18	8.75	9.23	9.81	11.21
	12H	13.01	13.56	14.07	14.60	16.03	8.21	8.76	9.27	9.81	11.23
4H	2H	10.21	10.87	11.26	11.90	13.30	6.76	7.42	7.81	8.45	9.84
	3H	12.01	12.56	13.06	13.62	15.02	8.09	8.64	9.14	9.70	11.10
	4H	12.68	13.18	13.74	14.24	15.66	8.62	9.12	9.68	10.17	11.60
	6H	13.17	13.60	14.24	14.68	16.10	9.02	9.45	10.09	10.53	11.95
	8H	13.33	13.73	14.40	14.80	16.24	9.14	9.54	10.21	10.61	12.04
	12H	13.41	13.77	14.50	14.86	16.30	9.19	9.55	10.28	10.64	12.08
8H	4H	12.64	13.04	13.71	14.11	15.55	8.88	9.28	9.95	10.35	11.79
	6H	13.18	13.51	14.27	14.62	16.06	9.38	9.71	10.47	10.82	12.25
	8H	13.38	13.67	14.48	14.77	16.22	9.55	9.85	10.65	10.94	12.39
	12H	13.50	13.76	14.60	14.85	16.34	9.66	9.91	10.76	11.00	12.50
12H	4H	12.59	12.95	13.68	14.04	15.48	8.88	9.24	9.97	10.33	11.77
	6H	13.15	13.44	14.25	14.54	15.99	9.42	9.71	10.52	10.81	12.26
	8H	13.36	13.61	14.46	14.70	16.19	9.61	9.87	10.72	10.96	12.45