

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917981

Luminaire Tested: DFN2DIP-TR2F0-060D020US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917981
REPORT IS A COMBINATION OF REPORTS P901749 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-060D020US930-FLLONL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6285.9 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 74.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917981

CATALOG NUMBER: DFN2DIP-TR2F0-060D020US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P917981

CATALOG NUMBER: DFN2DIP-TR2F0-060D020US930-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81
1	104	99	95	92	99	95	91	88	86	84	81	79	77	75	72	70	68
2	95	87	80	75	90	83	77	72	76	71	67	69	66	62	63	60	58
3	86	76	69	63	82	73	66	61	67	61	57	61	57	53	56	52	49
4	79	68	59	53	75	65	57	52	60	53	48	55	50	45	50	46	42
5	73	61	52	46	69	58	50	44	53	47	42	49	44	39	45	41	37
6	67	55	46	40	64	52	45	39	48	42	37	45	39	35	41	36	33
7	62	49	41	35	59	48	40	34	44	37	33	41	35	31	37	33	29
8	58	45	37	31	55	43	36	31	40	34	29	37	32	28	34	30	26
9	54	41	33	28	52	40	32	27	37	31	26	34	29	25	32	27	24
10	51	38	30	25	48	37	30	25	34	28	24	32	26	23	30	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4245	4245	4245
5°	4246	4177	4207
10°	4205	4111	4143
15°	4137	4034	4047
20°	4047	3930	3948
25°	3958	3809	3836
30°	3847	3695	3695
35°	3742	3562	3546
40°	3613	3427	3404
45°	3484	3292	3258
50°	3343	3149	3091
55°	3195	2985	2934
60°	3027	2791	2755
65°	2843	2588	2544
70°	2609	2341	2316
75°	2287	2046	2094
80°	1896	1669	1693
85°	1292	1051	1052

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3484 cd/sqm

TEST NUMBER: P917981

CATALOG NUMBER: DFN2DIP-TR2F0-060D020US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.1	2.8
10°-20°	504.1	8.0
20°-30°	740.8	11.8
30°-40°	860.4	13.7
40°-50°	859.3	13.7
50°-60°	749.3	11.9
60°-70°	553.9	8.8
70°-80°	313.4	5.0
80°-90°	84.2	1.3
90°-100°	31.9	0.5
100°-110°	101.4	1.6
110°-120°	173.5	2.8
120°-130°	228.2	3.6
130°-140°	256.1	4.1
140°-150°	251.2	4.0
150°-160°	210.7	3.4
160°-170°	139.7	2.2
170°-180°	48.8	0.8
0°-30°	1424.0	22.7
0°-40°	2284.3	36.3
0°-60°	3892.9	61.9
0°-90°	4844.3	77.1
90°-120°	306.8	4.9
90°-150°	1042.3	16.6
90°-180°	1442.0	22.9
0°-180°	6285.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1903	1903	1903	1903	1903	
5°	1903	1896	1876	1891	1887	181
15°	1812	1801	1777	1785	1776	510
25°	1640	1625	1594	1598	1594	755
35°	1415	1397	1367	1356	1347	884
45°	1151	1138	1111	1091	1084	889
55°	871	860	838	816	807	779
65°	588	577	558	542	533	581
75°	307	304	295	284	287	328
85°	75	73	71	66	64	84
90°	0	6	15	14	15	6
95°	23	27	28	28	27	25
105°	94	95	96	96	96	99
115°	174	177	176	175	174	172
125°	253	257	256	254	254	226
135°	328	332	333	333	332	253
145°	398	401	403	404	402	248
155°	455	456	457	460	458	209
165°	495	494	494	497	495	140
175°	515	514	513	516	513	49
180°	516	516	516	516	516	

TEST NUMBER: P917981

CATALOG NUMBER: DFN2DIP-TR2F0-060D020US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1903.4	1903.4	1903.4	1903.4	1903.4
2.5°	1914.5	1905.4	1885.1	1903.4	1899.9
5°	1903.4	1896.2	1876.0	1890.6	1887.1
7.5°	1890.6	1879.8	1859.5	1874.3	1870.6
10°	1870.6	1857.8	1835.8	1850.4	1844.9
12.5°	1843.1	1832.1	1810.2	1819.3	1815.7
15°	1811.9	1801.1	1777.2	1784.6	1775.5
17.5°	1773.5	1762.7	1738.8	1747.8	1738.8
20°	1731.4	1720.5	1694.8	1700.3	1693.1
22.5°	1689.5	1672.9	1649.0	1649.0	1645.4
25°	1639.9	1625.4	1594.2	1597.7	1594.2
27.5°	1584.9	1572.1	1548.4	1543.0	1533.9
30°	1530.2	1515.4	1488.1	1482.6	1475.2
32.5°	1471.5	1460.7	1431.3	1420.2	1412.9
35°	1414.9	1396.6	1367.3	1356.2	1347.0
37.5°	1350.8	1334.2	1305.0	1292.1	1283.0
40°	1284.9	1270.2	1240.9	1224.6	1217.2
42.5°	1220.8	1206.1	1177.0	1158.5	1147.6
45°	1151.4	1138.5	1110.9	1091.0	1083.5
47.5°	1083.5	1070.7	1041.5	1021.2	1010.3
50°	1012.1	1003.0	977.4	951.7	942.6
52.5°	942.6	929.8	906.0	885.9	873.1
55°	871.3	860.2	838.3	816.4	807.2
57.5°	799.9	790.8	766.9	744.9	737.5
60°	728.4	721.2	695.6	675.4	669.9
62.5°	658.8	646.0	627.8	609.5	602.2
65°	587.6	576.6	558.3	541.8	532.6
67.5°	514.4	505.1	488.8	476.0	468.6
70°	446.6	439.3	422.7	409.9	402.8
72.5°	377.1	369.7	360.6	347.8	342.3
75°	307.4	303.9	294.6	283.7	287.4
77.5°	245.2	237.9	234.2	228.8	223.3
80°	183.1	181.2	177.5	172.0	168.4
82.5°	124.5	124.5	122.7	115.4	115.4
85°	74.9	73.2	71.4	65.8	64.1
87.5°	33.0	29.4	25.6	20.2	18.3
90°	0.5	5.6	15.2	14.3	14.8
92.5°	9.6	13.0	13.5	14.0	14.0
95°	22.7	27.1	27.8	27.8	27.1
97.5°	37.7	41.8	43.5	43.5	43.5
100°	55.2	58.8	60.0	60.0	59.5
102.5°	73.5	76.1	77.9	78.4	77.9
105°	93.6	94.8	95.8	96.5	96.5
107.5°	113.5	115.4	115.4	115.7	113.5
110°	132.8	135.3	135.3	135.3	134.0

TEST NUMBER: P917981

CATALOG NUMBER: DFN2DIP-TR2F0-060D020US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	153.6	156.2	155.8	154.5	153.6
115°	174.1	176.6	175.9	175.4	174.1
117.5°	194.5	198.0	195.8	194.5	193.2
120°	215.0	218.4	215.0	215.0	213.6
122.5°	233.7	238.0	235.9	234.6	233.7
125°	253.2	257.1	255.9	254.5	254.0
127.5°	272.4	277.2	275.5	273.6	272.4
130°	290.2	295.9	295.1	294.2	292.4
132.5°	310.3	314.7	314.9	312.8	311.5
135°	327.6	332.4	333.3	332.9	331.6
137.5°	346.8	350.7	351.6	351.2	349.4
140°	363.8	367.7	369.9	369.9	368.2
142.5°	381.2	385.1	386.4	386.8	385.1
145°	397.7	400.8	403.3	403.7	402.0
147.5°	412.5	416.4	418.2	419.0	417.3
150°	427.7	430.3	432.0	433.4	432.0
152.5°	441.2	443.8	446.0	447.8	446.0
155°	454.8	456.0	457.4	459.6	458.2
157.5°	466.4	467.3	468.1	471.2	469.0
160°	476.9	477.8	478.3	480.9	479.0
162.5°	486.5	486.5	486.9	489.9	487.7
165°	494.7	494.2	494.2	497.3	495.2
167.5°	502.1	500.8	500.8	503.9	501.7
170°	507.8	506.5	506.1	509.2	506.5
172.5°	511.7	510.4	510.0	513.1	510.4
175°	514.8	513.6	512.6	515.7	513.1
177.5°	516.5	515.3	514.3	516.9	514.3
180°	515.7	515.7	515.7	515.7	515.7

TEST NUMBER: P917981

CATALOG NUMBER: DFN2DIP-TR2F0-060D020US930-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.37	15.54	15.05	16.24	17.06	13.94	15.11	14.63	15.82	16.64
	3H	16.02	17.08	16.72	17.79	18.65	15.56	16.62	16.26	17.33	18.19
	4H	16.61	17.60	17.33	18.33	19.20	16.15	17.14	16.87	17.87	18.74
	6H	17.01	17.93	17.74	18.66	19.54	16.55	17.47	17.28	18.20	19.08
	8H	17.11	17.99	17.85	18.74	19.63	16.65	17.53	17.39	18.28	19.17
	12H	17.16	18.00	17.91	18.74	19.66	16.70	17.53	17.44	18.28	19.19
4H	2H	14.85	15.85	15.57	16.57	17.44	14.51	15.51	15.23	16.23	17.10
	3H	16.72	17.55	17.45	18.31	19.20	16.34	17.17	17.07	17.93	18.81
	4H	17.43	18.18	18.18	18.94	19.86	17.03	17.79	17.78	18.55	19.47
	6H	17.94	18.59	18.70	19.38	20.30	17.54	18.20	18.31	18.98	19.91
	8H	18.08	18.70	18.85	19.48	20.41	17.69	18.30	18.46	19.08	20.02
	12H	18.16	18.71	18.95	19.52	20.46	17.76	18.31	18.55	19.11	20.05
8H	4H	17.64	18.25	18.41	19.03	19.97	17.29	17.90	18.06	18.68	19.62
	6H	18.25	18.76	19.06	19.59	20.53	17.90	18.41	18.70	19.23	20.17
	8H	18.46	18.91	19.28	19.74	20.69	18.11	18.56	18.92	19.38	20.34
	12H	18.59	18.99	19.41	19.81	20.82	18.22	18.62	19.04	19.44	20.45
12H	4H	17.64	18.19	18.43	18.99	19.93	17.29	17.84	18.08	18.65	19.59
	6H	18.28	18.74	19.10	19.56	20.51	17.94	18.39	18.75	19.22	20.17
	8H	18.52	18.92	19.34	19.73	20.75	18.18	18.57	18.99	19.39	20.40