

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907160

Luminaire Tested: DFN2DIP-TR3F0-050D080US835-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P907160  
REPORT IS A COMBINATION OF REPORTS P900345 AND P897195  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR3F0-050D080US835-FLLFLL  
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 12030.0 lumens  
Efficiency: N/A  
Efficacy: 113.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 106.5  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9933  
Total Harmonic Distortion (THDi): 0.066  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P907160  
CATALOG NUMBER: DFN2DIP-TR3F0-050D080US835-FLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P907160

CATALOG NUMBER: DFN2DIP-TR3F0-050D080US835-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	48	48	48	41
1	96	92	88	84	87	84	80	77	69	66	64	55	53	52	42	41	41	41	41	41	35
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	34	34	34	29
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	29	29	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25	25	25	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	22	22	22	18
6	61	50	42	36	56	46	38	33	38	33	29	31	27	24	24	21	19	19	19	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	17	17	17	14
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	15	15	15	13
9	49	37	30	25	45	34	27	23	29	23	20	24	20	17	19	16	14	14	14	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	13	13	13	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2424	2424	2424
5°	2427	2388	2405
10°	2406	2354	2371
15°	2369	2313	2318
20°	2320	2258	2265
25°	2271	2191	2203
30°	2210	2129	2125
35°	2152	2056	2042
40°	2081	1983	1964
45°	2010	1909	1883
50°	1933	1831	1790
55°	1851	1741	1704
60°	1759	1635	1605
65°	1658	1525	1488
70°	1530	1390	1363
75°	1353	1228	1245
80°	1139	1022	1023
85°	804	673	660

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 2471 cd/sqm



TEST NUMBER: P907160

CATALOG NUMBER: DFN2DIP-TR3F0-050D080US835-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.1	1.5
10°-20°	515.2	4.3
20°-30°	757.2	6.3
30°-40°	879.4	7.3
40°-50°	878.3	7.3
50°-60°	765.8	6.4
60°-70°	566.1	4.7
70°-80°	320.3	2.7
80°-90°	91.7	0.8
90°-100°	156.6	1.3
100°-110°	497.5	4.1
110°-120°	851.3	7.1
120°-130°	1119.6	9.3
130°-140°	1256.7	10.4
140°-150°	1232.3	10.2
150°-160°	1033.7	8.6
160°-170°	685.6	5.7
170°-180°	239.6	2.0
0°-30°	1455.5	12.1
0°-40°	2334.9	19.4
0°-60°	3979.0	33.1
0°-90°	4957.2	41.2
90°-120°	1505.3	12.5
90°-150°	5113.9	42.5
90°-180°	7073.0	58.8
0°-180°	12030.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1946	1938	1918	1932	1929	185
15°	1852	1841	1816	1824	1815	522
25°	1676	1661	1630	1633	1630	771
35°	1446	1428	1398	1386	1377	903
45°	1177	1164	1136	1115	1108	908
55°	891	879	857	834	825	796
65°	601	589	571	554	544	594
75°	314	311	301	290	294	335
85°	77	75	73	67	66	85
90°	2	28	75	70	72	12
95°	111	133	136	136	133	124
105°	459	465	470	474	474	485
115°	854	866	863	860	854	845
125°	1242	1262	1256	1249	1246	1110
135°	1607	1631	1635	1633	1627	1242
145°	1951	1966	1979	1981	1972	1219
155°	2231	2237	2244	2255	2248	1027
165°	2427	2425	2425	2440	2429	685
175°	2526	2519	2515	2530	2517	240
180°	2530	2530	2530	2530	2530	



TEST NUMBER: P907160

CATALOG NUMBER: DFN2DIP-TR3F0-050D080US835-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1945.5	1945.5	1945.5	1945.5	1945.5
2.5°	1956.8	1947.5	1926.9	1945.5	1942.0
5°	1945.5	1938.2	1917.5	1932.4	1928.9
7.5°	1932.4	1921.3	1900.7	1915.8	1912.0
10°	1912.0	1898.9	1876.5	1891.3	1885.8
12.5°	1883.8	1872.7	1850.3	1859.6	1855.8
15°	1852.0	1840.9	1816.5	1824.1	1814.7
17.5°	1812.7	1801.6	1777.2	1786.5	1777.2
20°	1769.7	1758.6	1732.4	1737.9	1730.6
22.5°	1726.8	1709.9	1685.5	1685.5	1681.7
25°	1676.2	1661.3	1629.5	1633.1	1629.5
27.5°	1620.0	1606.9	1582.7	1577.1	1567.8
30°	1564.0	1549.0	1521.0	1515.4	1507.9
32.5°	1504.1	1493.0	1463.0	1451.7	1444.2
35°	1446.1	1427.5	1397.5	1386.2	1376.9
37.5°	1380.6	1363.8	1333.8	1320.7	1311.4
40°	1313.4	1298.3	1268.3	1251.6	1244.1
42.5°	1247.9	1232.8	1203.0	1184.1	1173.0
45°	1176.8	1163.7	1135.5	1115.1	1107.5
47.5°	1107.5	1094.4	1064.5	1043.8	1032.7
50°	1034.5	1025.2	999.0	972.8	963.4
52.5°	963.4	950.3	926.1	905.5	892.4
55°	890.6	879.3	856.8	834.4	825.1
57.5°	817.5	808.2	783.8	761.4	753.8
60°	744.5	737.2	711.0	690.3	684.8
62.5°	673.5	660.4	641.7	623.0	615.5
65°	600.6	589.3	570.6	553.8	544.4
67.5°	525.8	516.3	499.6	486.5	478.9
70°	456.5	449.0	432.1	419.0	411.7
72.5°	385.5	377.9	368.6	355.5	349.9
75°	314.2	310.6	301.1	290.0	293.8
77.5°	250.7	243.1	239.4	233.8	228.3
80°	187.2	185.2	181.4	175.9	172.1
82.5°	127.2	127.2	125.4	117.9	117.9
85°	76.6	74.8	73.0	67.3	65.5
87.5°	33.7	30.0	26.2	20.6	18.7
90°	2.3	27.5	74.8	70.2	72.5
92.5°	47.3	64.1	66.4	68.6	68.6
95°	111.4	132.7	136.5	136.5	132.7
97.5°	185.4	205.2	213.6	213.6	213.6
100°	270.8	288.3	294.4	294.4	292.1
102.5°	360.8	373.8	382.1	384.4	382.1
105°	459.2	465.3	469.9	473.7	473.7
107.5°	556.8	566.0	566.0	567.5	556.8
110°	651.4	663.6	663.6	663.6	657.5



TEST NUMBER: P907160

CATALOG NUMBER: DFN2DIP-TR3F0-050D080US835-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	753.6	766.6	764.3	758.2	753.6
115°	854.3	866.5	862.7	860.4	854.3
117.5°	954.2	971.0	960.3	954.2	948.1
120°	1054.9	1071.7	1054.9	1054.9	1048.0
122.5°	1146.4	1167.8	1157.1	1151.0	1146.4
125°	1242.5	1261.6	1255.5	1248.6	1246.4
127.5°	1336.4	1360.0	1351.6	1342.5	1336.4
130°	1424.1	1451.5	1447.7	1443.2	1434.8
132.5°	1522.5	1543.8	1545.4	1534.7	1528.6
135°	1607.1	1630.8	1635.4	1633.1	1627.0
137.5°	1701.7	1720.8	1724.6	1723.1	1713.9
140°	1784.9	1803.9	1814.6	1814.6	1806.2
142.5°	1870.3	1889.4	1895.5	1897.8	1889.4
145°	1951.2	1966.4	1978.6	1980.9	1972.5
147.5°	2023.6	2042.7	2051.8	2055.7	2047.3
150°	2098.4	2111.3	2119.7	2126.6	2119.7
152.5°	2164.7	2177.7	2188.4	2196.8	2188.4
155°	2231.1	2237.2	2244.1	2254.7	2247.9
157.5°	2288.3	2292.9	2296.7	2311.9	2301.3
160°	2339.4	2344.0	2346.3	2359.2	2350.1
162.5°	2386.7	2386.7	2389.0	2403.5	2392.8
165°	2427.1	2424.8	2424.8	2440.1	2429.4
167.5°	2463.7	2456.9	2456.9	2472.1	2461.4
170°	2491.2	2485.1	2482.8	2498.1	2485.1
172.5°	2510.3	2504.2	2501.9	2517.1	2504.2
175°	2525.5	2519.4	2514.8	2530.1	2517.1
177.5°	2533.9	2527.8	2523.2	2536.2	2523.2
180°	2530.1	2530.1	2530.1	2530.1	2530.1



TEST NUMBER: P907160  
 CATALOG NUMBER: DFN2DIP-TR3F0-050D080US835-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.42	10.21	10.45	11.25	12.64	8.99	9.78	10.02	10.82	12.21
	3H	11.07	11.77	12.11	12.82	14.23	10.60	11.31	11.64	12.35	13.76
	4H	11.65	12.32	12.70	13.36	14.78	11.18	11.85	12.23	12.90	14.31
	6H	12.04	12.65	13.10	13.70	15.13	11.57	12.18	12.63	13.23	14.66
	8H	12.13	12.72	13.20	13.79	15.21	11.67	12.25	12.73	13.32	14.75
	12H	12.18	12.73	13.25	13.80	15.25	11.70	12.26	12.77	13.32	14.77
4H	2H	9.87	10.54	10.93	11.59	13.01	9.53	10.20	10.59	11.25	12.66
	3H	11.72	12.28	12.79	13.35	14.79	11.33	11.89	12.40	12.97	14.40
	4H	12.42	12.94	13.50	14.00	15.46	12.02	12.54	13.10	13.60	15.05
	6H	12.93	13.37	14.01	14.46	15.90	12.52	12.96	13.60	14.05	15.50
	8H	13.07	13.48	14.15	14.56	16.03	12.66	13.08	13.74	14.16	15.62
	12H	13.14	13.51	14.23	14.60	16.07	12.72	13.09	13.82	14.19	15.66
8H	4H	12.61	13.02	13.69	14.10	15.57	12.25	12.67	13.34	13.75	15.21
	6H	13.23	13.57	14.33	14.69	16.15	12.87	13.21	13.97	14.33	15.79
	8H	13.44	13.74	14.55	14.85	16.33	13.08	13.38	14.19	14.48	15.96
	12H	13.56	13.83	14.68	14.93	16.45	13.19	13.45	14.30	14.55	16.07
12H	4H	12.59	12.96	13.69	14.06	15.53	12.24	12.62	13.34	13.71	15.18
	6H	13.26	13.55	14.37	14.66	16.14	12.91	13.21	14.02	14.31	15.79
	8H	13.49	13.75	14.60	14.85	16.37	13.13	13.40	14.25	14.50	16.02