

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P917982

Luminaire Tested: DFN2DIP-TR2F0-060D020US930-RLFL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P917982
REPORT IS A COMBINATION OF REPORTS P900230 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-060D020US930-RLLFLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5601.1 lumens
Efficiency: N/A
Efficacy: 75.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 74.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P917982

CATALOG NUMBER: DFN2DIP-TR2F0-060D020US930-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P917982

CATALOG NUMBER: DFN2DIP-TR2F0-060D020US930-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78
1	104	100	96	93	99	95	92	89	86	84	81	78	76	74	70	69	68
2	95	88	82	77	90	84	79	74	76	72	68	69	66	63	63	60	58
3	87	78	71	65	83	75	68	63	68	63	58	62	58	54	56	53	50
4	80	70	62	56	76	67	60	54	61	55	51	56	51	47	51	47	44
5	74	63	54	48	70	60	53	47	55	49	44	51	45	42	46	42	39
6	69	57	48	43	65	54	47	41	50	44	39	46	41	37	42	38	35
7	64	51	43	38	61	49	42	37	46	39	35	42	37	33	39	34	31
8	59	47	39	34	57	45	38	33	42	36	31	39	34	30	36	31	28
9	56	43	36	31	53	42	35	30	39	33	28	36	31	27	33	29	26
10	52	40	33	28	50	39	32	27	36	30	26	33	28	25	31	27	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4509	4509	4509
5°	4510	4428	4458
10°	4459	4331	4306
15°	4391	4178	4074
20°	4302	3971	3793
25°	4213	3742	3522
30°	4094	3507	3180
35°	3977	3256	2880
40°	3858	2997	2538
45°	3721	2711	2228
50°	3578	2423	1926
55°	3428	2117	1636
60°	3255	1799	1339
65°	3054	1476	1197
70°	2811	1175	1072
75°	2505	1016	960
80°	2064	825	810
85°	1355	511	570

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3721 cd/sqm

TEST NUMBER: P917982

CATALOG NUMBER: DFN2DIP-TR2F0-060D020US930-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.5	3.4
10°-20°	520.2	9.3
20°-30°	730.3	13.0
30°-40°	796.1	14.2
40°-50°	731.7	13.1
50°-60°	574.6	10.3
60°-70°	374.0	6.7
70°-80°	192.5	3.4
80°-90°	50.6	0.9
90°-100°	31.9	0.6
100°-110°	101.4	1.8
110°-120°	173.5	3.1
120°-130°	228.2	4.1
130°-140°	256.1	4.6
140°-150°	251.2	4.5
150°-160°	210.7	3.8
160°-170°	139.7	2.5
170°-180°	48.8	0.9
0°-30°	1439.9	25.7
0°-40°	2236.0	39.9
0°-60°	3542.3	63.2
0°-90°	4159.5	74.3
90°-120°	306.8	5.5
90°-150°	1042.3	18.6
90°-180°	1442.0	25.7
0°-180°	5601.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2022	2022	2022	2022	2022	
5°	2022	2013	1989	2005	2000	192
15°	1923	1903	1841	1806	1788	542
25°	1746	1687	1566	1491	1464	803
35°	1504	1411	1250	1134	1094	941
45°	1230	1107	915	785	741	950
55°	935	792	595	485	450	835
65°	631	483	318	256	251	626
75°	337	208	146	134	132	356
85°	79	40	35	35	35	90
90°	0	6	15	14	15	5
95°	23	27	28	28	27	25
105°	94	95	96	96	96	99
115°	174	177	176	175	174	172
125°	253	257	256	254	254	226
135°	328	332	333	333	332	253
145°	398	401	403	404	402	248
155°	455	456	457	460	458	209
165°	495	494	494	497	495	140
175°	515	514	513	516	513	49
180°	516	516	516	516	516	



TEST NUMBER: P917982

CATALOG NUMBER: DFN2DIP-TR2F0-060D020US930-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2021.8	2021.8	2021.8	2021.8	2021.8
2.5°	2030.9	2021.8	2001.6	2020.0	2016.3
5°	2021.8	2012.6	1988.8	2005.3	1999.8
7.5°	2005.3	1994.4	1968.8	1976.0	1966.8
10°	1983.3	1970.5	1934.1	1928.4	1917.5
12.5°	1956.0	1939.4	1889.9	1879.1	1858.9
15°	1923.0	1902.7	1840.6	1805.9	1787.6
17.5°	1884.6	1855.2	1778.3	1738.1	1708.9
20°	1840.6	1803.9	1712.5	1666.9	1626.5
22.5°	1793.1	1750.9	1644.8	1582.7	1555.3
25°	1745.6	1686.9	1566.2	1491.3	1463.7
27.5°	1688.9	1626.5	1493.0	1407.0	1364.9
30°	1628.5	1558.8	1412.4	1319.2	1269.7
32.5°	1569.9	1485.6	1335.8	1225.9	1180.1
35°	1504.1	1410.7	1249.8	1134.4	1094.0
37.5°	1440.0	1339.2	1169.2	1042.8	997.2
40°	1372.2	1262.6	1084.9	955.0	907.5
42.5°	1302.8	1185.7	1000.9	865.4	819.8
45°	1229.6	1106.8	914.9	784.8	740.9
47.5°	1160.1	1030.2	832.6	702.5	662.3
50°	1083.2	953.3	752.0	625.7	587.4
52.5°	1008.0	870.8	675.1	554.4	519.7
55°	934.9	792.2	594.6	484.9	450.1
57.5°	860.0	713.5	523.3	420.9	391.5
60°	783.1	636.7	448.3	355.1	325.7
62.5°	708.2	561.8	384.2	296.4	281.8
65°	631.3	483.0	318.4	256.2	250.6
67.5°	558.1	409.8	256.2	225.0	219.6
70°	481.2	338.5	212.1	194.0	186.5
72.5°	408.1	272.6	177.4	162.9	159.1
75°	336.6	208.5	146.3	133.5	131.8
77.5°	265.4	148.1	115.3	107.9	104.3
80°	199.3	106.2	87.7	80.6	80.6
82.5°	139.0	71.4	60.3	56.7	56.7
85°	78.6	40.2	34.7	34.7	34.7
87.5°	29.4	14.6	14.6	12.8	12.8
90°	0.5	5.6	15.2	14.3	14.8
92.5°	9.6	13.0	13.5	14.0	14.0
95°	22.7	27.1	27.8	27.8	27.1
97.5°	37.7	41.8	43.5	43.5	43.5
100°	55.2	58.8	60.0	60.0	59.5
102.5°	73.5	76.1	77.9	78.4	77.9
105°	93.6	94.8	95.8	96.5	96.5
107.5°	113.5	115.4	115.4	115.7	113.5
110°	132.8	135.3	135.3	135.3	134.0



TEST NUMBER: P917982

CATALOG NUMBER: DFN2DIP-TR2F0-060D020US930-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	153.6	156.2	155.8	154.5	153.6
115°	174.1	176.6	175.9	175.4	174.1
117.5°	194.5	198.0	195.8	194.5	193.2
120°	215.0	218.4	215.0	215.0	213.6
122.5°	233.7	238.0	235.9	234.6	233.7
125°	253.2	257.1	255.9	254.5	254.0
127.5°	272.4	277.2	275.5	273.6	272.4
130°	290.2	295.9	295.1	294.2	292.4
132.5°	310.3	314.7	314.9	312.8	311.5
135°	327.6	332.4	333.3	332.9	331.6
137.5°	346.8	350.7	351.6	351.2	349.4
140°	363.8	367.7	369.9	369.9	368.2
142.5°	381.2	385.1	386.4	386.8	385.1
145°	397.7	400.8	403.3	403.7	402.0
147.5°	412.5	416.4	418.2	419.0	417.3
150°	427.7	430.3	432.0	433.4	432.0
152.5°	441.2	443.8	446.0	447.8	446.0
155°	454.8	456.0	457.4	459.6	458.2
157.5°	466.4	467.3	468.1	471.2	469.0
160°	476.9	477.8	478.3	480.9	479.0
162.5°	486.5	486.5	486.9	489.9	487.7
165°	494.7	494.2	494.2	497.3	495.2
167.5°	502.1	500.8	500.8	503.9	501.7
170°	507.8	506.5	506.1	509.2	506.5
172.5°	511.7	510.4	510.0	513.1	510.4
175°	514.8	513.6	512.6	515.7	513.1
177.5°	516.5	515.3	514.3	516.9	514.3
180°	515.7	515.7	515.7	515.7	515.7

TEST NUMBER: P917982

CATALOG NUMBER: DFN2DIP-TR2F0-060D020US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.27	15.35	14.99	16.09	16.97	10.25	11.33	10.98	12.07	12.95
	3H	15.94	16.91	16.68	17.66	18.57	11.45	12.41	12.18	13.16	14.07
	4H	16.55	17.46	17.30	18.21	19.14	11.90	12.80	12.65	13.56	14.49
	6H	16.96	17.80	17.73	18.57	19.50	12.22	13.05	12.98	13.82	14.76
	8H	17.08	17.88	17.86	18.67	19.61	12.31	13.10	13.08	13.89	14.83
	12H	17.14	17.90	17.93	18.68	19.65	12.35	13.11	13.13	13.89	14.85
4H	2H	14.32	15.22	15.07	15.98	16.91	10.87	11.77	11.63	12.53	13.46
	3H	16.14	16.89	16.91	17.69	18.63	12.22	12.97	12.99	13.77	14.71
	4H	16.82	17.51	17.61	18.30	19.27	12.76	13.45	13.55	14.24	15.21
	6H	17.33	17.92	18.13	18.74	19.72	13.18	13.77	13.98	14.59	15.57
	8H	17.50	18.05	18.30	18.86	19.85	13.30	13.85	14.11	14.67	15.66
	12H	17.59	18.08	18.42	18.92	19.91	13.37	13.87	14.20	14.70	15.70
8H	4H	16.80	17.36	17.61	18.17	19.16	13.05	13.60	13.85	14.41	15.40
	6H	17.35	17.81	18.19	18.67	19.66	13.55	14.01	14.39	14.87	15.85
	8H	17.56	17.96	18.40	18.82	19.82	13.73	14.14	14.58	14.99	16.00
	12H	17.69	18.05	18.54	18.89	19.95	13.85	14.21	14.70	15.05	16.11
12H	4H	16.77	17.26	17.59	18.10	19.09	13.06	13.55	13.89	14.39	15.38
	6H	17.33	17.73	18.18	18.59	19.59	13.60	14.00	14.44	14.86	15.86
	8H	17.54	17.90	18.39	18.75	19.81	13.80	14.16	14.65	15.00	16.07