

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907175

Luminaire Tested: DFN2DIP-TR3F0-060D050US835-FLLONL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P907175  
REPORT IS A COMBINATION OF REPORTS P901825 AND P898751  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR3F0-060D050US835-FLLONL  
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10890.0 lumens  
Efficiency: N/A  
Efficacy: 115.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 94.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9789  
Total Harmonic Distortion (THDi): 0.074  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P907175  
CATALOG NUMBER: DFN2DIP-TR3F0-060D050US835-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P907175  
 CATALOG NUMBER: DFN2DIP-TR3F0-060D050US835-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	60	60	60	55
1	99	94	91	87	92	88	84	81	75	73	71	64	62	60	53	52	51	51	51	51	46
2	90	82	76	71	83	77	71	67	66	62	58	56	53	51	47	45	43	43	43	43	39
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	37	37	37	33
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	32	32	32	28
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	27	27	27	27	24
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	30	27	24	24	24	24	21
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22	22	22	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19	19	19	19	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	17	17	17	15
10	48	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	16	16	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2909	2909	2909
5°	2912	2866	2886
10°	2887	2825	2845
15°	2843	2776	2782
20°	2784	2709	2718
25°	2725	2629	2643
30°	2652	2555	2550
35°	2583	2468	2451
40°	2497	2379	2356
45°	2412	2291	2259
50°	2319	2198	2148
55°	2221	2090	2044
60°	2111	1962	1926
65°	1990	1830	1786
70°	1836	1668	1636
75°	1623	1474	1493
80°	1366	1227	1227
85°	965	807	793

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2412 cd/sqm



TEST NUMBER: P907175

CATALOG NUMBER: DFN2DIP-TR3F0-060D050US835-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	219.7	2.0
10°-20°	618.3	5.7
20°-30°	908.6	8.3
30°-40°	1055.3	9.7
40°-50°	1054.0	9.7
50°-60°	919.0	8.4
60°-70°	679.4	6.2
70°-80°	384.4	3.5
80°-90°	104.4	1.0
90°-100°	55.7	0.5
100°-110°	207.4	1.9
110°-120°	550.1	5.1
120°-130°	912.4	8.4
130°-140°	969.2	8.9
140°-150°	900.8	8.3
150°-160°	724.2	6.7
160°-170°	466.6	4.3
170°-180°	160.6	1.5
0°-30°	1746.6	16.0
0°-40°	2801.8	25.7
0°-60°	4774.8	43.8
0°-90°	5943.0	54.6
90°-120°	813.2	7.5
90°-150°	3595.6	33.0
90°-180°	4947.0	45.4
0°-180°	10890.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2335	2335	2335	2335	2335	
5°	2335	2326	2301	2319	2315	222
15°	2222	2209	2180	2189	2178	626
25°	2011	1994	1955	1960	1955	926
35°	1735	1713	1677	1663	1652	1084
45°	1412	1396	1363	1338	1329	1090
55°	1069	1055	1028	1001	990	955
65°	721	707	685	664	653	713
75°	377	373	361	348	352	402
85°	92	90	88	81	79	103
90°	1	15	24	31	33	10
95°	79	39	48	54	52	94
105°	371	408	74	88	93	397
115°	702	723	753	188	100	691
125°	993	1009	1032	1040	1044	885
135°	1228	1248	1259	1271	1269	949
145°	1425	1424	1444	1453	1447	891
155°	1569	1558	1573	1580	1570	723
165°	1653	1646	1650	1658	1650	467
175°	1691	1682	1685	1694	1681	161
180°	1687	1687	1687	1687	1687	



TEST NUMBER: P907175

CATALOG NUMBER: DFN2DIP-TR3F0-060D050US835-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2334.6	2334.6	2334.6	2334.6	2334.6
2.5°	2348.2	2337.0	2312.2	2334.6	2330.3
5°	2334.6	2325.8	2301.0	2318.9	2314.6
7.5°	2318.9	2305.6	2280.8	2298.9	2294.4
10°	2294.4	2278.7	2251.7	2269.6	2262.9
12.5°	2260.6	2247.2	2220.3	2231.5	2227.0
15°	2222.4	2209.1	2179.8	2188.9	2177.7
17.5°	2175.3	2162.0	2132.7	2143.8	2132.7
20°	2123.6	2110.3	2078.8	2085.5	2076.7
22.5°	2072.2	2051.9	2022.6	2022.6	2018.1
25°	2011.4	1993.6	1955.4	1959.7	1955.4
27.5°	1944.0	1928.3	1899.2	1892.6	1881.4
30°	1876.9	1858.7	1825.2	1818.5	1809.4
32.5°	1804.9	1791.6	1755.6	1742.0	1733.0
35°	1735.4	1713.0	1677.0	1663.4	1652.2
37.5°	1656.8	1636.5	1600.6	1584.8	1573.6
40°	1576.0	1557.9	1522.0	1502.0	1492.9
42.5°	1497.4	1479.3	1443.6	1421.0	1407.6
45°	1412.2	1396.4	1362.6	1338.1	1329.0
47.5°	1329.0	1313.3	1277.4	1252.6	1239.2
50°	1241.4	1230.2	1198.8	1167.3	1156.1
52.5°	1156.1	1140.4	1111.3	1086.6	1070.9
55°	1068.7	1055.1	1028.2	1001.3	990.1
57.5°	981.1	969.9	940.6	913.7	904.6
60°	893.4	884.6	853.2	828.4	821.7
62.5°	808.1	792.4	770.0	747.6	738.6
65°	720.7	707.2	684.8	664.5	653.3
67.5°	630.9	619.5	599.5	583.8	574.7
70°	547.8	538.8	518.5	502.8	494.0
72.5°	462.5	453.5	442.3	426.6	419.9
75°	377.0	372.8	361.3	348.0	352.5
77.5°	300.8	291.8	287.2	280.6	273.9
80°	224.6	222.2	217.7	211.0	206.5
82.5°	152.7	152.7	150.5	141.5	141.5
85°	91.9	89.8	87.6	80.7	78.6
87.5°	40.5	36.0	31.4	24.8	22.4
90°	1.2	14.6	24.4	30.6	32.9
92.5°	30.6	25.7	29.3	31.8	32.9
95°	79.3	39.0	47.6	53.8	52.5
97.5°	142.8	42.8	62.2	66.0	67.1
100°	216.2	48.9	69.6	79.3	81.8
102.5°	296.7	294.3	72.1	85.4	89.2
105°	371.2	407.9	74.5	87.9	92.8
107.5°	457.9	488.3	77.0	90.3	95.3
110°	541.0	566.5	213.7	91.6	96.4



TEST NUMBER: P907175

CATALOG NUMBER: DFN2DIP-TR3F0-060D050US835-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	619.1	641.0	620.3	94.0	97.7
115°	702.1	722.8	753.4	188.1	100.2
117.5°	774.1	798.5	819.4	644.6	324.8
120°	854.7	873.0	895.0	909.7	744.8
122.5°	923.0	942.6	967.1	974.4	975.7
125°	992.6	1008.6	1031.8	1040.3	1044.0
127.5°	1056.1	1073.2	1091.7	1103.8	1105.0
130°	1116.0	1135.6	1148.9	1162.4	1161.3
132.5°	1177.1	1193.0	1206.3	1217.4	1216.2
135°	1228.4	1248.0	1258.8	1271.2	1268.7
137.5°	1282.0	1296.7	1309.0	1321.2	1317.6
140°	1334.5	1344.4	1357.7	1368.7	1362.7
142.5°	1378.6	1387.2	1403.0	1412.7	1406.6
145°	1425.0	1423.7	1444.4	1453.0	1446.9
147.5°	1465.2	1461.5	1482.3	1488.4	1483.6
150°	1504.3	1495.8	1515.3	1522.6	1516.5
152.5°	1537.2	1527.5	1545.8	1553.2	1544.6
155°	1569.0	1558.1	1572.7	1580.0	1570.3
157.5°	1594.6	1584.9	1595.9	1604.5	1594.6
160°	1616.7	1609.3	1616.7	1623.9	1615.4
162.5°	1636.1	1628.9	1634.9	1643.5	1632.5
165°	1653.2	1646.0	1649.6	1658.1	1649.6
167.5°	1666.7	1659.3	1663.1	1671.6	1660.6
170°	1677.7	1670.3	1672.8	1681.3	1670.3
172.5°	1685.0	1677.7	1680.2	1688.7	1677.7
175°	1691.1	1682.5	1685.0	1693.5	1681.3
177.5°	1693.5	1685.0	1686.3	1694.8	1683.8
180°	1687.4	1687.4	1687.4	1687.4	1687.4



TEST NUMBER: P907175  
 CATALOG NUMBER: DFN2DIP-TR3F0-060D050US835-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.34	12.25	12.26	13.18	14.39	10.91	11.82	11.83	12.75	13.96
	3H	13.00	13.81	13.93	14.75	15.98	12.53	13.34	13.46	14.28	15.51
	4H	13.58	14.35	14.52	15.30	16.53	13.11	13.88	14.06	14.83	16.07
	6H	13.98	14.68	14.93	15.64	16.89	13.51	14.21	14.46	15.17	16.42
	8H	14.08	14.75	15.04	15.72	16.97	13.61	14.28	14.57	15.26	16.50
	12H	14.12	14.76	15.09	15.73	17.00	13.65	14.29	14.62	15.26	16.53
4H	2H	11.81	12.57	12.76	13.52	14.76	11.46	12.23	12.41	13.18	14.42
	3H	13.67	14.31	14.62	15.29	16.54	13.28	13.92	14.23	14.90	16.15
	4H	14.37	14.96	15.34	15.93	17.21	13.97	14.56	14.94	15.53	16.81
	6H	14.88	15.39	15.86	16.38	17.66	14.48	14.98	15.46	15.98	17.26
	8H	15.03	15.50	16.01	16.49	17.78	14.62	15.09	15.61	16.08	17.37
	12H	15.10	15.52	16.10	16.53	17.83	14.68	15.11	15.69	16.12	17.41
8H	4H	14.57	15.04	15.55	16.03	17.32	14.21	14.68	15.20	15.68	16.96
	6H	15.19	15.58	16.20	16.61	17.90	14.83	15.22	15.84	16.26	17.54
	8H	15.41	15.75	16.42	16.77	18.08	15.04	15.39	16.06	16.41	17.71
	12H	15.53	15.84	16.55	16.85	18.20	15.16	15.46	16.18	16.47	17.82
12H	4H	14.56	14.98	15.56	15.99	17.28	14.21	14.63	15.21	15.64	16.94
	6H	15.22	15.57	16.24	16.58	17.89	14.87	15.22	15.89	16.24	17.54
	8H	15.46	15.76	16.48	16.77	18.13	15.10	15.41	16.13	16.42	17.77