

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920657

Luminaire Tested: DFN2DIP-TR2F0-030D040US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920657
REPORT IS A COMBINATION OF REPORTS P901763 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-030D040US935-FLLONL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5605.1 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 54.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920657

CATALOG NUMBER: DFN2DIP-TR2F0-030D040US935-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P920657

CATALOG NUMBER: DFN2DIP-TR2F0-030D040US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	93	89	85	89	85	82	79	71	69	66	58	56	55	46	45	44
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	41	39	37
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	34	32
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27
5	67	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24
6	62	50	42	36	57	46	39	34	39	34	30	33	28	25	26	23	21
7	57	45	37	32	53	42	35	30	36	30	26	30	25	22	24	21	19
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2242	2242	2242
5°	2242	2205	2221
10°	2220	2171	2188
15°	2184	2130	2137
20°	2137	2075	2085
25°	2090	2011	2025
30°	2031	1951	1951
35°	1976	1881	1873
40°	1908	1810	1798
45°	1840	1738	1720
50°	1765	1663	1632
55°	1687	1576	1549
60°	1598	1474	1455
65°	1501	1367	1344
70°	1377	1237	1223
75°	1208	1081	1106
80°	1001	881	894
85°	683	555	555

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1840 cd/sqm

TEST NUMBER: P920657

CATALOG NUMBER: DFN2DIP-TR2F0-030D040US935-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	1.7
10°-20°	266.2	4.7
20°-30°	391.1	7.0
30°-40°	454.3	8.1
40°-50°	453.7	8.1
50°-60°	395.6	7.1
60°-70°	292.5	5.2
70°-80°	165.5	3.0
80°-90°	46.8	0.8
90°-100°	67.4	1.2
100°-110°	214.2	3.8
110°-120°	366.5	6.5
120°-130°	482.0	8.6
130°-140°	541.0	9.7
140°-150°	530.5	9.5
150°-160°	445.0	7.9
160°-170°	295.1	5.3
170°-180°	103.2	1.8
0°-30°	751.9	13.4
0°-40°	1206.2	21.5
0°-60°	2055.6	36.7
0°-90°	2560.3	45.7
90°-120°	648.0	11.6
90°-150°	2201.5	39.3
90°-180°	3045.0	54.3
0°-180°	5605.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1005	1005	1005	1005	1005	
5°	1005	1001	991	998	996	95
15°	957	951	938	942	938	269
25°	866	858	842	844	842	398
35°	747	737	722	716	711	467
45°	608	601	587	576	572	469
55°	460	454	443	431	426	411
65°	310	304	295	286	281	307
75°	162	160	156	150	152	173
85°	40	39	38	35	34	44
90°	1	12	32	30	31	5
95°	48	57	59	59	57	53
105°	198	200	202	204	204	209
115°	368	373	371	370	368	364
125°	535	543	540	538	537	478
135°	692	702	704	703	700	535
145°	840	846	852	853	849	525
155°	960	963	966	971	968	442
165°	1045	1044	1044	1050	1046	295
175°	1087	1085	1083	1089	1084	103
180°	1089	1089	1089	1089	1089	

TEST NUMBER: P920657

CATALOG NUMBER: DFN2DIP-TR2F0-030D040US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1005.0	1005.0	1005.0	1005.0	1005.0
2.5°	1010.9	1006.1	995.4	1005.0	1003.2
5°	1005.0	1001.3	990.6	998.3	996.4
7.5°	998.3	992.6	981.9	989.7	987.7
10°	987.7	980.9	969.4	977.1	974.2
12.5°	973.2	967.4	955.9	960.6	958.7
15°	956.7	951.1	938.4	942.3	937.5
17.5°	936.4	930.7	918.1	922.9	918.1
20°	914.2	908.4	894.9	897.8	894.0
22.5°	892.1	883.4	870.7	870.7	868.7
25°	865.9	858.2	841.8	843.7	841.8
27.5°	836.9	830.1	817.6	814.8	809.9
30°	808.0	800.2	785.7	782.8	778.9
32.5°	777.1	771.3	755.8	749.9	746.1
35°	747.1	737.4	721.9	716.1	711.3
37.5°	713.3	704.6	689.1	682.3	677.4
40°	678.5	670.7	655.2	646.6	642.7
42.5°	644.6	636.9	621.5	611.7	606.0
45°	608.0	601.1	586.6	576.0	572.1
47.5°	572.1	565.4	549.9	539.2	533.5
50°	534.4	529.6	516.1	502.6	497.7
52.5°	497.7	490.9	478.5	467.8	461.0
55°	460.1	454.3	442.6	431.1	426.3
57.5°	422.3	417.5	404.9	393.3	389.4
60°	384.6	380.8	367.3	356.6	353.8
62.5°	347.9	341.1	331.5	321.8	318.0
65°	310.3	304.4	294.8	286.1	281.3
67.5°	271.6	266.7	258.0	251.3	247.5
70°	235.8	232.0	223.3	216.5	212.7
72.5°	199.1	195.2	190.4	183.7	180.8
75°	162.3	160.5	155.6	149.8	151.8
77.5°	129.5	125.6	123.6	120.8	118.0
80°	96.7	95.7	93.7	90.8	88.9
82.5°	65.7	65.7	64.8	60.9	60.9
85°	39.6	38.7	37.7	34.8	33.8
87.5°	17.4	15.5	13.5	10.7	9.6
90°	0.9	11.8	32.2	30.2	31.2
92.5°	20.3	27.6	28.6	29.5	29.5
95°	48.0	57.2	58.8	58.8	57.2
97.5°	79.8	88.3	92.0	92.0	92.0
100°	116.6	124.2	126.7	126.7	125.8
102.5°	155.3	160.9	164.5	165.5	164.5
105°	197.7	200.3	202.2	203.9	203.9
107.5°	239.7	243.7	243.7	244.3	239.7
110°	280.4	285.7	285.7	285.7	283.1

TEST NUMBER: P920657

CATALOG NUMBER: DFN2DIP-TR2F0-030D040US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	324.4	330.0	329.0	326.4	324.4
115°	367.7	373.1	371.3	370.4	367.7
117.5°	410.8	418.0	413.5	410.8	408.2
120°	454.2	461.3	454.2	454.2	451.2
122.5°	493.5	502.7	498.2	495.5	493.5
125°	534.9	543.1	540.5	537.5	536.6
127.5°	575.3	585.5	581.9	577.9	575.3
130°	613.0	624.9	623.3	621.3	617.7
132.5°	655.4	664.6	665.3	660.6	658.1
135°	691.9	702.1	704.0	703.0	700.4
137.5°	732.6	740.8	742.4	741.7	737.9
140°	768.4	776.6	781.2	781.2	777.6
142.5°	805.2	813.4	816.0	817.0	813.4
145°	840.0	846.5	851.8	852.8	849.2
147.5°	871.2	879.3	883.3	884.9	881.3
150°	903.4	909.0	912.6	915.5	912.6
152.5°	931.9	937.5	942.1	945.7	942.1
155°	960.4	963.1	966.0	970.7	967.7
157.5°	985.2	987.0	988.7	995.3	990.7
160°	1007.1	1009.1	1010.0	1015.6	1011.7
162.5°	1027.4	1027.4	1028.5	1034.7	1030.1
165°	1044.9	1043.9	1043.9	1050.4	1045.9
167.5°	1060.7	1057.6	1057.6	1064.3	1059.6
170°	1072.5	1069.8	1068.8	1075.4	1069.8
172.5°	1080.6	1078.1	1077.0	1083.7	1078.1
175°	1087.3	1084.6	1082.6	1089.2	1083.7
177.5°	1090.9	1088.2	1086.2	1091.8	1086.2
180°	1089.2	1089.2	1089.2	1089.2	1089.2

TEST NUMBER: P920657

CATALOG NUMBER: DFN2DIP-TR2F0-030D040US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.53	10.36	10.53	11.36	12.69	9.11	9.93	10.10	10.94	12.27
	3H	11.17	11.91	12.17	12.92	14.27	10.71	11.44	11.71	12.46	13.81
	4H	11.74	12.44	12.75	13.45	14.81	11.28	11.98	12.29	12.99	14.35
	6H	12.12	12.76	13.14	13.78	15.16	11.66	12.30	12.68	13.32	14.70
	8H	12.21	12.82	13.24	13.86	15.23	11.75	12.37	12.79	13.40	14.77
	12H	12.25	12.83	13.29	13.86	15.26	11.79	12.37	12.82	13.40	14.80
4H	2H	9.98	10.68	11.00	11.70	13.06	9.64	10.34	10.66	11.36	12.72
	3H	11.82	12.40	12.85	13.45	14.82	11.43	12.02	12.46	13.06	14.44
	4H	12.51	13.04	13.55	14.08	15.48	12.12	12.65	13.15	13.69	15.08
	6H	13.00	13.46	14.05	14.52	15.91	12.60	13.06	13.65	14.13	15.52
	8H	13.14	13.57	14.19	14.62	16.03	12.74	13.17	13.79	14.22	15.63
	12H	13.20	13.59	14.27	14.65	16.07	12.79	13.18	13.86	14.25	15.66
8H	4H	12.69	13.12	13.74	14.18	15.58	12.34	12.77	13.39	13.82	15.23
	6H	13.29	13.65	14.37	14.75	16.15	12.94	13.30	14.02	14.39	15.80
	8H	13.50	13.81	14.58	14.89	16.31	13.14	13.46	14.22	14.53	15.96
	12H	13.61	13.89	14.70	14.96	16.43	13.24	13.52	14.33	14.59	16.06
12H	4H	12.67	13.06	13.74	14.13	15.54	12.33	12.72	13.40	13.79	15.20
	6H	13.32	13.63	14.40	14.71	16.14	12.98	13.29	14.06	14.37	15.79
	8H	13.54	13.82	14.63	14.89	16.36	13.20	13.47	14.28	14.55	16.01