

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907198

Luminaire Tested: DFN2DIP-TR3F0-070D040US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907198
REPORT IS A COMBINATION OF REPORTS P900294 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-070D040US835-RLLFLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9490.0 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 99.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907198
CATALOG NUMBER: DFN2DIP-TR3F0-070D040US835-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P907198

CATALOG NUMBER: DFN2DIP-TR3F0-070D040US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63		
1	101	97	93	90	95	91	88	85	80	78	76	70	68	67	61	60	58	54		
2	93	85	80	75	87	80	75	71	71	67	64	62	59	57	54	52	50	46		
3	85	76	69	63	79	71	65	60	63	58	54	56	52	49	49	46	43	40		
4	78	67	60	54	73	64	57	51	57	51	47	50	46	42	44	41	38	35		
5	72	61	53	47	67	57	50	45	51	45	41	45	41	37	40	36	33	31		
6	67	55	47	41	62	52	44	39	46	40	36	41	36	33	36	33	30	27		
7	62	50	42	36	58	47	40	35	42	36	32	38	33	29	33	30	27	24		
8	57	45	38	32	54	43	36	31	39	33	29	35	30	26	31	27	24	22		
9	54	42	34	29	50	40	33	28	36	30	26	32	27	24	29	25	22	20		
10	50	38	31	26	47	36	30	25	33	27	24	30	25	22	27	23	20	18		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3605	3605	3605
5°	3609	3545	3568
10°	3571	3472	3450
15°	3520	3355	3268
20°	3453	3194	3046
25°	3384	3014	2832
30°	3293	2829	2560
35°	3203	2632	2322
40°	3111	2427	2050
45°	3006	2201	1803
50°	2896	1973	1562
55°	2781	1729	1330
60°	2648	1475	1092
65°	2494	1217	980
70°	2308	977	884
75°	2074	854	799
80°	1736	708	685
85°	1181	458	501

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3006 cd/sqm



TEST NUMBER: P907198
 CATALOG NUMBER: DFN2DIP-TR3F0-070D040US835-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.1	2.9
10°-20°	744.3	7.8
20°-30°	1045.0	11.0
30°-40°	1139.2	12.0
40°-50°	1047.0	11.0
50°-60°	822.3	8.7
60°-70°	535.2	5.6
70°-80°	275.5	2.9
80°-90°	73.9	0.8
90°-100°	78.3	0.8
100°-110°	248.7	2.6
110°-120°	425.6	4.5
120°-130°	559.8	5.9
130°-140°	628.3	6.6
140°-150°	616.2	6.5
150°-160°	516.9	5.4
160°-170°	342.8	3.6
170°-180°	119.8	1.3
0°-30°	2060.5	21.7
0°-40°	3199.7	33.7
0°-60°	5068.9	53.4
0°-90°	5953.6	62.7
90°-120°	752.7	7.9
90°-150°	2556.9	26.9
90°-180°	3536.0	37.3
0°-180°	9490.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2893	2893	2893	2893	2893	
5°	2893	2880	2846	2870	2862	274
15°	2752	2723	2634	2584	2558	775
25°	2498	2414	2241	2134	2094	1149
35°	2152	2019	1788	1623	1566	1347
45°	1760	1584	1309	1123	1060	1359
55°	1338	1134	851	694	644	1195
65°	903	691	456	367	359	896
75°	482	298	209	191	189	509
85°	112	58	50	50	50	129
90°	1	14	37	35	36	9
95°	56	66	68	68	66	62
105°	230	233	235	237	237	242
115°	427	433	431	430	427	422
125°	621	631	628	624	623	555
135°	804	815	818	816	814	621
145°	976	983	989	990	986	610
155°	1116	1119	1122	1127	1124	513
165°	1214	1212	1212	1220	1215	342
175°	1263	1260	1257	1265	1259	120
180°	1265	1265	1265	1265	1265	



TEST NUMBER: P907198

CATALOG NUMBER: DFN2DIP-TR3F0-070D040US835-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2893.1	2893.1	2893.1	2893.1	2893.1
2.5°	2906.1	2893.1	2864.2	2890.6	2885.3
5°	2893.1	2880.0	2845.9	2869.5	2861.7
7.5°	2869.5	2853.9	2817.3	2827.5	2814.5
10°	2838.1	2819.8	2767.5	2759.5	2743.9
12.5°	2798.9	2775.3	2704.5	2688.9	2660.0
15°	2751.7	2722.8	2633.9	2584.2	2558.1
17.5°	2696.7	2654.8	2544.8	2487.2	2445.3
20°	2633.9	2581.4	2450.6	2385.3	2327.5
22.5°	2565.9	2505.6	2353.6	2264.7	2225.6
25°	2497.8	2413.9	2241.1	2133.9	2094.5
27.5°	2416.7	2327.5	2136.4	2013.4	1953.1
30°	2330.3	2230.6	2021.1	1887.8	1817.0
32.5°	2246.4	2125.9	1911.4	1754.2	1688.6
35°	2152.2	2018.6	1788.4	1623.4	1565.6
37.5°	2060.6	1916.4	1673.1	1492.2	1427.0
40°	1963.6	1806.7	1552.5	1366.7	1298.6
42.5°	1864.2	1696.7	1432.2	1238.3	1173.1
45°	1759.5	1583.9	1309.2	1123.1	1060.3
47.5°	1660.0	1474.2	1191.4	1005.3	947.8
50°	1550.0	1364.2	1076.1	895.3	840.6
52.5°	1442.5	1246.1	966.1	793.3	743.6
55°	1337.8	1133.6	850.8	693.9	644.2
57.5°	1230.6	1021.1	748.9	602.2	560.3
60°	1120.6	911.1	641.4	508.1	466.1
62.5°	1013.3	803.9	549.7	424.2	403.3
65°	903.3	691.1	455.6	366.7	358.6
67.5°	798.6	586.4	366.7	321.9	314.2
70°	688.6	484.4	303.6	277.5	266.9
72.5°	583.9	390.0	253.9	233.1	227.8
75°	481.7	298.3	209.4	191.1	188.6
77.5°	379.7	211.9	165.0	154.4	149.2
80°	285.3	151.9	125.6	115.3	115.3
82.5°	198.9	102.2	86.4	81.1	81.1
85°	112.5	57.5	49.7	49.7	49.7
87.5°	41.9	20.8	20.8	18.3	18.3
90°	1.1	13.7	37.4	35.1	36.2
92.5°	23.6	32.0	33.2	34.3	34.3
95°	55.7	66.4	68.3	68.3	66.4
97.5°	92.7	102.6	106.8	106.8	106.8
100°	135.4	144.2	147.2	147.2	146.1
102.5°	180.4	186.9	191.1	192.2	191.1
105°	229.6	232.6	234.9	236.8	236.8
107.5°	278.4	283.0	283.0	283.7	278.4
110°	325.7	331.8	331.8	331.8	328.8



TEST NUMBER: P907198

CATALOG NUMBER: DFN2DIP-TR3F0-070D040US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.8	383.3	382.1	379.1	376.8
115°	427.1	433.3	431.3	430.2	427.1
117.5°	477.1	485.5	480.2	477.1	474.1
120°	527.5	535.8	527.5	527.5	524.0
122.5°	573.2	583.9	578.6	575.5	573.2
125°	621.3	630.8	627.8	624.3	623.2
127.5°	668.2	680.0	675.8	671.2	668.2
130°	712.0	725.8	723.9	721.6	717.4
132.5°	761.2	771.9	772.7	767.3	764.3
135°	803.6	815.4	817.7	816.5	813.5
137.5°	850.9	860.4	862.3	861.5	857.0
140°	892.4	902.0	907.3	907.3	903.1
142.5°	935.2	944.7	947.7	948.9	944.7
145°	975.6	983.2	989.3	990.5	986.3
147.5°	1011.8	1021.3	1025.9	1027.8	1023.6
150°	1049.2	1055.7	1059.9	1063.3	1059.9
152.5°	1082.4	1088.8	1094.2	1098.4	1094.2
155°	1115.5	1118.6	1122.0	1127.4	1123.9
157.5°	1144.2	1146.4	1148.3	1156.0	1150.6
160°	1169.7	1172.0	1173.1	1179.6	1175.0
162.5°	1193.3	1193.3	1194.5	1201.7	1196.4
165°	1213.6	1212.4	1212.4	1220.0	1214.7
167.5°	1231.9	1228.4	1228.4	1236.1	1230.7
170°	1245.6	1242.5	1241.4	1249.0	1242.5
172.5°	1255.1	1252.1	1250.9	1258.6	1252.1
175°	1262.8	1259.7	1257.4	1265.0	1258.6
177.5°	1267.0	1263.9	1261.6	1268.1	1261.6
180°	1265.0	1265.0	1265.0	1265.0	1265.0



TEST NUMBER: P907198
 CATALOG NUMBER: DFN2DIP-TR3F0-070D040US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.66	13.61	13.51	14.47	15.55	8.64	9.59	9.49	10.45	11.53
	3H	14.34	15.19	15.20	16.06	17.17	9.83	10.68	10.69	11.55	12.66
	4H	14.95	15.75	15.82	16.63	17.74	10.28	11.08	11.16	11.96	13.08
	6H	15.37	16.10	16.25	16.99	18.12	10.60	11.34	11.49	12.23	13.36
	8H	15.49	16.19	16.39	17.10	18.23	10.70	11.40	11.59	12.30	13.43
	12H	15.55	16.22	16.45	17.12	18.27	10.74	11.41	11.64	12.30	13.46
4H	2H	12.69	13.49	13.57	14.37	15.49	9.24	10.04	10.12	10.92	12.04
	3H	14.52	15.19	15.41	16.10	17.23	10.60	11.26	11.49	12.17	13.30
	4H	15.21	15.82	16.11	16.72	17.88	11.15	11.75	12.05	12.66	13.82
	6H	15.72	16.24	16.64	17.18	18.34	11.56	12.08	12.48	13.02	14.18
	8H	15.90	16.38	16.82	17.31	18.48	11.69	12.18	12.61	13.10	14.28
	12H	15.99	16.43	16.93	17.37	18.55	11.76	12.20	12.70	13.14	14.32
8H	4H	15.19	15.67	16.11	16.60	17.77	11.43	11.91	12.35	12.84	14.01
	6H	15.75	16.15	16.69	17.12	18.29	11.94	12.34	12.89	13.31	14.48
	8H	15.96	16.31	16.91	17.27	18.46	12.13	12.48	13.09	13.44	14.63
	12H	16.09	16.41	17.05	17.36	18.60	12.25	12.56	13.21	13.51	14.75
12H	4H	15.14	15.58	16.08	16.53	17.70	11.44	11.87	12.38	12.82	14.00
	6H	15.72	16.08	16.68	17.04	18.23	11.99	12.35	12.95	13.30	14.49
	8H	15.94	16.25	16.90	17.20	18.45	12.20	12.51	13.16	13.46	14.70