

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920670

Luminaire Tested: DFN2DIP-TR2F0-040D020US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920670
REPORT IS A COMBINATION OF REPORTS P900226 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-040D020US935-RLLFLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4451.3 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920670

CATALOG NUMBER: DFN2DIP-TR2F0-040D020US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P920670

CATALOG NUMBER: DFN2DIP-TR2F0-040D020US935-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61
2	93	86	80	75	88	81	76	72	72	68	65	64	61	58	57	54	52
3	86	76	69	63	80	72	66	61	65	59	55	57	53	50	51	48	45
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35
6	67	55	47	41	63	52	45	40	47	41	37	42	38	34	38	34	31
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25
9	54	42	35	29	51	40	33	29	36	31	27	33	28	25	30	26	23
10	51	39	31	27	48	37	30	26	34	28	24	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3175	3175	3175
5°	3175	3117	3139
10°	3139	3049	3031
15°	3091	2942	2869
20°	3029	2796	2670
25°	2966	2634	2479
30°	2882	2469	2239
35°	2800	2292	2028
40°	2716	2110	1787
45°	2619	1909	1569
50°	2519	1706	1356
55°	2413	1490	1152
60°	2291	1266	943
65°	2150	1039	843
70°	1979	828	755
75°	1763	716	676
80°	1453	580	570
85°	955	361	402

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2619 cd/sqm

TEST NUMBER: P920670

CATALOG NUMBER: DFN2DIP-TR2F0-040D020US935-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.4	3.0
10°-20°	366.2	8.2
20°-30°	514.2	11.6
30°-40°	560.5	12.6
40°-50°	515.1	11.6
50°-60°	404.5	9.1
60°-70°	263.3	5.9
70°-80°	135.6	3.0
80°-90°	36.1	0.8
90°-100°	33.7	0.8
100°-110°	107.1	2.4
110°-120°	183.2	4.1
120°-130°	241.0	5.4
130°-140°	270.5	6.1
140°-150°	265.3	6.0
150°-160°	222.5	5.0
160°-170°	147.6	3.3
170°-180°	51.6	1.2
0°-30°	1013.8	22.8
0°-40°	1574.2	35.4
0°-60°	2493.9	56.0
0°-90°	2928.9	65.8
90°-120°	324.0	7.3
90°-150°	1100.8	24.7
90°-180°	1522.0	34.2
0°-180°	4451.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1423	1423	1423	1423	1423	
5°	1423	1417	1400	1412	1408	135
15°	1354	1340	1296	1271	1259	382
25°	1229	1188	1103	1050	1030	565
35°	1059	993	880	799	770	663
45°	866	779	644	553	522	668
55°	658	558	419	341	317	588
65°	444	340	224	180	176	441
75°	237	147	103	94	93	251
85°	55	28	24	24	24	64
90°	0	6	16	15	16	4
95°	24	29	29	29	29	27
105°	99	100	101	102	102	104
115°	184	186	186	185	184	182
125°	267	272	270	269	268	239
135°	346	351	352	352	350	267
145°	420	423	426	426	425	262
155°	480	482	483	485	484	221
165°	522	522	522	525	523	147
175°	544	542	541	545	542	52
180°	545	545	545	545	545	



TEST NUMBER: P920670

CATALOG NUMBER: DFN2DIP-TR2F0-040D020US935-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1423.4	1423.4	1423.4	1423.4	1423.4
2.5°	1429.9	1423.4	1409.2	1422.2	1419.5
5°	1423.4	1416.9	1400.2	1411.8	1408.0
7.5°	1411.8	1404.1	1386.1	1391.1	1384.7
10°	1396.4	1387.3	1361.6	1357.6	1350.0
12.5°	1377.1	1365.5	1330.6	1322.9	1308.7
15°	1353.8	1339.6	1295.9	1271.4	1258.6
17.5°	1326.8	1306.1	1252.0	1223.7	1203.1
20°	1295.9	1270.1	1205.7	1173.5	1145.1
22.5°	1262.4	1232.8	1158.0	1114.2	1095.0
25°	1228.9	1187.7	1102.6	1049.9	1030.4
27.5°	1189.0	1145.1	1051.1	990.6	960.9
30°	1146.5	1097.4	994.4	928.8	894.0
32.5°	1105.3	1045.9	940.4	863.1	830.8
35°	1058.9	993.2	879.9	798.7	770.2
37.5°	1013.8	942.9	823.1	734.2	702.1
40°	966.1	888.9	763.9	672.4	638.9
42.5°	917.1	834.7	704.6	609.2	577.1
45°	865.6	779.3	644.1	552.6	521.7
47.5°	816.7	725.3	586.2	494.6	466.3
50°	762.6	671.1	529.4	440.5	413.5
52.5°	709.7	613.1	475.4	390.3	365.8
55°	658.2	557.8	418.6	341.4	316.9
57.5°	605.5	502.4	368.4	296.3	275.7
60°	551.3	448.2	315.6	249.9	229.4
62.5°	498.6	395.5	270.4	208.7	198.5
65°	444.4	340.0	224.1	180.4	176.4
67.5°	393.0	288.5	180.4	158.4	154.5
70°	338.8	238.3	149.4	136.6	131.3
72.5°	287.3	191.9	124.9	114.7	112.1
75°	236.9	146.8	103.1	94.0	92.8
77.5°	186.8	104.3	81.2	76.0	73.4
80°	140.3	74.7	61.7	56.7	56.7
82.5°	97.9	50.3	42.5	39.9	39.9
85°	55.4	28.3	24.5	24.5	24.5
87.5°	20.7	10.2	10.2	9.0	9.0
90°	0.5	5.9	16.1	15.1	15.6
92.5°	10.2	13.8	14.3	14.8	14.8
95°	23.9	28.6	29.4	29.4	28.6
97.5°	39.9	44.2	46.0	46.0	46.0
100°	58.3	62.1	63.4	63.4	62.9
102.5°	77.7	80.4	82.2	82.7	82.2
105°	98.8	100.1	101.2	101.9	101.9
107.5°	119.9	121.8	121.8	122.2	119.9
110°	140.3	142.8	142.8	142.8	141.5



TEST NUMBER: P920670

CATALOG NUMBER: DFN2DIP-TR2F0-040D020US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	162.2	165.0	164.5	163.2	162.2
115°	183.9	186.5	185.7	185.2	183.9
117.5°	205.4	209.1	206.7	205.4	204.1
120°	227.0	230.7	227.0	227.0	225.6
122.5°	246.8	251.3	249.1	247.8	246.8
125°	267.4	271.6	270.3	268.8	268.3
127.5°	287.7	292.7	290.9	289.0	287.7
130°	306.5	312.5	311.6	310.6	308.8
132.5°	327.7	332.3	332.6	330.4	329.0
135°	345.9	351.0	352.0	351.5	350.2
137.5°	366.3	370.4	371.3	370.9	368.9
140°	384.2	388.3	390.6	390.6	388.8
142.5°	402.6	406.6	408.0	408.5	406.6
145°	420.0	423.3	425.9	426.4	424.6
147.5°	435.6	439.7	441.7	442.5	440.7
150°	451.7	454.4	456.2	457.7	456.2
152.5°	466.0	468.7	471.1	472.9	471.1
155°	480.3	481.6	483.0	485.3	483.9
157.5°	492.6	493.5	494.4	497.7	495.3
160°	503.6	504.5	505.1	507.8	505.8
162.5°	513.8	513.8	514.2	517.4	515.0
165°	522.5	521.9	521.9	525.2	523.0
167.5°	530.3	528.8	528.8	532.1	529.9
170°	536.2	534.9	534.4	537.7	534.9
172.5°	540.4	539.0	538.6	541.8	539.0
175°	543.6	542.3	541.3	544.6	541.8
177.5°	545.4	544.2	543.1	545.9	543.1
180°	544.6	544.6	544.6	544.6	544.6

TEST NUMBER: P920670

CATALOG NUMBER: DFN2DIP-TR2F0-040D020US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.39	13.37	13.21	14.20	15.23	8.37	9.35	9.19	10.19	11.21
	3H	14.06	14.93	14.89	15.78	16.83	9.56	10.43	10.39	11.28	12.33
	4H	14.66	15.48	15.50	16.33	17.40	10.00	10.83	10.85	11.68	12.75
	6H	15.07	15.83	15.92	16.68	17.77	10.32	11.08	11.18	11.94	13.02
	8H	15.19	15.91	16.05	16.79	17.87	10.41	11.13	11.27	12.01	13.09
	12H	15.24	15.93	16.12	16.80	17.91	10.45	11.14	11.32	12.01	13.11
4H	2H	12.42	13.25	13.28	14.10	15.17	8.97	9.80	9.82	10.65	11.72
	3H	14.24	14.93	15.10	15.81	16.89	10.32	11.00	11.18	11.89	12.97
	4H	14.92	15.54	15.79	16.42	17.53	10.86	11.48	11.73	12.36	13.47
	6H	15.42	15.96	16.31	16.86	17.98	11.27	11.81	12.16	12.71	13.83
	8H	15.59	16.09	16.48	16.99	18.11	11.39	11.89	12.28	12.79	13.92
	12H	15.67	16.13	16.59	17.04	18.18	11.46	11.91	12.37	12.82	13.96
8H	4H	14.89	15.40	15.79	16.30	17.42	11.14	11.64	12.03	12.54	13.66
	6H	15.44	15.85	16.36	16.80	17.92	11.64	12.05	12.56	12.99	14.12
	8H	15.64	16.01	16.57	16.94	18.09	11.82	12.18	12.75	13.12	14.26
	12H	15.77	16.09	16.70	17.02	18.21	11.93	12.25	12.86	13.18	14.37
12H	4H	14.85	15.30	15.76	16.22	17.35	11.14	11.60	12.06	12.51	13.65
	6H	15.41	15.78	16.34	16.72	17.86	11.68	12.05	12.61	12.98	14.13
	8H	15.63	15.95	16.56	16.87	18.07	11.88	12.21	12.82	13.13	14.33