

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907219

Luminaire Tested: DFN2DIP-TR3F0-080D030US835-FLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907219
REPORT IS A COMBINATION OF REPORTS P901801 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-080D030US835-FLLONL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10890.0 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 103.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907219
CATALOG NUMBER: DFN2DIP-TR3F0-080D030US835-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P907219

CATALOG NUMBER: DFN2DIP-TR3F0-080D030US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	77	77	77	73
1	103	98	94	91	97	94	90	87	84	82	79	76	74	72	68	67	65	65	65	65	61
2	94	86	80	74	89	82	76	71	74	69	66	67	63	60	60	57	55	55	55	55	51
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	47	47	47	44
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	40	40	40	40	37
5	72	60	51	45	68	57	50	44	52	46	41	47	42	38	43	39	35	35	35	35	32
6	67	54	45	39	63	52	44	38	47	41	36	43	37	33	39	35	31	31	31	31	29
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	28	28	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25	25	25	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	22	22	22	20
10	50	38	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	20	20	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3879	3879	3879
5°	3883	3822	3848
10°	3849	3767	3793
15°	3791	3702	3709
20°	3712	3612	3624
25°	3634	3506	3525
30°	3536	3407	3400
35°	3443	3290	3268
40°	3330	3173	3142
45°	3216	3054	3013
50°	3092	2930	2864
55°	2962	2787	2726
60°	2814	2616	2568
65°	2653	2440	2382
70°	2448	2224	2180
75°	2165	1966	1991
80°	1822	1636	1636
85°	1287	1077	1057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3216 cd/sqm



TEST NUMBER: P907219

CATALOG NUMBER: DFN2DIP-TR3F0-080D030US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	293.0	2.7
10°-20°	824.3	7.6
20°-30°	1211.5	11.1
30°-40°	1407.0	12.9
40°-50°	1405.3	12.9
50°-60°	1225.4	11.3
60°-70°	905.8	8.3
70°-80°	512.5	4.7
80°-90°	137.1	1.3
90°-100°	33.4	0.3
100°-110°	124.4	1.1
110°-120°	330.1	3.0
120°-130°	547.5	5.0
130°-140°	581.5	5.3
140°-150°	540.5	5.0
150°-160°	434.5	4.0
160°-170°	280.0	2.6
170°-180°	96.4	0.9
0°-30°	2328.8	21.4
0°-40°	3735.8	34.3
0°-60°	6366.4	58.5
0°-90°	7921.8	72.7
90°-120°	487.9	4.5
90°-150°	2157.3	19.8
90°-180°	2968.0	27.3
0°-180°	10890.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3113	3113	3113	3113	3113	
5°	3113	3101	3068	3092	3086	295
15°	2963	2946	2906	2918	2904	835
25°	2682	2658	2607	2613	2607	1234
35°	2314	2284	2236	2218	2203	1445
45°	1883	1862	1817	1784	1772	1453
55°	1425	1407	1371	1335	1320	1274
65°	961	943	913	886	871	950
75°	503	497	482	464	470	537
85°	123	120	117	108	105	137
90°	1	9	15	18	20	10
95°	48	23	28	32	32	56
105°	223	245	45	53	56	238
115°	421	434	452	113	60	415
125°	596	605	619	624	626	531
135°	737	749	755	763	761	569
145°	855	854	867	872	868	535
155°	941	935	944	948	942	434
165°	992	988	990	995	990	280
175°	1015	1010	1011	1016	1009	97
180°	1012	1012	1012	1012	1012	



TEST NUMBER: P907219

CATALOG NUMBER: DFN2DIP-TR3F0-080D030US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3112.8	3112.8	3112.8	3112.8	3112.8
2.5°	3130.9	3116.0	3083.0	3112.8	3107.1
5°	3112.8	3101.1	3068.1	3091.9	3086.2
7.5°	3091.9	3074.1	3041.1	3065.2	3059.2
10°	3059.2	3038.2	3002.3	3026.1	3017.3
12.5°	3014.1	2996.3	2960.4	2975.3	2969.3
15°	2963.3	2945.5	2906.4	2918.5	2903.6
17.5°	2900.4	2882.6	2843.5	2858.5	2843.5
20°	2831.5	2813.7	2771.8	2780.7	2768.9
22.5°	2762.9	2735.9	2696.8	2696.8	2690.8
25°	2681.9	2658.1	2607.3	2613.0	2607.3
27.5°	2592.0	2571.1	2532.3	2523.4	2508.5
30°	2502.5	2478.3	2433.6	2424.7	2412.6
32.5°	2406.6	2388.8	2340.8	2322.7	2310.7
35°	2313.8	2284.0	2236.0	2217.9	2203.0
37.5°	2209.0	2182.0	2134.1	2113.1	2098.2
40°	2101.4	2077.2	2029.3	2002.6	1990.5
42.5°	1996.6	1972.4	1924.8	1894.6	1876.9
45°	1882.9	1861.9	1816.8	1784.1	1772.1
47.5°	1772.1	1751.1	1703.1	1670.1	1652.3
50°	1655.2	1640.3	1598.3	1556.4	1541.5
52.5°	1541.5	1520.5	1481.8	1448.8	1427.8
55°	1424.9	1406.8	1371.0	1335.1	1320.1
57.5°	1308.1	1293.2	1254.1	1218.2	1206.1
60°	1191.2	1179.5	1137.5	1104.5	1095.6
62.5°	1077.5	1056.6	1026.7	996.9	984.8
65°	961.0	942.9	913.0	886.0	871.1
67.5°	841.2	826.0	799.3	778.4	766.3
70°	730.4	718.3	691.4	670.4	658.6
72.5°	616.7	604.7	589.7	568.8	559.9
75°	502.7	497.0	481.8	464.0	470.0
77.5°	401.1	389.0	383.0	374.1	365.2
80°	299.5	296.3	290.3	281.4	275.3
82.5°	203.6	203.6	200.7	188.6	188.6
85°	122.6	119.7	116.9	107.7	104.8
87.5°	54.0	48.0	41.9	33.0	29.9
90°	0.7	8.8	14.6	18.4	19.7
92.5°	18.4	15.4	17.6	19.1	19.7
95°	47.6	23.4	28.5	32.3	31.5
97.5°	85.7	25.7	37.3	39.6	40.3
100°	129.7	29.3	41.8	47.6	49.1
102.5°	178.0	176.6	43.2	51.2	53.5
105°	222.7	244.7	44.7	52.7	55.7
107.5°	274.7	293.0	46.2	54.2	57.2
110°	324.6	339.9	128.2	55.0	57.9



TEST NUMBER: P907219

CATALOG NUMBER: DFN2DIP-TR3F0-080D030US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	371.5	384.6	372.2	56.4	58.6
115°	421.2	433.7	452.0	112.8	60.1
117.5°	464.5	479.1	491.6	386.8	194.9
120°	512.8	523.8	537.0	545.8	446.9
122.5°	553.8	565.6	580.3	584.6	585.4
125°	595.6	605.1	619.1	624.2	626.4
127.5°	633.7	643.9	655.0	662.3	663.0
130°	669.6	681.4	689.4	697.4	696.8
132.5°	706.2	715.8	723.8	730.4	729.7
135°	737.0	748.8	755.3	762.7	761.2
137.5°	769.2	778.0	785.4	792.7	790.5
140°	800.7	806.6	814.6	821.2	817.6
142.5°	827.2	832.3	841.8	847.6	844.0
145°	855.0	854.2	866.7	871.8	868.1
147.5°	879.1	876.9	889.4	893.0	890.1
150°	902.6	897.5	909.2	913.5	909.9
152.5°	922.3	916.5	927.5	931.9	926.8
155°	941.4	934.9	943.6	948.0	942.2
157.5°	956.8	951.0	957.6	962.7	956.8
160°	970.0	965.6	970.0	974.4	969.2
162.5°	981.7	977.3	981.0	986.1	979.5
165°	991.9	987.6	989.8	994.9	989.8
167.5°	1000.0	995.6	997.8	1003.0	996.4
170°	1006.6	1002.2	1003.7	1008.8	1002.2
172.5°	1011.0	1006.6	1008.1	1013.2	1006.6
175°	1014.6	1009.5	1011.0	1016.1	1008.8
177.5°	1016.1	1011.0	1011.8	1016.9	1010.3
180°	1012.5	1012.5	1012.5	1012.5	1012.5



TEST NUMBER: P907219
 CATALOG NUMBER: DFN2DIP-TR3F0-080D030US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.81	14.92	14.54	15.67	16.58	13.38	14.49	14.11	15.24	16.15
	3H	15.48	16.48	16.22	17.24	18.18	15.01	16.01	15.76	16.77	17.71
	4H	16.07	17.01	16.83	17.79	18.73	15.60	16.54	16.37	17.32	18.27
	6H	16.47	17.34	17.25	18.13	19.09	16.00	16.88	16.78	17.66	18.62
	8H	16.58	17.41	17.37	18.21	19.18	16.11	16.94	16.90	17.75	18.71
	12H	16.64	17.43	17.43	18.22	19.21	16.16	16.95	16.96	17.75	18.74
4H	2H	14.29	15.24	15.06	16.01	16.96	13.95	14.89	14.72	15.67	16.62
	3H	16.17	16.96	16.95	17.77	18.73	15.78	16.57	16.56	17.38	18.34
	4H	16.89	17.61	17.69	18.41	19.41	16.49	17.20	17.28	18.01	19.01
	6H	17.41	18.03	18.22	18.86	19.86	17.01	17.63	17.82	18.46	19.46
	8H	17.56	18.14	18.38	18.97	19.98	17.15	17.73	17.97	18.56	19.57
	12H	17.64	18.16	18.48	19.01	20.03	17.23	17.75	18.06	18.60	19.62
8H	4H	17.10	17.68	17.92	18.51	19.52	16.74	17.32	17.56	18.15	19.17
	6H	17.73	18.21	18.58	19.08	20.10	17.37	17.85	18.22	18.73	19.74
	8H	17.95	18.38	18.81	19.24	20.27	17.59	18.01	18.44	18.88	19.91
	12H	18.09	18.46	18.95	19.32	20.41	17.71	18.08	18.57	18.94	20.03
12H	4H	17.10	17.62	17.94	18.47	19.49	16.75	17.27	17.59	18.12	19.14
	6H	17.76	18.19	18.62	19.06	20.09	17.41	17.84	18.27	18.71	19.74
	8H	18.01	18.39	18.87	19.24	20.33	17.66	18.03	18.52	18.89	19.98