

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920673

Luminaire Tested: DFN2DIP-TR2F0-040D030US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920673
REPORT IS A COMBINATION OF REPORTS P901755 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-040D030US935-FLLONL
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5695.4 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920673

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US935-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P920673

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US935-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	100	96	92	88	93	89	86	83	78	75	73	67	66	64	58	56	55
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	48	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2989	2989	2989
5°	2989	2941	2962
10°	2961	2894	2917
15°	2913	2840	2849
20°	2849	2767	2780
25°	2786	2682	2701
30°	2708	2601	2601
35°	2634	2508	2497
40°	2544	2413	2397
45°	2453	2317	2294
50°	2354	2217	2176
55°	2250	2101	2066
60°	2131	1965	1940
65°	2002	1822	1792
70°	1837	1648	1630
75°	1611	1440	1474
80°	1335	1174	1193
85°	910	741	740

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2453 cd/sqm

TEST NUMBER: P920673

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US935-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.1	2.2
10°-20°	354.9	6.2
20°-30°	521.5	9.2
30°-40°	605.7	10.6
40°-50°	605.0	10.6
50°-60°	527.5	9.3
60°-70°	389.9	6.8
70°-80°	220.6	3.9
80°-90°	60.5	1.1
90°-100°	50.6	0.9
100°-110°	160.6	2.8
110°-120°	274.9	4.8
120°-130°	361.5	6.3
130°-140°	405.7	7.1
140°-150°	397.9	7.0
150°-160°	333.8	5.9
160°-170°	221.3	3.9
170°-180°	77.4	1.4
0°-30°	1002.5	17.6
0°-40°	1608.3	28.2
0°-60°	2740.7	48.1
0°-90°	3411.8	59.9
90°-120°	486.0	8.5
90°-150°	1651.1	29.0
90°-180°	2284.0	40.1
0°-180°	5695.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1340	1340	1340	1340	1340	
5°	1340	1335	1321	1331	1329	127
15°	1276	1268	1251	1256	1250	359
25°	1154	1144	1122	1125	1122	531
35°	996	983	963	955	948	622
45°	810	802	782	768	763	626
55°	614	606	590	575	568	548
65°	414	406	393	381	375	409
75°	216	214	207	200	202	231
85°	53	52	50	46	45	59
90°	1	9	24	23	23	5
95°	36	43	44	44	43	40
105°	148	150	152	153	153	156
115°	276	280	278	278	276	273
125°	401	407	405	403	402	358
135°	519	526	528	527	525	401
145°	630	635	639	640	637	394
155°	720	722	724	728	726	332
165°	784	783	783	788	784	221
175°	816	814	812	817	813	77
180°	817	817	817	817	817	

TEST NUMBER: P920673

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1340.1	1340.1	1340.1	1340.1	1340.1
2.5°	1347.9	1341.4	1327.2	1340.1	1337.6
5°	1340.1	1335.0	1320.8	1331.0	1328.6
7.5°	1331.0	1323.4	1309.1	1319.6	1317.0
10°	1317.0	1307.9	1292.5	1302.8	1298.9
12.5°	1297.5	1289.9	1274.4	1280.9	1278.2
15°	1275.7	1268.0	1251.2	1256.4	1250.0
17.5°	1248.6	1241.0	1224.2	1230.5	1224.2
20°	1218.9	1211.3	1193.3	1197.0	1192.1
22.5°	1189.4	1177.8	1161.0	1161.0	1158.4
25°	1154.5	1144.3	1122.4	1124.9	1122.4
27.5°	1115.9	1106.8	1090.2	1086.3	1079.9
30°	1077.3	1066.9	1047.7	1043.8	1038.6
32.5°	1036.0	1028.4	1007.7	1000.0	994.7
35°	996.1	983.3	962.6	954.8	948.4
37.5°	951.0	939.3	918.7	909.7	903.3
40°	904.7	894.2	873.6	862.1	857.0
42.5°	859.5	849.1	828.6	815.6	808.0
45°	810.5	801.6	782.1	768.1	762.8
47.5°	762.8	753.8	733.2	719.0	711.4
50°	712.6	706.1	688.1	670.0	663.6
52.5°	663.6	654.6	637.9	623.7	614.7
55°	613.5	605.6	590.2	574.7	568.3
57.5°	563.1	556.7	539.8	524.4	519.3
60°	512.8	507.7	489.7	475.5	471.7
62.5°	463.9	454.9	442.0	429.1	424.0
65°	413.7	405.9	393.0	381.4	375.1
67.5°	362.1	355.6	344.1	335.1	329.9
70°	314.4	309.3	297.6	288.6	283.5
72.5°	265.5	260.3	253.9	244.9	241.0
75°	216.5	214.0	207.4	199.8	202.3
77.5°	172.6	167.5	164.9	161.0	157.2
80°	128.9	127.5	124.9	121.1	118.6
82.5°	87.6	87.6	86.4	81.2	81.2
85°	52.8	51.6	50.3	46.3	45.1
87.5°	23.2	20.7	18.1	14.2	12.8
90°	0.8	8.9	24.1	22.6	23.4
92.5°	15.2	20.7	21.4	22.1	22.1
95°	36.0	42.9	44.1	44.1	42.9
97.5°	59.8	66.2	69.0	69.0	69.0
100°	87.4	93.1	95.1	95.1	94.4
102.5°	116.5	120.7	123.4	124.2	123.4
105°	148.3	150.2	151.7	152.9	152.9
107.5°	179.8	182.7	182.7	183.2	179.8
110°	210.3	214.3	214.3	214.3	212.3

TEST NUMBER: P920673

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	243.3	247.5	246.8	244.8	243.3
115°	275.9	279.7	278.5	277.8	275.9
117.5°	308.1	313.5	310.0	308.1	306.1
120°	340.6	346.0	340.6	340.6	338.4
122.5°	370.1	377.0	373.6	371.6	370.1
125°	401.2	407.3	405.4	403.1	402.4
127.5°	431.4	439.1	436.4	433.4	431.4
130°	459.8	468.6	467.4	466.0	463.2
132.5°	491.5	498.4	498.9	495.5	493.5
135°	518.9	526.5	528.0	527.3	525.3
137.5°	549.4	555.6	556.8	556.4	553.4
140°	576.3	582.5	585.9	585.9	583.2
142.5°	603.9	610.0	612.0	612.8	610.0
145°	630.0	634.9	638.9	639.5	636.9
147.5°	653.4	659.5	662.5	663.7	661.0
150°	677.5	681.7	684.4	686.6	684.4
152.5°	699.0	703.1	706.5	709.3	706.5
155°	720.4	722.3	724.5	728.0	725.8
157.5°	738.8	740.3	741.6	746.5	743.0
160°	755.4	756.8	757.6	761.7	758.8
162.5°	770.6	770.6	771.4	776.0	772.6
165°	783.7	782.9	782.9	787.8	784.4
167.5°	795.5	793.2	793.2	798.1	794.7
170°	804.3	802.4	801.7	806.6	802.4
172.5°	810.5	808.6	807.8	812.7	808.6
175°	815.5	813.5	812.0	816.9	812.7
177.5°	818.1	816.1	814.7	818.9	814.7
180°	816.9	816.9	816.9	816.9	816.9

TEST NUMBER: P920673

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.81	12.77	12.68	13.66	14.78	11.39	12.35	12.26	13.24	14.36
	3H	13.46	14.32	14.34	15.22	16.36	13.00	13.86	13.88	14.75	15.90
	4H	14.03	14.85	14.93	15.75	16.91	13.57	14.39	14.47	15.29	16.45
	6H	14.42	15.17	15.33	16.08	17.25	13.96	14.71	14.87	15.62	16.79
	8H	14.52	15.23	15.43	16.16	17.33	14.06	14.77	14.97	15.70	16.87
	12H	14.56	15.24	15.48	16.16	17.36	14.10	14.78	15.02	15.70	16.90
4H	2H	12.28	13.09	13.18	13.99	15.15	11.94	12.75	12.84	13.65	14.81
	3H	14.12	14.80	15.04	15.74	16.91	13.74	14.42	14.65	15.35	16.53
	4H	14.82	15.44	15.75	16.37	17.57	14.43	15.05	15.35	15.98	17.18
	6H	15.32	15.86	16.26	16.81	18.01	14.93	15.46	15.86	16.42	17.61
	8H	15.46	15.96	16.40	16.91	18.12	15.07	15.56	16.00	16.51	17.73
	12H	15.53	15.98	16.49	16.95	18.17	15.12	15.57	16.08	16.54	17.76
8H	4H	15.02	15.52	15.96	16.47	17.68	14.67	15.17	15.60	16.11	17.33
	6H	15.63	16.04	16.59	17.03	18.24	15.27	15.69	16.24	16.68	17.89
	8H	15.83	16.20	16.81	17.18	18.41	15.48	15.84	16.45	16.82	18.05
	12H	15.95	16.27	16.93	17.25	18.53	15.58	15.90	16.56	16.88	18.16
12H	4H	15.01	15.46	15.96	16.42	17.64	14.66	15.11	15.62	16.08	17.30
	6H	15.65	16.02	16.63	17.00	18.23	15.31	15.68	16.28	16.66	17.89
	8H	15.88	16.20	16.86	17.18	18.45	15.53	15.86	16.51	16.83	18.11