

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920683

Luminaire Tested: DFN2DIP-TR2F0-040D050US935-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920683
REPORT IS A COMBINATION OF REPORTS P901776 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-040D050US935-RLLONL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6737.3 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 74.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920683
CATALOG NUMBER: DFN2DIP-TR2F0-040D050US935-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P920683

CATALOG NUMBER: DFN2DIP-TR2F0-040D050US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44			44
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43	37			37
2	88	81	75	71	81	75	70	65	62	59	55	51	48	46	40	38	37	32			32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28			28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28	24			24
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	29	27	25	21			21
6	63	51	43	38	57	47	41	35	40	35	31	33	29	26	27	24	22	19			19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17			17
8	54	42	35	30	50	39	32	28	33	28	24	28	24	21	23	20	18	15			15
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14			14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3175	3175	3175
5°	3175	3117	3139
10°	3139	3049	3031
15°	3091	2942	2869
20°	3029	2796	2670
25°	2966	2634	2479
30°	2882	2469	2239
35°	2800	2292	2028
40°	2716	2110	1787
45°	2619	1909	1569
50°	2519	1706	1356
55°	2413	1490	1152
60°	2291	1266	943
65°	2150	1039	843
70°	1979	828	755
75°	1763	716	676
80°	1453	580	570
85°	955	361	402

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2619 cd/sqm



TEST NUMBER: P920683

CATALOG NUMBER: DFN2DIP-TR2F0-040D050US935-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.4	2.0
10°-20°	366.2	5.4
20°-30°	514.2	7.6
30°-40°	560.5	8.3
40°-50°	515.1	7.6
50°-60°	404.5	6.0
60°-70°	263.3	3.9
70°-80°	135.6	2.0
80°-90°	38.5	0.6
90°-100°	84.2	1.3
100°-110°	267.7	4.0
110°-120°	458.1	6.8
120°-130°	602.5	8.9
130°-140°	676.3	10.0
140°-150°	663.1	9.8
150°-160°	556.3	8.3
160°-170°	368.9	5.5
170°-180°	128.9	1.9
0°-30°	1013.8	15.0
0°-40°	1574.2	23.4
0°-60°	2493.9	37.0
0°-90°	2931.2	43.5
90°-120°	810.0	12.0
90°-150°	2751.9	40.8
90°-180°	3806.0	56.5
0°-180°	6737.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1423	1423	1423	1423	1423	
5°	1423	1417	1400	1412	1408	135
15°	1354	1340	1296	1271	1259	382
25°	1229	1188	1103	1050	1030	565
35°	1059	993	880	799	770	663
45°	866	779	644	553	522	668
55°	658	558	419	341	317	588
65°	444	340	224	180	176	441
75°	237	147	103	94	93	251
85°	55	28	24	24	24	64
90°	1	15	40	38	39	7
95°	60	72	73	73	72	67
105°	247	250	253	255	255	261
115°	460	466	464	463	460	455
125°	669	679	676	672	671	598
135°	865	878	880	879	876	669
145°	1050	1058	1065	1066	1061	656
155°	1201	1204	1208	1213	1210	553
165°	1306	1305	1305	1313	1307	368
175°	1359	1356	1353	1362	1354	129
180°	1362	1362	1362	1362	1362	



TEST NUMBER: P920683

CATALOG NUMBER: DFN2DIP-TR2F0-040D050US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1423.4	1423.4	1423.4	1423.4	1423.4
2.5°	1429.9	1423.4	1409.2	1422.2	1419.5
5°	1423.4	1416.9	1400.2	1411.8	1408.0
7.5°	1411.8	1404.1	1386.1	1391.1	1384.7
10°	1396.4	1387.3	1361.6	1357.6	1350.0
12.5°	1377.1	1365.5	1330.6	1322.9	1308.7
15°	1353.8	1339.6	1295.9	1271.4	1258.6
17.5°	1326.8	1306.1	1252.0	1223.7	1203.1
20°	1295.9	1270.1	1205.7	1173.5	1145.1
22.5°	1262.4	1232.8	1158.0	1114.2	1095.0
25°	1228.9	1187.7	1102.6	1049.9	1030.4
27.5°	1189.0	1145.1	1051.1	990.6	960.9
30°	1146.5	1097.4	994.4	928.8	894.0
32.5°	1105.3	1045.9	940.4	863.1	830.8
35°	1058.9	993.2	879.9	798.7	770.2
37.5°	1013.8	942.9	823.1	734.2	702.1
40°	966.1	888.9	763.9	672.4	638.9
42.5°	917.1	834.7	704.6	609.2	577.1
45°	865.6	779.3	644.1	552.6	521.7
47.5°	816.7	725.3	586.2	494.6	466.3
50°	762.6	671.1	529.4	440.5	413.5
52.5°	709.7	613.1	475.4	390.3	365.8
55°	658.2	557.8	418.6	341.4	316.9
57.5°	605.5	502.4	368.4	296.3	275.7
60°	551.3	448.2	315.6	249.9	229.4
62.5°	498.6	395.5	270.4	208.7	198.5
65°	444.4	340.0	224.1	180.4	176.4
67.5°	393.0	288.5	180.4	158.4	154.5
70°	338.8	238.3	149.4	136.6	131.3
72.5°	287.3	191.9	124.9	114.7	112.1
75°	236.9	146.8	103.1	94.0	92.8
77.5°	186.8	104.3	81.2	76.0	73.4
80°	140.3	74.7	61.7	56.7	56.7
82.5°	97.9	50.3	42.5	39.9	39.9
85°	55.4	28.3	24.5	24.5	24.5
87.5°	20.7	10.2	10.2	9.0	9.0
90°	1.2	14.8	40.2	37.8	39.0
92.5°	25.5	34.4	35.7	36.9	36.9
95°	59.9	71.5	73.4	73.4	71.5
97.5°	99.7	110.4	114.9	114.9	114.9
100°	145.7	155.2	158.4	158.4	157.2
102.5°	194.2	201.1	205.6	206.9	205.6
105°	247.1	250.4	252.9	254.9	254.9
107.5°	299.6	304.5	304.5	305.4	299.6
110°	350.5	357.1	357.1	357.1	353.8



TEST NUMBER: P920683

CATALOG NUMBER: DFN2DIP-TR2F0-040D050US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	405.5	412.5	411.3	408.0	405.5
115°	459.7	466.3	464.3	463.0	459.7
117.5°	513.5	522.5	516.8	513.5	510.2
120°	567.7	576.7	567.7	567.7	564.0
122.5°	616.9	628.4	622.7	619.4	616.9
125°	668.7	678.9	675.6	671.9	670.7
127.5°	719.1	731.8	727.4	722.4	719.1
130°	766.4	781.1	779.0	776.6	772.1
132.5°	819.3	830.8	831.6	825.9	822.6
135°	864.9	877.5	880.0	878.8	875.5
137.5°	915.8	926.0	928.1	927.2	922.3
140°	960.4	970.8	976.5	976.5	972.0
142.5°	1006.4	1016.8	1020.0	1021.2	1016.8
145°	1050.0	1058.2	1064.7	1066.0	1061.4
147.5°	1089.0	1099.2	1104.1	1106.2	1101.6
150°	1129.2	1136.2	1140.6	1144.4	1140.6
152.5°	1164.9	1171.9	1177.6	1182.2	1177.6
155°	1200.6	1203.8	1207.5	1213.3	1209.6
157.5°	1231.4	1233.8	1235.9	1244.1	1238.4
160°	1258.9	1261.4	1262.6	1269.5	1264.6
162.5°	1284.4	1284.4	1285.6	1293.4	1287.6
165°	1306.1	1304.8	1304.8	1313.1	1307.3
167.5°	1325.8	1322.1	1322.1	1330.3	1324.6
170°	1340.6	1337.3	1336.1	1344.3	1337.3
172.5°	1350.8	1347.5	1346.3	1354.5	1347.5
175°	1359.1	1355.7	1353.3	1361.5	1354.5
177.5°	1363.6	1360.3	1357.8	1364.8	1357.8
180°	1361.5	1361.5	1361.5	1361.5	1361.5



TEST NUMBER: P920683
 CATALOG NUMBER: DFN2DIP-TR2F0-040D050US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.39	11.17	11.41	12.19	13.56	6.37	7.15	7.39	8.18	9.54
	3H	12.04	12.74	13.07	13.77	15.15	7.54	8.24	8.57	9.27	10.66
	4H	12.63	13.29	13.67	14.33	15.72	7.98	8.64	9.02	9.67	11.07
	6H	13.03	13.64	14.08	14.68	16.08	8.29	8.89	9.33	9.93	11.33
	8H	13.15	13.72	14.20	14.78	16.18	8.37	8.94	9.42	10.00	11.40
	12H	13.20	13.75	14.26	14.79	16.22	8.40	8.95	9.46	10.00	11.42
4H	2H	10.40	11.06	11.45	12.09	13.49	6.95	7.61	8.00	8.64	10.04
	3H	12.20	12.75	13.25	13.81	15.21	8.28	8.83	9.33	9.89	11.29
	4H	12.87	13.37	13.93	14.43	15.85	8.81	9.31	9.87	10.36	11.79
	6H	13.36	13.79	14.43	14.87	16.29	9.21	9.64	10.28	10.72	12.14
	8H	13.52	13.92	14.59	14.99	16.43	9.33	9.73	10.40	10.80	12.24
	12H	13.60	13.96	14.69	15.05	16.49	9.38	9.75	10.47	10.83	12.27
8H	4H	12.83	13.23	13.90	14.30	15.74	9.07	9.47	10.14	10.54	11.98
	6H	13.37	13.70	14.46	14.81	16.24	9.57	9.90	10.66	11.01	12.44
	8H	13.57	13.86	14.67	14.95	16.41	9.74	10.04	10.84	11.13	12.58
	12H	13.69	13.95	14.79	15.04	16.53	9.85	10.11	10.95	11.19	12.69
12H	4H	12.78	13.14	13.87	14.23	15.67	9.07	9.43	10.16	10.52	11.96
	6H	13.34	13.63	14.44	14.73	16.18	9.61	9.90	10.71	10.99	12.45
	8H	13.54	13.80	14.65	14.89	16.38	9.80	10.06	10.91	11.15	12.64