

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907253

Luminaire Tested: DFN2DIP-TR3F0-090D050US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907253
REPORT IS A COMBINATION OF REPORTS P901831 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-090D050US835-FLLONL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13860.0 lumens
Efficiency: N/A
Efficacy: 105.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 132
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907253
CATALOG NUMBER: DFN2DIP-TR3F0-090D050US835-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P907253
 CATALOG NUMBER: DFN2DIP-TR3F0-090D050US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64		
1	101	97	93	89	95	91	87	84	80	78	75	70	68	67	61	60	59	54		
2	92	84	78	73	86	79	74	69	70	66	62	62	59	56	54	51	49	45		
3	84	74	67	61	79	70	63	58	62	57	52	55	51	47	48	45	42	38		
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36	33		
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	39	35	32	29		
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	25		
7	60	48	40	34	57	45	38	33	41	34	30	36	31	27	32	28	25	22		
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	29	25	22	20		
9	52	40	32	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18		
10	49	37	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4364	4364	4364
5°	4368	4299	4329
10°	4331	4238	4268
15°	4265	4164	4173
20°	4176	4064	4076
25°	4088	3944	3965
30°	3978	3832	3825
35°	3874	3702	3676
40°	3746	3569	3534
45°	3618	3436	3389
50°	3479	3296	3222
55°	3332	3135	3067
60°	3166	2943	2889
65°	2985	2745	2679
70°	2754	2502	2453
75°	2435	2211	2240
80°	2050	1840	1841
85°	1448	1212	1189

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3618 cd/sqm



TEST NUMBER: P907253

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.6	2.4
10°-20°	927.4	6.7
20°-30°	1362.9	9.8
30°-40°	1582.9	11.4
40°-50°	1580.9	11.4
50°-60°	1378.5	9.9
60°-70°	1019.0	7.4
70°-80°	576.6	4.2
80°-90°	155.1	1.1
90°-100°	55.7	0.4
100°-110°	207.4	1.5
110°-120°	550.1	4.0
120°-130°	912.4	6.6
130°-140°	969.2	7.0
140°-150°	900.8	6.5
150°-160°	724.2	5.2
160°-170°	466.6	3.4
170°-180°	160.6	1.2
0°-30°	2619.9	18.9
0°-40°	4202.8	30.3
0°-60°	7162.3	51.7
0°-90°	8913.0	64.3
90°-120°	813.2	5.9
90°-150°	3595.6	25.9
90°-180°	4947.0	35.7
0°-180°	13860.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3502	3502	3502	3502	3502	
5°	3502	3489	3452	3478	3472	332
15°	3334	3314	3270	3283	3266	939
25°	3017	2990	2933	2940	2933	1388
35°	2603	2570	2516	2495	2478	1626
45°	2118	2095	2044	2007	1994	1635
55°	1603	1583	1542	1502	1485	1433
65°	1081	1061	1027	997	980	1069
75°	566	559	542	522	529	604
85°	138	135	132	121	118	154
90°	1	15	24	31	33	13
95°	79	39	48	54	52	94
105°	371	408	74	88	93	397
115°	702	723	753	188	100	691
125°	993	1009	1032	1040	1044	885
135°	1228	1248	1259	1271	1269	949
145°	1425	1424	1444	1453	1447	891
155°	1569	1558	1573	1580	1570	723
165°	1653	1646	1650	1658	1650	467
175°	1691	1682	1685	1694	1681	161
180°	1687	1687	1687	1687	1687	



TEST NUMBER: P907253

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3501.9	3501.9	3501.9	3501.9	3501.9
2.5°	3522.3	3505.5	3468.4	3501.9	3495.5
5°	3501.9	3488.7	3451.6	3478.4	3471.9
7.5°	3478.4	3458.4	3421.2	3448.4	3441.6
10°	3441.6	3418.0	3377.6	3404.4	3394.4
12.5°	3390.8	3370.8	3330.5	3347.2	3340.5
15°	3333.7	3313.7	3269.7	3283.3	3266.5
17.5°	3262.9	3242.9	3199.0	3215.8	3199.0
20°	3185.4	3165.4	3118.2	3128.2	3115.0
22.5°	3108.2	3077.9	3033.9	3033.9	3027.1
25°	3017.1	2990.3	2933.2	2939.6	2933.2
27.5°	2916.0	2892.4	2848.9	2838.9	2822.1
30°	2815.3	2788.1	2737.7	2727.7	2714.2
32.5°	2707.4	2687.4	2633.4	2613.1	2599.5
35°	2603.1	2569.5	2515.5	2495.2	2478.4
37.5°	2485.2	2454.8	2400.8	2377.3	2360.5
40°	2364.0	2336.9	2282.9	2252.9	2239.4
42.5°	2246.1	2219.0	2165.4	2131.5	2111.5
45°	2118.2	2094.7	2043.9	2007.1	1993.6
47.5°	1993.6	1970.0	1916.0	1878.9	1858.9
50°	1862.1	1845.3	1798.1	1751.0	1734.2
52.5°	1734.2	1710.6	1667.0	1629.9	1606.3
55°	1603.1	1582.7	1542.3	1502.0	1485.2
57.5°	1471.6	1454.8	1410.9	1370.5	1356.9
60°	1340.1	1326.9	1279.7	1242.6	1232.6
62.5°	1212.2	1188.6	1155.0	1121.5	1107.9
65°	1081.1	1060.7	1027.1	996.8	980.0
67.5°	946.4	929.3	899.2	875.7	862.1
70°	821.7	808.1	777.8	754.2	741.0
72.5°	693.8	680.2	663.4	639.9	629.9
75°	565.6	559.1	542.0	522.0	528.8
77.5°	451.2	437.7	430.9	420.9	410.9
80°	336.9	333.3	326.5	316.5	309.8
82.5°	229.0	229.0	225.8	212.2	212.2
85°	137.9	134.7	131.5	121.1	117.9
87.5°	60.7	53.9	47.2	37.2	33.6
90°	1.2	14.6	24.4	30.6	32.9
92.5°	30.6	25.7	29.3	31.8	32.9
95°	79.3	39.0	47.6	53.8	52.5
97.5°	142.8	42.8	62.2	66.0	67.1
100°	216.2	48.9	69.6	79.3	81.8
102.5°	296.7	294.3	72.1	85.4	89.2
105°	371.2	407.9	74.5	87.9	92.8
107.5°	457.9	488.3	77.0	90.3	95.3
110°	541.0	566.5	213.7	91.6	96.4



TEST NUMBER: P907253

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	619.1	641.0	620.3	94.0	97.7
115°	702.1	722.8	753.4	188.1	100.2
117.5°	774.1	798.5	819.4	644.6	324.8
120°	854.7	873.0	895.0	909.7	744.8
122.5°	923.0	942.6	967.1	974.4	975.7
125°	992.6	1008.6	1031.8	1040.3	1044.0
127.5°	1056.1	1073.2	1091.7	1103.8	1105.0
130°	1116.0	1135.6	1148.9	1162.4	1161.3
132.5°	1177.1	1193.0	1206.3	1217.4	1216.2
135°	1228.4	1248.0	1258.8	1271.2	1268.7
137.5°	1282.0	1296.7	1309.0	1321.2	1317.6
140°	1334.5	1344.4	1357.7	1368.7	1362.7
142.5°	1378.6	1387.2	1403.0	1412.7	1406.6
145°	1425.0	1423.7	1444.4	1453.0	1446.9
147.5°	1465.2	1461.5	1482.3	1488.4	1483.6
150°	1504.3	1495.8	1515.3	1522.6	1516.5
152.5°	1537.2	1527.5	1545.8	1553.2	1544.6
155°	1569.0	1558.1	1572.7	1580.0	1570.3
157.5°	1594.6	1584.9	1595.9	1604.5	1594.6
160°	1616.7	1609.3	1616.7	1623.9	1615.4
162.5°	1636.1	1628.9	1634.9	1643.5	1632.5
165°	1653.2	1646.0	1649.6	1658.1	1649.6
167.5°	1666.7	1659.3	1663.1	1671.6	1660.6
170°	1677.7	1670.3	1672.8	1681.3	1670.3
172.5°	1685.0	1677.7	1680.2	1688.7	1677.7
175°	1691.1	1682.5	1685.0	1693.5	1681.3
177.5°	1693.5	1685.0	1686.3	1694.8	1683.8
180°	1687.4	1687.4	1687.4	1687.4	1687.4



TEST NUMBER: P907253
 CATALOG NUMBER: DFN2DIP-TR3F0-090D050US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.56	14.57	14.39	15.42	16.47	13.14	14.14	13.96	14.99	16.04
	3H	15.23	16.13	16.06	16.99	18.06	14.76	15.66	15.59	16.52	17.60
	4H	15.81	16.67	16.67	17.53	18.62	15.35	16.20	16.20	17.06	18.15
	6H	16.21	17.00	17.08	17.87	18.97	15.74	16.53	16.61	17.40	18.51
	8H	16.32	17.07	17.19	17.96	19.06	15.85	16.60	16.72	17.49	18.59
	12H	16.37	17.08	17.25	17.97	19.09	15.90	16.61	16.77	17.49	18.62
4H	2H	14.04	14.89	14.90	15.76	16.85	13.70	14.55	14.55	15.41	16.50
	3H	15.91	16.62	16.78	17.52	18.62	15.52	16.23	16.39	17.13	18.23
	4H	16.62	17.27	17.50	18.16	19.29	16.22	16.87	17.10	17.76	18.89
	6H	17.14	17.70	18.03	18.61	19.75	16.73	17.29	17.63	18.21	19.34
	8H	17.28	17.81	18.18	18.72	19.87	16.88	17.40	17.78	18.31	19.46
	12H	17.36	17.83	18.28	18.76	19.91	16.94	17.42	17.86	18.35	19.50
8H	4H	16.82	17.35	17.72	18.26	19.41	16.47	16.99	17.37	17.90	19.05
	6H	17.45	17.89	18.38	18.84	19.98	17.09	17.53	18.02	18.48	19.63
	8H	17.67	18.05	18.60	19.00	20.16	17.30	17.69	18.24	18.63	19.80
	12H	17.80	18.14	18.74	19.07	20.29	17.42	17.76	18.36	18.70	19.91
12H	4H	16.82	17.29	17.74	18.22	19.37	16.47	16.94	17.39	17.87	19.02
	6H	17.48	17.87	18.42	18.81	19.97	17.13	17.52	18.07	18.46	19.63
	8H	17.72	18.06	18.66	19.00	20.21	17.37	17.71	18.31	18.65	19.86