

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920714

Luminaire Tested: DFN2DIP-TR2F0-060D030US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920714
REPORT IS A COMBINATION OF REPORTS P900240 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-060D030US935-RLLFLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6677.0 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 81.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920714

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US935-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P920714

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61
2	93	86	80	75	88	81	76	72	72	68	65	64	61	58	57	54	52
3	86	76	69	63	80	72	66	61	65	59	55	57	53	50	51	48	45
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35
6	67	55	47	41	63	52	45	40	47	41	37	42	38	34	38	34	31
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25
9	54	42	35	29	51	40	33	29	36	31	27	33	28	25	30	26	23
10	51	39	31	27	48	37	30	26	34	28	24	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4762	4762	4762
5°	4763	4676	4708
10°	4709	4574	4547
15°	4636	4412	4303
20°	4544	4194	4006
25°	4449	3952	3719
30°	4324	3704	3359
35°	4200	3438	3042
40°	4074	3164	2680
45°	3929	2863	2353
50°	3779	2559	2034
55°	3620	2236	1728
60°	3437	1899	1415
65°	3226	1559	1264
70°	2969	1241	1132
75°	2645	1073	1014
80°	2180	871	856
85°	1431	540	602

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3929 cd/sqm

TEST NUMBER: P920714

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US935-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.1	3.0
10°-20°	549.3	8.2
20°-30°	771.2	11.6
30°-40°	840.7	12.6
40°-50°	772.7	11.6
50°-60°	606.8	9.1
60°-70°	395.0	5.9
70°-80°	203.3	3.0
80°-90°	54.2	0.8
90°-100°	50.6	0.8
100°-110°	160.6	2.4
110°-120°	274.9	4.1
120°-130°	361.5	5.4
130°-140°	405.7	6.1
140°-150°	397.9	6.0
150°-160°	333.8	5.0
160°-170°	221.3	3.3
170°-180°	77.4	1.2
0°-30°	1520.7	22.8
0°-40°	2361.4	35.4
0°-60°	3740.9	56.0
0°-90°	4393.4	65.8
90°-120°	486.0	7.3
90°-150°	1651.1	24.7
90°-180°	2284.0	34.2
0°-180°	6677.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2135	2135	2135	2135	2135	
5°	2135	2126	2100	2118	2112	202
15°	2031	2009	1944	1907	1888	572
25°	1843	1782	1654	1575	1546	848
35°	1588	1490	1320	1198	1155	994
45°	1298	1169	966	829	782	1003
55°	987	837	628	512	475	882
65°	667	510	336	271	265	661
75°	356	220	154	141	139	376
85°	83	42	37	37	37	95
90°	1	9	24	23	23	7
95°	36	43	44	44	43	40
105°	148	150	152	153	153	156
115°	276	280	278	278	276	273
125°	401	407	405	403	402	358
135°	519	526	528	527	525	401
145°	630	635	639	640	637	394
155°	720	722	724	728	726	332
165°	784	783	783	788	784	221
175°	816	814	812	817	813	77
180°	817	817	817	817	817	

TEST NUMBER: P920714

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US935-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2135.1	2135.1	2135.1	2135.1	2135.1
2.5°	2144.7	2135.1	2113.7	2133.2	2129.3
5°	2135.1	2125.5	2100.2	2117.7	2111.9
7.5°	2117.7	2106.2	2079.1	2086.7	2077.1
10°	2094.5	2080.9	2042.5	2036.5	2025.0
12.5°	2065.6	2048.1	1995.9	1984.4	1963.1
15°	2030.7	2009.4	1943.8	1907.1	1887.8
17.5°	1990.2	1959.2	1878.0	1835.6	1804.7
20°	1943.8	1905.0	1808.5	1760.3	1717.7
22.5°	1893.6	1849.1	1737.0	1671.4	1642.4
25°	1843.4	1781.5	1654.0	1574.9	1545.7
27.5°	1783.6	1717.7	1576.7	1485.8	1441.4
30°	1719.8	1646.1	1491.6	1393.2	1340.9
32.5°	1657.9	1568.9	1410.7	1294.6	1246.2
35°	1588.4	1489.8	1319.8	1198.0	1155.4
37.5°	1520.7	1414.3	1234.8	1101.3	1053.1
40°	1449.1	1333.3	1145.7	1008.6	958.4
42.5°	1375.8	1252.1	1057.0	913.9	865.7
45°	1298.5	1168.9	966.2	828.8	782.5
47.5°	1225.1	1088.0	879.3	741.9	699.5
50°	1143.9	1006.8	794.2	660.7	620.3
52.5°	1064.5	919.6	713.0	585.5	548.8
55°	987.3	836.6	627.9	512.1	475.4
57.5°	908.2	753.5	552.7	444.4	413.5
60°	827.0	672.4	473.4	375.0	344.0
62.5°	747.9	593.3	405.7	313.1	297.6
65°	666.7	510.1	336.2	270.6	264.7
67.5°	589.4	432.7	270.6	237.6	231.9
70°	508.2	357.5	224.0	204.8	197.0
72.5°	430.9	287.8	187.4	172.0	168.1
75°	355.5	220.2	154.5	141.0	139.2
77.5°	280.3	156.4	121.7	114.0	110.1
80°	210.5	112.1	92.6	85.1	85.1
82.5°	146.8	75.4	63.7	59.8	59.8
85°	83.0	42.4	36.7	36.7	36.7
87.5°	31.0	15.4	15.4	13.5	13.5
90°	0.8	8.9	24.1	22.6	23.4
92.5°	15.2	20.7	21.4	22.1	22.1
95°	36.0	42.9	44.1	44.1	42.9
97.5°	59.8	66.2	69.0	69.0	69.0
100°	87.4	93.1	95.1	95.1	94.4
102.5°	116.5	120.7	123.4	124.2	123.4
105°	148.3	150.2	151.7	152.9	152.9
107.5°	179.8	182.7	182.7	183.2	179.8
110°	210.3	214.3	214.3	214.3	212.3



TEST NUMBER: P920714

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	243.3	247.5	246.8	244.8	243.3
115°	275.9	279.7	278.5	277.8	275.9
117.5°	308.1	313.5	310.0	308.1	306.1
120°	340.6	346.0	340.6	340.6	338.4
122.5°	370.1	377.0	373.6	371.6	370.1
125°	401.2	407.3	405.4	403.1	402.4
127.5°	431.4	439.1	436.4	433.4	431.4
130°	459.8	468.6	467.4	466.0	463.2
132.5°	491.5	498.4	498.9	495.5	493.5
135°	518.9	526.5	528.0	527.3	525.3
137.5°	549.4	555.6	556.8	556.4	553.4
140°	576.3	582.5	585.9	585.9	583.2
142.5°	603.9	610.0	612.0	612.8	610.0
145°	630.0	634.9	638.9	639.5	636.9
147.5°	653.4	659.5	662.5	663.7	661.0
150°	677.5	681.7	684.4	686.6	684.4
152.5°	699.0	703.1	706.5	709.3	706.5
155°	720.4	722.3	724.5	728.0	725.8
157.5°	738.8	740.3	741.6	746.5	743.0
160°	755.4	756.8	757.6	761.7	758.8
162.5°	770.6	770.6	771.4	776.0	772.6
165°	783.7	782.9	782.9	787.8	784.4
167.5°	795.5	793.2	793.2	798.1	794.7
170°	804.3	802.4	801.7	806.6	802.4
172.5°	810.5	808.6	807.8	812.7	808.6
175°	815.5	813.5	812.0	816.9	812.7
177.5°	818.1	816.1	814.7	818.9	814.7
180°	816.9	816.9	816.9	816.9	816.9

TEST NUMBER: P920714

CATALOG NUMBER: DFN2DIP-TR2F0-060D030US935-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.80	14.78	14.62	15.61	16.64	9.78	10.76	10.60	11.59	12.62
	3H	15.47	16.34	16.29	17.18	18.24	10.97	11.84	11.80	12.69	13.74
	4H	16.07	16.89	16.91	17.74	18.81	11.41	12.24	12.26	13.09	14.16
	6H	16.48	17.24	17.33	18.09	19.17	11.73	12.49	12.59	13.35	14.43
	8H	16.60	17.32	17.46	18.19	19.28	11.82	12.54	12.68	13.41	14.50
	12H	16.65	17.34	17.52	18.21	19.32	11.86	12.55	12.73	13.41	14.52
4H	2H	13.83	14.66	14.68	15.51	16.58	10.38	11.21	11.23	12.06	13.13
	3H	15.65	16.33	16.51	17.22	18.30	11.73	12.41	12.59	13.30	14.38
	4H	16.33	16.95	17.20	17.83	18.94	12.27	12.89	13.14	13.77	14.88
	6H	16.83	17.37	17.72	18.27	19.38	12.68	13.22	13.57	14.12	15.23
	8H	16.99	17.50	17.89	18.39	19.52	12.80	13.30	13.69	14.20	15.33
	12H	17.08	17.53	17.99	18.45	19.58	12.86	13.31	13.77	14.23	15.36
8H	4H	16.30	16.80	17.20	17.70	18.83	12.54	13.05	13.44	13.95	15.07
	6H	16.85	17.26	17.77	18.20	19.33	13.05	13.46	13.97	14.40	15.53
	8H	17.05	17.42	17.98	18.35	19.49	13.23	13.59	14.15	14.53	15.67
	12H	17.18	17.50	18.11	18.43	19.62	13.34	13.66	14.27	14.59	15.78
12H	4H	16.26	16.71	17.17	17.63	18.76	12.55	13.00	13.46	13.92	15.05
	6H	16.82	17.19	17.75	18.12	19.27	13.09	13.46	14.02	14.39	15.53
	8H	17.03	17.36	17.96	18.28	19.48	13.29	13.62	14.22	14.54	15.74