

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923398

Luminaire Tested: DFN2DIP-TR2F0-040D020US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923398
REPORT IS A COMBINATION OF REPORTS P900226 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-040D020US940-RLLFLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4610.1 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923398

CATALOG NUMBER: DFN2DIP-TR2F0-040D020US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P923398

CATALOG NUMBER: DFN2DIP-TR2F0-040D020US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61
2	93	86	80	75	88	81	76	72	72	68	65	64	61	58	57	54	52
3	86	76	69	63	80	72	66	61	65	59	55	57	53	50	51	48	45
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35
6	67	55	47	41	63	52	45	40	47	41	37	42	38	34	38	34	31
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25
9	54	42	35	29	51	40	33	29	36	31	27	33	28	25	30	26	23
10	51	39	31	27	48	37	30	26	34	28	24	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3288	3288	3288
5°	3288	3228	3251
10°	3251	3158	3140
15°	3201	3046	2971
20°	3137	2896	2766
25°	3071	2728	2568
30°	2985	2557	2319
35°	2900	2374	2100
40°	2813	2185	1851
45°	2713	1977	1625
50°	2609	1767	1404
55°	2500	1543	1193
60°	2373	1311	977
65°	2227	1076	873
70°	2050	857	782
75°	1826	741	700
80°	1505	601	591
85°	988	373	415

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2713 cd/sqm

TEST NUMBER: P923398

CATALOG NUMBER: DFN2DIP-TR2F0-040D020US940-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.2	3.0
10°-20°	379.3	8.2
20°-30°	532.5	11.6
30°-40°	580.5	12.6
40°-50°	533.5	11.6
50°-60°	419.0	9.1
60°-70°	272.7	5.9
70°-80°	140.4	3.0
80°-90°	37.4	0.8
90°-100°	34.9	0.8
100°-110°	110.9	2.4
110°-120°	189.8	4.1
120°-130°	249.6	5.4
130°-140°	280.2	6.1
140°-150°	274.7	6.0
150°-160°	230.4	5.0
160°-170°	152.8	3.3
170°-180°	53.4	1.2
0°-30°	1049.9	22.8
0°-40°	1630.4	35.4
0°-60°	2582.9	56.0
0°-90°	3033.4	65.8
90°-120°	335.6	7.3
90°-150°	1140.0	24.7
90°-180°	1577.0	34.2
0°-180°	4610.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1474	1474	1474	1474	1474	
5°	1474	1468	1450	1462	1458	140
15°	1402	1387	1342	1317	1304	395
25°	1273	1230	1142	1087	1067	585
35°	1097	1029	911	827	798	686
45°	896	807	667	572	540	692
55°	682	578	434	354	328	609
65°	460	352	232	187	183	456
75°	245	152	107	97	96	260
85°	57	29	25	25	25	66
90°	0	6	17	16	16	5
95°	25	30	30	30	30	28
105°	102	104	105	106	106	108
115°	190	193	192	192	190	188
125°	277	281	280	278	278	248
135°	358	364	364	364	363	277
145°	435	438	441	442	440	272
155°	497	499	500	503	501	229
165°	541	541	541	544	542	153
175°	563	562	561	564	561	53
180°	564	564	564	564	564	

TEST NUMBER: P923398

CATALOG NUMBER: DFN2DIP-TR2F0-040D020US940-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1474.2	1474.2	1474.2	1474.2	1474.2
2.5°	1480.9	1474.2	1459.5	1472.9	1470.2
5°	1474.2	1467.5	1450.1	1462.1	1458.2
7.5°	1462.1	1454.2	1435.6	1440.7	1434.1
10°	1446.2	1436.8	1410.2	1406.0	1398.2
12.5°	1426.2	1414.2	1378.0	1370.1	1355.4
15°	1402.1	1387.4	1342.1	1316.8	1303.5
17.5°	1374.1	1352.7	1296.6	1267.4	1246.0
20°	1342.1	1315.4	1248.7	1215.4	1186.0
22.5°	1307.4	1276.8	1199.3	1154.0	1134.1
25°	1272.7	1230.0	1141.9	1087.4	1067.2
27.5°	1231.5	1186.0	1088.6	1025.9	995.1
30°	1187.4	1136.6	1029.8	961.9	925.9
32.5°	1144.7	1083.2	973.9	893.9	860.4
35°	1096.7	1028.6	911.2	827.2	797.7
37.5°	1050.0	976.5	852.5	760.4	727.1
40°	1000.6	920.6	791.1	696.4	661.7
42.5°	949.8	864.5	729.8	631.0	597.7
45°	896.5	807.1	667.1	572.3	540.3
47.5°	845.9	751.2	607.1	512.3	483.0
50°	789.8	695.1	548.3	456.2	428.3
52.5°	735.0	635.0	492.3	404.2	378.9
55°	681.7	577.6	433.5	353.6	328.2
57.5°	627.1	520.3	381.6	306.8	285.5
60°	571.0	464.2	326.8	258.9	237.6
62.5°	516.4	409.7	280.1	216.2	205.5
65°	460.3	352.1	232.1	186.8	182.7
67.5°	407.0	298.8	186.8	164.1	160.1
70°	350.9	246.8	154.7	141.4	136.0
72.5°	297.6	198.8	129.4	118.8	116.1
75°	245.4	152.0	106.7	97.4	96.1
77.5°	193.5	108.0	84.1	78.7	76.0
80°	145.3	77.4	63.9	58.8	58.8
82.5°	101.4	52.1	44.1	41.3	41.3
85°	57.3	29.3	25.3	25.3	25.3
87.5°	21.4	10.6	10.6	9.4	9.4
90°	0.5	6.2	16.7	15.6	16.1
92.5°	10.5	14.3	14.8	15.3	15.3
95°	24.8	29.6	30.4	30.4	29.6
97.5°	41.3	45.7	47.6	47.6	47.6
100°	60.4	64.3	65.6	65.6	65.1
102.5°	80.4	83.3	85.2	85.7	85.2
105°	102.4	103.7	104.8	105.6	105.6
107.5°	124.1	126.2	126.2	126.5	124.1
110°	145.3	147.9	147.9	147.9	146.6



TEST NUMBER: P923398

CATALOG NUMBER: DFN2DIP-TR2F0-040D020US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	168.0	170.9	170.4	169.0	168.0
115°	190.5	193.1	192.3	191.8	190.5
117.5°	212.8	216.5	214.1	212.8	211.3
120°	235.1	238.9	235.1	235.1	233.6
122.5°	255.6	260.3	258.0	256.6	255.6
125°	277.0	281.2	279.9	278.4	277.9
127.5°	297.9	303.2	301.3	299.3	297.9
130°	317.4	323.6	322.7	321.7	319.9
132.5°	339.4	344.2	344.5	342.1	340.7
135°	358.3	363.6	364.5	364.1	362.7
137.5°	379.3	383.6	384.5	384.1	382.1
140°	397.9	402.2	404.6	404.6	402.7
142.5°	417.0	421.2	422.6	423.0	421.2
145°	435.0	438.4	441.1	441.6	439.7
147.5°	451.1	455.4	457.4	458.2	456.4
150°	467.8	470.6	472.5	474.0	472.5
152.5°	482.6	485.4	487.9	489.7	487.9
155°	497.4	498.7	500.2	502.7	501.1
157.5°	510.1	511.1	512.0	515.4	513.0
160°	521.6	522.5	523.1	525.9	523.9
162.5°	532.1	532.1	532.5	535.8	533.4
165°	541.1	540.6	540.6	543.9	541.6
167.5°	549.2	547.7	547.7	551.1	548.8
170°	555.4	554.0	553.5	556.9	554.0
172.5°	559.6	558.2	557.8	561.2	558.2
175°	563.0	561.7	560.6	564.0	561.2
177.5°	564.9	563.6	562.5	565.3	562.5
180°	564.0	564.0	564.0	564.0	564.0

TEST NUMBER: P923398

CATALOG NUMBER: DFN2DIP-TR2F0-040D020US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.51	13.49	13.33	14.33	15.35	8.49	9.47	9.31	10.31	11.34
	3H	14.18	15.05	15.01	15.90	16.96	9.68	10.56	10.51	11.40	12.46
	4H	14.78	15.60	15.62	16.45	17.52	10.13	10.95	10.97	11.80	12.87
	6H	15.19	15.95	16.05	16.81	17.89	10.44	11.20	11.30	12.06	13.14
	8H	15.31	16.03	16.18	16.91	17.99	10.53	11.25	11.40	12.13	13.21
	12H	15.37	16.05	16.24	16.92	18.03	10.57	11.26	11.44	12.13	13.23
4H	2H	12.55	13.37	13.40	14.22	15.29	9.10	9.92	9.95	10.77	11.84
	3H	14.36	15.05	15.22	15.93	17.01	10.44	11.13	11.30	12.01	13.09
	4H	15.04	15.66	15.92	16.55	17.66	10.98	11.60	11.86	12.48	13.60
	6H	15.54	16.08	16.43	16.98	18.10	11.39	11.93	12.28	12.83	13.95
	8H	15.71	16.21	16.60	17.11	18.23	11.51	12.02	12.41	12.91	14.04
	12H	15.80	16.25	16.71	17.17	18.30	11.58	12.03	12.49	12.95	14.08
8H	4H	15.02	15.52	15.91	16.42	17.54	11.26	11.76	12.15	12.66	13.79
	6H	15.56	15.98	16.48	16.92	18.04	11.76	12.17	12.68	13.12	14.24
	8H	15.76	16.13	16.69	17.06	18.21	11.94	12.31	12.87	13.24	14.38
	12H	15.89	16.22	16.82	17.14	18.34	12.05	12.37	12.98	13.30	14.50
12H	4H	14.97	15.43	15.89	16.34	17.48	11.27	11.72	12.18	12.64	13.77
	6H	15.54	15.90	16.47	16.84	17.98	11.80	12.17	12.73	13.10	14.25
	8H	15.75	16.07	16.68	17.00	18.19	12.01	12.33	12.94	13.25	14.45