

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923407

Luminaire Tested: DFN2DIP-TR2F0-040D040US940-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923407
REPORT IS A COMBINATION OF REPORTS P901766 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-040D040US940-RLLONL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6188.5 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 65.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923407
CATALOG NUMBER: DFN2DIP-TR2F0-040D040US940-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P923407

CATALOG NUMBER: DFN2DIP-TR2F0-040D040US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49			49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42			42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36			36
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35	31			31
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31	27			27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24			24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24	21			21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19			19
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17			17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	16			16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14			14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3288	3288	3288
5°	3288	3228	3251
10°	3251	3158	3140
15°	3201	3046	2971
20°	3137	2896	2766
25°	3071	2728	2568
30°	2985	2557	2319
35°	2900	2374	2100
40°	2813	2185	1851
45°	2713	1977	1625
50°	2609	1767	1404
55°	2500	1543	1193
60°	2373	1311	977
65°	2227	1076	873
70°	2050	857	782
75°	1826	741	700
80°	1505	601	591
85°	988	373	415

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2713 cd/sqm



TEST NUMBER: P923407

CATALOG NUMBER: DFN2DIP-TR2F0-040D040US940-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.2	2.2
10°-20°	379.3	6.1
20°-30°	532.5	8.6
30°-40°	580.5	9.4
40°-50°	533.5	8.6
50°-60°	419.0	6.8
60°-70°	272.7	4.4
70°-80°	140.4	2.3
80°-90°	39.0	0.6
90°-100°	69.8	1.1
100°-110°	221.8	3.6
110°-120°	379.5	6.1
120°-130°	499.2	8.1
130°-140°	560.3	9.1
140°-150°	549.4	8.9
150°-160°	460.9	7.4
160°-170°	305.7	4.9
170°-180°	106.8	1.7
0°-30°	1049.9	17.0
0°-40°	1630.4	26.3
0°-60°	2582.9	41.7
0°-90°	3035.0	49.0
90°-120°	671.2	10.8
90°-150°	2280.1	36.8
90°-180°	3153.0	50.9
0°-180°	6188.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1474	1474	1474	1474	1474	
5°	1474	1468	1450	1462	1458	140
15°	1402	1387	1342	1317	1304	395
25°	1273	1230	1142	1087	1067	585
35°	1097	1029	911	827	798	686
45°	896	807	667	572	540	692
55°	682	578	434	354	328	609
65°	460	352	232	187	183	456
75°	245	152	107	97	96	260
85°	57	29	25	25	25	66
90°	1	12	33	31	32	6
95°	50	59	61	61	59	55
105°	205	207	210	211	211	216
115°	381	386	385	384	381	377
125°	554	562	560	557	556	495
135°	717	727	729	728	725	554
145°	870	877	882	883	880	544
155°	995	998	1000	1005	1002	458
165°	1082	1081	1081	1088	1083	305
175°	1126	1123	1121	1128	1122	107
180°	1128	1128	1128	1128	1128	



TEST NUMBER: P923407

CATALOG NUMBER: DFN2DIP-TR2F0-040D040US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1474.2	1474.2	1474.2	1474.2	1474.2
2.5°	1480.9	1474.2	1459.5	1472.9	1470.2
5°	1474.2	1467.5	1450.1	1462.1	1458.2
7.5°	1462.1	1454.2	1435.6	1440.7	1434.1
10°	1446.2	1436.8	1410.2	1406.0	1398.2
12.5°	1426.2	1414.2	1378.0	1370.1	1355.4
15°	1402.1	1387.4	1342.1	1316.8	1303.5
17.5°	1374.1	1352.7	1296.6	1267.4	1246.0
20°	1342.1	1315.4	1248.7	1215.4	1186.0
22.5°	1307.4	1276.8	1199.3	1154.0	1134.1
25°	1272.7	1230.0	1141.9	1087.4	1067.2
27.5°	1231.5	1186.0	1088.6	1025.9	995.1
30°	1187.4	1136.6	1029.8	961.9	925.9
32.5°	1144.7	1083.2	973.9	893.9	860.4
35°	1096.7	1028.6	911.2	827.2	797.7
37.5°	1050.0	976.5	852.5	760.4	727.1
40°	1000.6	920.6	791.1	696.4	661.7
42.5°	949.8	864.5	729.8	631.0	597.7
45°	896.5	807.1	667.1	572.3	540.3
47.5°	845.9	751.2	607.1	512.3	483.0
50°	789.8	695.1	548.3	456.2	428.3
52.5°	735.0	635.0	492.3	404.2	378.9
55°	681.7	577.6	433.5	353.6	328.2
57.5°	627.1	520.3	381.6	306.8	285.5
60°	571.0	464.2	326.8	258.9	237.6
62.5°	516.4	409.7	280.1	216.2	205.5
65°	460.3	352.1	232.1	186.8	182.7
67.5°	407.0	298.8	186.8	164.1	160.1
70°	350.9	246.8	154.7	141.4	136.0
72.5°	297.6	198.8	129.4	118.8	116.1
75°	245.4	152.0	106.7	97.4	96.1
77.5°	193.5	108.0	84.1	78.7	76.0
80°	145.3	77.4	63.9	58.8	58.8
82.5°	101.4	52.1	44.1	41.3	41.3
85°	57.3	29.3	25.3	25.3	25.3
87.5°	21.4	10.6	10.6	9.4	9.4
90°	1.0	12.2	33.3	31.3	32.3
92.5°	21.0	28.5	29.6	30.6	30.6
95°	49.7	59.2	60.9	60.9	59.2
97.5°	82.7	91.5	95.2	95.2	95.2
100°	120.7	128.6	131.3	131.3	130.3
102.5°	160.9	166.7	170.4	171.4	170.4
105°	204.7	207.4	209.5	211.2	211.2
107.5°	248.3	252.4	252.4	253.0	248.3
110°	290.4	295.9	295.9	295.9	293.2



TEST NUMBER: P923407

CATALOG NUMBER: DFN2DIP-TR2F0-040D040US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	336.0	341.8	340.7	338.0	336.0
115°	380.8	386.4	384.6	383.6	380.8
117.5°	425.4	432.9	428.2	425.4	422.8
120°	470.4	477.8	470.4	470.4	467.3
122.5°	511.1	520.7	515.9	513.2	511.1
125°	554.0	562.5	559.8	556.7	555.7
127.5°	595.8	606.4	602.6	598.5	595.8
130°	634.9	647.2	645.5	643.5	639.7
132.5°	678.8	688.3	689.0	684.2	681.5
135°	716.6	727.1	729.2	728.1	725.4
137.5°	758.8	767.2	768.9	768.2	764.2
140°	795.8	804.3	809.0	809.0	805.3
142.5°	833.9	842.4	845.1	846.1	842.4
145°	870.0	876.7	882.2	883.2	879.5
147.5°	902.2	910.7	914.8	916.5	912.8
150°	935.6	941.4	945.1	948.2	945.1
152.5°	965.2	970.9	975.7	979.5	975.7
155°	994.7	997.5	1000.5	1005.3	1002.2
157.5°	1020.3	1022.3	1024.0	1030.8	1026.0
160°	1043.0	1045.1	1046.1	1051.9	1047.8
162.5°	1064.1	1064.1	1065.1	1071.6	1066.8
165°	1082.2	1081.1	1081.1	1087.9	1083.2
167.5°	1098.5	1095.4	1095.4	1102.2	1097.4
170°	1110.7	1108.0	1107.0	1113.7	1108.0
172.5°	1119.2	1116.5	1115.4	1122.3	1116.5
175°	1126.1	1123.3	1121.2	1128.0	1122.3
177.5°	1129.8	1127.0	1125.0	1130.8	1125.0
180°	1128.0	1128.0	1128.0	1128.0	1128.0



TEST NUMBER: P923407
 CATALOG NUMBER: DFN2DIP-TR2F0-040D040US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.06	11.88	12.03	12.87	14.15	7.04	7.87	8.01	8.85	10.13
	3H	12.72	13.45	13.70	14.44	15.75	8.22	8.95	9.20	9.94	11.25
	4H	13.31	14.00	14.30	15.00	16.32	8.66	9.35	9.65	10.34	11.66
	6H	13.71	14.35	14.72	15.35	16.68	8.96	9.60	9.97	10.60	11.93
	8H	13.83	14.43	14.84	15.45	16.78	9.05	9.65	10.06	10.67	12.00
	12H	13.88	14.46	14.89	15.46	16.82	9.08	9.66	10.10	10.67	12.02
4H	2H	11.08	11.77	12.08	12.76	14.08	7.62	8.32	8.63	9.31	10.63
	3H	12.88	13.46	13.89	14.48	15.81	8.96	9.53	9.97	10.56	11.89
	4H	13.55	14.08	14.57	15.09	16.45	9.49	10.02	10.51	11.03	12.39
	6H	14.04	14.50	15.07	15.54	16.89	9.89	10.35	10.92	11.39	12.74
	8H	14.20	14.63	15.24	15.66	17.03	10.01	10.44	11.04	11.47	12.83
	12H	14.29	14.67	15.33	15.72	17.09	10.07	10.45	11.12	11.50	12.87
8H	4H	13.51	13.94	14.54	14.97	16.34	9.76	10.18	10.79	11.21	12.58
	6H	14.05	14.40	15.11	15.48	16.84	10.25	10.60	11.31	11.68	13.04
	8H	14.26	14.56	15.32	15.62	17.00	10.43	10.74	11.49	11.80	13.18
	12H	14.38	14.65	15.44	15.70	17.13	10.54	10.81	11.60	11.86	13.29
12H	4H	13.46	13.85	14.51	14.89	16.26	9.76	10.14	10.80	11.19	12.56
	6H	14.03	14.34	15.09	15.39	16.78	10.30	10.60	11.36	11.66	13.04
	8H	14.23	14.50	15.30	15.56	16.98	10.49	10.76	11.56	11.81	13.24