

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909844

Luminaire Tested: DFN2DIP-TR3F0-040D030US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909844
REPORT IS A COMBINATION OF REPORTS P900274 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-040D030US840-RLLFLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6114.7 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909844

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P909844

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		74	74	74		62	62	62
1	100	96	92	88		93	89	86	83		77	75	72		66	64	63		55	54	53
2	91	84	78	73		85	79	73	69		68	64	61		58	56	53		49	47	46
3	84	74	67	62		78	70	63	58		61	56	52		52	49	46		44	42	40
4	77	66	59	53		71	62	55	50		54	49	45		47	43	40		40	37	35
5	71	59	51	46		66	56	49	43		49	43	39		42	38	35		36	33	30
6	65	53	46	40		61	50	43	38		44	38	34		38	34	31		33	30	27
7	61	48	41	35		56	46	39	34		40	35	30		35	31	27		30	27	24
8	56	44	37	31		52	42	35	30		37	31	27		32	28	25		28	25	22
9	53	41	33	28		49	38	32	27		34	28	25		30	25	22		26	23	20
10	49	37	30	25		46	35	29	24		31	26	22		28	23	20		24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2080	2080	2080
5°	2083	2046	2059
10°	2061	2004	1991
15°	2031	1936	1886
20°	1993	1843	1758
25°	1953	1739	1634
30°	1900	1633	1477
35°	1848	1519	1340
40°	1796	1401	1183
45°	1734	1270	1040
50°	1671	1138	901
55°	1605	998	767
60°	1528	851	630
65°	1439	702	566
70°	1332	564	510
75°	1197	493	461
80°	1001	408	396
85°	681	264	289

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1734 cd/sqm

TEST NUMBER: P909844

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US840-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.5	2.6
10°-20°	429.5	7.0
20°-30°	603.0	9.9
30°-40°	657.4	10.8
40°-50°	604.2	9.9
50°-60°	474.5	7.8
60°-70°	308.9	5.1
70°-80°	159.0	2.6
80°-90°	43.3	0.7
90°-100°	59.3	1.0
100°-110°	188.4	3.1
110°-120°	322.4	5.3
120°-130°	424.0	6.9
130°-140°	475.9	7.8
140°-150°	466.7	7.6
150°-160°	391.5	6.4
160°-170°	259.6	4.2
170°-180°	90.7	1.5
0°-30°	1189.0	19.4
0°-40°	1846.4	30.2
0°-60°	2925.1	47.8
0°-90°	3436.3	56.2
90°-120°	570.1	9.3
90°-150°	1936.6	31.7
90°-180°	2678.0	43.8
0°-180°	6114.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1670	1670	1670	1670	1670	
5°	1670	1662	1642	1656	1651	158
15°	1588	1571	1520	1491	1476	447
25°	1441	1393	1293	1231	1209	663
35°	1242	1165	1032	937	903	777
45°	1015	914	756	648	612	784
55°	772	654	491	400	372	690
65°	521	399	263	212	207	517
75°	278	172	121	110	109	294
85°	65	33	29	29	29	75
90°	1	10	28	27	28	6
95°	42	50	52	52	50	47
105°	174	176	178	179	179	184
115°	324	328	327	326	324	320
125°	471	478	475	473	472	420
135°	609	618	619	618	616	470
145°	739	745	749	750	747	462
155°	845	847	850	854	851	389
165°	919	918	918	924	920	259
175°	956	954	952	958	953	91
180°	958	958	958	958	958	

TEST NUMBER: P909844

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US840-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1669.5	1669.5	1669.5	1669.5	1669.5
2.5°	1677.1	1669.5	1652.8	1668.1	1665.0
5°	1669.5	1661.9	1642.2	1655.9	1651.4
7.5°	1655.9	1646.9	1625.8	1631.6	1624.2
10°	1637.8	1627.2	1597.0	1592.4	1583.5
12.5°	1615.2	1601.5	1560.6	1551.7	1535.0
15°	1587.9	1571.2	1519.9	1491.3	1476.2
17.5°	1556.2	1532.0	1468.4	1435.3	1411.1
20°	1519.9	1489.7	1414.1	1376.4	1343.1
22.5°	1480.7	1445.9	1358.2	1306.9	1284.3
25°	1441.4	1393.0	1293.2	1231.4	1208.6
27.5°	1394.6	1343.1	1232.8	1161.9	1127.0
30°	1344.7	1287.2	1166.3	1089.3	1048.5
32.5°	1296.4	1226.8	1103.0	1012.3	974.4
35°	1242.0	1164.9	1032.0	936.8	903.4
37.5°	1189.1	1105.9	965.4	861.1	823.4
40°	1133.2	1042.6	896.0	788.7	749.4
42.5°	1075.7	979.1	826.5	714.6	676.9
45°	1015.3	914.0	755.5	648.1	611.9
47.5°	958.0	850.7	687.5	580.2	546.9
50°	894.4	787.2	621.0	516.6	485.0
52.5°	832.4	719.1	557.5	457.8	429.1
55°	772.0	654.2	491.0	400.4	371.7
57.5°	710.1	589.3	432.1	347.5	323.4
60°	646.6	525.7	370.1	293.2	269.0
62.5°	584.8	463.9	317.2	244.8	232.8
65°	521.3	398.8	262.9	211.6	206.9
67.5°	460.9	338.4	211.6	185.8	181.3
70°	397.4	279.5	175.2	160.2	154.0
72.5°	337.0	225.1	146.5	134.5	131.5
75°	277.9	172.2	120.9	110.3	108.9
77.5°	219.1	122.3	95.2	89.2	86.0
80°	164.6	87.7	72.4	66.6	66.6
82.5°	114.8	59.0	49.9	46.8	46.8
85°	64.9	33.2	28.7	28.7	28.7
87.5°	24.2	12.0	12.0	10.6	10.6
90°	0.9	10.4	28.3	26.6	27.5
92.5°	17.9	24.2	25.1	26.0	26.0
95°	42.2	50.3	51.7	51.7	50.3
97.5°	70.2	77.7	80.9	80.9	80.9
100°	102.5	109.2	111.5	111.5	110.7
102.5°	136.6	141.6	144.7	145.6	144.7
105°	173.9	176.2	177.9	179.4	179.4
107.5°	210.9	214.3	214.3	214.9	210.9
110°	246.7	251.4	251.4	251.4	249.0



TEST NUMBER: P909844

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US840-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	285.4	290.3	289.4	287.1	285.4
115°	323.6	328.1	326.7	325.9	323.6
117.5°	361.3	367.7	363.7	361.3	359.0
120°	399.5	405.9	399.5	399.5	396.9
122.5°	434.1	442.2	438.2	435.9	434.1
125°	470.6	477.8	475.4	472.8	472.0
127.5°	506.0	515.0	511.9	508.4	506.0
130°	539.3	549.7	548.3	546.5	543.3
132.5°	576.5	584.6	585.2	581.2	578.9
135°	608.6	617.5	619.4	618.4	616.1
137.5°	644.4	651.7	653.1	652.6	649.0
140°	675.9	683.2	687.2	687.2	684.0
142.5°	708.3	715.5	717.8	718.7	715.5
145°	738.9	744.7	749.3	750.1	747.0
147.5°	766.4	773.6	777.0	778.5	775.3
150°	794.7	799.6	802.7	805.4	802.7
152.5°	819.8	824.7	828.7	831.9	828.7
155°	845.0	847.2	849.8	853.8	851.3
157.5°	866.6	868.3	869.8	875.6	871.5
160°	886.0	887.7	888.6	893.4	890.0
162.5°	903.8	903.8	904.7	910.2	906.2
165°	919.2	918.3	918.3	924.0	920.0
167.5°	933.0	930.4	930.4	936.1	932.1
170°	943.4	941.1	940.3	946.0	941.1
172.5°	950.6	948.4	947.5	953.2	948.4
175°	956.4	954.1	952.4	958.2	953.2
177.5°	959.6	957.3	955.5	960.5	955.5
180°	958.2	958.2	958.2	958.2	958.2

TEST NUMBER: P909844

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.20	11.08	11.11	12.01	13.19	6.18	7.06	7.08	7.98	9.17
	3H	11.87	12.66	12.79	13.59	14.80	7.36	8.15	8.28	9.09	10.29
	4H	12.48	13.22	13.41	14.16	15.38	7.81	8.56	8.75	9.50	10.71
	6H	12.89	13.58	13.84	14.52	15.75	8.13	8.82	9.08	9.76	10.99
	8H	13.02	13.67	13.97	14.63	15.86	8.22	8.87	9.18	9.84	11.06
	12H	13.08	13.70	14.04	14.65	15.90	8.26	8.89	9.22	9.84	11.09
4H	2H	10.22	10.97	11.16	11.91	13.12	6.77	7.52	7.71	8.46	9.67
	3H	12.05	12.67	13.00	13.63	14.87	8.12	8.74	9.07	9.71	10.94
	4H	12.73	13.30	13.69	14.26	15.52	8.67	9.23	9.63	10.19	11.45
	6H	13.24	13.73	14.22	14.71	15.97	9.08	9.57	10.06	10.56	11.81
	8H	13.41	13.87	14.39	14.85	16.12	9.21	9.66	10.19	10.64	11.91
	12H	13.51	13.91	14.50	14.91	16.18	9.27	9.68	10.27	10.68	11.95
8H	4H	12.70	13.16	13.68	14.14	15.41	8.95	9.40	9.92	10.38	11.65
	6H	13.26	13.64	14.26	14.66	15.93	9.46	9.83	10.46	10.85	12.12
	8H	13.47	13.80	14.48	14.81	16.10	9.64	9.98	10.65	10.99	12.27
	12H	13.61	13.90	14.62	14.90	16.23	9.76	10.05	10.77	11.06	12.39
12H	4H	12.66	13.07	13.65	14.06	15.34	8.95	9.36	9.94	10.36	11.63
	6H	13.24	13.57	14.25	14.58	15.86	9.50	9.84	10.51	10.85	12.13
	8H	13.45	13.74	14.46	14.75	16.08	9.71	10.00	10.72	11.01	12.34

END OF REPORT