

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909885

Luminaire Tested: DFN2DIP-TR3F0-050D070US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909885
REPORT IS A COMBINATION OF REPORTS P901851 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-050D070US840-FLLONL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11997.2 lumens
Efficiency: N/A
Efficacy: 121.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 98.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909885

CATALOG NUMBER: DFN2DIP-TR3F0-050D070US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P909885

CATALOG NUMBER: DFN2DIP-TR3F0-050D070US840-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	88	84	87	84	80	78	69	67	65	55	54	52	43	42	41
2	87	80	74	69	79	73	68	64	60	57	53	49	46	44	38	36	34
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29
4	73	62	54	48	66	57	50	45	47	42	38	38	35	32	30	27	25
5	67	55	47	41	61	51	44	39	42	37	33	34	30	27	27	24	22
6	62	50	42	36	56	46	39	33	38	33	29	31	27	24	24	22	19
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	20	18	15
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2448	2448	2448
5°	2451	2412	2429
10°	2430	2378	2394
15°	2393	2336	2341
20°	2343	2280	2287
25°	2293	2213	2225
30°	2232	2150	2146
35°	2173	2077	2062
40°	2102	2002	1983
45°	2030	1928	1901
50°	1952	1850	1807
55°	1869	1759	1720
60°	1776	1651	1621
65°	1675	1540	1503
70°	1545	1404	1377
75°	1366	1241	1257
80°	1150	1032	1033
85°	813	679	667

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2030 cd/sqm

TEST NUMBER: P909885

CATALOG NUMBER: DFN2DIP-TR3F0-050D070US840-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.9	1.5
10°-20°	520.3	4.3
20°-30°	764.6	6.4
30°-40°	888.1	7.4
40°-50°	887.0	7.4
50°-60°	773.4	6.4
60°-70°	571.7	4.8
70°-80°	323.5	2.7
80°-90°	89.6	0.7
90°-100°	78.7	0.7
100°-110°	293.3	2.4
110°-120°	777.8	6.5
120°-130°	1290.0	10.8
130°-140°	1370.3	11.4
140°-150°	1273.5	10.6
150°-160°	1023.9	8.5
160°-170°	659.7	5.5
170°-180°	227.1	1.9
0°-30°	1469.8	12.3
0°-40°	2357.9	19.7
0°-60°	4018.3	33.5
0°-90°	5003.0	41.7
90°-120°	1149.7	9.6
90°-150°	5083.5	42.4
90°-180°	6994.0	58.3
0°-180°	11997.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1965	1965	1965	1965	1965	
5°	1965	1957	1936	1952	1948	187
15°	1870	1859	1834	1842	1833	527
25°	1693	1678	1646	1649	1646	779
35°	1460	1442	1411	1400	1390	912
45°	1188	1175	1147	1126	1118	917
55°	899	888	865	843	833	804
65°	606	595	576	559	550	600
75°	317	314	304	293	297	339
85°	77	76	74	68	66	86
90°	2	21	34	43	47	11
95°	112	55	67	76	74	133
105°	525	577	105	124	131	561
115°	993	1022	1065	266	142	977
125°	1403	1426	1459	1471	1476	1252
135°	1737	1764	1780	1797	1794	1342
145°	2015	2013	2042	2054	2046	1260
155°	2218	2203	2224	2234	2220	1022
165°	2337	2327	2332	2344	2332	660
175°	2391	2379	2382	2394	2377	228
180°	2386	2386	2386	2386	2386	

TEST NUMBER: P909885

CATALOG NUMBER: DFN2DIP-TR3F0-050D070US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1964.7	1964.7	1964.7	1964.7	1964.7
2.5°	1976.1	1966.7	1945.9	1964.7	1961.2
5°	1964.7	1957.3	1936.4	1951.5	1947.9
7.5°	1951.5	1940.3	1919.5	1934.7	1930.9
10°	1930.9	1917.6	1895.0	1910.0	1904.4
12.5°	1902.4	1891.2	1868.6	1877.9	1874.1
15°	1870.3	1859.1	1834.4	1842.1	1832.6
17.5°	1830.6	1819.4	1794.7	1804.1	1794.7
20°	1787.2	1775.9	1749.5	1755.0	1747.7
22.5°	1743.8	1726.8	1702.1	1702.1	1698.3
25°	1692.7	1677.7	1645.6	1649.2	1645.6
27.5°	1636.0	1622.8	1598.3	1592.7	1583.3
30°	1579.4	1564.3	1536.0	1530.4	1522.8
32.5°	1518.9	1507.7	1477.4	1466.0	1458.4
35°	1460.4	1441.6	1411.3	1399.9	1390.5
37.5°	1394.2	1377.3	1347.0	1333.7	1324.3
40°	1326.4	1311.1	1280.8	1263.9	1256.4
42.5°	1260.2	1245.0	1214.9	1195.8	1184.6
45°	1188.4	1175.2	1146.7	1126.1	1118.4
47.5°	1118.4	1105.2	1075.0	1054.1	1042.9
50°	1044.7	1035.3	1008.9	982.4	972.9
52.5°	972.9	959.7	935.2	914.4	901.2
55°	899.4	888.0	865.3	842.6	833.2
57.5°	825.6	816.2	791.5	768.9	761.2
60°	751.8	744.5	718.0	697.1	691.6
62.5°	680.1	666.9	648.0	629.1	621.6
65°	606.5	595.1	576.2	559.3	549.8
67.5°	531.0	521.4	504.5	491.3	483.6
70°	461.0	453.4	436.4	423.1	415.8
72.5°	389.3	381.6	372.2	359.0	353.4
75°	317.3	313.7	304.1	292.9	296.7
77.5°	253.2	245.5	241.8	236.1	230.6
80°	189.0	187.0	183.2	177.6	173.8
82.5°	128.5	128.5	126.6	119.1	119.1
85°	77.4	75.5	73.7	68.0	66.1
87.5°	34.0	30.3	26.5	20.8	18.9
90°	1.6	20.7	34.4	43.2	46.6
92.5°	43.2	36.3	41.4	44.9	46.6
95°	112.1	55.1	67.3	76.0	74.2
97.5°	201.9	60.5	88.0	93.3	94.9
100°	305.7	69.1	98.4	112.1	115.6
102.5°	419.4	416.2	101.9	120.8	126.0
105°	524.8	576.6	105.3	124.2	131.2
107.5°	647.3	690.4	108.9	127.7	134.7
110°	764.9	800.9	302.2	129.6	136.3

TEST NUMBER: P909885

CATALOG NUMBER: DFN2DIP-TR3F0-050D070US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	875.4	906.3	877.0	132.8	138.1
115°	992.6	1021.9	1065.1	265.9	141.7
117.5°	1094.5	1128.9	1158.4	911.4	459.2
120°	1208.4	1234.3	1265.5	1286.2	1053.1
122.5°	1304.9	1332.6	1367.4	1377.6	1379.4
125°	1403.4	1425.9	1458.8	1470.9	1475.9
127.5°	1493.2	1517.3	1543.4	1560.6	1562.3
130°	1577.8	1605.5	1624.4	1643.5	1641.8
132.5°	1664.2	1686.7	1705.6	1721.1	1719.5
135°	1736.7	1764.3	1779.8	1797.2	1793.7
137.5°	1812.5	1833.3	1850.7	1867.9	1862.8
140°	1886.7	1900.7	1919.6	1935.1	1926.5
142.5°	1949.0	1961.2	1983.5	1997.2	1988.6
145°	2014.7	2012.9	2042.2	2054.3	2045.7
147.5°	2071.4	2066.4	2095.7	2104.3	2097.5
150°	2126.8	2114.8	2142.4	2152.6	2144.0
152.5°	2173.3	2159.6	2185.5	2195.9	2183.8
155°	2218.3	2202.8	2223.5	2233.8	2220.1
157.5°	2254.5	2240.8	2256.3	2268.5	2254.5
160°	2285.7	2275.2	2285.7	2295.9	2283.8
162.5°	2313.2	2302.9	2311.5	2323.6	2308.0
165°	2337.3	2327.1	2332.2	2344.3	2332.2
167.5°	2356.4	2345.9	2351.3	2363.4	2347.8
170°	2372.0	2361.6	2365.0	2377.1	2361.6
172.5°	2382.3	2372.0	2375.5	2387.5	2372.0
175°	2390.9	2378.7	2382.3	2394.3	2377.1
177.5°	2394.3	2382.3	2384.1	2396.2	2380.6
180°	2385.7	2385.7	2385.7	2385.7	2385.7

TEST NUMBER: P909885

CATALOG NUMBER: DFN2DIP-TR3F0-050D070US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.51	10.30	10.54	11.34	12.72	9.08	9.87	10.11	10.91	12.29
	3H	11.16	11.87	12.19	12.91	14.31	10.69	11.40	11.72	12.44	13.85
	4H	11.74	12.41	12.78	13.45	14.86	11.27	11.94	12.32	12.98	14.40
	6H	12.13	12.74	13.18	13.79	15.22	11.66	12.28	12.71	13.32	14.75
	8H	12.22	12.81	13.29	13.88	15.30	11.76	12.35	12.82	13.41	14.83
	12H	12.27	12.83	13.33	13.89	15.33	11.79	12.35	12.86	13.41	14.85
4H	2H	9.96	10.63	11.02	11.68	13.09	9.62	10.29	10.67	11.34	12.75
	3H	11.81	12.37	12.87	13.44	14.87	11.42	11.98	12.48	13.05	14.48
	4H	12.51	13.03	13.58	14.09	15.54	12.11	12.63	13.18	13.69	15.14
	6H	13.02	13.46	14.09	14.55	15.99	12.61	13.05	13.69	14.14	15.58
	8H	13.16	13.57	14.24	14.65	16.11	12.75	13.17	13.83	14.25	15.70
	12H	13.23	13.60	14.32	14.69	16.15	12.81	13.18	13.91	14.28	15.74
8H	4H	12.70	13.11	13.78	14.19	15.65	12.34	12.76	13.42	13.84	15.29
	6H	13.32	13.66	14.42	14.78	16.23	12.96	13.30	14.06	14.42	15.88
	8H	13.53	13.83	14.64	14.94	16.41	13.17	13.47	14.28	14.57	16.04
	12H	13.65	13.92	14.77	15.02	16.53	13.28	13.54	14.39	14.64	16.15
12H	4H	12.68	13.06	13.78	14.15	15.61	12.33	12.71	13.43	13.80	15.26
	6H	13.35	13.65	14.45	14.75	16.22	13.00	13.30	14.11	14.40	15.88
	8H	13.58	13.84	14.69	14.94	16.45	13.23	13.49	14.34	14.59	16.10