

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909930

Luminaire Tested: DFN2DIP-TR3F0-070D050US840-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909930
REPORT IS A COMBINATION OF REPORTS P900308 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-070D050US840-RLLFLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10477.3 lumens
Efficiency: N/A
Efficacy: 97.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 107.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909930
CATALOG NUMBER: DFN2DIP-TR3F0-070D050US840-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P909930
 CATALOG NUMBER: DFN2DIP-TR3F0-070D050US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57			57
1	100	96	92	89	93	89	86	83	78	75	73	67	65	63	56	55	54	49			49
2	92	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	47	42			42
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	42	40	36			36
4	77	66	59	53	72	62	56	50	55	49	45	47	43	40	41	38	35	32			32
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31	28			28
6	66	54	46	40	61	51	43	38	45	39	35	39	34	31	34	30	28	25			25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	27	25	22			22
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	29	25	22	20			20
9	53	41	33	28	49	38	32	27	34	29	25	30	26	23	26	23	20	18			18
10	49	37	30	26	46	35	29	25	32	26	23	28	24	21	25	21	19	17			17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3641	3641	3641
5°	3644	3580	3603
10°	3606	3507	3484
15°	3555	3388	3300
20°	3487	3225	3076
25°	3418	3043	2859
30°	3325	2857	2586
35°	3234	2658	2345
40°	3142	2451	2070
45°	3035	2223	1820
50°	2924	1992	1577
55°	2808	1746	1343
60°	2674	1490	1103
65°	2519	1229	990
70°	2331	986	892
75°	2095	863	807
80°	1753	714	692
85°	1193	463	506

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3035 cd/sqm



TEST NUMBER: P909930

CATALOG NUMBER: DFN2DIP-TR3F0-070D050US840-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	273.8	2.6
10°-20°	751.7	7.2
20°-30°	1055.3	10.1
30°-40°	1150.4	11.0
40°-50°	1057.3	10.1
50°-60°	830.4	7.9
60°-70°	540.5	5.2
70°-80°	278.2	2.7
80°-90°	75.6	0.7
90°-100°	98.8	0.9
100°-110°	314.0	3.0
110°-120°	537.3	5.1
120°-130°	706.6	6.7
130°-140°	793.2	7.6
140°-150°	777.8	7.4
150°-160°	652.5	6.2
160°-170°	432.7	4.1
170°-180°	151.2	1.4
0°-30°	2080.9	19.9
0°-40°	3231.2	30.8
0°-60°	5118.9	48.9
0°-90°	6013.2	57.4
90°-120°	950.1	9.1
90°-150°	3227.7	30.8
90°-180°	4464.0	42.6
0°-180°	10477.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2922	2922	2922	2922	2922	
5°	2922	2908	2874	2898	2890	277
15°	2779	2750	2660	2610	2583	783
25°	2522	2438	2263	2155	2115	1160
35°	2173	2038	1806	1639	1581	1360
45°	1777	1600	1322	1134	1071	1372
55°	1351	1145	859	701	651	1207
65°	912	698	460	370	362	904
75°	486	301	212	193	190	515
85°	114	58	50	50	50	130
90°	1	17	47	44	46	10
95°	70	84	86	86	84	78
105°	290	294	297	299	299	306
115°	539	547	544	543	539	533
125°	784	796	792	788	787	701
135°	1014	1029	1032	1031	1027	784
145°	1232	1241	1249	1250	1245	769
155°	1408	1412	1416	1423	1419	648
165°	1532	1530	1530	1540	1533	432
175°	1594	1590	1587	1597	1589	151
180°	1597	1597	1597	1597	1597	



TEST NUMBER: P909930

CATALOG NUMBER: DFN2DIP-TR3F0-070D050US840-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2921.6	2921.6	2921.6	2921.6	2921.6
2.5°	2934.8	2921.6	2892.5	2919.1	2913.8
5°	2921.6	2908.4	2874.0	2897.8	2889.9
7.5°	2897.8	2882.1	2845.1	2855.4	2842.3
10°	2866.1	2847.6	2794.8	2786.7	2771.0
12.5°	2826.5	2802.7	2731.2	2715.4	2686.2
15°	2778.8	2749.7	2659.9	2609.7	2583.3
17.5°	2723.3	2681.0	2569.9	2511.7	2469.4
20°	2659.9	2606.9	2474.8	2408.8	2350.5
22.5°	2591.2	2530.3	2376.8	2287.0	2247.6
25°	2522.4	2437.7	2263.2	2155.0	2115.2
27.5°	2440.5	2350.5	2157.5	2033.3	1972.4
30°	2353.3	2252.6	2041.0	1906.4	1834.9
32.5°	2268.6	2146.9	1930.3	1771.5	1705.3
35°	2173.4	2038.5	1806.0	1639.4	1581.0
37.5°	2080.9	1935.3	1689.6	1506.9	1441.1
40°	1983.0	1824.5	1567.8	1380.2	1311.4
42.5°	1882.6	1713.4	1446.3	1250.5	1184.7
45°	1776.9	1599.5	1322.1	1134.2	1070.8
47.5°	1676.4	1488.7	1203.2	1015.2	957.2
50°	1565.3	1377.7	1086.7	904.1	848.9
52.5°	1456.7	1258.4	975.6	801.1	750.9
55°	1351.0	1144.8	859.2	700.7	650.6
57.5°	1242.7	1031.2	756.3	608.1	565.8
60°	1131.7	920.1	647.7	513.1	470.7
62.5°	1023.3	811.8	555.1	428.4	407.3
65°	912.2	697.9	460.1	370.3	362.1
67.5°	806.5	592.2	370.3	325.1	317.3
70°	695.4	489.2	306.6	280.2	269.5
72.5°	589.7	393.8	256.4	235.4	230.0
75°	486.5	301.2	211.5	193.0	190.5
77.5°	383.4	214.0	166.6	155.9	150.7
80°	288.1	153.4	126.8	116.4	116.4
82.5°	200.9	103.2	87.3	81.9	81.9
85°	113.6	58.1	50.2	50.2	50.2
87.5°	42.3	21.0	21.0	18.5	18.5
90°	1.4	17.4	47.2	44.3	45.7
92.5°	29.9	40.4	41.9	43.3	43.3
95°	70.3	83.8	86.1	86.1	83.8
97.5°	116.9	129.5	134.8	134.8	134.8
100°	170.9	182.0	185.8	185.8	184.4
102.5°	227.7	235.9	241.2	242.7	241.2
105°	289.8	293.7	296.6	298.9	298.9
107.5°	351.4	357.2	357.2	358.2	351.4
110°	411.1	418.9	418.9	418.9	415.0



TEST NUMBER: P909930

CATALOG NUMBER: DFN2DIP-TR3F0-070D050US840-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	475.6	483.8	482.4	478.6	475.6
115°	539.2	546.9	544.5	543.1	539.2
117.5°	602.3	612.9	606.1	602.3	598.4
120°	665.8	676.4	665.8	665.8	661.5
122.5°	723.6	737.1	730.3	726.5	723.6
125°	784.3	796.3	792.4	788.1	786.7
127.5°	843.4	858.4	853.1	847.3	843.4
130°	898.9	916.2	913.7	910.9	905.5
132.5°	961.0	974.4	975.4	968.7	964.8
135°	1014.4	1029.3	1032.2	1030.8	1026.9
137.5°	1074.1	1086.1	1088.5	1087.5	1081.8
140°	1126.5	1138.6	1145.3	1145.3	1140.0
142.5°	1180.4	1192.6	1196.4	1197.8	1192.6
145°	1231.5	1241.1	1248.8	1250.3	1245.0
147.5°	1277.3	1289.3	1295.1	1297.5	1292.1
150°	1324.4	1332.6	1337.9	1342.2	1337.9
152.5°	1366.3	1374.5	1381.2	1386.5	1381.2
155°	1408.2	1412.0	1416.3	1423.1	1418.8
157.5°	1444.3	1447.1	1449.6	1459.3	1452.5
160°	1476.5	1479.5	1480.9	1489.0	1483.3
162.5°	1506.4	1506.4	1507.8	1517.0	1510.3
165°	1532.0	1530.5	1530.5	1540.1	1533.4
167.5°	1555.0	1550.6	1550.6	1560.3	1553.6
170°	1572.4	1568.5	1567.1	1576.7	1568.5
172.5°	1584.4	1580.5	1579.1	1588.7	1580.5
175°	1594.1	1590.1	1587.3	1596.9	1588.7
177.5°	1599.3	1595.5	1592.6	1600.7	1592.6
180°	1596.9	1596.9	1596.9	1596.9	1596.9



TEST NUMBER: P909930
 CATALOG NUMBER: DFN2DIP-TR3F0-070D050US840-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.25	13.14	13.15	14.05	15.22	8.22	9.12	9.12	10.03	11.20
	3H	13.92	14.72	14.83	15.64	16.83	9.41	10.21	10.32	11.13	12.32
	4H	14.53	15.28	15.45	16.21	17.41	9.86	10.62	10.79	11.54	12.74
	6H	14.94	15.64	15.88	16.57	17.78	10.18	10.88	11.12	11.81	13.02
	8H	15.07	15.73	16.01	16.68	17.89	10.27	10.93	11.21	11.88	13.09
	12H	15.13	15.76	16.08	16.70	17.93	10.31	10.94	11.26	11.89	13.12
4H	2H	12.27	13.03	13.20	13.95	15.15	8.82	9.58	9.75	10.50	11.70
	3H	14.10	14.72	15.04	15.68	16.90	10.17	10.80	11.11	11.76	12.97
	4H	14.78	15.36	15.73	16.31	17.55	10.72	11.29	11.67	12.24	13.48
	6H	15.29	15.79	16.26	16.76	18.00	11.13	11.63	12.10	12.60	13.84
	8H	15.46	15.92	16.43	16.89	18.15	11.26	11.72	12.23	12.69	13.94
	12H	15.56	15.97	16.54	16.96	18.22	11.33	11.74	12.31	12.73	13.98
8H	4H	14.76	15.21	15.72	16.18	17.44	11.00	11.46	11.96	12.43	13.68
	6H	15.31	15.69	16.30	16.70	17.96	11.51	11.89	12.50	12.90	14.15
	8H	15.52	15.86	16.52	16.86	18.13	11.70	12.03	12.70	13.03	14.30
	12H	15.66	15.95	16.66	16.95	18.26	11.81	12.11	12.81	13.10	14.42
12H	4H	14.71	15.12	15.69	16.11	17.37	11.00	11.42	11.99	12.40	13.66
	6H	15.29	15.62	16.29	16.62	17.89	11.56	11.89	12.56	12.89	14.16
	8H	15.51	15.80	16.51	16.79	18.11	11.76	12.06	12.77	13.05	14.37