

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926130

Luminaire Tested: DFN2DIP-TR2F0-040D030US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926130
REPORT IS A COMBINATION OF REPORTS P900236 AND P897145
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR2F0-040D030US950-RLLFLL
Description: 2 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5776.4 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926130

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P926130

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		74	74	74		62	62	62
1	100	96	92	88		93	89	86	83		77	75	72		66	64	63		55	54	53
2	91	84	78	73		85	79	73	69		68	64	61		58	56	53		49	47	46
3	84	74	67	62		78	70	63	58		61	56	52		52	49	46		44	42	40
4	77	66	59	53		71	62	55	50		54	49	45		47	43	40		40	37	35
5	71	59	51	46		66	56	49	43		49	43	39		42	38	35		36	33	30
6	65	53	46	40		61	50	43	38		44	38	34		38	34	31		33	30	27
7	61	48	41	35		56	46	39	34		40	35	30		35	31	27		30	27	24
8	56	44	37	31		52	42	35	30		37	31	27		32	28	25		28	25	22
9	53	41	33	28		49	38	32	27		34	28	25		30	25	22		26	23	20
10	49	37	30	25		46	35	29	24		31	26	22		28	23	20		24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3518	3518	3518
5°	3518	3454	3478
10°	3478	3379	3359
15°	3425	3259	3179
20°	3356	3098	2959
25°	3286	2919	2747
30°	3194	2736	2481
35°	3103	2540	2247
40°	3010	2338	1980
45°	2903	2115	1738
50°	2791	1890	1502
55°	2674	1651	1277
60°	2538	1403	1045
65°	2383	1151	934
70°	2193	917	836
75°	1953	793	749
80°	1610	643	632
85°	1057	399	445

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2903 cd/sqm

TEST NUMBER: P926130

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US950-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.8	2.6
10°-20°	405.8	7.0
20°-30°	569.7	9.9
30°-40°	621.0	10.8
40°-50°	570.8	9.9
50°-60°	448.2	7.8
60°-70°	291.8	5.1
70°-80°	150.2	2.6
80°-90°	40.9	0.7
90°-100°	56.0	1.0
100°-110°	178.0	3.1
110°-120°	304.6	5.3
120°-130°	400.5	6.9
130°-140°	449.6	7.8
140°-150°	440.9	7.6
150°-160°	369.8	6.4
160°-170°	245.3	4.2
170°-180°	85.7	1.5
0°-30°	1123.3	19.4
0°-40°	1744.3	30.2
0°-60°	2763.3	47.8
0°-90°	3246.2	56.2
90°-120°	538.5	9.3
90°-150°	1829.5	31.7
90°-180°	2530.0	43.8
0°-180°	5776.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1577	1577	1577	1577	1577	
5°	1577	1570	1551	1564	1560	150
15°	1500	1484	1436	1409	1395	423
25°	1362	1316	1222	1163	1142	626
35°	1173	1100	975	885	853	734
45°	959	864	714	612	578	741
55°	729	618	464	378	351	652
65°	492	377	248	200	196	488
75°	262	163	114	104	103	278
85°	61	31	27	27	27	70
90°	1	10	27	25	26	6
95°	40	48	49	49	48	44
105°	164	166	168	169	169	173
115°	306	310	309	308	306	302
125°	445	451	449	447	446	397
135°	575	583	585	584	582	444
145°	698	704	708	709	706	436
155°	798	800	803	807	804	367
165°	868	868	868	873	869	245
175°	904	901	900	905	900	86
180°	905	905	905	905	905	

TEST NUMBER: P926130

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US950-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1577.2	1577.2	1577.2	1577.2	1577.2
2.5°	1584.3	1577.2	1561.4	1575.8	1572.9
5°	1577.2	1570.0	1551.4	1564.3	1560.1
7.5°	1564.3	1555.8	1535.8	1541.4	1534.3
10°	1547.2	1537.2	1508.7	1504.3	1495.9
12.5°	1525.8	1512.9	1474.3	1465.8	1450.1
15°	1500.1	1484.3	1435.9	1408.8	1394.6
17.5°	1470.1	1447.2	1387.2	1355.9	1333.0
20°	1435.9	1407.2	1335.9	1300.3	1268.8
22.5°	1398.8	1365.9	1283.0	1234.6	1213.3
25°	1361.6	1315.9	1221.7	1163.3	1141.7
27.5°	1317.5	1268.8	1164.6	1097.6	1064.7
30°	1270.3	1216.0	1101.8	1029.1	990.5
32.5°	1224.6	1158.9	1042.0	956.3	920.5
35°	1173.3	1100.4	974.9	884.9	853.4
37.5°	1123.3	1044.7	912.0	813.5	777.9
40°	1070.5	984.9	846.4	745.1	708.0
42.5°	1016.2	924.9	780.8	675.1	639.5
45°	959.2	863.5	713.7	612.3	578.0
47.5°	905.0	803.6	649.5	548.1	516.7
50°	845.0	743.6	586.6	488.1	458.2
52.5°	786.4	679.3	526.7	432.4	405.4
55°	729.3	618.0	463.8	378.3	351.2
57.5°	670.9	556.7	408.2	328.3	305.5
60°	610.8	496.7	349.6	276.9	254.1
62.5°	552.5	438.3	299.7	231.2	219.9
65°	492.5	376.7	248.3	199.9	195.5
67.5°	435.4	319.7	199.9	175.5	171.2
70°	375.4	264.1	165.5	151.3	145.5
72.5°	318.3	212.6	138.4	127.1	124.2
75°	262.5	162.7	114.2	104.2	102.8
77.5°	207.0	115.5	90.0	84.2	81.3
80°	155.5	82.8	68.4	62.9	62.9
82.5°	108.5	55.7	47.1	44.2	44.2
85°	61.3	31.4	27.1	27.1	27.1
87.5°	22.9	11.4	11.4	10.0	10.0
90°	0.9	9.8	26.7	25.1	25.9
92.5°	16.9	22.9	23.8	24.5	24.5
95°	39.9	47.5	48.8	48.8	47.5
97.5°	66.3	73.4	76.4	76.4	76.4
100°	96.8	103.1	105.3	105.3	104.6
102.5°	129.1	133.8	136.7	137.6	136.7
105°	164.3	166.5	168.1	169.4	169.4
107.5°	199.2	202.4	202.4	203.0	199.2
110°	233.1	237.5	237.5	237.5	235.3

TEST NUMBER: P926130

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.6	274.3	273.4	271.2	269.6
115°	305.7	310.0	308.6	307.9	305.7
117.5°	341.3	347.4	343.5	341.3	339.1
120°	377.4	383.4	377.4	377.4	374.9
122.5°	410.1	417.8	413.9	411.7	410.1
125°	444.6	451.3	449.1	446.7	445.9
127.5°	478.0	486.5	483.6	480.2	478.0
130°	509.4	519.3	517.9	516.3	513.3
132.5°	544.6	552.3	552.8	549.0	546.8
135°	575.0	583.4	585.1	584.2	582.0
137.5°	608.7	615.6	617.0	616.5	613.1
140°	638.5	645.4	649.2	649.2	646.1
142.5°	669.1	675.9	678.1	679.0	675.9
145°	698.0	703.5	707.9	708.6	705.7
147.5°	724.0	730.8	734.0	735.4	732.4
150°	750.7	755.4	758.3	760.8	758.3
152.5°	774.5	779.0	782.9	785.9	782.9
155°	798.2	800.3	802.8	806.6	804.2
157.5°	818.6	820.2	821.7	827.1	823.3
160°	836.9	838.6	839.4	844.0	840.8
162.5°	853.8	853.8	854.7	859.8	856.0
165°	868.3	867.5	867.5	872.9	869.1
167.5°	881.4	878.9	878.9	884.4	880.5
170°	891.2	889.0	888.3	893.7	889.0
172.5°	898.0	895.9	895.0	900.5	895.9
175°	903.5	901.3	899.7	905.2	900.5
177.5°	906.5	904.3	902.7	907.3	902.7
180°	905.2	905.2	905.2	905.2	905.2

TEST NUMBER: P926130

CATALOG NUMBER: DFN2DIP-TR2F0-040D030US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.95	12.83	12.86	13.76	14.94	7.93	8.81	8.84	9.74	10.92
	3H	13.61	14.40	14.53	15.33	16.54	9.11	9.90	10.03	10.83	12.04
	4H	14.20	14.95	15.14	15.88	17.10	9.55	10.29	10.48	11.23	12.45
	6H	14.61	15.29	15.55	16.24	17.47	9.86	10.55	10.81	11.49	12.72
	8H	14.72	15.38	15.68	16.34	17.56	9.94	10.60	10.90	11.56	12.78
	12H	14.78	15.40	15.74	16.35	17.60	9.98	10.60	10.94	11.56	12.81
4H	2H	11.97	12.72	12.91	13.65	14.87	8.52	9.26	9.46	10.20	11.42
	3H	13.78	14.40	14.73	15.36	16.60	9.85	10.47	10.81	11.44	12.67
	4H	14.45	15.02	15.41	15.98	17.24	10.39	10.96	11.35	11.92	13.17
	6H	14.95	15.43	15.92	16.42	17.67	10.80	11.28	11.77	12.27	13.52
	8H	15.11	15.56	16.09	16.54	17.81	10.92	11.37	11.89	12.35	13.62
	12H	15.19	15.60	16.19	16.60	17.87	10.98	11.38	11.97	12.38	13.65
8H	4H	14.42	14.87	15.39	15.85	17.12	10.66	11.12	11.64	12.09	13.36
	6H	14.96	15.34	15.96	16.36	17.63	11.16	11.53	12.16	12.56	13.82
	8H	15.16	15.49	16.17	16.50	17.79	11.34	11.67	12.35	12.68	13.96
	12H	15.29	15.58	16.30	16.58	17.91	11.45	11.74	12.46	12.74	14.07
12H	4H	14.37	14.78	15.37	15.78	17.05	10.66	11.07	11.66	12.07	13.34
	6H	14.94	15.27	15.94	16.28	17.56	11.20	11.53	12.21	12.54	13.83
	8H	15.14	15.43	16.15	16.44	17.77	11.40	11.69	12.41	12.70	14.03