

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926141

Luminaire Tested: DFN2DIP-TR2F0-040D060US950-FLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P926141  
REPORT IS A COMBINATION OF REPORTS P901785 AND P897145  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR2F0-040D060US950-FLLONL  
Description: 2 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8843.6 lumens  
Efficiency: N/A  
Efficacy: 104.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.04' x L: 2.36' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 84.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9933  
Total Harmonic Distortion (THDi): 0.066  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P926141  
CATALOG NUMBER: DFN2DIP-TR2F0-040D060US950-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P926141  
 CATALOG NUMBER: DFN2DIP-TR2F0-040D060US950-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	49	49	49	43
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	44	43	42	42	42	42	36
2	88	80	74	69	80	73	68	64	61	57	54	49	47	44	38	37	35	35	35	35	30
3	80	70	63	57	73	65	58	53	54	49	45	44	40	37	34	32	30	30	30	30	26
4	73	62	55	49	66	57	50	45	48	43	39	39	35	32	30	28	26	26	26	26	22
5	67	56	47	42	61	51	44	39	43	37	33	35	31	28	27	25	22	22	22	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	20	20	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	24	21	23	20	18	18	18	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	16	16	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	14	14	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	13	13	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3312	3312	3312
5°	3312	3258	3282
10°	3280	3207	3232
15°	3227	3147	3157
20°	3157	3066	3080
25°	3087	2971	2992
30°	3001	2882	2882
35°	2919	2779	2766
40°	2818	2673	2656
45°	2718	2568	2542
50°	2608	2457	2411
55°	2492	2329	2289
60°	2361	2177	2149
65°	2218	2019	1985
70°	2035	1827	1806
75°	1784	1596	1634
80°	1479	1301	1321
85°	1009	820	821

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2718 cd/sqm



TEST NUMBER: P926141

CATALOG NUMBER: DFN2DIP-TR2F0-040D060US950-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.8	1.6
10°-20°	393.2	4.4
20°-30°	577.9	6.5
30°-40°	671.2	7.6
40°-50°	670.3	7.6
50°-60°	584.5	6.6
60°-70°	432.1	4.9
70°-80°	244.5	2.8
80°-90°	69.7	0.8
90°-100°	112.0	1.3
100°-110°	355.9	4.0
110°-120°	609.1	6.9
120°-130°	801.1	9.1
130°-140°	899.2	10.2
140°-150°	881.7	10.0
150°-160°	739.6	8.4
160°-170°	490.5	5.5
170°-180°	171.4	1.9
0°-30°	1110.8	12.6
0°-40°	1782.0	20.1
0°-60°	3036.8	34.3
0°-90°	3783.0	42.8
90°-120°	1077.0	12.2
90°-150°	3659.0	41.4
90°-180°	5061.0	57.2
0°-180°	8843.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1485	1485	1485	1485	1485	
5°	1485	1479	1463	1475	1472	141
15°	1413	1405	1386	1392	1385	398
25°	1279	1268	1244	1246	1244	589
35°	1104	1090	1067	1058	1051	689
45°	898	888	867	851	845	693
55°	680	671	654	637	630	608
65°	458	450	436	423	416	453
75°	240	237	230	221	224	256
85°	58	57	56	51	50	65
90°	2	20	54	50	52	9
95°	80	95	98	98	95	89
105°	329	333	336	339	339	347
115°	611	620	617	616	611	605
125°	889	903	898	893	892	794
135°	1150	1167	1170	1168	1164	889
145°	1396	1407	1416	1417	1411	872
155°	1596	1601	1606	1613	1608	735
165°	1737	1735	1735	1746	1738	490
175°	1807	1803	1799	1810	1801	172
180°	1810	1810	1810	1810	1810	



TEST NUMBER: P926141

CATALOG NUMBER: DFN2DIP-TR2F0-040D060US950-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1484.8	1484.8	1484.8	1484.8	1484.8
2.5°	1493.5	1486.3	1470.6	1484.8	1482.1
5°	1484.8	1479.2	1463.4	1474.8	1472.1
7.5°	1474.8	1466.3	1450.6	1462.1	1459.2
10°	1459.2	1449.2	1432.1	1443.5	1439.2
12.5°	1437.7	1429.2	1412.1	1419.3	1416.3
15°	1413.4	1405.0	1386.4	1392.1	1385.0
17.5°	1383.5	1375.0	1356.4	1363.5	1356.4
20°	1350.6	1342.1	1322.1	1326.3	1320.8
22.5°	1317.9	1305.0	1286.4	1286.4	1283.5
25°	1279.2	1267.9	1243.6	1246.4	1243.6
27.5°	1236.4	1226.4	1208.0	1203.7	1196.6
30°	1193.6	1182.2	1160.8	1156.5	1150.8
32.5°	1147.9	1139.5	1116.6	1108.0	1102.2
35°	1103.7	1089.5	1066.6	1058.0	1050.8
37.5°	1053.7	1040.8	1017.9	1008.0	1000.8
40°	1002.4	990.8	967.9	955.2	949.5
42.5°	952.4	940.8	918.1	903.7	895.2
45°	898.1	888.2	866.6	851.1	845.2
47.5°	845.2	835.2	812.4	796.7	788.2
50°	789.5	782.4	762.4	742.4	735.2
52.5°	735.2	725.3	706.8	691.1	681.1
55°	679.7	671.0	654.0	636.8	629.7
57.5°	623.9	616.9	598.2	581.1	575.4
60°	568.2	562.6	542.6	526.9	522.6
62.5°	514.0	504.0	489.8	475.5	469.7
65°	458.4	449.7	435.5	422.6	415.6
67.5°	401.3	394.0	381.3	371.3	365.6
70°	348.4	342.7	329.8	319.8	314.2
72.5°	294.2	288.4	281.3	271.3	267.0
75°	239.8	237.1	229.8	221.3	224.2
77.5°	191.3	185.6	182.7	178.4	174.2
80°	142.8	141.3	138.4	134.2	131.4
82.5°	97.1	97.1	95.8	90.0	90.0
85°	58.5	57.1	55.7	51.3	50.0
87.5°	25.8	22.9	20.0	15.7	14.2
90°	1.6	19.7	53.5	50.2	51.8
92.5°	33.9	45.9	47.5	49.1	49.1
95°	79.7	94.9	97.7	97.7	94.9
97.5°	132.6	146.8	152.8	152.8	152.8
100°	193.8	206.3	210.6	210.6	209.0
102.5°	258.2	267.4	273.4	275.0	273.4
105°	328.6	332.9	336.2	339.0	339.0
107.5°	398.4	405.0	405.0	406.0	398.4
110°	466.1	474.8	474.8	474.8	470.4



TEST NUMBER: P926141

CATALOG NUMBER: DFN2DIP-TR2F0-040D060US950-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	539.2	548.5	546.8	542.4	539.2
115°	611.2	620.0	617.2	615.6	611.2
117.5°	682.8	694.8	687.1	682.8	678.4
120°	754.8	766.8	754.8	754.8	749.8
122.5°	820.2	835.5	827.9	823.6	820.2
125°	889.0	902.7	898.3	893.4	891.8
127.5°	956.2	973.1	967.1	960.6	956.2
130°	1019.0	1038.6	1035.9	1032.6	1026.6
132.5°	1089.4	1104.6	1105.7	1098.1	1093.7
135°	1150.0	1166.8	1170.1	1168.5	1164.1
137.5°	1217.6	1231.2	1234.0	1232.9	1226.4
140°	1277.1	1290.8	1298.4	1298.4	1292.4
142.5°	1338.2	1351.8	1356.2	1357.8	1351.8
145°	1396.1	1407.0	1415.7	1417.4	1411.3
147.5°	1447.9	1461.5	1468.1	1470.8	1464.8
150°	1501.4	1510.7	1516.7	1521.5	1516.7
152.5°	1548.8	1558.2	1565.8	1571.8	1565.8
155°	1596.3	1600.7	1605.6	1613.3	1608.3
157.5°	1637.3	1640.6	1643.3	1654.2	1646.6
160°	1673.9	1677.1	1678.8	1688.0	1681.5
162.5°	1707.7	1707.7	1709.3	1719.7	1712.0
165°	1736.6	1734.9	1734.9	1745.9	1738.3
167.5°	1762.8	1757.9	1757.9	1768.8	1761.2
170°	1782.5	1778.1	1776.4	1787.3	1778.1
172.5°	1796.1	1791.7	1790.1	1801.0	1791.7
175°	1807.0	1802.7	1799.3	1810.3	1801.0
177.5°	1813.0	1808.7	1805.3	1814.6	1805.3
180°	1810.3	1810.3	1810.3	1810.3	1810.3



TEST NUMBER: P926141  
 CATALOG NUMBER: DFN2DIP-TR2F0-040D060US950-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.60	11.40	11.61	12.42	13.79	10.17	10.97	11.19	12.00	13.37
	3H	12.23	12.94	13.25	13.98	15.37	11.77	12.48	12.79	13.52	14.91
	4H	12.80	13.48	13.84	14.51	15.91	12.34	13.02	13.38	14.05	15.45
	6H	13.18	13.80	14.22	14.84	16.25	12.71	13.34	13.76	14.38	15.79
	8H	13.27	13.86	14.32	14.92	16.33	12.81	13.41	13.86	14.46	15.87
	12H	13.31	13.87	14.37	14.92	16.35	12.84	13.41	13.90	14.46	15.89
4H	2H	11.04	11.72	12.09	12.76	14.16	10.70	11.38	11.75	12.42	13.82
	3H	12.87	13.44	13.93	14.51	15.92	12.49	13.06	13.54	14.12	15.53
	4H	13.57	14.09	14.63	15.14	16.58	13.17	13.69	14.23	14.75	16.18
	6H	14.06	14.50	15.13	15.58	17.01	13.66	14.11	14.73	15.19	16.61
	8H	14.19	14.61	15.26	15.68	17.13	13.79	14.21	14.87	15.28	16.73
	12H	14.25	14.63	15.34	15.72	17.16	13.85	14.22	14.93	15.31	16.76
8H	4H	13.75	14.17	14.82	15.24	16.68	13.40	13.81	14.47	14.89	16.33
	6H	14.35	14.69	15.44	15.81	17.25	14.00	14.34	15.09	15.46	16.90
	8H	14.55	14.86	15.65	15.95	17.41	14.20	14.50	15.30	15.60	17.06
	12H	14.67	14.93	15.77	16.03	17.52	14.30	14.56	15.40	15.66	17.16
12H	4H	13.73	14.11	14.82	15.19	16.64	13.38	13.76	14.47	14.85	16.30
	6H	14.37	14.68	15.47	15.77	17.23	14.03	14.33	15.13	15.43	16.89
	8H	14.59	14.86	15.70	15.95	17.45	14.25	14.52	15.35	15.61	17.11