

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912620

Luminaire Tested: DFN2DIP-TR3F0-050D090US850-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P912620  
REPORT IS A COMBINATION OF REPORTS P900359 AND P897195  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR3F0-050D090US850-FLLFLL  
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 14322.8 lumens  
Efficiency: N/A  
Efficacy: 123.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 116.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9933  
Total Harmonic Distortion (THDi): 0.066  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P912620  
CATALOG NUMBER: DFN2DIP-TR3F0-050D090US850-FLLFLL

### Luminous Intensity Polar Plot



— 0°-180°    - - - 45°-225°    - - - 90°-270°



TEST NUMBER: P912620  
 CATALOG NUMBER: DFN2DIP-TR3F0-050D090US850-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	45	45	45	38				38
1	95	91	87	84	86	83	79	77	67	65	63	53	52	50	40	39	38	32				32
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32	27				27
3	79	70	63	57	71	64	57	52	52	47	44	41	38	35	31	29	27	23				23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24	20				20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17				17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15				15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13				13
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	16	14	12				12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11				11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	16	14	12	10				10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2689	2689	2689
5°	2691	2649	2667
10°	2668	2611	2629
15°	2627	2566	2571
20°	2573	2504	2512
25°	2519	2430	2443
30°	2451	2361	2356
35°	2387	2281	2265
40°	2308	2199	2178
45°	2229	2117	2088
50°	2143	2031	1985
55°	2053	1931	1889
60°	1951	1814	1780
65°	1839	1691	1651
70°	1697	1542	1512
75°	1500	1362	1380
80°	1263	1134	1135
85°	891	746	732

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 3081 cd/sqm



TEST NUMBER: P912620

CATALOG NUMBER: DFN2DIP-TR3F0-050D090US850-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	203.1	1.4
10°-20°	571.4	4.0
20°-30°	839.7	5.9
30°-40°	975.2	6.8
40°-50°	974.0	6.8
50°-60°	849.3	5.9
60°-70°	627.9	4.4
70°-80°	355.2	2.5
80°-90°	102.7	0.7
90°-100°	195.3	1.4
100°-110°	620.6	4.3
110°-120°	1062.1	7.4
120°-130°	1396.8	9.8
130°-140°	1567.9	10.9
140°-150°	1537.5	10.7
150°-160°	1289.7	9.0
160°-170°	855.3	6.0
170°-180°	299.0	2.1
0°-30°	1614.1	11.3
0°-40°	2589.4	18.1
0°-60°	4412.7	30.8
0°-90°	5498.5	38.4
90°-120°	1878.1	13.1
90°-150°	6380.2	44.5
90°-180°	8824.0	61.6
0°-180°	14322.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2158	2158	2158	2158	2158	
5°	2158	2150	2126	2143	2139	205
15°	2054	2042	2014	2023	2012	578
25°	1859	1842	1807	1811	1807	855
35°	1604	1583	1550	1537	1527	1001
45°	1305	1290	1259	1237	1228	1007
55°	988	975	950	925	915	883
65°	666	654	633	614	604	659
75°	348	344	334	322	326	372
85°	85	83	81	75	73	95
90°	3	34	93	88	90	14
95°	139	166	170	170	166	155
105°	573	580	586	591	591	605
115°	1066	1081	1076	1074	1066	1054
125°	1550	1574	1566	1558	1555	1385
135°	2005	2035	2040	2038	2030	1550
145°	2434	2453	2468	2471	2461	1521
155°	2784	2791	2800	2813	2805	1281
165°	3028	3025	3025	3044	3031	854
175°	3151	3143	3138	3157	3140	299
180°	3157	3157	3157	3157	3157	



TEST NUMBER: P912620

CATALOG NUMBER: DFN2DIP-TR3F0-050D090US850-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2157.6	2157.6	2157.6	2157.6	2157.6
2.5°	2170.1	2159.8	2136.9	2157.6	2153.7
5°	2157.6	2149.5	2126.5	2143.0	2139.2
7.5°	2143.0	2130.7	2107.9	2124.6	2120.4
10°	2120.4	2105.9	2081.0	2097.5	2091.4
12.5°	2089.1	2076.8	2052.0	2062.3	2058.1
15°	2053.9	2041.6	2014.5	2022.9	2012.5
17.5°	2010.3	1998.0	1970.9	1981.2	1970.9
20°	1962.6	1950.3	1921.2	1927.3	1919.2
22.5°	1915.0	1896.3	1869.2	1869.2	1865.0
25°	1858.9	1842.4	1807.1	1811.1	1807.1
27.5°	1796.6	1782.1	1755.2	1749.0	1738.7
30°	1734.5	1717.8	1686.8	1680.6	1672.3
32.5°	1668.0	1655.7	1622.5	1609.9	1601.6
35°	1603.7	1583.1	1549.8	1537.3	1527.0
37.5°	1531.1	1512.5	1479.2	1464.7	1454.3
40°	1456.6	1439.8	1406.5	1388.0	1379.7
42.5°	1383.9	1367.2	1334.1	1313.2	1300.9
45°	1305.1	1290.5	1259.3	1236.6	1228.2
47.5°	1228.2	1213.7	1180.5	1157.6	1145.3
50°	1147.3	1136.9	1107.9	1078.8	1068.4
52.5°	1068.4	1053.9	1027.0	1004.2	989.7
55°	987.7	975.1	950.2	925.3	915.0
57.5°	906.6	896.3	869.2	844.4	836.0
60°	825.7	817.6	788.5	765.5	759.4
62.5°	746.9	732.4	711.6	690.9	682.6
65°	666.1	653.5	632.8	614.2	603.7
67.5°	583.1	572.6	554.1	539.5	531.1
70°	506.3	497.9	479.2	464.7	456.6
72.5°	427.5	419.1	408.8	394.2	388.0
75°	348.4	344.5	333.9	321.6	325.8
77.5°	278.0	269.6	265.5	259.3	253.2
80°	207.6	205.4	201.2	195.1	190.9
82.5°	141.1	141.1	139.1	130.8	130.8
85°	84.9	83.0	81.0	74.6	72.6
87.5°	37.4	33.3	29.1	22.8	20.7
90°	2.9	34.3	93.3	87.5	90.4
92.5°	59.0	80.0	82.8	85.6	85.6
95°	139.0	165.6	170.3	170.3	165.6
97.5°	231.2	256.0	266.5	266.5	266.5
100°	337.8	359.8	367.3	367.3	364.5
102.5°	450.1	466.3	476.8	479.6	476.8
105°	572.9	580.5	586.2	591.0	591.0
107.5°	694.7	706.1	706.1	708.0	694.7
110°	812.7	828.0	828.0	828.0	820.3



TEST NUMBER: P912620

CATALOG NUMBER: DFN2DIP-TR3F0-050D090US850-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	940.2	956.4	953.5	946.0	940.2
115°	1065.9	1081.1	1076.3	1073.5	1065.9
117.5°	1190.5	1211.5	1198.2	1190.5	1182.9
120°	1316.2	1337.0	1316.2	1316.2	1307.5
122.5°	1430.3	1457.0	1443.7	1436.0	1430.3
125°	1550.3	1574.0	1566.5	1557.8	1555.0
127.5°	1667.3	1696.8	1686.3	1674.9	1667.3
130°	1776.7	1811.0	1806.2	1800.5	1790.0
132.5°	1899.5	1926.1	1928.0	1914.7	1907.1
135°	2005.1	2034.6	2040.3	2037.5	2029.9
137.5°	2123.1	2146.9	2151.7	2149.8	2138.4
140°	2226.9	2250.6	2263.9	2263.9	2253.5
142.5°	2333.4	2357.2	2364.8	2367.7	2357.2
145°	2434.4	2453.3	2468.5	2471.4	2461.0
147.5°	2524.7	2548.5	2559.9	2564.7	2554.2
150°	2618.0	2634.2	2644.6	2653.2	2644.6
152.5°	2700.7	2716.9	2730.2	2740.8	2730.2
155°	2783.6	2791.1	2799.8	2813.1	2804.6
157.5°	2854.9	2860.7	2865.4	2884.4	2871.1
160°	2918.7	2924.4	2927.3	2943.4	2932.0
162.5°	2977.7	2977.7	2980.5	2998.6	2985.3
165°	3028.1	3025.2	3025.2	3044.3	3031.0
167.5°	3073.8	3065.3	3065.3	3084.2	3070.9
170°	3108.1	3100.4	3097.7	3116.6	3100.4
172.5°	3131.8	3124.3	3121.4	3140.5	3124.3
175°	3150.9	3143.2	3137.6	3156.7	3140.5
177.5°	3161.3	3153.8	3148.0	3164.2	3148.0
180°	3156.7	3156.7	3156.7	3156.7	3156.7



TEST NUMBER: P912620  
 CATALOG NUMBER: DFN2DIP-TR3F0-050D090US850-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.47	10.24	10.53	11.30	12.72	9.05	9.81	10.10	10.87	12.30
	3H	11.12	11.81	12.18	12.87	14.32	10.65	11.34	11.71	12.40	13.85
	4H	11.70	12.35	12.77	13.41	14.87	11.23	11.88	12.30	12.94	14.40
	6H	12.08	12.68	13.16	13.75	15.22	11.61	12.21	12.70	13.28	14.75
	8H	12.18	12.75	13.27	13.84	15.30	11.71	12.28	12.80	13.37	14.83
	12H	12.22	12.76	13.31	13.84	15.33	11.75	12.29	12.84	13.37	14.85
4H	2H	9.92	10.57	11.00	11.64	13.09	9.58	10.23	10.66	11.30	12.75
	3H	11.77	12.31	12.85	13.40	14.87	11.38	11.92	12.46	13.01	14.48
	4H	12.47	12.97	13.56	14.05	15.54	12.07	12.57	13.16	13.65	15.14
	6H	12.97	13.40	14.07	14.51	15.99	12.57	13.00	13.67	14.10	15.58
	8H	13.11	13.51	14.21	14.61	16.11	12.71	13.11	13.81	14.21	15.70
	12H	13.18	13.54	14.30	14.65	16.15	12.76	13.13	13.88	14.24	15.74
8H	4H	12.66	13.06	13.76	14.15	15.65	12.30	12.70	13.40	13.80	15.29
	6H	13.27	13.60	14.39	14.74	16.24	12.91	13.24	14.04	14.38	15.88
	8H	13.49	13.77	14.61	14.90	16.41	13.12	13.41	14.25	14.53	16.05
	12H	13.61	13.86	14.74	14.98	16.53	13.23	13.48	14.36	14.60	16.15
12H	4H	12.64	13.00	13.75	14.11	15.61	12.29	12.65	13.40	13.76	15.26
	6H	13.30	13.59	14.43	14.71	16.22	12.95	13.24	14.08	14.36	15.88
	8H	13.53	13.78	14.66	14.90	16.45	13.18	13.43	14.31	14.55	16.10