

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912648

Luminaire Tested: DFN2DIP-TR3F0-070D030US850-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912648
REPORT IS A COMBINATION OF REPORTS P900279 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-070D030US850-FLLFLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10629.7 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 92.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912648
CATALOG NUMBER: DFN2DIP-TR3F0-070D030US850-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P912648

CATALOG NUMBER: DFN2DIP-TR3F0-070D030US850-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77	77	77	77	77
1	103	98	94	91	97	93	90	87	84	81	79	76	74	72	68	66	65	65	65	65	61
2	94	86	80	74	89	82	76	71	74	69	65	66	63	60	60	57	55	55	55	55	51
3	85	76	68	62	81	72	65	60	65	60	55	59	54	51	53	49	46	46	46	46	43
4	78	67	59	52	74	64	56	51	58	52	47	52	48	44	47	43	40	40	40	40	37
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	38	35	35	35	35	32
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31	31	31	31	28
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	35	31	27	27	27	27	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25	25	25	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	22	22	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	22	28	24	20	20	20	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3764	3764	3764
5°	3768	3708	3734
10°	3735	3655	3681
15°	3678	3592	3599
20°	3602	3505	3516
25°	3526	3402	3420
30°	3431	3306	3299
35°	3342	3193	3171
40°	3231	3078	3048
45°	3121	2964	2923
50°	3001	2843	2779
55°	2874	2704	2645
60°	2731	2539	2492
65°	2575	2367	2311
70°	2376	2158	2116
75°	2100	1907	1932
80°	1768	1587	1588
85°	1249	1046	1025

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3121 cd/sqm



TEST NUMBER: P912648

CATALOG NUMBER: DFN2DIP-TR3F0-070D030US850-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.3	2.7
10°-20°	799.9	7.5
20°-30°	1175.6	11.1
30°-40°	1365.3	12.8
40°-50°	1363.6	12.8
50°-60°	1189.1	11.2
60°-70°	879.0	8.3
70°-80°	497.3	4.7
80°-90°	134.3	1.3
90°-100°	65.1	0.6
100°-110°	206.9	1.9
110°-120°	354.0	3.3
120°-130°	465.6	4.4
130°-140°	522.6	4.9
140°-150°	512.5	4.8
150°-160°	429.9	4.0
160°-170°	285.1	2.7
170°-180°	99.7	0.9
0°-30°	2259.8	21.3
0°-40°	3625.1	34.1
0°-60°	6177.8	58.1
0°-90°	7688.4	72.3
90°-120°	626.0	5.9
90°-150°	2126.7	20.0
90°-180°	2941.0	27.7
0°-180°	10629.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3021	3021	3021	3021	3021	
5°	3021	3009	2977	3000	2995	287
15°	2876	2858	2820	2832	2818	810
25°	2602	2579	2530	2536	2530	1198
35°	2245	2216	2170	2152	2138	1402
45°	1827	1807	1763	1731	1720	1410
55°	1383	1365	1330	1296	1281	1236
65°	933	915	886	860	845	922
75°	488	482	467	450	456	521
85°	119	116	114	104	102	133
90°	1	11	31	29	30	10
95°	46	55	57	57	55	52
105°	191	194	195	197	197	202
115°	355	360	359	358	355	351
125°	517	525	522	519	518	462
135°	668	678	680	679	677	517
145°	812	818	823	824	820	507
155°	928	930	933	938	935	427
165°	1009	1008	1008	1015	1010	285
175°	1050	1048	1046	1052	1047	100
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P912648

CATALOG NUMBER: DFN2DIP-TR3F0-070D030US850-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3020.6	3020.6	3020.6	3020.6	3020.6
2.5°	3038.2	3023.7	2991.6	3020.6	3015.0
5°	3020.6	3009.3	2977.2	3000.3	2994.7
7.5°	3000.3	2983.0	2950.9	2974.4	2968.6
10°	2968.6	2948.2	2913.3	2936.5	2927.9
12.5°	2924.8	2907.6	2872.8	2887.2	2881.3
15°	2875.5	2858.2	2820.3	2832.1	2817.5
17.5°	2814.4	2797.2	2759.3	2773.8	2759.3
20°	2747.5	2730.4	2689.7	2698.3	2686.9
22.5°	2681.0	2654.8	2616.9	2616.9	2611.0
25°	2602.5	2579.3	2530.1	2535.6	2530.1
27.5°	2515.2	2494.9	2457.3	2448.7	2434.1
30°	2428.4	2404.9	2361.5	2352.9	2341.1
32.5°	2335.2	2318.0	2271.5	2253.9	2242.2
35°	2245.3	2216.3	2169.8	2152.2	2137.7
37.5°	2143.6	2117.4	2070.8	2050.5	2036.0
40°	2039.1	2015.7	1969.1	1943.3	1931.5
42.5°	1937.4	1914.0	1867.8	1838.5	1821.2
45°	1827.1	1806.8	1763.0	1731.3	1719.5
47.5°	1719.5	1699.2	1652.6	1620.6	1603.4
50°	1606.2	1591.6	1550.9	1510.3	1495.8
52.5°	1495.8	1475.5	1437.9	1405.9	1385.5
55°	1382.7	1365.2	1330.4	1295.5	1281.0
57.5°	1269.4	1254.8	1216.9	1182.1	1170.4
60°	1155.9	1144.5	1103.9	1071.8	1063.2
62.5°	1045.6	1025.3	996.3	967.4	955.6
65°	932.6	914.9	886.0	859.8	845.3
67.5°	816.3	801.6	775.6	755.3	743.6
70°	708.8	697.1	670.8	650.5	639.1
72.5°	598.4	586.8	572.2	551.9	543.3
75°	487.8	482.3	467.4	450.3	456.1
77.5°	389.3	377.5	371.6	363.0	354.4
80°	290.6	287.6	281.7	273.0	267.2
82.5°	197.5	197.5	194.7	183.1	183.1
85°	119.0	116.2	113.5	104.5	101.7
87.5°	52.3	46.6	40.7	32.1	28.9
90°	1.0	11.4	31.1	29.2	30.2
92.5°	19.6	26.6	27.6	28.5	28.5
95°	46.4	55.2	56.8	56.8	55.2
97.5°	77.1	85.3	88.8	88.8	88.8
100°	112.6	119.9	122.4	122.4	121.5
102.5°	150.0	155.5	158.9	159.9	158.9
105°	191.0	193.5	195.4	197.0	197.0
107.5°	231.6	235.3	235.3	236.0	231.6
110°	270.9	276.0	276.0	276.0	273.5



TEST NUMBER: P912648

CATALOG NUMBER: DFN2DIP-TR3F0-070D030US850-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	313.4	318.8	317.8	315.3	313.4
115°	355.3	360.3	358.8	357.9	355.3
117.5°	396.8	403.8	399.4	396.8	394.2
120°	438.7	445.7	438.7	438.7	435.8
122.5°	476.8	485.6	481.2	478.6	476.8
125°	516.8	524.7	522.1	519.2	518.3
127.5°	555.7	565.6	562.2	558.3	555.7
130°	592.2	603.6	602.1	600.2	596.6
132.5°	633.1	642.0	642.7	638.2	635.7
135°	668.4	678.2	680.1	679.2	676.6
137.5°	707.7	715.6	717.2	716.6	712.8
140°	742.3	750.2	754.7	754.7	751.1
142.5°	777.9	785.7	788.3	789.3	785.7
145°	811.5	817.8	822.9	823.8	820.3
147.5°	841.6	849.5	853.3	854.9	851.4
150°	872.7	878.1	881.5	884.4	881.5
152.5°	900.3	905.6	910.0	913.6	910.0
155°	927.9	930.3	933.2	937.7	934.9
157.5°	951.6	953.5	955.2	961.5	957.1
160°	972.9	974.8	975.8	981.1	977.4
162.5°	992.6	992.6	993.6	999.5	995.1
165°	1009.4	1008.4	1008.4	1014.7	1010.3
167.5°	1024.6	1021.7	1021.7	1028.0	1023.6
170°	1036.0	1033.5	1032.6	1038.9	1033.5
172.5°	1043.9	1041.5	1040.5	1046.8	1041.5
175°	1050.3	1047.8	1045.9	1052.2	1046.8
177.5°	1053.8	1051.2	1049.3	1054.8	1049.3
180°	1052.2	1052.2	1052.2	1052.2	1052.2



TEST NUMBER: P912648
 CATALOG NUMBER: DFN2DIP-TR3F0-070D030US850-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.67	14.78	14.41	15.54	16.45	13.24	14.35	13.98	15.11	16.02
	3H	15.34	16.33	16.09	17.10	18.05	14.87	15.87	15.62	16.63	17.58
	4H	15.93	16.87	16.70	17.65	18.60	15.46	16.40	16.23	17.18	18.14
	6H	16.34	17.20	17.12	17.99	18.96	15.87	16.73	16.65	17.52	18.49
	8H	16.45	17.27	17.24	18.08	19.05	15.98	16.80	16.77	17.61	18.58
	12H	16.50	17.29	17.30	18.09	19.08	16.02	16.81	16.82	17.61	18.61
4H	2H	14.16	15.10	14.93	15.87	16.83	13.82	14.75	14.59	15.53	16.49
	3H	16.03	16.82	16.82	17.63	18.60	15.65	16.43	16.43	17.24	18.21
	4H	16.75	17.46	17.55	18.28	19.28	16.35	17.06	17.15	17.88	18.88
	6H	17.27	17.89	18.09	18.73	19.73	16.87	17.48	17.69	18.32	19.33
	8H	17.42	18.00	18.24	18.83	19.85	17.02	17.59	17.84	18.43	19.45
	12H	17.50	18.02	18.34	18.88	19.90	17.09	17.61	17.93	18.46	19.49
8H	4H	16.96	17.54	17.79	18.37	19.39	16.61	17.18	17.43	18.02	19.04
	6H	17.59	18.07	18.44	18.95	19.97	17.24	17.71	18.09	18.59	19.61
	8H	17.81	18.24	18.67	19.11	20.14	17.45	17.87	18.31	18.74	19.78
	12H	17.95	18.32	18.81	19.18	20.28	17.57	17.94	18.43	18.81	19.90
12H	4H	16.96	17.48	17.80	18.33	19.36	16.61	17.13	17.45	17.99	19.01
	6H	17.62	18.05	18.49	18.92	19.96	17.28	17.70	18.14	18.57	19.61
	8H	17.87	18.25	18.73	19.11	20.20	17.52	17.89	18.38	18.76	19.85