

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904406

Luminaire Tested: DFN2DIP-TR3F0-040D080US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904406
REPORT IS A COMBINATION OF REPORTS P900343 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-040D080US830-FLLFLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10405.7 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 96.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904406

CATALOG NUMBER: DFN2DIP-TR3F0-040D080US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904406

CATALOG NUMBER: DFN2DIP-TR3F0-040D080US830-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	90	87	83	85	82	79	76	66	64	62	52	50	49	38	37	36
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	27	24	22
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	22	20
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1828	1828	1828
5°	1830	1801	1813
10°	1814	1775	1788
15°	1786	1744	1748
20°	1749	1702	1708
25°	1712	1652	1661
30°	1666	1606	1602
35°	1623	1551	1540
40°	1569	1495	1481
45°	1516	1439	1420
50°	1457	1381	1349
55°	1396	1313	1285
60°	1326	1233	1210
65°	1250	1150	1123
70°	1154	1048	1028
75°	1020	927	938
80°	858	771	771
85°	607	507	498

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2328 cd/sqm

TEST NUMBER: P904406

CATALOG NUMBER: DFN2DIP-TR3F0-040D080US830-FLLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.1	1.3
10°-20°	388.5	3.7
20°-30°	570.9	5.5
30°-40°	663.1	6.4
40°-50°	662.3	6.4
50°-60°	577.5	5.5
60°-70°	426.9	4.1
70°-80°	241.5	2.3
80°-90°	70.5	0.7
90°-100°	147.6	1.4
100°-110°	468.9	4.5
110°-120°	802.4	7.7
120°-130°	1055.3	10.1
130°-140°	1184.5	11.4
140°-150°	1161.5	11.2
150°-160°	974.4	9.4
160°-170°	646.2	6.2
170°-180°	225.9	2.2
0°-30°	1097.5	10.5
0°-40°	1760.6	16.9
0°-60°	3000.3	28.8
0°-90°	3739.2	35.9
90°-120°	1418.8	13.6
90°-150°	4820.1	46.3
90°-180°	6666.0	64.1
0°-180°	10405.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1467	1467	1467	1467	1467	
5°	1467	1461	1446	1457	1454	139
15°	1396	1388	1370	1375	1368	393
25°	1264	1253	1229	1231	1229	582
35°	1090	1076	1054	1045	1038	681
45°	887	878	856	841	835	685
55°	672	663	646	629	622	600
65°	453	444	430	418	411	448
75°	237	234	227	219	222	253
85°	58	56	55	51	49	64
90°	2	26	70	66	68	10
95°	105	125	129	129	125	117
105°	433	439	443	446	446	457
115°	805	817	813	811	805	796
125°	1171	1189	1183	1177	1175	1047
135°	1515	1537	1541	1539	1534	1171
145°	1839	1853	1865	1867	1859	1149
155°	2103	2109	2115	2125	2119	968
165°	2288	2286	2286	2300	2290	645
175°	2380	2375	2370	2385	2372	226
180°	2385	2385	2385	2385	2385	

TEST NUMBER: P904406

CATALOG NUMBER: DFN2DIP-TR3F0-040D080US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1467.0	1467.0	1467.0	1467.0	1467.0
2.5°	1475.5	1468.5	1452.9	1467.0	1464.3
5°	1467.0	1461.4	1445.9	1457.1	1454.4
7.5°	1457.1	1448.7	1433.1	1444.5	1441.7
10°	1441.7	1431.8	1414.9	1426.2	1421.9
12.5°	1420.4	1412.0	1395.2	1402.2	1399.3
15°	1396.5	1388.1	1369.7	1375.4	1368.4
17.5°	1366.9	1358.5	1340.1	1347.1	1340.1
20°	1334.4	1326.0	1306.3	1310.4	1304.9
22.5°	1302.0	1289.3	1270.9	1270.9	1268.1
25°	1263.9	1252.6	1228.7	1231.4	1228.7
27.5°	1221.5	1211.6	1193.4	1189.2	1182.2
30°	1179.3	1168.0	1146.9	1142.6	1137.0
32.5°	1134.2	1125.8	1103.2	1094.7	1088.9
35°	1090.4	1076.4	1053.8	1045.3	1038.2
37.5°	1041.0	1028.3	1005.7	995.9	988.8
40°	990.3	978.9	956.3	943.8	938.1
42.5°	940.9	929.5	907.1	892.9	884.5
45°	887.3	877.5	856.2	840.8	835.1
47.5°	835.1	825.2	802.7	787.1	778.7
50°	780.0	773.0	753.3	733.5	726.4
52.5°	726.4	716.6	698.3	682.8	672.9
55°	671.6	663.0	646.1	629.1	622.2
57.5°	616.4	609.4	591.0	574.1	568.4
60°	561.4	555.8	536.1	520.6	516.3
62.5°	507.8	497.9	483.9	469.8	464.1
65°	452.9	444.3	430.3	417.5	410.6
67.5°	396.4	389.3	376.7	366.8	361.2
70°	344.2	338.6	325.8	315.9	310.4
72.5°	290.7	284.9	278.0	268.1	263.8
75°	237.0	234.2	227.1	218.7	221.5
77.5°	189.0	183.3	180.5	176.3	172.1
80°	141.1	139.6	136.8	132.6	129.8
82.5°	96.0	96.0	94.6	88.9	88.9
85°	57.8	56.5	55.0	50.7	49.4
87.5°	25.4	22.6	19.8	15.6	14.0
90°	2.2	25.9	70.5	66.2	68.3
92.5°	44.6	60.4	62.6	64.7	64.7
95°	105.0	125.1	128.7	128.7	125.1
97.5°	174.7	193.4	201.3	201.3	201.3
100°	255.2	271.7	277.5	277.5	275.3
102.5°	340.1	352.3	360.1	362.3	360.1
105°	432.8	438.6	442.9	446.5	446.5
107.5°	524.8	533.5	533.5	534.9	524.8
110°	614.0	625.5	625.5	625.5	619.7

TEST NUMBER: P904406

CATALOG NUMBER: DFN2DIP-TR3F0-040D080US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	710.3	722.6	720.4	714.6	710.3
115°	805.2	816.7	813.1	811.0	805.2
117.5°	899.4	915.2	905.1	899.4	893.6
120°	994.3	1010.1	994.3	994.3	987.8
122.5°	1080.5	1100.7	1090.6	1084.9	1080.5
125°	1171.1	1189.1	1183.4	1176.9	1174.8
127.5°	1259.6	1281.9	1273.9	1265.4	1259.6
130°	1342.3	1368.1	1364.5	1360.3	1352.4
132.5°	1435.0	1455.1	1456.6	1446.5	1440.8
135°	1514.8	1537.1	1541.4	1539.3	1533.5
137.5°	1603.9	1621.9	1625.5	1624.1	1615.4
140°	1682.3	1700.3	1710.3	1710.3	1702.4
142.5°	1762.8	1780.8	1786.6	1788.8	1780.8
145°	1839.1	1853.4	1864.9	1867.1	1859.2
147.5°	1907.3	1925.3	1933.9	1937.6	1929.7
150°	1977.8	1990.0	1997.9	2004.4	1997.9
152.5°	2040.3	2052.6	2062.7	2070.6	2062.7
155°	2102.9	2108.7	2115.2	2125.2	2118.7
157.5°	2156.8	2161.2	2164.7	2179.1	2169.1
160°	2205.0	2209.3	2211.5	2223.6	2215.1
162.5°	2249.6	2249.6	2251.7	2265.4	2255.3
165°	2287.6	2285.5	2285.5	2299.9	2289.8
167.5°	2322.1	2315.7	2315.7	2330.1	2320.0
170°	2348.1	2342.3	2340.1	2354.6	2342.3
172.5°	2366.1	2360.3	2358.1	2372.5	2360.3
175°	2380.4	2374.6	2370.3	2384.7	2372.5
177.5°	2388.3	2382.6	2378.2	2390.5	2378.2
180°	2384.7	2384.7	2384.7	2384.7	2384.7

TEST NUMBER: P904406

CATALOG NUMBER: DFN2DIP-TR3F0-040D080US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.85	8.60	8.92	9.67	11.13	7.42	8.17	8.49	9.24	10.70
	3H	9.49	10.16	10.57	11.24	12.72	9.03	9.70	10.10	10.78	12.25
	4H	10.07	10.71	11.16	11.79	13.27	9.60	10.24	10.69	11.32	12.80
	6H	10.46	11.04	11.56	12.13	13.62	9.99	10.57	11.09	11.66	13.15
	8H	10.55	11.11	11.66	12.21	13.70	10.09	10.64	11.19	11.74	13.23
	12H	10.60	11.12	11.70	12.22	13.73	10.12	10.65	11.23	11.74	13.26
4H	2H	8.30	8.93	9.39	10.01	11.50	7.95	8.59	9.05	9.67	11.15
	3H	10.14	10.67	11.24	11.78	13.27	9.75	10.28	10.85	11.39	12.89
	4H	10.84	11.33	11.95	12.43	13.94	10.44	10.93	11.55	12.03	13.54
	6H	11.34	11.76	12.46	12.88	14.39	10.94	11.36	12.05	12.48	13.99
	8H	11.49	11.88	12.60	12.99	14.51	11.08	11.47	12.19	12.58	14.11
	12H	11.55	11.90	12.68	13.03	14.56	11.13	11.49	12.27	12.61	14.14
8H	4H	11.03	11.42	12.14	12.53	14.06	10.67	11.06	11.78	12.17	13.70
	6H	11.64	11.96	12.78	13.12	14.64	11.28	11.61	12.42	12.76	14.28
	8H	11.86	12.14	13.00	13.27	14.82	11.49	11.77	12.63	12.91	14.45
	12H	11.98	12.22	13.12	13.36	14.93	11.60	11.84	12.74	12.98	14.56
12H	4H	11.01	11.36	12.14	12.48	14.02	10.66	11.01	11.79	12.14	13.67
	6H	11.67	11.95	12.81	13.09	14.63	11.32	11.60	12.46	12.74	14.28
	8H	11.90	12.15	13.05	13.28	14.86	11.55	11.79	12.69	12.93	14.50