

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912664

Luminaire Tested: DFN2DIP-TR3F0-070D070US850-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912664
REPORT IS A COMBINATION OF REPORTS P900335 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-070D070US850-FLLFLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14555.7 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 123.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912664
CATALOG NUMBER: DFN2DIP-TR3F0-070D070US850-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P912664

CATALOG NUMBER: DFN2DIP-TR3F0-070D070US850-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53			
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50	45			
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	37			
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	32			
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31	27			
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27	24			
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	21			
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21	18			
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19	16			
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15			
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3764	3764	3764
5°	3768	3708	3734
10°	3735	3655	3681
15°	3678	3592	3599
20°	3602	3505	3516
25°	3526	3402	3420
30°	3431	3306	3299
35°	3342	3193	3171
40°	3231	3078	3048
45°	3121	2964	2923
50°	3001	2843	2779
55°	2874	2704	2645
60°	2731	2539	2492
65°	2575	2367	2311
70°	2376	2158	2116
75°	2100	1907	1932
80°	1768	1587	1588
85°	1249	1046	1025

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3121 cd/sqm



TEST NUMBER: P912664

CATALOG NUMBER: DFN2DIP-TR3F0-070D070US850-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.3	2.0
10°-20°	799.9	5.5
20°-30°	1175.6	8.1
30°-40°	1365.3	9.4
40°-50°	1363.6	9.4
50°-60°	1189.1	8.2
60°-70°	879.0	6.0
70°-80°	497.3	3.4
80°-90°	138.2	0.9
90°-100°	151.9	1.0
100°-110°	482.7	3.3
110°-120°	826.1	5.7
120°-130°	1086.4	7.5
130°-140°	1219.5	8.4
140°-150°	1195.8	8.2
150°-160°	1003.1	6.9
160°-170°	665.3	4.6
170°-180°	232.5	1.6
0°-30°	2259.8	15.5
0°-40°	3625.1	24.9
0°-60°	6177.8	42.4
0°-90°	7692.3	52.8
90°-120°	1460.7	10.0
90°-150°	4962.4	34.1
90°-180°	6863.0	47.2
0°-180°	14555.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3021	3021	3021	3021	3021	
5°	3021	3009	2977	3000	2995	287
15°	2876	2858	2820	2832	2818	810
25°	2602	2579	2530	2536	2530	1198
35°	2245	2216	2170	2152	2138	1402
45°	1827	1807	1763	1731	1720	1410
55°	1383	1365	1330	1296	1281	1236
65°	933	915	886	860	845	922
75°	488	482	467	450	456	521
85°	119	116	114	104	102	133
90°	2	27	72	68	70	14
95°	108	129	132	132	129	120
105°	446	452	456	460	460	470
115°	829	841	837	835	829	820
125°	1206	1224	1218	1212	1210	1077
135°	1560	1582	1587	1585	1579	1205
145°	1893	1908	1920	1922	1914	1183
155°	2165	2171	2178	2188	2181	997
165°	2355	2353	2353	2368	2357	664
175°	2451	2445	2440	2455	2443	233
180°	2455	2455	2455	2455	2455	



TEST NUMBER: P912664

CATALOG NUMBER: DFN2DIP-TR3F0-070D070US850-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3020.6	3020.6	3020.6	3020.6	3020.6
2.5°	3038.2	3023.7	2991.6	3020.6	3015.0
5°	3020.6	3009.3	2977.2	3000.3	2994.7
7.5°	3000.3	2983.0	2950.9	2974.4	2968.6
10°	2968.6	2948.2	2913.3	2936.5	2927.9
12.5°	2924.8	2907.6	2872.8	2887.2	2881.3
15°	2875.5	2858.2	2820.3	2832.1	2817.5
17.5°	2814.4	2797.2	2759.3	2773.8	2759.3
20°	2747.5	2730.4	2689.7	2698.3	2686.9
22.5°	2681.0	2654.8	2616.9	2616.9	2611.0
25°	2602.5	2579.3	2530.1	2535.6	2530.1
27.5°	2515.2	2494.9	2457.3	2448.7	2434.1
30°	2428.4	2404.9	2361.5	2352.9	2341.1
32.5°	2335.2	2318.0	2271.5	2253.9	2242.2
35°	2245.3	2216.3	2169.8	2152.2	2137.7
37.5°	2143.6	2117.4	2070.8	2050.5	2036.0
40°	2039.1	2015.7	1969.1	1943.3	1931.5
42.5°	1937.4	1914.0	1867.8	1838.5	1821.2
45°	1827.1	1806.8	1763.0	1731.3	1719.5
47.5°	1719.5	1699.2	1652.6	1620.6	1603.4
50°	1606.2	1591.6	1550.9	1510.3	1495.8
52.5°	1495.8	1475.5	1437.9	1405.9	1385.5
55°	1382.7	1365.2	1330.4	1295.5	1281.0
57.5°	1269.4	1254.8	1216.9	1182.1	1170.4
60°	1155.9	1144.5	1103.9	1071.8	1063.2
62.5°	1045.6	1025.3	996.3	967.4	955.6
65°	932.6	914.9	886.0	859.8	845.3
67.5°	816.3	801.6	775.6	755.3	743.6
70°	708.8	697.1	670.8	650.5	639.1
72.5°	598.4	586.8	572.2	551.9	543.3
75°	487.8	482.3	467.4	450.3	456.1
77.5°	389.3	377.5	371.6	363.0	354.4
80°	290.6	287.6	281.7	273.0	267.2
82.5°	197.5	197.5	194.7	183.1	183.1
85°	119.0	116.2	113.5	104.5	101.7
87.5°	52.3	46.6	40.7	32.1	28.9
90°	2.2	26.6	72.5	68.1	70.3
92.5°	45.9	62.2	64.4	66.7	66.7
95°	108.0	128.8	132.5	132.5	128.8
97.5°	179.9	199.1	207.3	207.3	207.3
100°	262.7	279.8	285.7	285.7	283.5
102.5°	350.1	362.6	370.8	373.1	370.8
105°	445.6	451.5	455.9	459.7	459.7
107.5°	540.3	549.2	549.2	550.7	540.3
110°	632.1	644.0	644.0	644.0	638.0



TEST NUMBER: P912664

CATALOG NUMBER: DFN2DIP-TR3F0-070D070US850-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	731.3	743.9	741.7	735.7	731.3
115°	829.0	840.8	837.2	835.0	829.0
117.5°	925.9	942.2	931.9	925.9	920.0
120°	1023.6	1039.9	1023.6	1023.6	1017.0
122.5°	1112.4	1133.2	1122.9	1116.9	1112.4
125°	1205.7	1224.2	1218.3	1211.7	1209.5
127.5°	1296.8	1319.7	1311.6	1302.7	1296.8
130°	1381.9	1408.5	1404.9	1400.4	1392.2
132.5°	1477.4	1498.1	1499.6	1489.3	1483.3
135°	1559.6	1582.4	1587.0	1584.7	1578.8
137.5°	1651.3	1669.8	1673.5	1672.0	1663.2
140°	1732.0	1750.6	1760.9	1760.9	1752.8
142.5°	1814.9	1833.4	1839.3	1841.5	1833.4
145°	1893.4	1908.1	1920.0	1922.2	1914.1
147.5°	1963.7	1982.2	1991.1	1994.8	1986.7
150°	2036.2	2048.8	2057.0	2063.6	2057.0
152.5°	2100.6	2113.2	2123.5	2131.7	2123.5
155°	2165.0	2170.9	2177.6	2187.9	2181.3
157.5°	2220.6	2225.0	2228.6	2243.5	2233.1
160°	2270.1	2274.6	2276.8	2289.3	2280.4
162.5°	2316.0	2316.0	2318.3	2332.2	2321.9
165°	2355.2	2353.0	2353.0	2367.8	2357.4
167.5°	2390.8	2384.1	2384.1	2398.9	2388.6
170°	2417.4	2411.5	2409.3	2424.1	2411.5
172.5°	2435.9	2429.9	2427.7	2442.6	2429.9
175°	2450.7	2444.8	2440.4	2455.1	2442.6
177.5°	2458.9	2452.9	2448.5	2461.1	2448.5
180°	2455.1	2455.1	2455.1	2455.1	2455.1



TEST NUMBER: P912664
 CATALOG NUMBER: DFN2DIP-TR3F0-070D070US850-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.08	12.97	13.02	13.92	15.15	11.66	12.54	12.59	13.49	14.72
	3H	13.74	14.53	14.68	15.49	16.75	13.27	14.06	14.21	15.02	16.28
	4H	14.32	15.07	15.28	16.04	17.30	13.85	14.60	14.81	15.57	16.83
	6H	14.71	15.41	15.68	16.38	17.65	14.24	14.94	15.21	15.91	17.18
	8H	14.82	15.48	15.79	16.46	17.73	14.35	15.01	15.32	15.99	17.27
	12H	14.86	15.49	15.84	16.47	17.77	14.39	15.02	15.37	16.00	17.29
4H	2H	12.54	13.30	13.51	14.26	15.52	12.20	12.96	13.17	13.92	15.18
	3H	14.40	15.03	15.38	16.02	17.30	14.01	14.64	14.99	15.64	16.91
	4H	15.11	15.69	16.09	16.67	17.97	14.71	15.28	15.69	16.27	17.57
	6H	15.62	16.11	16.61	17.12	18.42	15.21	15.71	16.21	16.72	18.02
	8H	15.76	16.23	16.76	17.23	18.54	15.36	15.82	16.35	16.82	18.14
	12H	15.83	16.25	16.85	17.27	18.59	15.42	15.84	16.43	16.86	18.17
8H	4H	15.31	15.77	16.30	16.77	18.08	14.95	15.41	15.94	16.41	17.73
	6H	15.93	16.31	16.95	17.36	18.67	15.57	15.95	16.59	17.00	18.31
	8H	16.14	16.48	17.17	17.51	18.84	15.78	16.12	16.81	17.15	18.48
	12H	16.27	16.57	17.30	17.59	18.97	15.89	16.19	16.92	17.21	18.59
12H	4H	15.29	15.71	16.31	16.73	18.05	14.94	15.36	15.96	16.38	17.70
	6H	15.96	16.29	16.98	17.32	18.65	15.61	15.95	16.64	16.98	18.31
	8H	16.19	16.49	17.22	17.51	18.89	15.84	16.14	16.87	17.16	18.54