

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912697

Luminaire Tested: DFN2DIP-TR3F0-080D080US850-RLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P912697  
REPORT IS A COMBINATION OF REPORTS P901872 AND P898751  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR3F0-080D080US850-RLLONL  
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 16324.5 lumens  
Efficiency: N/A  
Efficacy: 115.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 142  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P912697  
CATALOG NUMBER: DFN2DIP-TR3F0-080D080US850-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P912697

CATALOG NUMBER: DFN2DIP-TR3F0-080D080US850-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53				46
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45				40
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39				34
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34				29
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29				26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26				23
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23				20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21				18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19				16
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17				15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15				13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4569	4569	4569
5°	4574	4493	4522
10°	4526	4401	4372
15°	4461	4252	4142
20°	4376	4048	3860
25°	4289	3820	3589
30°	4173	3586	3245
35°	4060	3335	2943
40°	3944	3076	2598
45°	3809	2790	2285
50°	3670	2500	1979
55°	3524	2192	1686
60°	3355	1870	1385
65°	3161	1543	1243
70°	2925	1238	1120
75°	2629	1083	1013
80°	2199	896	868
85°	1497	581	635

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3809 cd/sqm



TEST NUMBER: P912697

CATALOG NUMBER: DFN2DIP-TR3F0-080D080US850-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	343.7	2.1
10°-20°	943.4	5.8
20°-30°	1324.5	8.1
30°-40°	1443.8	8.8
40°-50°	1327.0	8.1
50°-60°	1042.1	6.4
60°-70°	678.3	4.2
70°-80°	349.2	2.1
80°-90°	94.4	0.6
90°-100°	98.7	0.6
100°-110°	368.1	2.3
110°-120°	976.2	6.0
120°-130°	1619.0	9.9
130°-140°	1719.8	10.5
140°-150°	1598.3	9.8
150°-160°	1285.0	7.9
160°-170°	828.0	5.1
170°-180°	285.0	1.7
0°-30°	2611.6	16.0
0°-40°	4055.4	24.8
0°-60°	6424.5	39.4
0°-90°	7546.5	46.2
90°-120°	1442.9	8.8
90°-150°	6380.0	39.1
90°-180°	8778.0	53.8
0°-180°	16324.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3667	3667	3667	3667	3667	
5°	3667	3650	3607	3637	3627	348
15°	3488	3451	3338	3275	3242	983
25°	3166	3060	2840	2705	2655	1456
35°	2728	2558	2267	2058	1984	1707
45°	2230	2008	1659	1423	1344	1722
55°	1696	1437	1078	879	816	1515
65°	1145	876	577	465	454	1135
75°	610	378	266	242	239	646
85°	143	73	63	63	63	164
90°	2	26	43	54	58	15
95°	141	69	84	96	93	167
105°	659	724	132	156	165	704
115°	1246	1283	1337	334	178	1226
125°	1761	1790	1831	1846	1852	1571
135°	2180	2214	2234	2256	2251	1684
145°	2528	2526	2563	2578	2567	1581
155°	2784	2765	2791	2804	2786	1283
165°	2934	2921	2927	2942	2927	829
175°	3001	2985	2990	3005	2983	286
180°	2994	2994	2994	2994	2994	



TEST NUMBER: P912697

CATALOG NUMBER: DFN2DIP-TR3F0-080D080US850-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3666.8	3666.8	3666.8	3666.8	3666.8
2.5°	3683.3	3666.8	3630.2	3663.6	3656.9
5°	3666.8	3650.3	3606.9	3636.9	3627.0
7.5°	3636.9	3617.1	3570.6	3583.7	3567.1
10°	3597.0	3573.9	3507.7	3497.5	3477.7
12.5°	3547.5	3517.5	3427.7	3408.0	3371.4
15°	3487.6	3451.0	3338.3	3275.3	3242.2
17.5°	3417.8	3364.7	3225.3	3152.4	3099.2
20°	3338.3	3271.8	3106.0	3023.2	2949.9
22.5°	3252.0	3175.6	2983.1	2870.4	2820.7
25°	3165.8	3059.5	2840.5	2704.6	2654.6
27.5°	3062.9	2949.9	2707.7	2551.8	2475.4
30°	2953.5	2827.1	2561.7	2392.7	2302.8
32.5°	2847.1	2694.4	2422.6	2223.3	2140.3
35°	2727.8	2558.5	2266.6	2057.5	1984.2
37.5°	2611.6	2428.9	2120.5	1891.3	1808.6
40°	2488.8	2289.9	1967.7	1732.1	1645.9
42.5°	2362.7	2150.5	1815.2	1569.6	1486.7
45°	2230.0	2007.5	1659.3	1423.4	1343.9
47.5°	2104.0	1868.4	1510.0	1274.1	1201.3
50°	1964.5	1729.0	1364.0	1134.7	1065.3
52.5°	1828.3	1579.3	1224.4	1005.5	942.5
55°	1695.6	1436.8	1078.4	879.4	816.4
57.5°	1559.7	1294.2	949.2	763.3	710.1
60°	1420.2	1154.8	812.9	643.9	590.8
62.5°	1284.3	1018.8	696.8	537.6	511.2
65°	1144.9	875.9	577.3	464.8	454.5
67.5°	1012.2	743.3	464.8	408.0	398.2
70°	872.8	614.1	384.8	351.7	338.4
72.5°	740.0	494.3	321.8	295.4	288.7
75°	610.5	378.2	265.5	242.2	239.1
77.5°	481.3	268.6	209.2	195.7	189.1
80°	361.5	192.6	159.1	146.1	146.1
82.5°	252.1	129.5	109.5	102.8	102.8
85°	142.6	72.9	63.0	63.0	63.0
87.5°	53.1	26.4	26.4	23.3	23.3
90°	2.1	26.0	43.3	54.2	58.4
92.5°	54.2	45.6	52.0	56.3	58.4
95°	140.7	69.2	84.4	95.5	93.2
97.5°	253.4	75.9	110.3	117.1	119.1
100°	383.6	86.7	123.5	140.7	145.1
102.5°	526.4	522.2	127.9	151.5	158.3
105°	658.6	723.7	132.2	155.9	164.7
107.5°	812.5	866.5	136.6	160.3	169.0
110°	960.0	1005.2	379.3	162.6	171.1



TEST NUMBER: P912697

CATALOG NUMBER: DFN2DIP-TR3F0-080D080US850-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1098.6	1137.4	1100.7	166.7	173.4
115°	1245.7	1282.6	1336.8	333.7	177.8
117.5°	1373.6	1416.9	1453.9	1143.8	576.3
120°	1516.7	1549.1	1588.2	1614.1	1321.6
122.5°	1637.8	1672.6	1716.1	1728.9	1731.3
125°	1761.3	1789.6	1830.7	1845.9	1852.4
127.5°	1874.0	1904.4	1937.1	1958.6	1960.7
130°	1980.2	2014.9	2038.7	2062.6	2060.5
132.5°	2088.6	2116.9	2140.6	2160.1	2158.0
135°	2179.6	2214.3	2233.6	2255.6	2251.2
137.5°	2274.9	2300.8	2322.7	2344.3	2337.9
140°	2367.9	2385.5	2409.2	2428.7	2417.8
142.5°	2446.2	2461.3	2489.4	2506.7	2495.8
145°	2528.5	2526.2	2563.0	2578.2	2567.3
147.5°	2599.8	2593.4	2630.1	2641.0	2632.4
150°	2669.3	2654.1	2688.8	2701.6	2690.9
152.5°	2727.7	2710.4	2742.8	2756.0	2740.8
155°	2784.0	2764.7	2790.7	2803.6	2786.4
157.5°	2829.5	2812.3	2831.8	2847.0	2829.5
160°	2868.7	2855.6	2868.7	2881.5	2866.3
162.5°	2903.1	2890.3	2901.0	2916.2	2896.7
165°	2933.5	2920.7	2927.1	2942.2	2927.1
167.5°	2957.4	2944.3	2950.9	2966.1	2946.6
170°	2977.0	2963.8	2968.2	2983.4	2963.8
172.5°	2989.9	2977.0	2981.3	2996.5	2977.0
175°	3000.6	2985.4	2989.9	3004.9	2983.4
177.5°	3004.9	2989.9	2992.1	3007.3	2987.8
180°	2994.2	2994.2	2994.2	2994.2	2994.2



TEST NUMBER: P912697  
 CATALOG NUMBER: DFN2DIP-TR3F0-080D080US850-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.01	12.81	13.01	13.81	15.14	7.99	8.79	8.98	9.79	11.12
	3H	13.68	14.39	14.68	15.40	16.75	9.17	9.88	10.17	10.90	12.24
	4H	14.28	14.95	15.30	15.97	17.33	9.61	10.29	10.63	11.31	12.66
	6H	14.69	15.31	15.72	16.33	17.70	9.93	10.55	10.96	11.57	12.94
	8H	14.81	15.40	15.85	16.44	17.80	10.02	10.61	11.05	11.64	13.01
	12H	14.87	15.43	15.91	16.46	17.85	10.06	10.62	11.09	11.65	13.03
4H	2H	12.02	12.70	13.05	13.72	15.07	8.57	9.25	9.60	10.27	11.62
	3H	13.84	14.40	14.87	15.45	16.81	9.91	10.48	10.95	11.52	12.89
	4H	14.52	15.04	15.56	16.07	17.47	10.46	10.97	11.50	12.01	13.40
	6H	15.03	15.47	16.08	16.53	17.92	10.87	11.31	11.92	12.37	13.76
	8H	15.20	15.61	16.25	16.66	18.06	10.99	11.41	12.04	12.46	13.86
	12H	15.29	15.66	16.35	16.72	18.13	11.05	11.43	12.12	12.49	13.90
8H	4H	14.49	14.90	15.54	15.95	17.35	10.73	11.14	11.78	12.19	13.60
	6H	15.04	15.38	16.12	16.48	17.88	11.24	11.58	12.31	12.67	14.07
	8H	15.25	15.55	16.33	16.63	18.05	11.43	11.72	12.51	12.80	14.22
	12H	15.38	15.65	16.47	16.72	18.18	11.54	11.80	12.62	12.87	14.33
12H	4H	14.44	14.81	15.51	15.88	17.28	10.73	11.10	11.80	12.17	13.58
	6H	15.02	15.32	16.10	16.39	17.81	11.29	11.58	12.37	12.66	14.08
	8H	15.23	15.49	16.31	16.57	18.03	11.49	11.75	12.57	12.82	14.28