

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915308

Luminaire Tested: DFN2DIP-TR3F0-040D050US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915308
REPORT IS A COMBINATION OF REPORTS P900302 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-040D050US927-RLLFLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6198.8 lumens
Efficiency: N/A
Efficacy: 86.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 72.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915308

CATALOG NUMBER: DFN2DIP-TR3F0-040D050US927-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P915308

CATALOG NUMBER: DFN2DIP-TR3F0-040D050US927-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44		
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43	37		
2	88	81	75	71	81	75	70	65	62	59	55	51	48	46	40	38	37	32		
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28		
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28	24		
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	29	27	25	21		
6	63	51	43	38	57	47	41	35	40	35	31	33	29	26	27	24	22	19		
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17		
8	54	42	35	30	50	39	32	28	33	28	24	28	24	21	23	20	18	15		
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14		
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1632	1632	1632
5°	1634	1605	1615
10°	1617	1572	1562
15°	1593	1519	1479
20°	1563	1446	1379
25°	1532	1364	1282
30°	1491	1281	1159
35°	1450	1191	1051
40°	1409	1099	928
45°	1361	996	816
50°	1311	893	707
55°	1259	783	602
60°	1198	668	495
65°	1129	551	444
70°	1045	442	400
75°	939	387	362
80°	785	320	310
85°	534	207	227

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1361 cd/sqm

TEST NUMBER: P915308

CATALOG NUMBER: DFN2DIP-TR3F0-040D050US927-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.7	2.0
10°-20°	336.9	5.4
20°-30°	473.1	7.6
30°-40°	515.7	8.3
40°-50°	473.9	7.6
50°-60°	372.2	6.0
60°-70°	242.3	3.9
70°-80°	124.7	2.0
80°-90°	35.4	0.6
90°-100°	77.5	1.3
100°-110°	246.3	4.0
110°-120°	421.5	6.8
120°-130°	554.3	8.9
130°-140°	622.2	10.0
140°-150°	610.1	9.8
150°-160°	511.8	8.3
160°-170°	339.4	5.5
170°-180°	118.6	1.9
0°-30°	932.7	15.0
0°-40°	1448.4	23.4
0°-60°	2294.6	37.0
0°-90°	2696.9	43.5
90°-120°	745.3	12.0
90°-150°	2532.0	40.8
90°-180°	3502.0	56.5
0°-180°	6198.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1310	1310	1310	1310	1310	
5°	1310	1304	1288	1299	1296	124
15°	1246	1233	1192	1170	1158	351
25°	1131	1093	1014	966	948	520
35°	974	914	810	735	709	610
45°	796	717	593	508	480	615
55°	606	513	385	314	292	541
65°	409	313	206	166	162	405
75°	218	135	95	86	85	231
85°	51	26	22	22	22	58
90°	1	14	37	35	36	6
95°	55	66	68	68	66	61
105°	227	230	233	234	234	240
115°	423	429	427	426	423	418
125°	615	625	622	618	617	550
135°	796	807	810	809	806	615
145°	966	974	980	981	977	604
155°	1105	1108	1111	1116	1113	508
165°	1202	1201	1201	1208	1203	339
175°	1250	1247	1245	1253	1246	119
180°	1253	1253	1253	1253	1253	

TEST NUMBER: P915308

CATALOG NUMBER: DFN2DIP-TR3F0-040D050US927-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1309.6	1309.6	1309.6	1309.6	1309.6
2.5°	1315.6	1309.6	1296.6	1308.5	1306.1
5°	1309.6	1303.7	1288.2	1298.9	1295.5
7.5°	1298.9	1291.9	1275.3	1279.9	1274.1
10°	1284.8	1276.4	1252.8	1249.1	1242.1
12.5°	1267.0	1256.3	1224.2	1217.2	1204.1
15°	1245.6	1232.6	1192.3	1169.8	1158.0
17.5°	1220.8	1201.7	1151.9	1125.9	1106.9
20°	1192.3	1168.5	1109.3	1079.7	1053.6
22.5°	1161.5	1134.2	1065.4	1025.2	1007.5
25°	1130.7	1092.7	1014.5	966.0	948.1
27.5°	1094.0	1053.6	967.1	911.4	884.1
30°	1054.9	1009.7	914.9	854.5	822.5
32.5°	1016.9	962.3	865.2	794.1	764.4
35°	974.3	913.8	809.5	734.8	708.7
37.5°	932.8	867.5	757.3	675.5	645.9
40°	888.9	817.8	702.8	618.7	587.9
42.5°	843.8	768.0	648.3	560.5	531.0
45°	796.5	717.0	592.6	508.4	480.0
47.5°	751.5	667.3	539.3	455.1	429.0
50°	701.6	617.5	487.1	405.3	380.5
52.5°	653.0	564.1	437.4	359.1	336.6
55°	605.6	513.2	385.2	314.1	291.6
57.5°	557.1	462.2	339.0	272.6	253.7
60°	507.2	412.4	290.3	230.0	211.0
62.5°	458.8	363.9	248.8	192.0	182.6
65°	408.9	312.8	206.2	166.0	162.3
67.5°	361.6	265.5	166.0	145.8	142.2
70°	311.7	219.3	137.4	125.6	120.8
72.5°	264.4	176.6	114.9	105.5	103.1
75°	218.0	135.1	94.8	86.5	85.4
77.5°	171.9	95.9	74.7	69.9	67.5
80°	129.1	68.8	56.8	52.2	52.2
82.5°	90.1	46.3	39.1	36.7	36.7
85°	50.9	26.1	22.5	22.5	22.5
87.5°	19.0	9.4	9.4	8.3	8.3
90°	1.1	13.6	37.0	34.8	35.9
92.5°	23.4	31.7	32.9	34.0	34.0
95°	55.1	65.8	67.6	67.6	65.8
97.5°	91.7	101.6	105.8	105.8	105.8
100°	134.0	142.8	145.8	145.8	144.7
102.5°	178.6	185.1	189.2	190.4	189.2
105°	227.4	230.4	232.7	234.5	234.5
107.5°	275.7	280.2	280.2	281.0	275.7
110°	322.5	328.6	328.6	328.6	325.5

TEST NUMBER: P915308

CATALOG NUMBER: DFN2DIP-TR3F0-040D050US927-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	373.1	379.5	378.4	375.4	373.1
115°	422.9	429.0	427.1	426.0	422.9
117.5°	472.5	480.8	475.5	472.5	469.4
120°	522.3	530.6	522.3	522.3	518.9
122.5°	567.6	578.2	572.9	569.9	567.6
125°	615.2	624.6	621.6	618.2	617.1
127.5°	661.6	673.4	669.2	664.6	661.6
130°	705.1	718.7	716.8	714.5	710.3
132.5°	753.8	764.4	765.2	759.9	756.8
135°	795.7	807.4	809.7	808.6	805.6
137.5°	842.6	852.0	853.9	853.1	848.6
140°	883.7	893.2	898.4	898.4	894.3
142.5°	926.0	935.5	938.5	939.6	935.5
145°	966.1	973.6	979.6	980.8	976.6
147.5°	1002.0	1011.4	1015.9	1017.8	1013.6
150°	1038.9	1045.4	1049.5	1052.9	1049.5
152.5°	1071.8	1078.2	1083.5	1087.7	1083.5
155°	1104.6	1107.6	1111.0	1116.3	1112.9
157.5°	1133.0	1135.2	1137.1	1144.7	1139.4
160°	1158.2	1160.5	1161.7	1168.1	1163.6
162.5°	1181.7	1181.7	1182.8	1190.0	1184.7
165°	1201.7	1200.6	1200.6	1208.2	1202.8
167.5°	1219.8	1216.4	1216.4	1224.0	1218.7
170°	1233.4	1230.4	1229.3	1236.8	1230.4
172.5°	1242.9	1239.8	1238.7	1246.3	1239.8
175°	1250.5	1247.4	1245.2	1252.7	1246.3
177.5°	1254.6	1251.6	1249.3	1255.7	1249.3
180°	1252.7	1252.7	1252.7	1252.7	1252.7

TEST NUMBER: P915308

CATALOG NUMBER: DFN2DIP-TR3F0-040D050US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.16	8.94	9.17	9.96	11.32	4.13	4.91	5.15	5.94	7.30
	3H	9.82	10.52	10.85	11.55	12.93	5.31	6.01	6.34	7.04	8.43
	4H	10.42	11.08	11.46	12.11	13.51	5.76	6.42	6.80	7.45	8.84
	6H	10.83	11.44	11.88	12.48	13.88	6.07	6.68	7.12	7.72	9.12
	8H	10.95	11.53	12.01	12.58	13.98	6.16	6.73	7.21	7.79	9.19
	12H	11.01	11.56	12.07	12.61	14.03	6.20	6.75	7.26	7.79	9.21
4H	2H	8.17	8.83	9.21	9.86	11.25	4.72	5.38	5.76	6.41	7.80
	3H	9.98	10.53	11.04	11.59	13.00	6.06	6.61	7.11	7.67	9.07
	4H	10.67	11.17	11.73	12.22	13.65	6.60	7.10	7.66	8.15	9.58
	6H	11.17	11.60	12.24	12.68	14.10	7.01	7.44	8.08	8.52	9.94
	8H	11.34	11.74	12.41	12.81	14.24	7.13	7.54	8.20	8.60	10.04
	12H	11.42	11.79	12.51	12.87	14.31	7.19	7.56	8.28	8.64	10.08
8H	4H	10.63	11.03	11.70	12.10	13.53	6.87	7.27	7.94	8.34	9.78
	6H	11.18	11.51	12.27	12.62	14.06	7.38	7.71	8.47	8.82	10.25
	8H	11.39	11.68	12.49	12.78	14.23	7.56	7.85	8.66	8.95	10.40
	12H	11.52	11.78	12.62	12.87	14.36	7.68	7.93	8.78	9.02	10.51
12H	4H	10.58	10.94	11.66	12.02	13.46	6.87	7.23	7.96	8.32	9.76
	6H	11.16	11.45	12.26	12.54	13.99	7.42	7.72	8.52	8.81	10.26
	8H	11.37	11.62	12.47	12.71	14.21	7.63	7.88	8.73	8.97	10.46