

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907094

Luminaire Tested: DFN2DIP-TR3F0-030D040US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907094
REPORT IS A COMBINATION OF REPORTS P900286 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-030D040US835-RLLFLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6090.0 lumens
Efficiency: N/A
Efficacy: 113.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 53.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907094

CATALOG NUMBER: DFN2DIP-TR3F0-030D040US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P907094

CATALOG NUMBER: DFN2DIP-TR3F0-030D040US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	44	43	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	81	72	65	59	73	66	60	55	55	50	47	44	41	39	35	33	31
4	74	64	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	40	34	30	33	29	26	26	23	21
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	28	33	28	24	27	23	21	22	19	17
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	20	18	16
10	47	35	28	24	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1545	1545	1545
5°	1547	1519	1529
10°	1530	1488	1478
15°	1509	1438	1401
20°	1480	1369	1305
25°	1450	1292	1213
30°	1411	1213	1097
35°	1373	1128	995
40°	1334	1040	878
45°	1288	943	773
50°	1241	845	669
55°	1192	741	570
60°	1135	632	468
65°	1069	522	420
70°	989	419	379
75°	889	366	342
80°	744	303	294
85°	506	196	215

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1288 cd/sqm

TEST NUMBER: P907094

CATALOG NUMBER: DFN2DIP-TR3F0-030D040US835-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.2	1.9
10°-20°	319.0	5.2
20°-30°	447.9	7.4
30°-40°	488.2	8.0
40°-50°	448.7	7.4
50°-60°	352.4	5.8
60°-70°	229.4	3.8
70°-80°	118.1	1.9
80°-90°	33.7	0.6
90°-100°	78.3	1.3
100°-110°	248.7	4.1
110°-120°	425.6	7.0
120°-130°	559.8	9.2
130°-140°	628.3	10.3
140°-150°	616.2	10.1
150°-160°	516.9	8.5
160°-170°	342.8	5.6
170°-180°	119.8	2.0
0°-30°	883.1	14.5
0°-40°	1371.3	22.5
0°-60°	2172.4	35.7
0°-90°	2553.6	41.9
90°-120°	752.7	12.4
90°-150°	2556.9	42.0
90°-180°	3536.0	58.1
0°-180°	6090.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1240	1240	1240	1240	1240	
5°	1240	1234	1220	1230	1226	118
15°	1179	1167	1129	1108	1096	332
25°	1070	1034	960	914	898	492
35°	922	865	766	696	671	577
45°	754	679	561	481	454	582
55°	573	486	365	297	276	512
65°	387	296	195	157	154	384
75°	206	128	90	82	81	218
85°	48	25	21	21	21	55
90°	1	14	37	35	36	6
95°	56	66	68	68	66	62
105°	230	233	235	237	237	242
115°	427	433	431	430	427	422
125°	621	631	628	624	623	555
135°	804	815	818	816	814	621
145°	976	983	989	990	986	610
155°	1116	1119	1122	1127	1124	513
165°	1214	1212	1212	1220	1215	342
175°	1263	1260	1257	1265	1259	120
180°	1265	1265	1265	1265	1265	

TEST NUMBER: P907094

CATALOG NUMBER: DFN2DIP-TR3F0-030D040US835-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1239.9	1239.9	1239.9	1239.9	1239.9
2.5°	1245.5	1239.9	1227.5	1238.8	1236.6
5°	1239.9	1234.3	1219.7	1229.8	1226.4
7.5°	1229.8	1223.1	1207.4	1211.8	1206.2
10°	1216.3	1208.5	1186.1	1182.6	1176.0
12.5°	1199.5	1189.4	1159.1	1152.4	1140.0
15°	1179.3	1166.9	1128.8	1107.5	1096.3
17.5°	1155.7	1137.8	1090.6	1066.0	1048.0
20°	1128.8	1106.3	1050.2	1022.3	997.5
22.5°	1099.7	1073.8	1008.7	970.6	953.8
25°	1070.5	1034.5	960.5	914.5	897.6
27.5°	1035.7	997.5	915.6	862.9	837.0
30°	998.7	956.0	866.2	809.1	778.7
32.5°	962.7	911.1	819.2	751.8	723.7
35°	922.4	865.1	766.4	695.7	671.0
37.5°	883.1	821.3	717.0	639.5	611.6
40°	841.6	774.3	665.4	585.7	556.6
42.5°	798.9	727.2	613.8	530.7	502.7
45°	754.1	678.8	561.1	481.3	454.4
47.5°	711.4	631.8	510.6	430.8	406.2
50°	664.3	584.6	461.2	383.7	360.2
52.5°	618.2	534.1	414.1	340.0	318.7
55°	573.3	485.8	364.6	297.4	276.1
57.5°	527.4	437.6	321.0	258.1	240.1
60°	480.2	390.5	274.9	217.7	199.8
62.5°	434.3	344.5	235.6	181.8	172.9
65°	387.1	296.2	195.2	157.1	153.7
67.5°	342.3	251.3	157.1	138.0	134.6
70°	295.1	207.6	130.1	118.9	114.4
72.5°	250.2	167.1	108.8	99.9	97.6
75°	206.4	127.9	89.8	81.9	80.8
77.5°	162.7	90.8	70.7	66.2	63.9
80°	122.3	65.1	53.8	49.4	49.4
82.5°	85.2	43.8	37.0	34.8	34.8
85°	48.2	24.6	21.3	21.3	21.3
87.5°	18.0	8.9	8.9	7.9	7.9
90°	1.1	13.7	37.4	35.1	36.2
92.5°	23.6	32.0	33.2	34.3	34.3
95°	55.7	66.4	68.3	68.3	66.4
97.5°	92.7	102.6	106.8	106.8	106.8
100°	135.4	144.2	147.2	147.2	146.1
102.5°	180.4	186.9	191.1	192.2	191.1
105°	229.6	232.6	234.9	236.8	236.8
107.5°	278.4	283.0	283.0	283.7	278.4
110°	325.7	331.8	331.8	331.8	328.8

TEST NUMBER: P907094

CATALOG NUMBER: DFN2DIP-TR3F0-030D040US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.8	383.3	382.1	379.1	376.8
115°	427.1	433.3	431.3	430.2	427.1
117.5°	477.1	485.5	480.2	477.1	474.1
120°	527.5	535.8	527.5	527.5	524.0
122.5°	573.2	583.9	578.6	575.5	573.2
125°	621.3	630.8	627.8	624.3	623.2
127.5°	668.2	680.0	675.8	671.2	668.2
130°	712.0	725.8	723.9	721.6	717.4
132.5°	761.2	771.9	772.7	767.3	764.3
135°	803.6	815.4	817.7	816.5	813.5
137.5°	850.9	860.4	862.3	861.5	857.0
140°	892.4	902.0	907.3	907.3	903.1
142.5°	935.2	944.7	947.7	948.9	944.7
145°	975.6	983.2	989.3	990.5	986.3
147.5°	1011.8	1021.3	1025.9	1027.8	1023.6
150°	1049.2	1055.7	1059.9	1063.3	1059.9
152.5°	1082.4	1088.8	1094.2	1098.4	1094.2
155°	1115.5	1118.6	1122.0	1127.4	1123.9
157.5°	1144.2	1146.4	1148.3	1156.0	1150.6
160°	1169.7	1172.0	1173.1	1179.6	1175.0
162.5°	1193.3	1193.3	1194.5	1201.7	1196.4
165°	1213.6	1212.4	1212.4	1220.0	1214.7
167.5°	1231.9	1228.4	1228.4	1236.1	1230.7
170°	1245.6	1242.5	1241.4	1249.0	1242.5
172.5°	1255.1	1252.1	1250.9	1258.6	1252.1
175°	1262.8	1259.7	1257.4	1265.0	1258.6
177.5°	1267.0	1263.9	1261.6	1268.1	1261.6
180°	1265.0	1265.0	1265.0	1265.0	1265.0

TEST NUMBER: P907094

CATALOG NUMBER: DFN2DIP-TR3F0-030D040US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.80	8.57	8.83	9.60	10.99	3.78	4.55	4.81	5.58	6.96
	3H	9.47	10.15	10.50	11.19	12.60	4.96	5.64	6.00	6.69	8.09
	4H	10.06	10.72	11.12	11.76	13.17	5.40	6.05	6.45	7.09	8.51
	6H	10.48	11.07	11.54	12.12	13.55	5.71	6.31	6.77	7.36	8.78
	8H	10.60	11.16	11.66	12.23	13.65	5.80	6.37	6.87	7.43	8.85
	12H	10.65	11.19	11.72	12.25	13.69	5.84	6.38	6.91	7.44	8.88
4H	2H	7.81	8.46	8.87	9.51	10.92	4.36	5.01	5.42	6.06	7.47
	3H	9.62	10.16	10.69	11.24	12.66	5.70	6.24	6.76	7.31	8.74
	4H	10.31	10.80	11.38	11.86	13.31	6.24	6.73	7.31	7.80	9.24
	6H	10.81	11.23	11.89	12.32	13.76	6.65	7.07	7.73	8.16	9.60
	8H	10.98	11.37	12.06	12.45	13.91	6.77	7.17	7.85	8.25	9.70
	12H	11.06	11.42	12.16	12.52	13.98	6.83	7.19	7.93	8.28	9.74
8H	4H	10.27	10.66	11.35	11.74	13.20	6.51	6.91	7.59	7.98	9.44
	6H	10.82	11.15	11.92	12.27	13.72	7.02	7.34	8.12	8.47	9.92
	8H	11.03	11.32	12.14	12.42	13.89	7.20	7.49	8.31	8.59	10.07
	12H	11.16	11.41	12.27	12.51	14.02	7.32	7.57	8.43	8.67	10.18
12H	4H	10.22	10.58	11.31	11.67	13.13	6.51	6.87	7.61	7.96	9.42
	6H	10.80	11.08	11.91	12.19	13.66	7.06	7.35	8.17	8.45	9.93
	8H	11.01	11.26	12.12	12.36	13.87	7.27	7.52	8.38	8.62	10.13

END OF REPORT