

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907116

Luminaire Tested: DFN2DIP-TR3F0-040D030US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907116
REPORT IS A COMBINATION OF REPORTS P900274 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-040D030US835-RLLFLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6055.0 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907116
CATALOG NUMBER: DFN2DIP-TR3F0-040D030US835-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P907116
 CATALOG NUMBER: DFN2DIP-TR3F0-040D030US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56	56	56	56
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	55	54	53	48	48	48	48
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	49	47	46	41	41	41	41
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40	36	36	36	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35	31	31	31	31
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	30	27	27	27	27
6	65	53	46	40	61	50	43	38	44	38	34	38	34	31	33	30	27	24	24	24	24
7	61	48	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24	22	22	22	22
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22	20	20	20	20
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20	18	18	18	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16	16	16	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2060	2060	2060
5°	2062	2026	2039
10°	2041	1984	1971
15°	2011	1917	1868
20°	1973	1825	1741
25°	1934	1722	1618
30°	1882	1617	1463
35°	1830	1504	1327
40°	1778	1387	1171
45°	1717	1258	1030
50°	1655	1127	892
55°	1589	988	760
60°	1513	843	624
65°	1425	696	560
70°	1319	558	505
75°	1185	488	457
80°	992	404	392
85°	675	262	286

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1717 cd/sqm



TEST NUMBER: P907116

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US835-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.9	2.6
10°-20°	425.3	7.0
20°-30°	597.2	9.9
30°-40°	650.9	10.8
40°-50°	598.3	9.9
50°-60°	469.9	7.8
60°-70°	305.8	5.1
70°-80°	157.4	2.6
80°-90°	42.9	0.7
90°-100°	58.7	1.0
100°-110°	186.5	3.1
110°-120°	319.2	5.3
120°-130°	419.8	6.9
130°-140°	471.2	7.8
140°-150°	462.1	7.6
150°-160°	387.7	6.4
160°-170°	257.1	4.2
170°-180°	89.9	1.5
0°-30°	1177.4	19.4
0°-40°	1828.4	30.2
0°-60°	2896.5	47.8
0°-90°	3402.7	56.2
90°-120°	564.5	9.3
90°-150°	1917.7	31.7
90°-180°	2652.0	43.8
0°-180°	6055.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1653	1653	1653	1653	1653	
5°	1653	1646	1626	1640	1635	157
15°	1572	1556	1505	1477	1462	443
25°	1427	1379	1281	1219	1197	656
35°	1230	1154	1022	928	895	770
45°	1005	905	748	642	606	776
55°	764	648	486	396	368	683
65°	516	395	260	210	205	512
75°	275	170	120	109	108	291
85°	64	33	28	28	28	74
90°	1	10	28	26	27	6
95°	42	50	51	51	50	46
105°	172	174	176	178	178	182
115°	320	325	324	323	320	317
125°	466	473	471	468	467	416
135°	603	612	613	612	610	466
145°	732	737	742	743	740	457
155°	837	839	842	846	843	385
165°	910	909	909	915	911	257
175°	947	945	943	949	944	90
180°	949	949	949	949	949	



TEST NUMBER: P907116

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US835-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1653.2	1653.2	1653.2	1653.2	1653.2
2.5°	1660.7	1653.2	1636.7	1651.8	1648.7
5°	1653.2	1645.7	1626.2	1639.7	1635.3
7.5°	1639.7	1630.8	1609.9	1615.7	1608.3
10°	1621.8	1611.3	1581.4	1576.8	1568.0
12.5°	1599.4	1585.9	1545.4	1536.5	1520.0
15°	1572.4	1555.9	1505.1	1476.7	1461.8
17.5°	1541.0	1517.0	1454.1	1421.3	1397.3
20°	1505.1	1475.1	1400.3	1363.0	1330.0
22.5°	1466.2	1431.8	1344.9	1294.1	1271.8
25°	1427.3	1379.4	1280.6	1219.4	1196.8
27.5°	1381.0	1330.0	1220.8	1150.5	1116.0
30°	1331.6	1274.6	1154.9	1078.7	1038.3
32.5°	1283.7	1214.8	1092.2	1002.4	964.9
35°	1229.9	1153.5	1021.9	927.6	894.6
37.5°	1177.5	1095.1	956.0	852.7	815.4
40°	1122.1	1032.4	887.2	781.0	742.1
42.5°	1065.2	969.5	818.4	707.6	670.3
45°	1005.4	905.1	748.1	641.8	605.9
47.5°	948.6	842.4	680.8	574.5	541.6
50°	885.7	779.5	614.9	511.6	480.3
52.5°	824.3	712.1	552.1	453.3	424.9
55°	764.5	647.8	486.2	396.5	368.1
57.5°	703.2	583.5	427.9	344.1	320.2
60°	640.3	520.6	366.5	290.3	266.4
62.5°	579.1	459.4	314.1	242.4	230.5
65°	516.2	394.9	260.3	209.5	204.9
67.5°	456.4	335.1	209.5	184.0	179.5
70°	393.5	276.8	173.5	158.6	152.5
72.5°	333.7	222.9	145.1	133.2	130.2
75°	275.2	170.5	119.7	109.2	107.8
77.5°	217.0	121.1	94.3	88.3	85.2
80°	163.0	86.8	71.7	65.9	65.9
82.5°	113.7	58.4	49.4	46.3	46.3
85°	64.3	32.9	28.4	28.4	28.4
87.5°	24.0	11.9	11.9	10.5	10.5
90°	0.9	10.3	28.0	26.3	27.2
92.5°	17.7	24.0	24.9	25.7	25.7
95°	41.8	49.8	51.2	51.2	49.8
97.5°	69.5	76.9	80.1	80.1	80.1
100°	101.5	108.1	110.4	110.4	109.6
102.5°	135.3	140.2	143.3	144.2	143.3
105°	172.2	174.5	176.2	177.6	177.6
107.5°	208.8	212.2	212.2	212.8	208.8
110°	244.3	248.9	248.9	248.9	246.6



TEST NUMBER: P907116

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	282.6	287.5	286.6	284.3	282.6
115°	320.4	324.9	323.5	322.7	320.4
117.5°	357.8	364.1	360.1	357.8	355.5
120°	395.6	401.9	395.6	395.6	393.0
122.5°	429.9	437.9	433.9	431.6	429.9
125°	466.0	473.1	470.8	468.2	467.4
127.5°	501.1	510.0	506.9	503.4	501.1
130°	534.0	544.3	542.9	541.2	538.0
132.5°	570.9	578.9	579.5	575.5	573.2
135°	602.7	611.5	613.3	612.4	610.1
137.5°	638.1	645.3	646.7	646.2	642.7
140°	669.3	676.5	680.5	680.5	677.3
142.5°	701.4	708.5	710.8	711.7	708.5
145°	731.7	737.4	742.0	742.8	739.7
147.5°	758.9	766.0	769.4	770.9	767.7
150°	786.9	791.8	794.9	797.5	794.9
152.5°	811.8	816.6	820.6	823.8	820.6
155°	836.7	838.9	841.5	845.5	843.0
157.5°	858.1	859.8	861.3	867.0	863.0
160°	877.3	879.0	879.9	884.7	881.3
162.5°	895.0	895.0	895.9	901.3	897.3
165°	910.2	909.3	909.3	915.0	911.0
167.5°	923.9	921.3	921.3	927.0	923.0
170°	934.2	931.9	931.1	936.8	931.9
172.5°	941.3	939.1	938.2	943.9	939.1
175°	947.1	944.8	943.1	948.8	943.9
177.5°	950.2	947.9	946.2	951.1	946.2
180°	948.8	948.8	948.8	948.8	948.8



TEST NUMBER: P907116
 CATALOG NUMBER: DFN2DIP-TR3F0-040D030US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.17	11.05	11.07	11.97	13.15	6.14	7.03	7.05	7.95	9.13
	3H	11.84	12.63	12.76	13.56	14.77	7.33	8.12	8.25	9.05	10.26
	4H	12.44	13.19	13.38	14.13	15.34	7.78	8.52	8.71	9.46	10.68
	6H	12.86	13.55	13.81	14.49	15.72	8.10	8.78	9.04	9.73	10.96
	8H	12.98	13.64	13.94	14.60	15.82	8.19	8.84	9.14	9.80	11.03
	12H	13.04	13.66	14.00	14.62	15.87	8.23	8.85	9.19	9.80	11.06
4H	2H	10.19	10.93	11.13	11.87	13.09	6.74	7.48	7.68	8.42	9.64
	3H	12.01	12.63	12.96	13.60	14.83	8.09	8.71	9.04	9.68	10.91
	4H	12.70	13.26	13.66	14.23	15.48	8.63	9.20	9.59	10.16	11.42
	6H	13.21	13.69	14.18	14.68	15.94	9.05	9.53	10.02	10.52	11.78
	8H	13.38	13.83	14.35	14.81	16.08	9.17	9.63	10.15	10.61	11.88
	12H	13.47	13.88	14.47	14.88	16.15	9.24	9.65	10.23	10.64	11.92
8H	4H	12.67	13.12	13.64	14.10	15.37	8.91	9.37	9.89	10.34	11.61
	6H	13.23	13.60	14.23	14.62	15.89	9.42	9.80	10.42	10.82	12.09
	8H	13.44	13.77	14.45	14.78	16.06	9.61	9.94	10.62	10.95	12.24
	12H	13.57	13.86	14.58	14.87	16.20	9.73	10.02	10.74	11.02	12.35
12H	4H	12.62	13.03	13.62	14.03	15.30	8.92	9.33	9.91	10.32	11.60
	6H	13.20	13.53	14.21	14.54	15.83	9.47	9.80	10.48	10.81	12.10
	8H	13.42	13.71	14.43	14.71	16.04	9.68	9.97	10.69	10.97	12.30