

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907141

Luminaire Tested: DFN2DIP-TR3F0-050D030US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907141
REPORT IS A COMBINATION OF REPORTS P901795 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-050D030US835-FLLONL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7920.0 lumens
Efficiency: N/A
Efficacy: 116.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907141

CATALOG NUMBER: DFN2DIP-TR3F0-050D030US835-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P907141

CATALOG NUMBER: DFN2DIP-TR3F0-050D030US835-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57
2	92	84	78	72	86	79	73	69	69	65	62	61	58	55	53	50	48
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41
4	77	65	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27
7	60	47	39	34	56	45	38	32	40	34	30	35	31	27	31	27	24
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22
9	52	40	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2424	2424	2424
5°	2427	2388	2405
10°	2406	2354	2371
15°	2369	2313	2318
20°	2320	2258	2265
25°	2271	2191	2203
30°	2210	2129	2125
35°	2152	2056	2042
40°	2081	1983	1964
45°	2010	1909	1883
50°	1933	1831	1790
55°	1851	1741	1704
60°	1759	1635	1605
65°	1658	1525	1488
70°	1530	1390	1363
75°	1353	1228	1245
80°	1139	1022	1023
85°	804	673	660

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2010 cd/sqm

TEST NUMBER: P907141

CATALOG NUMBER: DFN2DIP-TR3F0-050D030US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.1	2.3
10°-20°	515.2	6.5
20°-30°	757.2	9.6
30°-40°	879.4	11.1
40°-50°	878.3	11.1
50°-60°	765.8	9.7
60°-70°	566.1	7.1
70°-80°	320.3	4.0
80°-90°	86.3	1.1
90°-100°	33.4	0.4
100°-110°	124.4	1.6
110°-120°	330.1	4.2
120°-130°	547.5	6.9
130°-140°	581.5	7.3
140°-150°	540.5	6.8
150°-160°	434.5	5.5
160°-170°	280.0	3.5
170°-180°	96.4	1.2
0°-30°	1455.5	18.4
0°-40°	2334.9	29.5
0°-60°	3979.0	50.2
0°-90°	4951.8	62.5
90°-120°	487.9	6.2
90°-150°	2157.3	27.2
90°-180°	2968.0	37.5
0°-180°	7920.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1946	1938	1918	1932	1929	185
15°	1852	1841	1816	1824	1815	522
25°	1676	1661	1630	1633	1630	771
35°	1446	1428	1398	1386	1377	903
45°	1177	1164	1136	1115	1108	908
55°	891	879	857	834	825	796
65°	601	589	571	554	544	594
75°	314	311	301	290	294	335
85°	77	75	73	67	66	85
90°	1	9	15	18	20	7
95°	48	23	28	32	32	56
105°	223	245	45	53	56	238
115°	421	434	452	113	60	415
125°	596	605	619	624	626	531
135°	737	749	755	763	761	569
145°	855	854	867	872	868	535
155°	941	935	944	948	942	434
165°	992	988	990	995	990	280
175°	1015	1010	1011	1016	1009	97
180°	1012	1012	1012	1012	1012	

TEST NUMBER: P907141

CATALOG NUMBER: DFN2DIP-TR3F0-050D030US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1945.5	1945.5	1945.5	1945.5	1945.5
2.5°	1956.8	1947.5	1926.9	1945.5	1942.0
5°	1945.5	1938.2	1917.5	1932.4	1928.9
7.5°	1932.4	1921.3	1900.7	1915.8	1912.0
10°	1912.0	1898.9	1876.5	1891.3	1885.8
12.5°	1883.8	1872.7	1850.3	1859.6	1855.8
15°	1852.0	1840.9	1816.5	1824.1	1814.7
17.5°	1812.7	1801.6	1777.2	1786.5	1777.2
20°	1769.7	1758.6	1732.4	1737.9	1730.6
22.5°	1726.8	1709.9	1685.5	1685.5	1681.7
25°	1676.2	1661.3	1629.5	1633.1	1629.5
27.5°	1620.0	1606.9	1582.7	1577.1	1567.8
30°	1564.0	1549.0	1521.0	1515.4	1507.9
32.5°	1504.1	1493.0	1463.0	1451.7	1444.2
35°	1446.1	1427.5	1397.5	1386.2	1376.9
37.5°	1380.6	1363.8	1333.8	1320.7	1311.4
40°	1313.4	1298.3	1268.3	1251.6	1244.1
42.5°	1247.9	1232.8	1203.0	1184.1	1173.0
45°	1176.8	1163.7	1135.5	1115.1	1107.5
47.5°	1107.5	1094.4	1064.5	1043.8	1032.7
50°	1034.5	1025.2	999.0	972.8	963.4
52.5°	963.4	950.3	926.1	905.5	892.4
55°	890.6	879.3	856.8	834.4	825.1
57.5°	817.5	808.2	783.8	761.4	753.8
60°	744.5	737.2	711.0	690.3	684.8
62.5°	673.5	660.4	641.7	623.0	615.5
65°	600.6	589.3	570.6	553.8	544.4
67.5°	525.8	516.3	499.6	486.5	478.9
70°	456.5	449.0	432.1	419.0	411.7
72.5°	385.5	377.9	368.6	355.5	349.9
75°	314.2	310.6	301.1	290.0	293.8
77.5°	250.7	243.1	239.4	233.8	228.3
80°	187.2	185.2	181.4	175.9	172.1
82.5°	127.2	127.2	125.4	117.9	117.9
85°	76.6	74.8	73.0	67.3	65.5
87.5°	33.7	30.0	26.2	20.6	18.7
90°	0.7	8.8	14.6	18.4	19.7
92.5°	18.4	15.4	17.6	19.1	19.7
95°	47.6	23.4	28.5	32.3	31.5
97.5°	85.7	25.7	37.3	39.6	40.3
100°	129.7	29.3	41.8	47.6	49.1
102.5°	178.0	176.6	43.2	51.2	53.5
105°	222.7	244.7	44.7	52.7	55.7
107.5°	274.7	293.0	46.2	54.2	57.2
110°	324.6	339.9	128.2	55.0	57.9

TEST NUMBER: P907141

CATALOG NUMBER: DFN2DIP-TR3F0-050D030US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	371.5	384.6	372.2	56.4	58.6
115°	421.2	433.7	452.0	112.8	60.1
117.5°	464.5	479.1	491.6	386.8	194.9
120°	512.8	523.8	537.0	545.8	446.9
122.5°	553.8	565.6	580.3	584.6	585.4
125°	595.6	605.1	619.1	624.2	626.4
127.5°	633.7	643.9	655.0	662.3	663.0
130°	669.6	681.4	689.4	697.4	696.8
132.5°	706.2	715.8	723.8	730.4	729.7
135°	737.0	748.8	755.3	762.7	761.2
137.5°	769.2	778.0	785.4	792.7	790.5
140°	800.7	806.6	814.6	821.2	817.6
142.5°	827.2	832.3	841.8	847.6	844.0
145°	855.0	854.2	866.7	871.8	868.1
147.5°	879.1	876.9	889.4	893.0	890.1
150°	902.6	897.5	909.2	913.5	909.9
152.5°	922.3	916.5	927.5	931.9	926.8
155°	941.4	934.9	943.6	948.0	942.2
157.5°	956.8	951.0	957.6	962.7	956.8
160°	970.0	965.6	970.0	974.4	969.2
162.5°	981.7	977.3	981.0	986.1	979.5
165°	991.9	987.6	989.8	994.9	989.8
167.5°	1000.0	995.6	997.8	1003.0	996.4
170°	1006.6	1002.2	1003.7	1008.8	1002.2
172.5°	1011.0	1006.6	1008.1	1013.2	1006.6
175°	1014.6	1009.5	1011.0	1016.1	1008.8
177.5°	1016.1	1011.0	1011.8	1016.9	1010.3
180°	1012.5	1012.5	1012.5	1012.5	1012.5

TEST NUMBER: P907141

CATALOG NUMBER: DFN2DIP-TR3F0-050D030US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.38	12.36	12.22	13.23	14.31	10.95	11.94	11.79	12.80	13.88
	3H	13.04	13.92	13.89	14.80	15.91	12.57	13.46	13.42	14.33	15.44
	4H	13.63	14.46	14.50	15.34	16.46	13.16	13.99	14.03	14.87	15.99
	6H	14.02	14.80	14.91	15.68	16.81	13.56	14.33	14.44	15.21	16.35
	8H	14.13	14.86	15.02	15.77	16.90	13.66	14.40	14.55	15.30	16.43
	12H	14.18	14.88	15.08	15.78	16.93	13.70	14.41	14.60	15.30	16.46
4H	2H	11.85	12.69	12.73	13.57	14.69	11.51	12.35	12.38	13.23	14.34
	3H	13.72	14.42	14.60	15.33	16.46	13.33	14.03	14.22	14.94	16.07
	4H	14.43	15.07	15.33	15.98	17.13	14.03	14.67	14.93	15.57	16.73
	6H	14.94	15.49	15.86	16.43	17.59	14.54	15.09	15.45	16.02	17.18
	8H	15.09	15.61	16.01	16.53	17.71	14.69	15.20	15.60	16.13	17.30
	12H	15.17	15.63	16.10	16.57	17.75	14.75	15.21	15.69	16.16	17.34
8H	4H	14.63	15.15	15.55	16.07	17.25	14.28	14.79	15.19	15.72	16.89
	6H	15.26	15.68	16.20	16.65	17.83	14.90	15.33	15.84	16.29	17.47
	8H	15.47	15.85	16.43	16.81	18.00	15.11	15.49	16.06	16.45	17.64
	12H	15.60	15.94	16.56	16.89	18.13	15.23	15.56	16.18	16.51	17.75
12H	4H	14.62	15.09	15.56	16.03	17.21	14.27	14.74	15.21	15.68	16.86
	6H	15.29	15.66	16.24	16.62	17.81	14.94	15.32	15.89	16.28	17.47
	8H	15.53	15.86	16.48	16.81	18.05	15.18	15.51	16.13	16.46	17.70

END OF REPORT