

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907147

Luminaire Tested: DFN2DIP-TR3F0-050D040US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907147
REPORT IS A COMBINATION OF REPORTS P901810 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-050D040US835-RLLONL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8210.0 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 74.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907147

CATALOG NUMBER: DFN2DIP-TR3F0-050D040US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P907147

CATALOG NUMBER: DFN2DIP-TR3F0-050D040US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58
1	99	95	91	87	91	88	84	82	75	72	70	63	61	60	52	51	50
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	46	44	43
3	83	74	66	61	76	68	62	57	59	54	50	50	46	43	41	39	37
4	76	65	58	52	70	61	54	49	52	47	43	45	41	38	37	35	32
5	70	59	51	45	64	55	48	42	47	42	38	40	36	33	34	31	28
6	65	53	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25
7	60	48	40	35	55	45	38	33	39	33	29	33	29	26	28	25	23
8	56	44	36	31	51	41	34	29	36	30	26	31	26	23	26	23	20
9	52	40	32	28	48	37	31	26	33	27	24	28	24	21	24	21	19
10	48	37	30	25	45	34	28	24	30	25	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2575	2575	2575
5°	2578	2532	2549
10°	2551	2480	2464
15°	2514	2396	2334
20°	2466	2281	2176
25°	2417	2153	2022
30°	2352	2021	1829
35°	2288	1880	1659
40°	2223	1734	1464
45°	2147	1572	1287
50°	2068	1409	1115
55°	1986	1235	950
60°	1891	1054	780
65°	1781	869	700
70°	1649	698	631
75°	1482	610	571
80°	1240	505	489
85°	844	327	358

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2147 cd/sqm

TEST NUMBER: P907147

CATALOG NUMBER: DFN2DIP-TR3F0-050D040US835-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.7	2.4
10°-20°	531.7	6.5
20°-30°	746.5	9.1
30°-40°	813.7	9.9
40°-50°	747.9	9.1
50°-60°	587.3	7.2
60°-70°	382.3	4.7
70°-80°	196.8	2.4
80°-90°	52.6	0.6
90°-100°	44.5	0.5
100°-110°	165.9	2.0
110°-120°	440.1	5.4
120°-130°	729.9	8.9
130°-140°	775.4	9.4
140°-150°	720.6	8.8
150°-160°	579.4	7.1
160°-170°	373.3	4.5
170°-180°	128.5	1.6
0°-30°	1471.8	17.9
0°-40°	2285.5	27.8
0°-60°	3620.7	44.1
0°-90°	4252.4	51.8
90°-120°	650.5	7.9
90°-150°	2876.4	35.0
90°-180°	3958.0	48.2
0°-180°	8210.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2066	2066	2066	2066	2066	
5°	2066	2057	2033	2050	2044	196
15°	1966	1945	1881	1846	1827	554
25°	1784	1724	1601	1524	1496	821
35°	1537	1442	1277	1160	1118	962
45°	1257	1131	935	802	757	971
55°	956	810	608	496	460	854
65°	645	494	325	262	256	640
75°	344	213	150	136	135	364
85°	80	41	36	36	36	92
90°	1	12	20	24	26	8
95°	63	31	38	43	42	75
105°	297	326	60	70	74	317
115°	562	578	603	150	80	553
125°	794	807	825	832	835	708
135°	983	998	1007	1017	1015	759
145°	1140	1139	1156	1162	1158	713
155°	1255	1246	1258	1264	1256	578
165°	1323	1317	1320	1326	1320	374
175°	1353	1346	1348	1355	1345	129
180°	1350	1350	1350	1350	1350	

TEST NUMBER: P907147

CATALOG NUMBER: DFN2DIP-TR3F0-050D040US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2066.5	2066.5	2066.5	2066.5	2066.5
2.5°	2075.8	2066.5	2045.9	2064.7	2060.9
5°	2066.5	2057.2	2032.8	2049.6	2044.1
7.5°	2049.6	2038.5	2012.3	2019.7	2010.3
10°	2027.2	2014.1	1976.8	1971.1	1959.9
12.5°	1999.2	1982.4	1931.8	1920.7	1900.0
15°	1965.5	1944.9	1881.4	1845.9	1827.2
17.5°	1926.2	1896.3	1817.7	1776.6	1746.6
20°	1881.4	1843.9	1750.4	1703.8	1662.5
22.5°	1832.8	1789.7	1681.2	1617.7	1589.7
25°	1784.1	1724.2	1600.8	1524.2	1496.0
27.5°	1726.2	1662.5	1526.0	1438.1	1395.1
30°	1664.5	1593.3	1443.7	1348.4	1297.8
32.5°	1604.6	1518.5	1365.3	1253.0	1206.2
35°	1537.3	1441.9	1277.4	1159.5	1118.3
37.5°	1471.8	1368.9	1195.1	1065.9	1019.3
40°	1402.6	1290.5	1108.9	976.2	927.6
42.5°	1331.6	1211.9	1023.0	884.5	837.9
45°	1256.8	1131.4	935.1	802.2	757.3
47.5°	1185.7	1053.0	851.0	718.1	677.0
50°	1107.2	974.4	768.7	639.5	600.4
52.5°	1030.4	890.1	690.1	566.7	531.2
55°	955.6	809.7	607.7	495.6	460.1
57.5°	879.0	729.4	534.9	430.2	400.2
60°	800.4	650.8	458.1	362.9	332.9
62.5°	723.8	574.2	392.7	303.0	288.1
65°	645.2	493.7	325.4	261.9	256.2
67.5°	570.4	418.9	261.9	230.0	224.4
70°	491.9	346.0	216.9	198.2	190.7
72.5°	417.1	278.6	181.4	166.5	162.7
75°	344.1	213.1	149.6	136.5	134.7
77.5°	271.2	151.4	117.9	110.3	106.5
80°	203.8	108.5	89.7	82.3	82.3
82.5°	142.1	73.0	61.7	57.9	57.9
85°	80.4	41.1	35.5	35.5	35.5
87.5°	30.0	14.9	14.9	13.1	13.1
90°	0.9	11.7	19.5	24.5	26.3
92.5°	24.5	20.5	23.4	25.4	26.3
95°	63.4	31.2	38.0	43.0	42.0
97.5°	114.3	34.2	49.8	52.8	53.7
100°	172.9	39.1	55.7	63.4	65.4
102.5°	237.3	235.5	57.6	68.3	71.3
105°	296.9	326.3	59.6	70.3	74.2
107.5°	366.3	390.7	61.6	72.3	76.2
110°	432.8	453.2	171.0	73.3	77.1

TEST NUMBER: P907147

CATALOG NUMBER: DFN2DIP-TR3F0-050D040US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	495.3	512.8	496.2	75.2	78.2
115°	561.6	578.2	602.7	150.4	80.2
117.5°	619.3	638.8	655.5	515.7	259.8
120°	683.8	698.4	716.0	727.8	595.9
122.5°	738.4	754.1	773.7	779.5	780.5
125°	794.1	806.9	825.4	832.3	835.2
127.5°	844.9	858.6	873.3	883.1	884.0
130°	892.8	908.5	919.1	929.9	929.0
132.5°	941.6	954.4	965.1	973.9	973.0
135°	982.7	998.4	1007.1	1016.9	1015.0
137.5°	1025.6	1037.3	1047.2	1056.9	1054.0
140°	1067.6	1075.5	1086.2	1095.0	1090.1
142.5°	1102.9	1109.7	1122.4	1130.1	1125.3
145°	1140.0	1139.0	1155.5	1162.4	1157.5
147.5°	1172.1	1169.2	1185.8	1190.7	1186.9
150°	1203.4	1196.6	1212.3	1218.1	1213.2
152.5°	1229.8	1222.0	1236.6	1242.5	1235.7
155°	1255.2	1246.5	1258.2	1264.0	1256.2
157.5°	1275.7	1267.9	1276.8	1283.6	1275.7
160°	1293.3	1287.4	1293.3	1299.1	1292.3
162.5°	1308.9	1303.1	1308.0	1314.8	1306.0
165°	1322.6	1316.8	1319.7	1326.5	1319.7
167.5°	1333.4	1327.4	1330.5	1337.3	1328.5
170°	1342.2	1336.3	1338.2	1345.1	1336.3
172.5°	1348.0	1342.2	1344.2	1351.0	1342.2
175°	1352.8	1346.0	1348.0	1354.8	1345.1
177.5°	1354.8	1348.0	1349.0	1355.9	1347.1
180°	1350.0	1350.0	1350.0	1350.0	1350.0

TEST NUMBER: P907147

CATALOG NUMBER: DFN2DIP-TR3F0-050D040US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.55	11.39	11.50	12.35	13.60	6.53	7.37	7.47	8.33	9.58
	3H	12.22	12.97	13.18	13.94	15.21	7.71	8.47	8.67	9.43	10.71
	4H	12.82	13.53	13.79	14.51	15.79	8.16	8.87	9.13	9.84	11.12
	6H	13.24	13.89	14.22	14.87	16.16	8.47	9.13	9.46	10.11	11.40
	8H	13.36	13.98	14.35	14.98	16.27	8.56	9.19	9.55	10.18	11.47
	12H	13.42	14.01	14.41	15.00	16.31	8.60	9.20	9.60	10.19	11.50
4H	2H	10.57	11.28	11.55	12.25	13.53	7.12	7.83	8.10	8.80	10.08
	3H	12.39	12.98	13.38	13.98	15.28	8.46	9.06	9.45	10.06	11.35
	4H	13.07	13.61	14.07	14.61	15.93	9.01	9.55	10.00	10.54	11.86
	6H	13.58	14.05	14.59	15.06	16.38	9.42	9.89	10.43	10.90	12.22
	8H	13.75	14.18	14.76	15.20	16.53	9.55	9.98	10.56	10.99	12.32
	12H	13.84	14.23	14.87	15.26	16.60	9.61	10.00	10.64	11.03	12.36
8H	4H	13.04	13.47	14.05	14.49	15.82	9.28	9.72	10.29	10.73	12.06
	6H	13.60	13.96	14.63	15.01	16.34	9.79	10.15	10.83	11.21	12.53
	8H	13.81	14.12	14.85	15.16	16.51	9.98	10.29	11.02	11.34	12.68
	12H	13.94	14.22	14.98	15.25	16.64	10.09	10.37	11.14	11.41	12.80
12H	4H	12.99	13.38	14.02	14.41	15.75	9.29	9.68	10.31	10.71	12.04
	6H	13.57	13.89	14.61	14.93	16.27	9.84	10.16	10.88	11.20	12.54
	8H	13.79	14.06	14.83	15.10	16.49	10.04	10.32	11.09	11.36	12.75