

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918026

Luminaire Tested: DFN2DIP-TR3F0-040D030US930-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918026
REPORT IS A COMBINATION OF REPORTS P900273 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-040D030US930-FLLFLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5393.2 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918026
CATALOG NUMBER: DFN2DIP-TR3F0-040D030US930-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P918026

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US930-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60			
1	100	96	92	88	93	89	86	83	78	75	73	67	66	64	58	56	55	50			
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	48	46	42			
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40	36			
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34	31			
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30	27			
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26	23			
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	21			
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21	19			
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17			
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1581	1581	1581
5°	1583	1558	1569
10°	1569	1536	1546
15°	1545	1509	1512
20°	1513	1472	1477
25°	1481	1429	1437
30°	1441	1389	1386
35°	1404	1341	1332
40°	1357	1293	1281
45°	1311	1245	1228
50°	1260	1195	1167
55°	1207	1136	1111
60°	1147	1067	1047
65°	1082	995	971
70°	998	907	889
75°	883	801	812
80°	743	667	667
85°	525	439	431

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1311 cd/sqm



TEST NUMBER: P918026

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US930-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.4	2.2
10°-20°	336.0	6.2
20°-30°	493.8	9.2
30°-40°	573.6	10.6
40°-50°	572.9	10.6
50°-60°	499.5	9.3
60°-70°	369.3	6.8
70°-80°	208.9	3.9
80°-90°	57.3	1.1
90°-100°	47.9	0.9
100°-110°	152.1	2.8
110°-120°	260.3	4.8
120°-130°	342.3	6.3
130°-140°	384.2	7.1
140°-150°	376.8	7.0
150°-160°	316.1	5.9
160°-170°	209.6	3.9
170°-180°	73.3	1.4
0°-30°	949.3	17.6
0°-40°	1522.9	28.2
0°-60°	2595.3	48.1
0°-90°	3230.8	59.9
90°-120°	460.2	8.5
90°-150°	1563.5	29.0
90°-180°	2162.0	40.1
0°-180°	5393.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1269	1264	1251	1260	1258	120
15°	1208	1201	1185	1190	1184	340
25°	1093	1084	1063	1065	1063	503
35°	943	931	912	904	898	589
45°	768	759	741	727	722	592
55°	581	574	559	544	538	519
65°	392	384	372	361	355	387
75°	205	203	196	189	192	219
85°	50	49	48	44	43	56
90°	1	8	23	21	22	5
95°	34	41	42	42	41	38
105°	140	142	144	145	145	148
115°	261	265	264	263	261	258
125°	380	386	384	382	381	339
135°	491	499	500	499	497	380
145°	597	601	605	606	603	373
155°	682	684	686	689	687	314
165°	742	741	741	746	743	209
175°	772	770	769	774	770	73
180°	774	774	774	774	774	



TEST NUMBER: P918026

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US930-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1268.9	1268.9	1268.9	1268.9	1268.9
2.5°	1276.3	1270.2	1256.8	1268.9	1266.6
5°	1268.9	1264.1	1250.7	1260.4	1258.1
7.5°	1260.4	1253.1	1239.7	1249.5	1247.1
10°	1247.1	1238.5	1223.9	1233.6	1230.0
12.5°	1228.7	1221.4	1206.8	1212.9	1210.4
15°	1207.9	1200.7	1184.8	1189.7	1183.6
17.5°	1182.3	1175.1	1159.2	1165.2	1159.2
20°	1154.2	1147.0	1129.9	1133.5	1128.8
22.5°	1126.3	1115.2	1099.3	1099.3	1096.9
25°	1093.2	1083.5	1062.8	1065.2	1062.8
27.5°	1056.6	1048.1	1032.3	1028.7	1022.6
30°	1020.1	1010.3	992.1	988.4	983.5
32.5°	981.0	973.8	954.2	946.9	941.9
35°	943.2	931.1	911.5	904.2	898.1
37.5°	900.5	889.5	869.9	861.4	855.3
40°	856.6	846.8	827.2	816.4	811.5
42.5°	813.9	804.0	784.6	772.3	765.1
45°	767.5	759.0	740.6	727.3	722.4
47.5°	722.4	713.8	694.3	680.9	673.6
50°	674.7	668.6	651.6	634.5	628.4
52.5°	628.4	619.9	604.1	590.6	582.0
55°	580.9	573.5	558.9	544.2	538.2
57.5°	533.2	527.2	511.2	496.6	491.7
60°	485.6	480.8	463.7	450.3	446.6
62.5°	439.3	430.7	418.6	406.3	401.5
65°	391.8	384.3	372.2	361.2	355.1
67.5°	342.9	336.7	325.9	317.3	312.4
70°	297.7	292.9	281.8	273.3	268.5
72.5°	251.4	246.5	240.4	231.9	228.2
75°	205.0	202.6	196.4	189.1	191.6
77.5°	163.5	158.6	156.1	152.5	148.9
80°	122.1	120.7	118.3	114.7	112.3
82.5°	83.0	83.0	81.9	76.9	76.9
85°	50.0	48.8	47.6	43.9	42.7
87.5°	22.0	19.6	17.1	13.5	12.1
90°	0.7	8.4	22.8	21.4	22.2
92.5°	14.4	19.6	20.3	21.0	21.0
95°	34.1	40.6	41.7	41.7	40.6
97.5°	56.7	62.7	65.3	65.3	65.3
100°	82.8	88.1	90.0	90.0	89.4
102.5°	110.3	114.3	116.8	117.6	116.8
105°	140.4	142.3	143.7	144.8	144.8
107.5°	170.2	173.0	173.0	173.5	170.2
110°	199.2	202.9	202.9	202.9	201.1



TEST NUMBER: P918026

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US930-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	230.4	234.4	233.7	231.8	230.4
115°	261.2	264.9	263.7	263.1	261.2
117.5°	291.7	296.9	293.6	291.7	289.8
120°	322.5	327.7	322.5	322.5	320.4
122.5°	350.5	357.0	353.8	351.9	350.5
125°	379.9	385.7	383.8	381.7	381.1
127.5°	408.5	415.8	413.3	410.4	408.5
130°	435.4	443.8	442.6	441.2	438.6
132.5°	465.5	472.0	472.5	469.2	467.3
135°	491.4	498.6	500.0	499.3	497.4
137.5°	520.2	526.1	527.3	526.8	524.0
140°	545.7	551.5	554.8	554.8	552.2
142.5°	571.9	577.6	579.5	580.2	577.6
145°	596.6	601.2	605.0	605.6	603.1
147.5°	618.7	624.5	627.3	628.5	625.9
150°	641.6	645.6	648.1	650.2	648.1
152.5°	661.9	665.8	669.0	671.6	669.0
155°	682.2	684.0	686.1	689.3	687.3
157.5°	699.6	701.0	702.2	706.9	703.6
160°	715.3	716.6	717.4	721.3	718.5
162.5°	729.7	729.7	730.4	734.8	731.6
165°	742.1	741.4	741.4	746.0	742.7
167.5°	753.3	751.1	751.1	755.8	752.5
170°	761.7	759.8	759.1	763.8	759.8
172.5°	767.4	765.6	764.9	769.6	765.6
175°	772.2	770.3	768.9	773.6	769.6
177.5°	774.7	772.8	771.4	775.4	771.4
180°	773.6	773.6	773.6	773.6	773.6



TEST NUMBER: P918026
 CATALOG NUMBER: DFN2DIP-TR3F0-040D030US930-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.68	10.64	10.55	11.53	12.65	9.25	10.21	10.12	11.10	12.22
	3H	11.34	12.20	12.22	13.09	14.24	10.87	11.73	11.75	12.63	13.77
	4H	11.92	12.74	12.82	13.64	14.80	11.45	12.27	12.35	13.17	14.33
	6H	12.32	13.07	13.23	13.98	15.15	11.85	12.60	12.76	13.51	14.68
	8H	12.42	13.14	13.34	14.07	15.24	11.96	12.67	12.87	13.60	14.77
	12H	12.47	13.15	13.39	14.07	15.27	12.00	12.68	12.92	13.60	14.80
4H	2H	10.15	10.96	11.05	11.87	13.02	9.81	10.62	10.71	11.52	12.68
	3H	12.01	12.69	12.92	13.63	14.80	11.62	12.30	12.53	13.24	14.41
	4H	12.72	13.34	13.65	14.27	15.47	12.32	12.94	13.24	13.87	15.07
	6H	13.23	13.77	14.17	14.72	15.92	12.83	13.37	13.77	14.32	15.52
	8H	13.38	13.88	14.32	14.83	16.04	12.98	13.48	13.91	14.42	15.64
	12H	13.46	13.91	14.41	14.87	16.09	13.04	13.49	14.00	14.46	15.68
8H	4H	12.92	13.42	13.86	14.37	15.58	12.57	13.07	13.50	14.01	15.23
	6H	13.55	13.96	14.51	14.95	16.16	13.19	13.60	14.15	14.59	15.80
	8H	13.76	14.13	14.74	15.11	16.34	13.40	13.76	14.37	14.74	15.97
	12H	13.89	14.21	14.87	15.19	16.47	13.51	13.84	14.49	14.81	16.09
12H	4H	12.91	13.36	13.87	14.33	15.55	12.56	13.01	13.52	13.98	15.20
	6H	13.58	13.94	14.55	14.92	16.15	13.23	13.59	14.20	14.57	15.80
	8H	13.82	14.14	14.79	15.11	16.39	13.46	13.79	14.44	14.76	16.04