

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907163

Luminaire Tested: DFN2DIP-TR3F0-050D080US835-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907163
REPORT IS A COMBINATION OF REPORTS P901866 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-050D080US835-RLLONL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12170.0 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 106.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907163

CATALOG NUMBER: DFN2DIP-TR3F0-050D080US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P907163

CATALOG NUMBER: DFN2DIP-TR3F0-050D080US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42
1	95	91	87	84	86	82	79	76	66	64	62	51	50	49	38	37	36
2	87	80	74	69	78	72	67	63	58	55	52	46	43	41	34	32	31
3	79	70	63	58	71	64	58	53	52	47	44	41	38	35	30	28	27
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23
5	67	56	48	42	60	51	44	39	41	36	33	33	29	27	25	22	21
6	61	50	42	37	55	45	39	34	37	32	29	30	26	23	22	20	18
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	21	18	16
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13
10	46	34	27	23	41	31	25	21	26	21	18	21	18	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2575	2575	2575
5°	2578	2532	2549
10°	2551	2480	2464
15°	2514	2396	2334
20°	2466	2281	2176
25°	2417	2153	2022
30°	2352	2021	1829
35°	2288	1880	1659
40°	2223	1734	1464
45°	2147	1572	1287
50°	2068	1409	1115
55°	1986	1235	950
60°	1891	1054	780
65°	1781	869	700
70°	1649	698	631
75°	1482	610	571
80°	1240	505	489
85°	844	327	358

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2147 cd/sqm

TEST NUMBER: P907163

CATALOG NUMBER: DFN2DIP-TR3F0-050D080US835-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.7	1.6
10°-20°	531.7	4.4
20°-30°	746.5	6.1
30°-40°	813.7	6.7
40°-50°	747.9	6.1
50°-60°	587.3	4.8
60°-70°	382.3	3.1
70°-80°	196.8	1.6
80°-90°	55.0	0.5
90°-100°	89.0	0.7
100°-110°	331.9	2.7
110°-120°	880.2	7.2
120°-130°	1459.9	12.0
130°-140°	1550.7	12.7
140°-150°	1441.2	11.8
150°-160°	1158.7	9.5
160°-170°	746.6	6.1
170°-180°	257.0	2.1
0°-30°	1471.8	12.1
0°-40°	2285.5	18.8
0°-60°	3620.7	29.8
0°-90°	4254.8	35.0
90°-120°	1301.1	10.7
90°-150°	5752.9	47.3
90°-180°	7915.0	65.0
0°-180°	12170.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2066	2066	2066	2066	2066	
5°	2066	2057	2033	2050	2044	196
15°	1966	1945	1881	1846	1827	554
25°	1784	1724	1601	1524	1496	821
35°	1537	1442	1277	1160	1118	962
45°	1257	1131	935	802	757	971
55°	956	810	608	496	460	854
65°	645	494	325	262	256	640
75°	344	213	150	136	135	364
85°	80	41	36	36	36	92
90°	2	23	39	49	53	11
95°	127	62	76	86	84	150
105°	594	653	119	141	148	635
115°	1123	1156	1205	301	160	1106
125°	1588	1614	1651	1664	1670	1416
135°	1965	1997	2014	2034	2030	1518
145°	2280	2278	2311	2325	2315	1426
155°	2510	2493	2516	2528	2512	1157
165°	2645	2634	2639	2653	2639	747
175°	2706	2692	2696	2710	2690	258
180°	2700	2700	2700	2700	2700	

TEST NUMBER: P907163

CATALOG NUMBER: DFN2DIP-TR3F0-050D080US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2066.5	2066.5	2066.5	2066.5	2066.5
2.5°	2075.8	2066.5	2045.9	2064.7	2060.9
5°	2066.5	2057.2	2032.8	2049.6	2044.1
7.5°	2049.6	2038.5	2012.3	2019.7	2010.3
10°	2027.2	2014.1	1976.8	1971.1	1959.9
12.5°	1999.2	1982.4	1931.8	1920.7	1900.0
15°	1965.5	1944.9	1881.4	1845.9	1827.2
17.5°	1926.2	1896.3	1817.7	1776.6	1746.6
20°	1881.4	1843.9	1750.4	1703.8	1662.5
22.5°	1832.8	1789.7	1681.2	1617.7	1589.7
25°	1784.1	1724.2	1600.8	1524.2	1496.0
27.5°	1726.2	1662.5	1526.0	1438.1	1395.1
30°	1664.5	1593.3	1443.7	1348.4	1297.8
32.5°	1604.6	1518.5	1365.3	1253.0	1206.2
35°	1537.3	1441.9	1277.4	1159.5	1118.3
37.5°	1471.8	1368.9	1195.1	1065.9	1019.3
40°	1402.6	1290.5	1108.9	976.2	927.6
42.5°	1331.6	1211.9	1023.0	884.5	837.9
45°	1256.8	1131.4	935.1	802.2	757.3
47.5°	1185.7	1053.0	851.0	718.1	677.0
50°	1107.2	974.4	768.7	639.5	600.4
52.5°	1030.4	890.1	690.1	566.7	531.2
55°	955.6	809.7	607.7	495.6	460.1
57.5°	879.0	729.4	534.9	430.2	400.2
60°	800.4	650.8	458.1	362.9	332.9
62.5°	723.8	574.2	392.7	303.0	288.1
65°	645.2	493.7	325.4	261.9	256.2
67.5°	570.4	418.9	261.9	230.0	224.4
70°	491.9	346.0	216.9	198.2	190.7
72.5°	417.1	278.6	181.4	166.5	162.7
75°	344.1	213.1	149.6	136.5	134.7
77.5°	271.2	151.4	117.9	110.3	106.5
80°	203.8	108.5	89.7	82.3	82.3
82.5°	142.1	73.0	61.7	57.9	57.9
85°	80.4	41.1	35.5	35.5	35.5
87.5°	30.0	14.9	14.9	13.1	13.1
90°	1.9	23.4	39.0	48.9	52.7
92.5°	48.9	41.1	46.9	50.8	52.7
95°	126.9	62.4	76.1	86.1	84.0
97.5°	228.5	68.4	99.5	105.6	107.4
100°	345.9	78.2	111.4	126.9	130.8
102.5°	474.7	470.9	115.3	136.6	142.7
105°	593.9	652.6	119.2	140.6	148.5
107.5°	732.6	781.3	123.2	144.5	152.4
110°	865.6	906.4	342.0	146.6	154.3

TEST NUMBER: P907163

CATALOG NUMBER: DFN2DIP-TR3F0-050D080US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	990.6	1025.6	992.5	150.3	156.4
115°	1123.3	1156.5	1205.4	300.9	160.3
117.5°	1238.6	1277.6	1311.0	1031.4	519.7
120°	1367.6	1396.8	1432.1	1455.5	1191.7
122.5°	1476.8	1508.2	1547.4	1559.0	1561.1
125°	1588.2	1613.7	1650.8	1664.5	1670.3
127.5°	1689.8	1717.2	1746.7	1766.1	1768.0
130°	1785.6	1816.9	1838.3	1859.9	1858.0
132.5°	1883.3	1908.8	1930.2	1947.8	1945.9
135°	1965.4	1996.7	2014.1	2033.9	2029.9
137.5°	2051.3	2074.7	2094.4	2113.9	2108.1
140°	2135.2	2151.0	2172.4	2190.0	2180.2
142.5°	2205.8	2219.4	2244.7	2260.3	2250.5
145°	2280.0	2277.9	2311.1	2324.8	2315.0
147.5°	2344.3	2338.5	2371.6	2381.4	2373.7
150°	2406.9	2393.2	2424.5	2436.1	2426.4
152.5°	2459.6	2444.0	2473.2	2485.1	2471.4
155°	2510.4	2493.0	2516.4	2528.0	2512.5
157.5°	2551.4	2535.9	2553.5	2567.2	2551.4
160°	2586.7	2574.9	2586.7	2598.3	2584.6
162.5°	2617.8	2606.2	2615.9	2629.6	2612.0
165°	2645.2	2633.6	2639.4	2653.0	2639.4
167.5°	2666.7	2654.9	2660.9	2674.6	2657.0
170°	2684.4	2672.5	2676.5	2690.2	2672.5
172.5°	2696.0	2684.4	2688.3	2702.0	2684.4
175°	2705.7	2692.0	2696.0	2709.6	2690.2
177.5°	2709.6	2696.0	2698.0	2711.7	2694.1
180°	2699.9	2699.9	2699.9	2699.9	2699.9

TEST NUMBER: P907163

CATALOG NUMBER: DFN2DIP-TR3F0-050D080US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.79	9.51	9.87	10.59	12.06	4.77	5.49	5.85	6.57	8.04
	3H	10.45	11.09	11.54	12.18	13.67	5.94	6.59	7.03	7.67	9.16
	4H	11.05	11.66	12.15	12.75	14.24	6.38	6.99	7.48	8.08	9.58
	6H	11.46	12.02	12.57	13.11	14.62	6.69	7.25	7.80	8.35	9.85
	8H	11.57	12.11	12.69	13.22	14.72	6.78	7.31	7.89	8.42	9.92
	12H	11.63	12.14	12.75	13.24	14.76	6.82	7.32	7.93	8.42	9.95
4H	2H	8.79	9.40	9.90	10.49	11.99	5.34	5.95	6.45	7.04	8.54
	3H	10.60	11.11	11.72	12.23	13.73	6.68	7.19	7.79	8.30	9.81
	4H	11.28	11.75	12.40	12.85	14.38	7.22	7.68	8.33	8.79	10.32
	6H	11.78	12.18	12.91	13.31	14.83	7.62	8.02	8.75	9.15	10.67
	8H	11.95	12.32	13.08	13.44	14.98	7.75	8.12	8.87	9.24	10.78
	12H	12.04	12.37	13.18	13.50	15.05	7.80	8.14	8.94	9.27	10.81
8H	4H	11.24	11.61	12.37	12.73	14.27	7.48	7.86	8.61	8.97	10.51
	6H	11.79	12.10	12.94	13.26	14.80	7.99	8.30	9.13	9.46	10.99
	8H	12.00	12.27	13.16	13.41	14.97	8.17	8.44	9.33	9.58	11.14
	12H	12.13	12.37	13.29	13.50	15.10	8.28	8.52	9.44	9.66	11.25
12H	4H	11.19	11.52	12.33	12.66	14.20	7.48	7.82	8.62	8.95	10.49
	6H	11.77	12.04	12.92	13.18	14.73	8.03	8.30	9.19	9.45	11.00
	8H	11.98	12.21	13.13	13.35	14.94	8.23	8.47	9.39	9.61	11.20