

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918133

Luminaire Tested: DFN2DIP-TR3F0-080D030US930-RLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P918133  
REPORT IS A COMBINATION OF REPORTS P901802 AND P898751  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR3F0-080D030US930-RLLONL  
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7965.5 lumens  
Efficiency: N/A  
Efficacy: 76.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 103.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P918133  
CATALOG NUMBER: DFN2DIP-TR3F0-080D030US930-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P918133

CATALOG NUMBER: DFN2DIP-TR3F0-080D030US930-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74	70
1	103	99	95	92	97	93	90	87	84	81	79	75	73	71	67	65	64	64	64	64	60
2	94	87	81	76	89	83	77	73	74	70	67	67	63	61	59	57	55	55	55	55	51
3	86	77	70	64	82	73	67	62	66	61	57	59	55	52	53	50	48	48	48	48	44
4	79	69	61	55	75	65	58	53	59	54	49	53	49	45	48	45	42	42	42	42	39
5	73	62	54	48	69	59	52	46	53	47	43	48	44	40	44	40	37	37	37	37	34
6	68	56	48	42	64	53	46	41	49	42	38	44	39	35	40	36	33	33	33	33	30
7	63	51	43	37	60	49	41	36	44	38	34	40	35	32	37	32	29	29	29	29	27
8	59	46	39	33	56	44	37	32	41	35	30	37	32	28	34	30	27	27	27	27	24
9	55	43	35	30	52	41	34	29	37	32	27	34	29	26	31	27	24	24	24	24	22
10	51	39	32	27	49	38	31	26	35	29	25	32	27	24	29	25	22	22	22	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3359	3359	3359
5°	3363	3303	3325
10°	3327	3235	3214
15°	3280	3126	3045
20°	3217	2976	2838
25°	3153	2808	2638
30°	3068	2636	2386
35°	2984	2452	2164
40°	2899	2262	1910
45°	2800	2051	1680
50°	2698	1838	1455
55°	2591	1611	1239
60°	2467	1374	1018
65°	2324	1134	913
70°	2151	910	823
75°	1932	796	745
80°	1617	659	638
85°	1100	427	467

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2800 cd/sqm



TEST NUMBER: P918133

CATALOG NUMBER: DFN2DIP-TR3F0-080D030US930-RLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	252.6	3.2
10°-20°	693.6	8.7
20°-30°	973.7	12.2
30°-40°	1061.4	13.3
40°-50°	975.6	12.2
50°-60°	766.2	9.6
60°-70°	498.7	6.3
70°-80°	256.7	3.2
80°-90°	67.0	0.8
90°-100°	27.2	0.3
100°-110°	101.5	1.3
110°-120°	269.1	3.4
120°-130°	446.3	5.6
130°-140°	474.1	6.0
140°-150°	440.6	5.5
150°-160°	354.3	4.4
160°-170°	228.3	2.9
170°-180°	78.6	1.0
0°-30°	1919.9	24.1
0°-40°	2981.4	37.4
0°-60°	4723.1	59.3
0°-90°	5545.5	69.6
90°-120°	397.8	5.0
90°-150°	1758.9	22.1
90°-180°	2420.0	30.4
0°-180°	7965.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2696	2696	2696	2696	2696	
5°	2696	2684	2652	2674	2666	256
15°	2564	2537	2454	2408	2384	722
25°	2327	2249	2088	1988	1952	1070
35°	2005	1881	1666	1513	1459	1255
45°	1639	1476	1220	1046	988	1266
55°	1246	1056	793	646	600	1114
65°	842	644	424	342	334	834
75°	449	278	195	178	176	475
85°	105	54	46	46	46	120
90°	1	7	12	15	16	8
95°	39	19	23	26	26	46
105°	182	200	36	43	45	194
115°	343	354	368	92	49	338
125°	486	493	505	509	511	433
135°	601	610	616	622	621	464
145°	697	696	707	711	708	436
155°	768	762	769	773	768	354
165°	809	805	807	811	807	228
175°	827	823	824	828	822	79
180°	826	826	826	826	826	



TEST NUMBER: P918133

CATALOG NUMBER: DFN2DIP-TR3F0-080D030US930-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2695.7	2695.7	2695.7	2695.7	2695.7
2.5°	2707.9	2695.7	2668.8	2693.3	2688.4
5°	2695.7	2683.6	2651.7	2673.7	2666.4
7.5°	2673.7	2659.2	2625.0	2634.6	2622.4
10°	2644.4	2627.4	2578.7	2571.2	2556.7
12.5°	2608.0	2586.0	2519.9	2505.4	2478.5
15°	2563.9	2537.0	2454.2	2407.9	2383.5
17.5°	2512.7	2473.6	2371.1	2317.6	2278.4
20°	2454.2	2405.3	2283.4	2222.6	2168.7
22.5°	2390.8	2334.6	2193.1	2110.2	2073.7
25°	2327.4	2249.2	2088.2	1988.3	1951.6
27.5°	2251.8	2168.7	1990.6	1876.0	1819.8
30°	2171.3	2078.4	1883.3	1759.0	1693.0
32.5°	2093.1	1980.8	1781.0	1634.5	1573.4
35°	2005.4	1880.9	1666.3	1512.6	1458.7
37.5°	1919.9	1785.7	1558.9	1390.4	1329.6
40°	1829.7	1683.4	1446.6	1273.4	1210.0
42.5°	1737.0	1580.9	1334.5	1153.9	1093.0
45°	1639.4	1475.9	1219.8	1046.4	988.0
47.5°	1546.8	1373.6	1110.1	936.7	883.1
50°	1444.2	1271.1	1002.7	834.2	783.2
52.5°	1344.1	1161.1	900.2	739.2	692.9
55°	1246.5	1056.3	792.8	646.5	600.2
57.5°	1146.6	951.5	697.8	561.2	522.0
60°	1044.1	849.0	597.6	473.4	434.3
62.5°	944.2	749.0	512.3	395.3	375.9
65°	841.7	643.9	424.4	341.7	334.1
67.5°	744.1	546.4	341.7	299.9	292.8
70°	641.6	451.4	282.9	258.5	248.7
72.5°	544.0	363.4	236.6	217.2	212.2
75°	448.8	278.0	195.2	178.1	175.8
77.5°	353.8	197.5	153.8	143.9	139.0
80°	265.8	141.6	117.0	107.4	107.4
82.5°	185.3	95.2	80.5	75.6	75.6
85°	104.8	53.6	46.3	46.3	46.3
87.5°	39.1	19.4	19.4	17.1	17.1
90°	0.6	7.2	11.9	15.0	16.1
92.5°	15.0	12.6	14.3	15.6	16.1
95°	38.8	19.1	23.2	26.3	25.7
97.5°	69.9	21.0	30.4	32.3	32.9
100°	105.7	23.9	34.1	38.8	40.0
102.5°	145.1	144.0	35.2	41.7	43.6
105°	181.6	199.5	36.4	43.0	45.4
107.5°	224.0	238.9	37.7	44.2	46.6
110°	264.6	277.1	104.5	44.8	47.2



TEST NUMBER: P918133

CATALOG NUMBER: DFN2DIP-TR3F0-080D030US930-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	302.9	313.6	303.5	46.0	47.8
115°	343.4	353.6	368.5	92.0	49.0
117.5°	378.7	390.6	400.8	315.4	158.9
120°	418.1	427.1	437.8	445.0	364.4
122.5°	451.5	461.1	473.1	476.6	477.3
125°	485.6	493.3	504.8	508.9	510.7
127.5°	516.7	525.0	534.0	540.0	540.5
130°	545.9	555.5	562.1	568.6	568.1
132.5°	575.8	583.6	590.1	595.5	594.9
135°	600.9	610.5	615.8	621.8	620.6
137.5°	627.1	634.3	640.3	646.3	644.5
140°	652.8	657.6	664.1	669.5	666.6
142.5°	674.4	678.6	686.3	691.0	688.1
145°	697.1	696.4	706.6	710.8	707.8
147.5°	716.7	714.9	725.1	728.1	725.7
150°	735.9	731.7	741.3	744.8	741.8
152.5°	751.9	747.2	756.2	759.8	755.6
155°	767.5	762.2	769.3	772.9	768.2
157.5°	780.1	775.3	780.7	784.9	780.1
160°	790.8	787.3	790.8	794.4	790.2
162.5°	800.4	796.8	799.8	804.0	798.6
165°	808.7	805.2	807.0	811.1	807.0
167.5°	815.3	811.7	813.5	817.7	812.4
170°	820.7	817.1	818.3	822.5	817.1
172.5°	824.3	820.7	821.9	826.1	820.7
175°	827.2	823.0	824.3	828.4	822.5
177.5°	828.4	824.3	824.9	829.1	823.7
180°	825.5	825.5	825.5	825.5	825.5



TEST NUMBER: P918133  
 CATALOG NUMBER: DFN2DIP-TR3F0-080D030US930-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.97	13.99	13.74	14.78	15.75	8.95	9.97	9.72	10.76	11.72
	3H	14.65	15.56	15.44	16.37	17.36	10.14	11.06	10.93	11.86	12.85
	4H	15.26	16.12	16.07	16.93	17.94	10.60	11.46	11.40	12.27	13.27
	6H	15.69	16.48	16.50	17.30	18.32	10.92	11.72	11.74	12.54	13.55
	8H	15.81	16.57	16.64	17.40	18.42	11.02	11.77	11.85	12.61	13.63
	12H	15.88	16.60	16.71	17.43	18.47	11.06	11.78	11.90	12.61	13.66
4H	2H	13.01	13.87	13.82	14.68	15.68	9.56	10.42	10.37	11.23	12.23
	3H	14.84	15.56	15.67	16.40	17.42	10.92	11.63	11.74	12.48	13.50
	4H	15.54	16.19	16.37	17.03	18.08	11.47	12.12	12.31	12.96	14.01
	6H	16.05	16.61	16.90	17.48	18.53	11.89	12.45	12.75	13.32	14.37
	8H	16.23	16.75	17.08	17.61	18.68	12.02	12.55	12.88	13.41	14.47
	12H	16.32	16.79	17.20	17.68	18.75	12.09	12.56	12.97	13.45	14.52
8H	4H	15.52	16.04	16.37	16.90	17.97	11.76	12.28	12.61	13.14	14.21
	6H	16.08	16.51	16.96	17.42	18.48	12.28	12.71	13.16	13.61	14.68
	8H	16.29	16.67	17.18	17.57	18.66	12.46	12.85	13.36	13.75	14.83
	12H	16.43	16.77	17.33	17.66	18.80	12.59	12.92	13.48	13.81	14.95
12H	4H	15.48	15.95	16.35	16.83	17.90	11.77	12.24	12.64	13.12	14.19
	6H	16.05	16.44	16.95	17.34	18.42	12.32	12.71	13.22	13.61	14.69
	8H	16.28	16.61	17.17	17.51	18.64	12.54	12.87	13.43	13.76	14.90