

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918141

Luminaire Tested: DFN2DIP-TR3F0-080D050US930-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918141
REPORT IS A COMBINATION OF REPORTS P901830 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-080D050US930-RLLONL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9579.8 lumens
Efficiency: N/A
Efficacy: 81.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 118
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918141
CATALOG NUMBER: DFN2DIP-TR3F0-080D050US930-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P918141
 CATALOG NUMBER: DFN2DIP-TR3F0-080D050US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58			58
1	100	96	92	89	93	90	86	83	78	75	73	67	65	64	57	56	55	50			50
2	92	84	79	74	85	79	74	69	69	65	62	59	57	54	51	49	47	43			43
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	43	41	37			37
4	77	67	59	53	72	62	56	50	55	49	45	48	44	40	41	38	35	32			32
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31	28			28
6	66	54	46	40	61	51	43	38	45	39	35	39	35	31	34	31	28	25			25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	28	25	22			22
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	29	25	23	20			20
9	53	41	33	28	49	39	32	27	34	29	25	30	26	23	27	23	20	18			18
10	49	38	30	26	46	36	29	25	32	26	23	28	24	21	25	21	19	17			17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3359	3359	3359
5°	3363	3303	3325
10°	3327	3235	3214
15°	3280	3126	3045
20°	3217	2976	2838
25°	3153	2808	2638
30°	3068	2636	2386
35°	2984	2452	2164
40°	2899	2262	1910
45°	2800	2051	1680
50°	2698	1838	1455
55°	2591	1611	1239
60°	2467	1374	1018
65°	2324	1134	913
70°	2151	910	823
75°	1932	796	745
80°	1617	659	638
85°	1100	427	467

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2800 cd/sqm



TEST NUMBER: P918141

CATALOG NUMBER: DFN2DIP-TR3F0-080D050US930-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.6	2.6
10°-20°	693.6	7.2
20°-30°	973.7	10.2
30°-40°	1061.4	11.1
40°-50°	975.6	10.2
50°-60°	766.2	8.0
60°-70°	498.7	5.2
70°-80°	256.7	2.7
80°-90°	68.0	0.7
90°-100°	45.4	0.5
100°-110°	169.1	1.8
110°-120°	448.5	4.7
120°-130°	743.9	7.8
130°-140°	790.2	8.2
140°-150°	734.4	7.7
150°-160°	590.4	6.2
160°-170°	380.5	4.0
170°-180°	130.9	1.4
0°-30°	1919.9	20.0
0°-40°	2981.4	31.1
0°-60°	4723.1	49.3
0°-90°	5546.4	57.9
90°-120°	663.0	6.9
90°-150°	2931.5	30.6
90°-180°	4033.0	42.1
0°-180°	9579.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2696	2696	2696	2696	2696	
5°	2696	2684	2652	2674	2666	256
15°	2564	2537	2454	2408	2384	722
25°	2327	2249	2088	1988	1952	1070
35°	2005	1881	1666	1513	1459	1255
45°	1639	1476	1220	1046	988	1266
55°	1246	1056	793	646	600	1114
65°	842	644	424	342	334	834
75°	449	278	195	178	176	475
85°	105	54	46	46	46	120
90°	1	12	20	25	27	9
95°	65	32	39	44	43	77
105°	303	333	61	72	76	323
115°	572	589	614	153	82	564
125°	809	822	841	848	851	722
135°	1002	1018	1026	1036	1034	774
145°	1162	1161	1178	1185	1180	727
155°	1279	1270	1282	1288	1280	589
165°	1348	1342	1345	1352	1345	381
175°	1379	1372	1374	1381	1371	131
180°	1376	1376	1376	1376	1376	



TEST NUMBER: P918141

CATALOG NUMBER: DFN2DIP-TR3F0-080D050US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2695.7	2695.7	2695.7	2695.7	2695.7
2.5°	2707.9	2695.7	2668.8	2693.3	2688.4
5°	2695.7	2683.6	2651.7	2673.7	2666.4
7.5°	2673.7	2659.2	2625.0	2634.6	2622.4
10°	2644.4	2627.4	2578.7	2571.2	2556.7
12.5°	2608.0	2586.0	2519.9	2505.4	2478.5
15°	2563.9	2537.0	2454.2	2407.9	2383.5
17.5°	2512.7	2473.6	2371.1	2317.6	2278.4
20°	2454.2	2405.3	2283.4	2222.6	2168.7
22.5°	2390.8	2334.6	2193.1	2110.2	2073.7
25°	2327.4	2249.2	2088.2	1988.3	1951.6
27.5°	2251.8	2168.7	1990.6	1876.0	1819.8
30°	2171.3	2078.4	1883.3	1759.0	1693.0
32.5°	2093.1	1980.8	1781.0	1634.5	1573.4
35°	2005.4	1880.9	1666.3	1512.6	1458.7
37.5°	1919.9	1785.7	1558.9	1390.4	1329.6
40°	1829.7	1683.4	1446.6	1273.4	1210.0
42.5°	1737.0	1580.9	1334.5	1153.9	1093.0
45°	1639.4	1475.9	1219.8	1046.4	988.0
47.5°	1546.8	1373.6	1110.1	936.7	883.1
50°	1444.2	1271.1	1002.7	834.2	783.2
52.5°	1344.1	1161.1	900.2	739.2	692.9
55°	1246.5	1056.3	792.8	646.5	600.2
57.5°	1146.6	951.5	697.8	561.2	522.0
60°	1044.1	849.0	597.6	473.4	434.3
62.5°	944.2	749.0	512.3	395.3	375.9
65°	841.7	643.9	424.4	341.7	334.1
67.5°	744.1	546.4	341.7	299.9	292.8
70°	641.6	451.4	282.9	258.5	248.7
72.5°	544.0	363.4	236.6	217.2	212.2
75°	448.8	278.0	195.2	178.1	175.8
77.5°	353.8	197.5	153.8	143.9	139.0
80°	265.8	141.6	117.0	107.4	107.4
82.5°	185.3	95.2	80.5	75.6	75.6
85°	104.8	53.6	46.3	46.3	46.3
87.5°	39.1	19.4	19.4	17.1	17.1
90°	1.0	11.9	19.9	24.9	26.8
92.5°	24.9	21.0	23.9	25.9	26.8
95°	64.7	31.8	38.8	43.9	42.8
97.5°	116.4	34.9	50.7	53.8	54.7
100°	176.3	39.9	56.7	64.7	66.7
102.5°	241.9	239.9	58.8	69.6	72.7
105°	302.6	332.6	60.7	71.7	75.7
107.5°	373.3	398.1	62.8	73.6	77.7
110°	441.1	461.9	174.2	74.7	78.6



TEST NUMBER: P918141

CATALOG NUMBER: DFN2DIP-TR3F0-080D050US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	504.8	522.6	505.7	76.6	79.7
115°	572.4	589.3	614.2	153.4	81.7
117.5°	631.1	651.0	668.1	525.5	264.8
120°	696.8	711.8	729.7	741.7	607.2
122.5°	752.5	768.5	788.5	794.4	795.5
125°	809.3	822.3	841.2	848.2	851.2
127.5°	861.0	875.0	890.1	899.9	900.9
130°	909.9	925.9	936.7	947.7	946.8
132.5°	959.7	972.7	983.5	992.5	991.6
135°	1001.5	1017.5	1026.3	1036.4	1034.4
137.5°	1045.2	1057.2	1067.2	1077.2	1074.2
140°	1088.0	1096.1	1106.9	1115.9	1111.0
142.5°	1124.0	1131.0	1143.9	1151.8	1146.8
145°	1161.8	1160.7	1177.6	1184.6	1179.7
147.5°	1194.6	1191.6	1208.5	1213.5	1209.6
150°	1226.5	1219.5	1235.4	1241.4	1236.4
152.5°	1253.3	1245.4	1260.3	1266.3	1259.3
155°	1279.2	1270.3	1282.2	1288.2	1280.3
157.5°	1300.1	1292.2	1301.1	1308.1	1300.1
160°	1318.1	1312.1	1318.1	1324.0	1317.0
162.5°	1333.9	1328.0	1332.9	1339.9	1331.0
165°	1347.9	1342.0	1344.9	1351.8	1344.9
167.5°	1358.9	1352.8	1355.9	1362.9	1353.9
170°	1367.8	1361.8	1363.8	1370.8	1361.8
172.5°	1373.8	1367.8	1369.9	1376.8	1367.8
175°	1378.8	1371.7	1373.8	1380.7	1370.8
177.5°	1380.7	1373.8	1374.8	1381.8	1372.8
180°	1375.7	1375.7	1375.7	1375.7	1375.7



TEST NUMBER: P918141
 CATALOG NUMBER: DFN2DIP-TR3F0-080D050US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.01	12.91	12.91	13.82	14.98	7.99	8.89	8.88	9.80	10.95
	3H	13.69	14.49	14.59	15.41	16.59	9.18	9.98	10.08	10.90	12.08
	4H	14.29	15.05	15.21	15.97	17.17	9.63	10.39	10.55	11.31	12.50
	6H	14.71	15.41	15.64	16.34	17.54	9.95	10.65	10.88	11.58	12.78
	8H	14.83	15.50	15.77	16.44	17.65	10.04	10.70	10.98	11.65	12.85
	12H	14.89	15.53	15.84	16.47	17.69	10.08	10.71	11.02	11.65	12.88
4H	2H	12.04	12.80	12.96	13.72	14.91	8.59	9.35	9.51	10.27	11.46
	3H	13.86	14.49	14.80	15.45	16.65	9.94	10.57	10.87	11.52	12.73
	4H	14.55	15.12	15.50	16.07	17.31	10.48	11.06	11.43	12.01	13.24
	6H	15.06	15.55	16.02	16.53	17.76	10.90	11.39	11.86	12.37	13.60
	8H	15.23	15.69	16.19	16.66	17.90	11.03	11.49	11.99	12.46	13.70
	12H	15.32	15.74	16.30	16.72	17.97	11.09	11.51	12.07	12.49	13.74
8H	4H	14.52	14.98	15.48	15.95	17.19	10.76	11.23	11.72	12.19	13.44
	6H	15.08	15.46	16.07	16.47	17.71	11.28	11.66	12.26	12.67	13.91
	8H	15.29	15.63	16.29	16.62	17.89	11.46	11.80	12.46	12.80	14.06
	12H	15.43	15.72	16.42	16.71	18.02	11.58	11.88	12.58	12.87	14.18
12H	4H	14.48	14.89	15.46	15.88	17.13	10.77	11.19	11.75	12.17	13.42
	6H	15.06	15.39	16.05	16.39	17.65	11.32	11.66	12.32	12.66	13.92
	8H	15.27	15.57	16.27	16.56	17.87	11.53	11.83	12.53	12.82	14.13