

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907251

Luminaire Tested: DFN2DIP-TR3F0-090D040US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907251
REPORT IS A COMBINATION OF REPORTS P901818 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-090D040US835-RLLONL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11610.0 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 124.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907251

CATALOG NUMBER: DFN2DIP-TR3F0-090D040US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P907251

CATALOG NUMBER: DFN2DIP-TR3F0-090D040US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	102	98	94	91	96	92	89	86	82	79	77	72	71	69	64	62	61
2	93	86	80	75	88	81	76	72	73	68	65	64	61	59	57	54	52
3	86	76	69	63	80	72	66	61	65	60	55	57	54	50	51	48	45
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35
6	67	55	47	41	63	52	45	40	47	41	37	43	38	34	38	34	31
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25
9	54	42	35	29	51	40	33	29	37	31	27	33	28	25	30	26	23
10	51	39	32	27	48	37	30	26	34	28	24	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4635	4635	4635
5°	4640	4558	4588
10°	4592	4464	4435
15°	4526	4313	4202
20°	4440	4106	3916
25°	4351	3875	3640
30°	4234	3638	3292
35°	4118	3383	2986
40°	4001	3121	2635
45°	3864	2830	2318
50°	3723	2536	2008
55°	3575	2223	1710
60°	3404	1897	1405
65°	3207	1565	1261
70°	2968	1256	1136
75°	2667	1099	1027
80°	2231	909	881
85°	1518	589	644

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3864 cd/sqm

TEST NUMBER: P907251

CATALOG NUMBER: DFN2DIP-TR3F0-090D040US835-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	348.6	3.0
10°-20°	957.0	8.2
20°-30°	1343.6	11.6
30°-40°	1464.6	12.6
40°-50°	1346.2	11.6
50°-60°	1057.2	9.1
60°-70°	688.1	5.9
70°-80°	354.2	3.1
80°-90°	92.8	0.8
90°-100°	44.5	0.4
100°-110°	165.9	1.4
110°-120°	440.1	3.8
120°-130°	729.9	6.3
130°-140°	775.4	6.7
140°-150°	720.6	6.2
150°-160°	579.4	5.0
160°-170°	373.3	3.2
170°-180°	128.5	1.1
0°-30°	2649.2	22.8
0°-40°	4113.9	35.4
0°-60°	6517.2	56.1
0°-90°	7652.4	65.9
90°-120°	650.5	5.6
90°-150°	2876.4	24.8
90°-180°	3958.0	34.1
0°-180°	11610.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3720	3720	3720	3720	3720	
5°	3720	3703	3659	3689	3679	353
15°	3538	3501	3386	3322	3289	997
25°	3212	3104	2882	2744	2693	1477
35°	2767	2595	2299	2087	2013	1732
45°	2262	2036	1683	1444	1363	1747
55°	1720	1458	1094	892	828	1537
65°	1161	889	586	471	461	1151
75°	619	384	269	246	242	655
85°	145	74	64	64	64	166
90°	1	12	20	24	26	11
95°	63	31	38	43	42	75
105°	297	326	60	70	74	317
115°	562	578	603	150	80	553
125°	794	807	825	832	835	708
135°	983	998	1007	1017	1015	759
145°	1140	1139	1156	1162	1158	713
155°	1255	1246	1258	1264	1256	578
165°	1323	1317	1320	1326	1320	374
175°	1353	1346	1348	1355	1345	129
180°	1350	1350	1350	1350	1350	

TEST NUMBER: P907251

CATALOG NUMBER: DFN2DIP-TR3F0-090D040US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3719.7	3719.7	3719.7	3719.7	3719.7
2.5°	3736.5	3719.7	3682.5	3716.5	3709.7
5°	3719.7	3702.9	3659.0	3689.3	3679.3
7.5°	3689.3	3669.3	3622.2	3635.4	3618.6
10°	3649.0	3625.4	3558.3	3547.9	3527.9
12.5°	3598.6	3568.3	3477.2	3457.2	3420.0
15°	3537.9	3500.8	3386.5	3322.5	3289.0
17.5°	3467.2	3413.3	3271.8	3197.9	3144.0
20°	3386.5	3319.0	3150.7	3066.8	2992.5
22.5°	3299.0	3221.5	3026.1	2911.8	2861.5
25°	3211.5	3103.6	2881.5	2743.6	2692.9
27.5°	3107.2	2992.5	2746.8	2588.6	2511.1
30°	2996.1	2867.9	2598.6	2427.2	2336.1
32.5°	2888.2	2733.2	2457.5	2255.4	2171.1
35°	2767.2	2595.4	2299.3	2087.2	2012.9
37.5°	2649.3	2464.0	2151.1	1918.6	1834.7
40°	2524.7	2322.9	1996.1	1757.2	1669.7
42.5°	2396.8	2181.5	1841.4	1592.2	1508.2
45°	2262.2	2036.5	1683.2	1443.9	1363.2
47.5°	2134.3	1895.4	1531.8	1292.5	1218.6
50°	1992.9	1753.9	1383.6	1151.1	1080.7
52.5°	1854.7	1602.2	1242.2	1020.0	956.1
55°	1720.0	1457.5	1093.9	892.2	828.2
57.5°	1582.2	1312.9	962.9	774.3	720.4
60°	1440.7	1171.4	824.7	653.2	599.3
62.5°	1302.9	1033.6	706.8	545.4	518.6
65°	1161.4	888.6	585.7	471.4	461.1
67.5°	1026.8	753.9	471.4	413.9	403.9
70°	885.4	622.9	390.4	356.8	343.2
72.5°	750.7	501.4	326.4	299.6	292.9
75°	619.3	383.6	269.3	245.7	242.5
77.5°	488.2	272.5	212.1	198.6	191.8
80°	366.8	195.4	161.4	148.2	148.2
82.5°	255.7	131.4	111.1	104.3	104.3
85°	144.6	73.9	63.9	63.9	63.9
87.5°	53.9	26.8	26.8	23.6	23.6
90°	0.9	11.7	19.5	24.5	26.3
92.5°	24.5	20.5	23.4	25.4	26.3
95°	63.4	31.2	38.0	43.0	42.0
97.5°	114.3	34.2	49.8	52.8	53.7
100°	172.9	39.1	55.7	63.4	65.4
102.5°	237.3	235.5	57.6	68.3	71.3
105°	296.9	326.3	59.6	70.3	74.2
107.5°	366.3	390.7	61.6	72.3	76.2
110°	432.8	453.2	171.0	73.3	77.1

TEST NUMBER: P907251

CATALOG NUMBER: DFN2DIP-TR3F0-090D040US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	495.3	512.8	496.2	75.2	78.2
115°	561.6	578.2	602.7	150.4	80.2
117.5°	619.3	638.8	655.5	515.7	259.8
120°	683.8	698.4	716.0	727.8	595.9
122.5°	738.4	754.1	773.7	779.5	780.5
125°	794.1	806.9	825.4	832.3	835.2
127.5°	844.9	858.6	873.3	883.1	884.0
130°	892.8	908.5	919.1	929.9	929.0
132.5°	941.6	954.4	965.1	973.9	973.0
135°	982.7	998.4	1007.1	1016.9	1015.0
137.5°	1025.6	1037.3	1047.2	1056.9	1054.0
140°	1067.6	1075.5	1086.2	1095.0	1090.1
142.5°	1102.9	1109.7	1122.4	1130.1	1125.3
145°	1140.0	1139.0	1155.5	1162.4	1157.5
147.5°	1172.1	1169.2	1185.8	1190.7	1186.9
150°	1203.4	1196.6	1212.3	1218.1	1213.2
152.5°	1229.8	1222.0	1236.6	1242.5	1235.7
155°	1255.2	1246.5	1258.2	1264.0	1256.2
157.5°	1275.7	1267.9	1276.8	1283.6	1275.7
160°	1293.3	1287.4	1293.3	1299.1	1292.3
162.5°	1308.9	1303.1	1308.0	1314.8	1306.0
165°	1322.6	1316.8	1319.7	1326.5	1319.7
167.5°	1333.4	1327.4	1330.5	1337.3	1328.5
170°	1342.2	1336.3	1338.2	1345.1	1336.3
172.5°	1348.0	1342.2	1344.2	1351.0	1342.2
175°	1352.8	1346.0	1348.0	1354.8	1345.1
177.5°	1354.8	1348.0	1349.0	1355.9	1347.1
180°	1350.0	1350.0	1350.0	1350.0	1350.0

TEST NUMBER: P907251

CATALOG NUMBER: DFN2DIP-TR3F0-090D040US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.79	14.77	14.61	15.61	16.63	9.77	10.75	10.59	11.58	12.61
	3H	15.47	16.35	16.30	17.19	18.25	10.97	11.84	11.79	12.68	13.74
	4H	16.08	16.91	16.93	17.76	18.82	11.42	12.24	12.26	13.09	14.16
	6H	16.50	17.26	17.36	18.12	19.20	11.74	12.50	12.60	13.36	14.44
	8H	16.63	17.35	17.50	18.23	19.31	11.83	12.56	12.70	13.43	14.51
	12H	16.69	17.38	17.56	18.25	19.36	11.88	12.57	12.75	13.44	14.54
4H	2H	13.83	14.66	14.68	15.50	16.57	10.38	11.21	11.23	12.05	13.12
	3H	15.66	16.35	16.52	17.23	18.31	11.74	12.42	12.60	13.30	14.39
	4H	16.35	16.98	17.22	17.85	18.96	12.29	12.91	13.16	13.79	14.90
	6H	16.87	17.40	17.75	18.31	19.42	12.71	13.24	13.59	14.15	15.26
	8H	17.04	17.54	17.93	18.44	19.56	12.83	13.34	13.73	14.23	15.36
	12H	17.14	17.59	18.05	18.50	19.63	12.90	13.35	13.81	14.27	15.40
8H	4H	16.33	16.83	17.22	17.73	18.85	12.57	13.07	13.46	13.97	15.10
	6H	16.89	17.31	17.81	18.25	19.37	13.09	13.50	14.00	14.44	15.57
	8H	17.10	17.47	18.03	18.40	19.54	13.27	13.64	14.20	14.57	15.72
	12H	17.24	17.56	18.17	18.49	19.68	13.39	13.72	14.32	14.64	15.84
12H	4H	16.29	16.74	17.20	17.66	18.79	12.58	13.03	13.49	13.95	15.08
	6H	16.87	17.23	17.79	18.17	19.31	13.13	13.50	14.06	14.43	15.58
	8H	17.09	17.41	18.02	18.33	19.53	13.35	13.67	14.28	14.59	15.79