

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918179

Luminaire Tested: DFN2DIP-TR3F0-090D080US930-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918179
REPORT IS A COMBINATION OF REPORTS P901874 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-090D080US930-RLLONL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12694.2 lumens
Efficiency: N/A
Efficacy: 81.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 156
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918179

CATALOG NUMBER: DFN2DIP-TR3F0-090D080US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P918179

CATALOG NUMBER: DFN2DIP-TR3F0-090D080US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	52	49	44	42	41
3	82	73	66	60	75	68	62	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	37	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	30	27
6	64	52	44	39	59	49	42	37	42	36	32	36	31	28	30	27	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	28	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3779	3779	3779
5°	3783	3716	3740
10°	3743	3640	3616
15°	3690	3516	3426
20°	3620	3348	3193
25°	3548	3159	2968
30°	3452	2966	2684
35°	3358	2758	2434
40°	3262	2544	2148
45°	3151	2307	1889
50°	3035	2068	1637
55°	2915	1813	1394
60°	2775	1547	1145
65°	2614	1276	1028
70°	2420	1024	926
75°	2174	896	838
80°	1820	741	718
85°	1238	480	525

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3151 cd/sqm

TEST NUMBER: P918179

CATALOG NUMBER: DFN2DIP-TR3F0-090D080US930-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.2	2.2
10°-20°	780.3	6.1
20°-30°	1095.5	8.6
30°-40°	1194.1	9.4
40°-50°	1097.5	8.6
50°-60°	861.9	6.8
60°-70°	561.0	4.4
70°-80°	288.8	2.3
80°-90°	77.6	0.6
90°-100°	72.6	0.6
100°-110°	270.6	2.1
110°-120°	717.6	5.7
120°-130°	1190.2	9.4
130°-140°	1264.3	10.0
140°-150°	1175.0	9.3
150°-160°	944.7	7.4
160°-170°	608.7	4.8
170°-180°	209.5	1.7
0°-30°	2159.9	17.0
0°-40°	3354.0	26.4
0°-60°	5313.5	41.9
0°-90°	6240.9	49.2
90°-120°	1060.8	8.4
90°-150°	4690.4	36.9
90°-180°	6453.0	50.8
0°-180°	12694.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3033	3033	3033	3033	3033	
5°	3033	3019	2983	3008	3000	288
15°	2884	2854	2761	2709	2682	813
25°	2618	2530	2349	2237	2196	1204
35°	2256	2116	1875	1702	1641	1412
45°	1844	1660	1372	1177	1111	1424
55°	1402	1188	892	727	675	1253
65°	947	724	478	384	376	939
75°	505	313	220	200	198	534
85°	118	60	52	52	52	135
90°	2	19	32	40	43	12
95°	104	51	62	70	68	123
105°	484	532	97	115	121	517
115°	916	943	983	245	131	902
125°	1295	1316	1346	1357	1362	1155
135°	1602	1628	1642	1658	1655	1238
145°	1859	1857	1884	1895	1887	1163
155°	2047	2032	2052	2061	2048	943
165°	2157	2147	2152	2163	2152	609
175°	2206	2195	2198	2209	2193	210
180°	2201	2201	2201	2201	2201	

TEST NUMBER: P918179

CATALOG NUMBER: DFN2DIP-TR3F0-090D080US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3032.7	3032.7	3032.7	3032.7	3032.7
2.5°	3046.4	3032.7	3002.3	3030.1	3024.5
5°	3032.7	3019.0	2983.2	3007.9	2999.7
7.5°	3007.9	2991.6	2953.2	2963.9	2950.2
10°	2975.0	2955.8	2901.1	2892.6	2876.3
12.5°	2933.9	2909.2	2835.0	2818.6	2788.3
15°	2884.4	2854.2	2761.0	2708.8	2681.5
17.5°	2826.8	2782.9	2667.5	2607.2	2563.3
20°	2761.0	2706.0	2568.8	2500.4	2439.8
22.5°	2689.7	2626.5	2467.2	2374.0	2333.0
25°	2618.3	2530.4	2349.3	2236.9	2195.5
27.5°	2533.3	2439.8	2239.5	2110.5	2047.3
30°	2442.7	2338.2	2118.6	1978.9	1904.6
32.5°	2354.7	2228.4	2003.6	1838.8	1770.1
35°	2256.1	2116.0	1874.6	1701.7	1641.1
37.5°	2160.0	2008.9	1753.8	1564.2	1495.8
40°	2058.4	1893.9	1627.4	1432.6	1361.3
42.5°	1954.1	1778.6	1501.3	1298.1	1229.6
45°	1844.4	1660.4	1372.3	1177.2	1111.4
47.5°	1740.1	1545.3	1248.9	1053.8	993.5
50°	1624.8	1430.0	1128.0	938.5	881.1
52.5°	1512.1	1306.3	1012.8	831.6	779.5
55°	1402.3	1188.3	891.9	727.4	675.2
57.5°	1290.0	1070.4	785.1	631.3	587.3
60°	1174.6	955.0	672.4	532.6	488.6
62.5°	1062.3	842.7	576.3	444.7	422.8
65°	946.9	724.5	477.5	384.3	375.9
67.5°	837.1	614.7	384.3	337.5	329.3
70°	721.9	507.8	318.3	290.9	279.8
72.5°	612.0	408.8	266.1	244.3	238.8
75°	504.9	312.7	219.6	200.3	197.7
77.5°	398.0	222.2	172.9	161.9	156.4
80°	299.1	159.3	131.6	120.8	120.8
82.5°	208.5	107.1	90.6	85.0	85.0
85°	117.9	60.3	52.1	52.1	52.1
87.5°	43.9	21.8	21.8	19.2	19.2
90°	1.5	19.1	31.8	39.9	43.0
92.5°	39.9	33.5	38.2	41.4	43.0
95°	103.5	50.9	62.0	70.2	68.5
97.5°	186.3	55.8	81.1	86.1	87.6
100°	282.0	63.8	90.8	103.5	106.6
102.5°	387.0	383.9	94.0	111.4	116.3
105°	484.2	532.1	97.2	114.6	121.1
107.5°	597.3	637.0	100.4	117.8	124.3
110°	705.7	739.0	278.8	119.5	125.8

TEST NUMBER: P918179

CATALOG NUMBER: DFN2DIP-TR3F0-090D080US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	807.6	836.2	809.2	122.5	127.5
115°	915.8	942.9	982.8	245.3	130.7
117.5°	1009.8	1041.6	1068.9	840.9	423.7
120°	1115.0	1138.8	1167.6	1186.7	971.6
122.5°	1204.0	1229.6	1261.6	1271.0	1272.8
125°	1294.9	1315.6	1345.9	1357.1	1361.8
127.5°	1377.7	1400.0	1424.1	1439.9	1441.4
130°	1455.8	1481.3	1498.8	1516.4	1514.8
132.5°	1535.5	1556.2	1573.7	1588.0	1586.5
135°	1602.4	1627.9	1642.1	1658.2	1655.0
137.5°	1672.4	1691.5	1707.6	1723.5	1718.7
140°	1740.8	1753.7	1771.2	1785.5	1777.5
142.5°	1798.4	1809.5	1830.1	1842.8	1834.8
145°	1858.9	1857.2	1884.2	1895.4	1887.4
147.5°	1911.3	1906.6	1933.6	1941.6	1935.3
150°	1962.3	1951.2	1976.7	1986.1	1978.2
152.5°	2005.3	1992.6	2016.4	2026.1	2014.9
155°	2046.7	2032.5	2051.6	2061.1	2048.4
157.5°	2080.2	2067.5	2081.9	2093.0	2080.2
160°	2108.9	2099.3	2108.9	2118.4	2107.2
162.5°	2134.3	2124.8	2132.7	2143.9	2129.6
165°	2156.6	2147.2	2151.9	2163.0	2151.9
167.5°	2174.2	2164.5	2169.4	2180.6	2166.2
170°	2188.6	2178.9	2182.1	2193.3	2178.9
172.5°	2198.0	2188.6	2191.8	2202.9	2188.6
175°	2206.0	2194.8	2198.0	2209.1	2193.3
177.5°	2209.1	2198.0	2199.7	2210.8	2196.5
180°	2201.2	2201.2	2201.2	2201.2	2201.2

TEST NUMBER: P918179

CATALOG NUMBER: DFN2DIP-TR3F0-090D080US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.64	12.46	12.61	13.44	14.73	7.61	8.44	8.58	9.42	10.70
	3H	13.30	14.04	14.29	15.03	16.34	8.79	9.53	9.78	10.52	11.83
	4H	13.91	14.60	14.90	15.59	16.91	9.24	9.94	10.24	10.93	12.25
	6H	14.32	14.96	15.32	15.96	17.29	9.56	10.20	10.56	11.20	12.52
	8H	14.44	15.05	15.45	16.06	17.39	9.64	10.25	10.66	11.27	12.59
	12H	14.50	15.08	15.51	16.09	17.43	9.69	10.26	10.70	11.27	12.62
4H	2H	11.65	12.35	12.65	13.34	14.66	8.20	8.90	9.20	9.89	11.21
	3H	13.47	14.05	14.48	15.07	16.40	9.54	10.12	10.55	11.15	12.48
	4H	14.15	14.68	15.17	15.70	17.05	10.09	10.62	11.11	11.63	12.98
	6H	14.66	15.11	15.69	16.15	17.50	10.50	10.95	11.53	11.99	13.34
	8H	14.83	15.25	15.86	16.28	17.65	10.63	11.05	11.66	12.08	13.44
	12H	14.92	15.30	15.97	16.35	17.72	10.69	11.07	11.73	12.12	13.49
8H	4H	14.12	14.54	15.15	15.58	16.94	10.36	10.79	11.39	11.82	13.18
	6H	14.68	15.03	15.73	16.10	17.46	10.87	11.22	11.92	12.29	13.66
	8H	14.89	15.19	15.95	16.25	17.63	11.06	11.37	12.12	12.42	13.80
	12H	15.02	15.29	16.08	16.34	17.76	11.17	11.44	12.24	12.50	13.92
12H	4H	14.07	14.45	15.12	15.50	16.87	10.36	10.75	11.41	11.79	13.16
	6H	14.65	14.96	15.71	16.02	17.40	10.92	11.23	11.98	12.28	13.67
	8H	14.86	15.14	15.93	16.19	17.61	11.12	11.39	12.19	12.45	13.87