

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907254

Luminaire Tested: DFN2DIP-TR3F0-090D050US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907254
REPORT IS A COMBINATION OF REPORTS P900312 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-090D050US835-RLLFLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12075.0 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 132
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907254

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P907254

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	61	60	59
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	53	51
3	85	76	69	63	80	72	65	60	64	59	54	56	52	49	49	46	44
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38
5	72	61	53	47	68	57	50	45	51	45	41	46	41	37	40	37	34
6	67	55	47	41	62	52	45	39	47	41	36	41	37	33	37	33	30
7	62	50	42	36	58	47	40	35	42	37	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24
9	54	42	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4635	4635	4635
5°	4640	4558	4588
10°	4592	4464	4435
15°	4526	4313	4202
20°	4440	4106	3916
25°	4351	3875	3640
30°	4234	3638	3292
35°	4118	3383	2986
40°	4001	3121	2635
45°	3864	2830	2318
50°	3723	2536	2008
55°	3575	2223	1710
60°	3404	1897	1405
65°	3207	1565	1261
70°	2968	1256	1136
75°	2667	1099	1027
80°	2231	909	881
85°	1518	589	644

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3864 cd/sqm

TEST NUMBER: P907254

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US835-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	348.6	2.9
10°-20°	957.0	7.9
20°-30°	1343.6	11.1
30°-40°	1464.6	12.1
40°-50°	1346.2	11.1
50°-60°	1057.2	8.8
60°-70°	688.1	5.7
70°-80°	354.2	2.9
80°-90°	94.9	0.8
90°-100°	97.8	0.8
100°-110°	310.9	2.6
110°-120°	532.1	4.4
120°-130°	699.7	5.8
130°-140°	785.4	6.5
140°-150°	770.2	6.4
150°-160°	646.1	5.4
160°-170°	428.5	3.5
170°-180°	149.8	1.2
0°-30°	2649.2	21.9
0°-40°	4113.9	34.1
0°-60°	6517.2	54.0
0°-90°	7654.5	63.4
90°-120°	940.8	7.8
90°-150°	3196.2	26.5
90°-180°	4421.0	36.6
0°-180°	12075.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3720	3720	3720	3720	3720	
5°	3720	3703	3659	3689	3679	353
15°	3538	3501	3386	3322	3289	997
25°	3212	3104	2882	2744	2693	1477
35°	2767	2595	2299	2087	2013	1732
45°	2262	2036	1683	1444	1363	1747
55°	1720	1458	1094	892	828	1537
65°	1161	889	586	471	461	1151
75°	619	384	269	246	242	655
85°	145	74	64	64	64	166
90°	1	17	47	44	45	12
95°	70	83	85	85	83	77
105°	287	291	294	296	296	303
115°	534	542	539	538	534	528
125°	777	788	785	780	779	694
135°	1004	1019	1022	1021	1017	776
145°	1220	1229	1237	1238	1233	762
155°	1394	1398	1402	1409	1405	642
165°	1517	1516	1516	1525	1518	428
175°	1578	1575	1572	1581	1573	150
180°	1581	1581	1581	1581	1581	

TEST NUMBER: P907254

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US835-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3719.7	3719.7	3719.7	3719.7	3719.7
2.5°	3736.5	3719.7	3682.5	3716.5	3709.7
5°	3719.7	3702.9	3659.0	3689.3	3679.3
7.5°	3689.3	3669.3	3622.2	3635.4	3618.6
10°	3649.0	3625.4	3558.3	3547.9	3527.9
12.5°	3598.6	3568.3	3477.2	3457.2	3420.0
15°	3537.9	3500.8	3386.5	3322.5	3289.0
17.5°	3467.2	3413.3	3271.8	3197.9	3144.0
20°	3386.5	3319.0	3150.7	3066.8	2992.5
22.5°	3299.0	3221.5	3026.1	2911.8	2861.5
25°	3211.5	3103.6	2881.5	2743.6	2692.9
27.5°	3107.2	2992.5	2746.8	2588.6	2511.1
30°	2996.1	2867.9	2598.6	2427.2	2336.1
32.5°	2888.2	2733.2	2457.5	2255.4	2171.1
35°	2767.2	2595.4	2299.3	2087.2	2012.9
37.5°	2649.3	2464.0	2151.1	1918.6	1834.7
40°	2524.7	2322.9	1996.1	1757.2	1669.7
42.5°	2396.8	2181.5	1841.4	1592.2	1508.2
45°	2262.2	2036.5	1683.2	1443.9	1363.2
47.5°	2134.3	1895.4	1531.8	1292.5	1218.6
50°	1992.9	1753.9	1383.6	1151.1	1080.7
52.5°	1854.7	1602.2	1242.2	1020.0	956.1
55°	1720.0	1457.5	1093.9	892.2	828.2
57.5°	1582.2	1312.9	962.9	774.3	720.4
60°	1440.7	1171.4	824.7	653.2	599.3
62.5°	1302.9	1033.6	706.8	545.4	518.6
65°	1161.4	888.6	585.7	471.4	461.1
67.5°	1026.8	753.9	471.4	413.9	403.9
70°	885.4	622.9	390.4	356.8	343.2
72.5°	750.7	501.4	326.4	299.6	292.9
75°	619.3	383.6	269.3	245.7	242.5
77.5°	488.2	272.5	212.1	198.6	191.8
80°	366.8	195.4	161.4	148.2	148.2
82.5°	255.7	131.4	111.1	104.3	104.3
85°	144.6	73.9	63.9	63.9	63.9
87.5°	53.9	26.8	26.8	23.6	23.6
90°	1.4	17.2	46.7	43.9	45.3
92.5°	29.6	40.0	41.5	42.9	42.9
95°	69.6	83.0	85.3	85.3	83.0
97.5°	115.8	128.2	133.5	133.5	133.5
100°	169.2	180.2	184.0	184.0	182.6
102.5°	225.5	233.6	238.8	240.3	238.8
105°	287.0	290.8	293.7	296.0	296.0
107.5°	348.0	353.7	353.7	354.7	348.0
110°	407.1	414.8	414.8	414.8	410.9

TEST NUMBER: P907254

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	471.0	479.1	477.7	473.9	471.0
115°	533.9	541.6	539.2	537.8	533.9
117.5°	596.4	606.9	600.2	596.4	592.6
120°	659.3	669.8	659.3	659.3	655.0
122.5°	716.5	729.9	723.2	719.4	716.5
125°	776.6	788.5	784.7	780.4	779.0
127.5°	835.2	850.0	844.8	839.0	835.2
130°	890.1	907.2	904.8	902.0	896.7
132.5°	951.6	964.9	965.9	959.2	955.4
135°	1004.5	1019.2	1022.1	1020.7	1016.9
137.5°	1063.6	1075.5	1077.9	1076.9	1071.2
140°	1115.5	1127.5	1134.1	1134.1	1128.9
142.5°	1168.9	1180.9	1184.7	1186.1	1180.9
145°	1219.5	1229.0	1236.6	1238.1	1232.8
147.5°	1264.8	1276.7	1282.4	1284.8	1279.5
150°	1311.5	1319.6	1324.8	1329.1	1324.8
152.5°	1353.0	1361.1	1367.7	1373.0	1367.7
155°	1394.4	1398.2	1402.5	1409.2	1404.9
157.5°	1430.2	1433.0	1435.4	1445.0	1438.3
160°	1462.1	1465.0	1466.4	1474.5	1468.8
162.5°	1491.7	1491.7	1493.1	1502.2	1495.5
165°	1517.0	1515.5	1515.5	1525.1	1518.4
167.5°	1539.8	1535.5	1535.5	1545.1	1538.4
170°	1557.0	1553.2	1551.8	1561.3	1553.2
172.5°	1568.9	1565.1	1563.7	1573.2	1565.1
175°	1578.5	1574.6	1571.8	1581.3	1573.2
177.5°	1583.7	1579.9	1577.0	1585.1	1577.0
180°	1581.3	1581.3	1581.3	1581.3	1581.3

TEST NUMBER: P907254

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.59	14.54	14.43	15.40	16.47	9.57	10.52	10.41	11.38	12.45
	3H	15.27	16.12	16.12	16.99	18.08	10.76	11.61	11.61	12.48	13.57
	4H	15.87	16.68	16.74	17.55	18.66	11.21	12.01	12.08	12.89	14.00
	6H	16.29	17.04	17.18	17.92	19.04	11.53	12.27	12.41	13.15	14.27
	8H	16.42	17.12	17.31	18.02	19.14	11.62	12.33	12.51	13.23	14.35
	12H	16.48	17.15	17.38	18.04	19.19	11.67	12.34	12.56	13.23	14.38
4H	2H	13.62	14.43	14.50	15.30	16.41	10.17	10.98	11.05	11.85	12.96
	3H	15.45	16.12	16.34	17.02	18.15	11.53	12.19	12.41	13.10	14.22
	4H	16.14	16.75	17.04	17.65	18.80	12.07	12.68	12.97	13.58	14.73
	6H	16.65	17.18	17.57	18.10	19.25	12.49	13.02	13.41	13.94	15.09
	8H	16.83	17.31	17.74	18.23	19.40	12.62	13.11	13.54	14.03	15.19
	12H	16.92	17.36	17.85	18.30	19.47	12.69	13.13	13.62	14.07	15.24
8H	4H	16.12	16.60	17.03	17.53	18.69	12.36	12.85	13.27	13.77	14.93
	6H	16.68	17.08	17.62	18.04	19.21	12.87	13.28	13.81	14.24	15.40
	8H	16.89	17.24	17.84	18.20	19.38	13.06	13.42	14.01	14.37	15.55
	12H	17.02	17.34	17.98	18.28	19.52	13.18	13.49	14.13	14.44	15.67
12H	4H	16.07	16.51	17.01	17.45	18.62	12.37	12.81	13.30	13.75	14.91
	6H	16.65	17.01	17.60	17.96	19.14	12.92	13.28	13.87	14.23	15.41
	8H	16.87	17.19	17.82	18.13	19.36	13.13	13.44	14.08	14.39	15.62