

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920739

Luminaire Tested: DFN2DIP-TR3F0-030D050US935-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920739
REPORT IS A COMBINATION OF REPORTS P901820 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-030D050US935-RLLONL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6457.5 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 61.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920739

CATALOG NUMBER: DFN2DIP-TR3F0-030D050US935-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P920739

CATALOG NUMBER: DFN2DIP-TR3F0-030D050US935-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	95	90	87	83	85	82	79	76	66	64	62	51	49	48	37	36	36
2	86	79	74	69	78	72	67	63	58	54	52	45	43	41	33	32	30
3	79	70	63	58	71	63	58	53	51	47	44	40	37	35	30	28	26
4	72	62	55	49	65	56	50	45	46	41	37	36	33	30	27	25	23
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	20	18
7	57	45	37	32	51	41	34	30	34	29	25	27	23	20	20	18	16
8	52	41	33	28	47	37	31	26	31	26	22	24	21	18	19	16	14
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1330	1330	1330
5°	1332	1308	1317
10°	1318	1281	1273
15°	1299	1238	1206
20°	1274	1178	1124
25°	1249	1112	1045
30°	1215	1044	945
35°	1182	971	857
40°	1148	896	756
45°	1109	812	665
50°	1069	728	576
55°	1026	638	491
60°	977	544	403
65°	920	449	362
70°	852	360	326
75°	765	315	295
80°	641	261	253
85°	436	169	185

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1109 cd/sqm

TEST NUMBER: P920739

CATALOG NUMBER: DFN2DIP-TR3F0-030D050US935-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.1	1.5
10°-20°	274.7	4.3
20°-30°	385.6	6.0
30°-40°	420.3	6.5
40°-50°	386.3	6.0
50°-60°	303.4	4.7
60°-70°	197.5	3.1
70°-80°	101.7	1.6
80°-90°	28.5	0.4
90°-100°	47.9	0.7
100°-110°	178.6	2.8
110°-120°	473.7	7.3
120°-130°	785.6	12.2
130°-140°	834.5	12.9
140°-150°	775.6	12.0
150°-160°	623.5	9.7
160°-170°	401.8	6.2
170°-180°	138.3	2.1
0°-30°	760.3	11.8
0°-40°	1180.7	18.3
0°-60°	1870.4	29.0
0°-90°	2198.1	34.0
90°-120°	700.2	10.8
90°-150°	3095.8	47.9
90°-180°	4259.0	66.0
0°-180°	6457.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1068	1068	1068	1068	1068	
5°	1068	1063	1050	1059	1056	101
15°	1015	1005	972	954	944	286
25°	922	891	827	787	773	424
35°	794	745	660	599	578	497
45°	649	584	483	414	391	501
55°	494	418	314	256	238	441
65°	333	255	168	135	132	330
75°	178	110	77	70	70	188
85°	42	21	18	18	18	48
90°	1	13	21	26	28	6
95°	68	34	41	46	45	81
105°	320	351	64	76	80	342
115°	604	622	649	162	86	595
125°	855	868	888	896	899	762
135°	1058	1074	1084	1094	1092	817
145°	1227	1226	1244	1251	1246	767
155°	1351	1342	1354	1360	1352	622
165°	1423	1417	1420	1428	1420	402
175°	1456	1449	1451	1458	1448	139
180°	1453	1453	1453	1453	1453	

TEST NUMBER: P920739

CATALOG NUMBER: DFN2DIP-TR3F0-030D050US935-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1067.6	1067.6	1067.6	1067.6	1067.6
2.5°	1072.4	1067.6	1056.9	1066.6	1064.7
5°	1067.6	1062.7	1050.2	1058.9	1055.9
7.5°	1058.9	1053.1	1039.6	1043.4	1038.5
10°	1047.2	1040.5	1021.2	1018.2	1012.5
12.5°	1032.8	1024.1	998.0	992.2	981.5
15°	1015.4	1004.7	971.9	953.6	943.9
17.5°	995.1	979.6	939.0	917.8	902.3
20°	971.9	952.5	904.2	880.2	858.8
22.5°	946.8	924.5	868.5	835.7	821.2
25°	921.7	890.7	827.0	787.4	772.8
27.5°	891.7	858.8	788.3	743.0	720.7
30°	859.9	823.1	745.8	696.6	670.5
32.5°	828.9	784.5	705.3	647.3	623.1
35°	794.2	744.8	659.9	599.0	577.7
37.5°	760.3	707.1	617.3	550.6	526.6
40°	724.6	666.7	572.9	504.3	479.2
42.5°	687.9	626.1	528.5	456.9	432.8
45°	649.3	584.4	483.1	414.4	391.2
47.5°	612.5	544.0	439.6	370.9	349.7
50°	572.0	503.3	397.1	330.4	310.1
52.5°	532.3	459.9	356.5	292.7	274.4
55°	493.6	418.3	313.9	256.1	237.7
57.5°	454.1	376.8	276.4	222.2	206.7
60°	413.5	336.2	236.7	187.4	172.0
62.5°	373.9	296.6	202.9	156.5	148.9
65°	333.3	255.0	168.1	135.3	132.3
67.5°	294.7	216.4	135.3	118.8	115.9
70°	254.1	178.7	112.0	102.4	98.5
72.5°	215.4	143.9	93.7	86.0	84.0
75°	177.7	110.1	77.3	70.5	69.6
77.5°	140.1	78.2	60.9	57.0	55.0
80°	105.3	56.1	46.3	42.5	42.5
82.5°	73.4	37.7	31.9	30.0	30.0
85°	41.5	21.2	18.3	18.3	18.3
87.5°	15.5	7.7	7.7	6.8	6.8
90°	1.0	12.6	21.0	26.3	28.3
92.5°	26.3	22.1	25.2	27.4	28.3
95°	68.3	33.6	41.0	46.3	45.2
97.5°	123.0	36.9	53.6	56.8	57.8
100°	186.1	42.1	59.9	68.3	70.4
102.5°	255.5	253.4	62.1	73.5	76.8
105°	319.6	351.2	64.1	75.7	79.9
107.5°	394.3	420.4	66.3	77.7	82.1
110°	465.8	487.8	184.0	78.9	83.0

TEST NUMBER: P920739

CATALOG NUMBER: DFN2DIP-TR3F0-030D050US935-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	533.0	551.9	534.1	80.9	84.1
115°	604.5	622.3	648.7	162.0	86.3
117.5°	666.5	687.5	705.5	555.0	279.7
120°	735.9	751.7	770.6	783.2	641.3
122.5°	794.7	811.6	832.7	839.0	840.1
125°	854.6	868.4	888.4	895.7	898.9
127.5°	909.3	924.0	940.0	950.4	951.4
130°	960.9	977.7	989.2	1000.8	999.9
132.5°	1013.5	1027.2	1038.6	1048.2	1047.1
135°	1057.6	1074.5	1083.8	1094.5	1092.3
137.5°	1103.8	1116.5	1127.0	1137.6	1134.5
140°	1149.0	1157.5	1169.0	1178.4	1173.3
142.5°	1187.0	1194.4	1208.0	1216.3	1211.1
145°	1226.9	1225.8	1243.6	1251.0	1245.8
147.5°	1261.5	1258.3	1276.3	1281.5	1277.4
150°	1295.2	1287.9	1304.7	1311.0	1305.7
152.5°	1323.5	1315.2	1330.9	1337.3	1329.9
155°	1350.9	1341.5	1354.1	1360.4	1352.0
157.5°	1372.9	1364.6	1374.1	1381.5	1372.9
160°	1392.0	1385.6	1392.0	1398.2	1390.9
162.5°	1408.7	1402.5	1407.6	1415.0	1405.6
165°	1423.4	1417.2	1420.3	1427.6	1420.3
167.5°	1435.0	1428.7	1431.9	1439.2	1429.8
170°	1444.5	1438.1	1440.3	1447.6	1438.1
172.5°	1450.8	1444.5	1446.6	1454.0	1444.5
175°	1456.0	1448.6	1450.8	1458.1	1447.6
177.5°	1458.1	1450.8	1451.9	1459.2	1449.7
180°	1452.8	1452.8	1452.8	1452.8	1452.8

TEST NUMBER: P920739

CATALOG NUMBER: DFN2DIP-TR3F0-030D050US935-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.38	7.10	7.47	8.18	9.67	2.36	3.07	3.45	4.16	5.64
	3H	8.04	8.68	9.14	9.77	11.27	3.53	4.17	4.63	5.26	6.77
	4H	8.64	9.24	9.75	10.34	11.85	3.97	4.58	5.08	5.67	7.18
	6H	9.05	9.60	10.16	10.70	12.22	4.28	4.84	5.40	5.94	7.46
	8H	9.16	9.69	10.28	10.81	12.32	4.37	4.90	5.49	6.01	7.52
	12H	9.22	9.72	10.34	10.83	12.36	4.41	4.91	5.53	6.01	7.55
4H	2H	6.38	6.99	7.50	8.08	9.59	2.93	3.54	4.05	4.63	6.14
	3H	8.19	8.70	9.31	9.82	11.34	4.27	4.77	5.39	5.89	7.41
	4H	8.87	9.34	10.00	10.45	11.99	4.81	5.27	5.93	6.38	7.92
	6H	9.37	9.77	10.50	10.90	12.43	5.21	5.61	6.34	6.74	8.27
	8H	9.54	9.91	10.67	11.03	12.58	5.34	5.71	6.47	6.83	8.38
	12H	9.62	9.96	10.77	11.10	12.65	5.39	5.73	6.54	6.86	8.42
8H	4H	8.83	9.20	9.96	10.32	11.87	5.07	5.44	6.20	6.57	8.11
	6H	9.38	9.69	10.53	10.85	12.40	5.58	5.88	6.73	7.05	8.59
	8H	9.59	9.86	10.75	11.01	12.57	5.76	6.03	6.92	7.18	8.74
	12H	9.72	9.95	10.88	11.10	12.70	5.87	6.11	7.03	7.25	8.85
12H	4H	8.78	9.11	9.92	10.25	11.80	5.07	5.40	6.22	6.54	8.09
	6H	9.36	9.62	10.51	10.77	12.34	5.62	5.89	6.78	7.04	8.60
	8H	9.57	9.80	10.73	10.94	12.54	5.82	6.06	6.99	7.20	8.80

END OF REPORT