

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909817

Luminaire Tested: DFN2DIP-TR3F0-030D030US840-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909817
REPORT IS A COMBINATION OF REPORTS P901791 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-030D030US840-FLLONL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5998.7 lumens
Efficiency: N/A
Efficacy: 128.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 46.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909817
CATALOG NUMBER: DFN2DIP-TR3F0-030D030US840-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P909817

CATALOG NUMBER: DFN2DIP-TR3F0-030D030US840-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47	50	48	47	42
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40	44	42	40	35
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34	39	36	34	30
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29	35	32	29	26
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26	31	28	26	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23	28	25	23	20
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20	26	23	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18	24	20	18	16
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1469	1469	1469
5°	1470	1447	1457
10°	1458	1427	1437
15°	1436	1402	1405
20°	1406	1368	1372
25°	1376	1328	1335
30°	1339	1290	1287
35°	1304	1246	1237
40°	1261	1201	1190
45°	1218	1157	1141
50°	1171	1110	1084
55°	1122	1055	1032
60°	1066	991	973
65°	1005	924	902
70°	927	843	826
75°	820	745	754
80°	690	619	620
85°	488	407	400

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1218 cd/sqm



TEST NUMBER: P909817

CATALOG NUMBER: DFN2DIP-TR3F0-030D030US840-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.0	1.8
10°-20°	312.2	5.2
20°-30°	458.8	7.6
30°-40°	532.8	8.9
40°-50°	532.2	8.9
50°-60°	464.1	7.7
60°-70°	343.1	5.7
70°-80°	194.1	3.2
80°-90°	53.0	0.9
90°-100°	33.7	0.6
100°-110°	125.7	2.1
110°-120°	333.3	5.6
120°-130°	552.9	9.2
130°-140°	587.3	9.8
140°-150°	545.8	9.1
150°-160°	438.8	7.3
160°-170°	282.8	4.7
170°-180°	97.3	1.6
0°-30°	881.9	14.7
0°-40°	1414.7	23.6
0°-60°	2411.0	40.2
0°-90°	3001.1	50.0
90°-120°	492.7	8.2
90°-150°	2178.7	36.3
90°-180°	2998.0	50.0
0°-180°	5998.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1179	1179	1179	1179	1179	
5°	1179	1174	1162	1171	1169	112
15°	1122	1116	1101	1105	1100	316
25°	1016	1007	987	990	987	467
35°	876	865	847	840	834	547
45°	713	705	688	676	671	550
55°	540	533	519	506	500	482
65°	364	357	346	336	330	360
75°	190	188	182	176	178	203
85°	46	45	44	41	40	52
90°	1	9	15	19	20	6
95°	48	24	29	33	32	57
105°	225	247	45	53	56	240
115°	425	438	456	114	61	419
125°	602	611	625	630	633	536
135°	744	756	763	770	769	575
145°	863	863	875	880	877	540
155°	951	944	953	957	952	438
165°	1002	997	1000	1005	1000	283
175°	1025	1020	1021	1026	1019	98
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P909817

CATALOG NUMBER: DFN2DIP-TR3F0-030D030US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1178.8	1178.8	1178.8	1178.8	1178.8
2.5°	1185.7	1180.0	1167.5	1178.8	1176.7
5°	1178.8	1174.4	1161.9	1170.9	1168.7
7.5°	1170.9	1164.2	1151.7	1160.8	1158.5
10°	1158.5	1150.5	1137.0	1146.0	1142.7
12.5°	1141.5	1134.7	1121.2	1126.7	1124.5
15°	1122.2	1115.5	1100.7	1105.2	1099.5
17.5°	1098.3	1091.7	1076.8	1082.5	1076.8
20°	1072.3	1065.5	1049.7	1053.0	1048.5
22.5°	1046.3	1036.1	1021.3	1021.3	1019.0
25°	1015.6	1006.6	987.3	989.6	987.3
27.5°	981.6	973.6	959.0	955.6	950.0
30°	947.7	938.6	921.6	918.2	913.6
32.5°	911.4	904.6	886.5	879.6	875.0
35°	876.3	864.9	846.8	839.9	834.2
37.5°	836.6	826.4	808.2	800.2	794.6
40°	795.8	786.7	768.5	758.4	753.9
42.5°	756.1	747.0	728.9	717.5	710.7
45°	713.1	705.1	688.0	675.6	671.1
47.5°	671.1	663.2	645.0	632.5	625.7
50°	626.8	621.2	605.3	589.5	583.8
52.5°	583.8	575.8	561.2	548.7	540.7
55°	539.7	532.8	519.2	505.6	500.0
57.5°	495.3	489.7	474.9	461.3	456.8
60°	451.1	446.7	430.8	418.3	415.0
62.5°	408.1	400.1	388.8	377.5	372.9
65°	364.0	357.1	345.8	335.6	329.9
67.5°	318.6	312.9	302.7	294.8	290.2
70°	276.6	272.1	261.9	253.9	249.4
72.5°	233.6	228.9	223.3	215.4	212.1
75°	190.4	188.2	182.5	175.7	178.0
77.5°	151.9	147.3	145.0	141.7	138.4
80°	113.4	112.2	109.9	106.5	104.3
82.5°	77.1	77.1	76.0	71.4	71.4
85°	46.5	45.3	44.2	40.8	39.7
87.5°	20.4	18.2	15.9	12.5	11.3
90°	0.7	8.9	14.7	18.6	19.9
92.5°	18.6	15.6	17.8	19.3	19.9
95°	48.1	23.6	28.8	32.6	31.8
97.5°	86.5	26.0	37.7	40.0	40.7
100°	131.0	29.6	42.2	48.1	49.6
102.5°	179.8	178.3	43.6	51.7	54.0
105°	224.9	247.1	45.1	53.2	56.2
107.5°	277.4	295.9	46.7	54.7	57.8
110°	327.8	343.3	129.5	55.5	58.5



TEST NUMBER: P909817

CATALOG NUMBER: DFN2DIP-TR3F0-030D030US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.2	388.4	375.9	57.0	59.2
115°	425.4	438.0	456.5	113.9	60.7
117.5°	469.1	483.8	496.4	390.6	196.8
120°	517.9	529.0	542.3	551.2	451.3
122.5°	559.3	571.2	586.0	590.4	591.2
125°	601.5	611.1	625.2	630.4	632.6
127.5°	640.0	650.3	661.5	668.8	669.5
130°	676.2	688.1	696.2	704.3	703.7
132.5°	713.2	722.9	730.9	737.6	736.9
135°	744.3	756.2	762.8	770.2	768.7
137.5°	776.8	785.7	793.1	800.5	798.3
140°	808.6	814.6	822.6	829.3	825.7
142.5°	835.4	840.5	850.1	856.0	852.3
145°	863.4	862.6	875.3	880.4	876.7
147.5°	887.8	885.6	898.2	901.8	898.9
150°	911.5	906.4	918.2	922.5	918.9
152.5°	931.4	925.5	936.7	941.1	935.9
155°	950.7	944.1	952.9	957.4	951.5
157.5°	966.2	960.4	967.0	972.2	966.2
160°	979.6	975.1	979.6	984.0	978.8
162.5°	991.4	986.9	990.7	995.8	989.2
165°	1001.7	997.3	999.6	1004.7	999.6
167.5°	1009.9	1005.4	1007.6	1012.9	1006.2
170°	1016.5	1012.1	1013.6	1018.8	1012.1
172.5°	1021.0	1016.5	1018.0	1023.2	1016.5
175°	1024.6	1019.5	1021.0	1026.1	1018.8
177.5°	1026.1	1021.0	1021.8	1026.9	1020.3
180°	1022.5	1022.5	1022.5	1022.5	1022.5



TEST NUMBER: P909817
 CATALOG NUMBER: DFN2DIP-TR3F0-030D030US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.56	9.42	9.52	10.39	11.66	8.13	8.99	9.09	9.96	11.24
	3H	10.21	10.98	11.18	11.96	13.26	9.74	10.51	10.71	11.50	12.79
	4H	10.79	11.52	11.77	12.51	13.81	10.32	11.06	11.31	12.04	13.34
	6H	11.18	11.86	12.18	12.85	14.16	10.72	11.39	11.71	12.38	13.69
	8H	11.29	11.93	12.28	12.93	14.25	10.82	11.46	11.82	12.47	13.78
	12H	11.33	11.94	12.33	12.94	14.28	10.86	11.47	11.86	12.47	13.80
4H	2H	9.02	9.75	10.00	10.73	12.04	8.67	9.41	9.66	10.39	11.69
	3H	10.87	11.48	11.87	12.50	13.81	10.48	11.09	11.48	12.11	13.42
	4H	11.58	12.14	12.59	13.15	14.48	11.18	11.74	12.18	12.74	14.08
	6H	12.09	12.57	13.10	13.60	14.93	11.68	12.16	12.70	13.19	14.53
	8H	12.23	12.68	13.25	13.70	15.05	11.83	12.27	12.84	13.30	14.65
	12H	12.30	12.71	13.34	13.74	15.10	11.88	12.29	12.92	13.33	14.69
8H	4H	11.77	12.22	12.79	13.25	14.60	11.42	11.86	12.43	12.89	14.24
	6H	12.39	12.76	13.43	13.83	15.18	12.03	12.41	13.08	13.47	14.82
	8H	12.61	12.93	13.66	13.99	15.35	12.24	12.57	13.29	13.62	14.99
	12H	12.73	13.02	13.79	14.07	15.48	12.35	12.64	13.41	13.69	15.10
12H	4H	11.76	12.16	12.79	13.20	14.56	11.41	11.81	12.44	12.85	14.21
	6H	12.42	12.75	13.47	13.80	15.17	12.07	12.40	13.12	13.45	14.82
	8H	12.66	12.94	13.71	13.99	15.40	12.30	12.59	13.36	13.64	15.05