

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920842

Luminaire Tested: DFN2DIP-TR3F0-070D050US935-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920842
REPORT IS A COMBINATION OF REPORTS P900308 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-070D050US935-RLLFLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8932.8 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 107.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920842
CATALOG NUMBER: DFN2DIP-TR3F0-070D050US935-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P920842

CATALOG NUMBER: DFN2DIP-TR3F0-070D050US935-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57		
1	100	96	92	89	93	89	86	83	78	75	73	67	65	63	56	55	54	49		
2	92	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	47	42		
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	42	40	36		
4	77	66	59	53	72	62	56	50	55	49	45	47	43	40	41	38	35	32		
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31	28		
6	66	54	46	40	61	51	43	38	45	39	35	39	34	31	34	30	28	25		
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	27	25	22		
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	29	25	22	20		
9	53	41	33	28	49	38	32	27	34	29	25	30	26	23	26	23	20	18		
10	49	37	30	26	46	35	29	25	32	26	23	28	24	21	25	21	19	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3104	3104	3104
5°	3107	3052	3072
10°	3075	2990	2970
15°	3031	2888	2814
20°	2973	2750	2623
25°	2914	2595	2438
30°	2835	2436	2204
35°	2758	2266	1999
40°	2679	2090	1765
45°	2588	1895	1552
50°	2493	1698	1345
55°	2394	1489	1145
60°	2279	1270	941
65°	2147	1048	844
70°	1987	841	761
75°	1786	736	688
80°	1494	609	590
85°	1017	394	432

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2588 cd/sqm



TEST NUMBER: P920842

CATALOG NUMBER: DFN2DIP-TR3F0-070D050US935-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.5	2.6
10°-20°	640.9	7.2
20°-30°	899.8	10.1
30°-40°	980.8	11.0
40°-50°	901.5	10.1
50°-60°	708.0	7.9
60°-70°	460.8	5.2
70°-80°	237.2	2.7
80°-90°	64.4	0.7
90°-100°	84.2	0.9
100°-110°	267.7	3.0
110°-120°	458.1	5.1
120°-130°	602.5	6.7
130°-140°	676.3	7.6
140°-150°	663.1	7.4
150°-160°	556.3	6.2
160°-170°	368.9	4.1
170°-180°	128.9	1.4
0°-30°	1774.1	19.9
0°-40°	2754.9	30.8
0°-60°	4364.3	48.9
0°-90°	5126.8	57.4
90°-120°	810.0	9.1
90°-150°	2751.9	30.8
90°-180°	3806.0	42.6
0°-180°	8932.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2491	2491	2491	2491	2491	
5°	2491	2480	2450	2471	2464	236
15°	2369	2344	2268	2225	2202	668
25°	2151	2078	1930	1837	1803	989
35°	1853	1738	1540	1398	1348	1160
45°	1515	1364	1127	967	913	1170
55°	1152	976	732	597	555	1029
65°	778	595	392	316	309	771
75°	415	257	180	164	162	439
85°	97	50	43	43	43	111
90°	1	15	40	38	39	9
95°	60	72	73	73	72	67
105°	247	250	253	255	255	261
115°	460	466	464	463	460	455
125°	669	679	676	672	671	598
135°	865	878	880	879	876	669
145°	1050	1058	1065	1066	1061	656
155°	1201	1204	1208	1213	1210	553
165°	1306	1305	1305	1313	1307	368
175°	1359	1356	1353	1362	1354	129
180°	1362	1362	1362	1362	1362	



TEST NUMBER: P920842

CATALOG NUMBER: DFN2DIP-TR3F0-070D050US935-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2491.0	2491.0	2491.0	2491.0	2491.0
2.5°	2502.1	2491.0	2466.1	2488.8	2484.2
5°	2491.0	2479.7	2450.3	2470.6	2463.9
7.5°	2470.6	2457.2	2425.7	2434.5	2423.3
10°	2443.6	2427.8	2382.8	2375.9	2362.5
12.5°	2409.8	2389.5	2328.6	2315.1	2290.3
15°	2369.2	2344.3	2267.8	2225.0	2202.5
17.5°	2321.9	2285.8	2191.1	2141.5	2105.4
20°	2267.8	2222.6	2110.0	2053.7	2004.0
22.5°	2209.2	2157.3	2026.4	1949.9	1916.2
25°	2150.6	2078.4	1929.6	1837.3	1803.4
27.5°	2080.8	2004.0	1839.4	1733.5	1681.6
30°	2006.4	1920.5	1740.2	1625.4	1564.4
32.5°	1934.1	1830.4	1645.7	1510.4	1453.9
35°	1853.0	1738.0	1539.8	1397.7	1348.0
37.5°	1774.2	1650.0	1440.5	1284.8	1228.6
40°	1690.7	1555.6	1336.7	1176.7	1118.1
42.5°	1605.1	1460.9	1233.1	1066.2	1010.0
45°	1514.9	1363.7	1127.2	967.0	912.9
47.5°	1429.3	1269.3	1025.8	865.6	816.1
50°	1334.5	1174.6	926.5	770.9	723.8
52.5°	1242.0	1072.9	831.8	683.0	640.2
55°	1151.8	976.0	732.5	597.4	554.7
57.5°	1059.5	879.2	644.8	518.5	482.4
60°	964.8	784.5	552.2	437.5	401.3
62.5°	872.4	692.2	473.3	365.2	347.2
65°	777.7	595.0	392.3	315.7	308.8
67.5°	687.6	504.9	315.7	277.2	270.5
70°	592.9	417.1	261.4	238.9	229.8
72.5°	502.7	335.8	218.6	200.7	196.1
75°	414.7	256.8	180.3	164.5	162.4
77.5°	326.9	182.4	142.1	132.9	128.5
80°	245.6	130.8	108.1	99.3	99.3
82.5°	171.3	88.0	74.4	69.8	69.8
85°	96.9	49.5	42.8	42.8	42.8
87.5°	36.1	17.9	17.9	15.8	15.8
90°	1.2	14.8	40.2	37.8	39.0
92.5°	25.5	34.4	35.7	36.9	36.9
95°	59.9	71.5	73.4	73.4	71.5
97.5°	99.7	110.4	114.9	114.9	114.9
100°	145.7	155.2	158.4	158.4	157.2
102.5°	194.2	201.1	205.6	206.9	205.6
105°	247.1	250.4	252.9	254.9	254.9
107.5°	299.6	304.5	304.5	305.4	299.6
110°	350.5	357.1	357.1	357.1	353.8



TEST NUMBER: P920842

CATALOG NUMBER: DFN2DIP-TR3F0-070D050US935-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	405.5	412.5	411.3	408.0	405.5
115°	459.7	466.3	464.3	463.0	459.7
117.5°	513.5	522.5	516.8	513.5	510.2
120°	567.7	576.7	567.7	567.7	564.0
122.5°	616.9	628.4	622.7	619.4	616.9
125°	668.7	678.9	675.6	671.9	670.7
127.5°	719.1	731.8	727.4	722.4	719.1
130°	766.4	781.1	779.0	776.6	772.1
132.5°	819.3	830.8	831.6	825.9	822.6
135°	864.9	877.5	880.0	878.8	875.5
137.5°	915.8	926.0	928.1	927.2	922.3
140°	960.4	970.8	976.5	976.5	972.0
142.5°	1006.4	1016.8	1020.0	1021.2	1016.8
145°	1050.0	1058.2	1064.7	1066.0	1061.4
147.5°	1089.0	1099.2	1104.1	1106.2	1101.6
150°	1129.2	1136.2	1140.6	1144.4	1140.6
152.5°	1164.9	1171.9	1177.6	1182.2	1177.6
155°	1200.6	1203.8	1207.5	1213.3	1209.6
157.5°	1231.4	1233.8	1235.9	1244.1	1238.4
160°	1258.9	1261.4	1262.6	1269.5	1264.6
162.5°	1284.4	1284.4	1285.6	1293.4	1287.6
165°	1306.1	1304.8	1304.8	1313.1	1307.3
167.5°	1325.8	1322.1	1322.1	1330.3	1324.6
170°	1340.6	1337.3	1336.1	1344.3	1337.3
172.5°	1350.8	1347.5	1346.3	1354.5	1347.5
175°	1359.1	1355.7	1353.3	1361.5	1354.5
177.5°	1363.6	1360.3	1357.8	1364.8	1357.8
180°	1361.5	1361.5	1361.5	1361.5	1361.5



TEST NUMBER: P920842
 CATALOG NUMBER: DFN2DIP-TR3F0-070D050US935-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.69	12.59	12.59	13.50	14.67	7.67	8.56	8.57	9.48	10.64
	3H	13.37	14.17	14.28	15.09	16.28	8.86	9.66	9.77	10.58	11.77
	4H	13.97	14.73	14.90	15.65	16.85	9.31	10.06	10.23	10.99	12.19
	6H	14.39	15.08	15.33	16.02	17.23	9.63	10.32	10.56	11.26	12.47
	8H	14.51	15.17	15.46	16.12	17.33	9.72	10.38	10.66	11.33	12.54
	12H	14.57	15.20	15.52	16.15	17.38	9.76	10.39	10.71	11.33	12.57
4H	2H	11.72	12.47	12.65	13.40	14.60	8.27	9.02	9.20	9.95	11.15
	3H	13.54	14.17	14.48	15.13	16.34	9.62	10.24	10.56	11.20	12.42
	4H	14.23	14.80	15.18	15.75	16.99	10.16	10.73	11.11	11.69	12.93
	6H	14.74	15.23	15.70	16.21	17.45	10.58	11.07	11.54	12.05	13.29
	8H	14.91	15.37	15.88	16.34	17.59	10.71	11.17	11.67	12.14	13.39
	12H	15.00	15.42	15.99	16.40	17.66	10.77	11.19	11.76	12.17	13.43
8H	4H	14.20	14.66	15.17	15.63	16.88	10.44	10.90	11.41	11.87	13.12
	6H	14.76	15.14	15.75	16.15	17.40	10.96	11.33	11.95	12.35	13.60
	8H	14.97	15.30	15.97	16.31	17.57	11.14	11.48	12.14	12.48	13.75
	12H	15.10	15.40	16.11	16.39	17.71	11.26	11.55	12.26	12.55	13.86
12H	4H	14.16	14.57	15.14	15.56	16.81	10.45	10.86	11.43	11.85	13.11
	6H	14.73	15.07	15.73	16.07	17.34	11.00	11.34	12.00	12.34	13.61
	8H	14.95	15.25	15.95	16.24	17.56	11.21	11.51	12.21	12.50	13.81