

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909910

Luminaire Tested: DFN2DIP-TR3F0-060D070US840-FLLFLL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P909910  
REPORT IS A COMBINATION OF REPORTS P900333 AND P897195  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR3F0-060D070US840-FLLFLL  
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 12254.7 lumens  
Efficiency: N/A  
Efficacy: 110.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 110.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9789  
Total Harmonic Distortion (THDi): 0.074  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P909910

CATALOG NUMBER: DFN2DIP-TR3F0-060D070US840-FLLFLL

### Luminous Intensity Polar Plot



TEST NUMBER: P909910

CATALOG NUMBER: DFN2DIP-TR3F0-060D070US840-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |
|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|----|----|
| RF  | 20  |     |     |     | 20 |    |    |    | 20 |    |    |    | 20 |    |    |    | 20 |
| RC  | 80  |     |     |     | 70 |    |    |    | 50 |    |    |    | 30 |    |    |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |
| 0   | 107 | 107 | 107 | 107 | 98 | 98 | 98 | 98 | 83 | 83 | 83 | 68 | 68 | 68 | 55 | 55 | 55 |
| 1   | 98  | 93  | 89  | 86  | 90 | 86 | 83 | 80 | 73 | 70 | 68 | 60 | 59 | 57 | 49 | 48 | 47 |
| 2   | 89  | 81  | 75  | 70  | 82 | 75 | 70 | 65 | 64 | 60 | 56 | 53 | 50 | 48 | 43 | 41 | 39 |
| 3   | 81  | 72  | 64  | 58  | 74 | 66 | 60 | 55 | 56 | 51 | 47 | 47 | 43 | 40 | 38 | 36 | 33 |
| 4   | 74  | 63  | 55  | 49  | 68 | 59 | 52 | 46 | 50 | 45 | 40 | 42 | 38 | 34 | 34 | 31 | 29 |
| 5   | 68  | 56  | 48  | 42  | 62 | 52 | 45 | 40 | 45 | 39 | 35 | 37 | 33 | 30 | 31 | 28 | 25 |
| 6   | 63  | 51  | 43  | 37  | 58 | 47 | 40 | 35 | 40 | 35 | 30 | 34 | 29 | 26 | 28 | 25 | 22 |
| 7   | 58  | 46  | 38  | 32  | 53 | 42 | 35 | 30 | 36 | 31 | 27 | 31 | 26 | 23 | 25 | 22 | 20 |
| 8   | 54  | 41  | 34  | 28  | 49 | 39 | 32 | 27 | 33 | 28 | 24 | 28 | 24 | 21 | 23 | 20 | 18 |
| 9   | 50  | 38  | 30  | 25  | 46 | 35 | 29 | 24 | 30 | 25 | 21 | 26 | 22 | 19 | 22 | 18 | 16 |
| 10  | 47  | 35  | 28  | 23  | 43 | 32 | 26 | 22 | 28 | 23 | 19 | 24 | 20 | 17 | 20 | 17 | 14 |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 45°  | 90°  |
|-----|------|------|------|
| 0°  | 2938 | 2938 | 2938 |
| 5°  | 2941 | 2894 | 2914 |
| 10° | 2915 | 2853 | 2873 |
| 15° | 2871 | 2804 | 2810 |
| 20° | 2812 | 2736 | 2745 |
| 25° | 2752 | 2655 | 2670 |
| 30° | 2678 | 2580 | 2575 |
| 35° | 2608 | 2492 | 2475 |
| 40° | 2522 | 2403 | 2379 |
| 45° | 2436 | 2313 | 2282 |
| 50° | 2342 | 2219 | 2169 |
| 55° | 2243 | 2110 | 2064 |
| 60° | 2132 | 1982 | 1945 |
| 65° | 2010 | 1848 | 1804 |
| 70° | 1854 | 1684 | 1652 |
| 75° | 1639 | 1489 | 1508 |
| 80° | 1380 | 1238 | 1239 |
| 85° | 974  | 816  | 801  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2436 cd/sqm

TEST NUMBER: P909910

CATALOG NUMBER: DFN2DIP-TR3F0-060D070US840-FLLFLL

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 221.9   | 1.8       |
| 10°-20°   | 624.4   | 5.1       |
| 20°-30°   | 917.5   | 7.5       |
| 30°-40°   | 1065.7  | 8.7       |
| 40°-50°   | 1064.4  | 8.7       |
| 50°-60°   | 928.1   | 7.6       |
| 60°-70°   | 686.1   | 5.6       |
| 70°-80°   | 388.2   | 3.2       |
| 80°-90°   | 108.8   | 0.9       |
| 90°-100°  | 138.3   | 1.1       |
| 100°-110° | 439.6   | 3.6       |
| 110°-120° | 752.2   | 6.1       |
| 120°-130° | 989.3   | 8.1       |
| 130°-140° | 1110.5  | 9.1       |
| 140°-150° | 1088.9  | 8.9       |
| 150°-160° | 913.5   | 7.5       |
| 160°-170° | 605.8   | 4.9       |
| 170°-180° | 211.7   | 1.7       |
| 0°-30°    | 1763.8  | 14.4      |
| 0°-40°    | 2829.5  | 23.1      |
| 0°-60°    | 4821.9  | 39.3      |
| 0°-90°    | 6004.9  | 49.0      |
| 90°-120°  | 1330.1  | 10.9      |
| 90°-150°  | 4518.8  | 36.9      |
| 90°-180°  | 6250.0  | 51.0      |
| 0°-180°   | 12254.7 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|------|------|-------|------|-------|------|------|
| 0°   | 2358 | 2358  | 2358 | 2358  | 2358 |      |
| 5°   | 2358 | 2349  | 2324 | 2342  | 2337 | 224  |
| 15°  | 2244 | 2231  | 2201 | 2210  | 2199 | 632  |
| 25°  | 2031 | 2013  | 1975 | 1979  | 1975 | 935  |
| 35°  | 1752 | 1730  | 1694 | 1680  | 1668 | 1094 |
| 45°  | 1426 | 1410  | 1376 | 1351  | 1342 | 1101 |
| 55°  | 1079 | 1066  | 1038 | 1011  | 1000 | 965  |
| 65°  | 728  | 714   | 692  | 671   | 660  | 720  |
| 75°  | 381  | 376   | 365  | 351   | 356  | 406  |
| 85°  | 93   | 91    | 88   | 82    | 79   | 104  |
| 90°  | 2    | 24    | 66   | 62    | 64   | 12   |
| 95°  | 98   | 117   | 121  | 121   | 117  | 109  |
| 105° | 406  | 411   | 415  | 419   | 419  | 428  |
| 115° | 755  | 766   | 762  | 760   | 755  | 747  |
| 125° | 1098 | 1115  | 1109 | 1103  | 1101 | 981  |
| 135° | 1420 | 1441  | 1445 | 1443  | 1438 | 1098 |
| 145° | 1724 | 1738  | 1748 | 1750  | 1743 | 1077 |
| 155° | 1972 | 1977  | 1983 | 1992  | 1986 | 907  |
| 165° | 2145 | 2143  | 2143 | 2156  | 2147 | 605  |
| 175° | 2232 | 2226  | 2222 | 2236  | 2224 | 212  |
| 180° | 2236 | 2236  | 2236 | 2236  | 2236 |      |

TEST NUMBER: P909910

CATALOG NUMBER: DFN2DIP-TR3F0-060D070US840-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|--------|--------|--------|--------|--------|--------|
| 0°     | 2357.6 | 2357.6 | 2357.6 | 2357.6 | 2357.6 |
| 2.5°   | 2371.4 | 2360.1 | 2335.0 | 2357.6 | 2353.3 |
| 5°     | 2357.6 | 2348.7 | 2323.7 | 2341.8 | 2337.4 |
| 7.5°   | 2341.8 | 2328.3 | 2303.3 | 2321.6 | 2317.0 |
| 10°    | 2317.0 | 2301.2 | 2273.9 | 2292.0 | 2285.2 |
| 12.5°  | 2282.9 | 2269.4 | 2242.2 | 2253.5 | 2249.0 |
| 15°    | 2244.3 | 2230.9 | 2201.3 | 2210.5 | 2199.2 |
| 17.5°  | 2196.8 | 2183.3 | 2153.7 | 2164.9 | 2153.7 |
| 20°    | 2144.6 | 2131.1 | 2099.3 | 2106.1 | 2097.2 |
| 22.5°  | 2092.6 | 2072.1 | 2042.6 | 2042.6 | 2038.0 |
| 25°    | 2031.2 | 2013.3 | 1974.7 | 1979.0 | 1974.7 |
| 27.5°  | 1963.2 | 1947.3 | 1917.9 | 1911.3 | 1900.0 |
| 30°    | 1895.4 | 1877.0 | 1843.2 | 1836.4 | 1827.3 |
| 32.5°  | 1822.7 | 1809.3 | 1772.9 | 1759.2 | 1750.1 |
| 35°    | 1752.5 | 1729.9 | 1693.5 | 1679.8 | 1668.5 |
| 37.5°  | 1673.1 | 1652.6 | 1616.4 | 1600.4 | 1589.1 |
| 40°    | 1591.5 | 1573.3 | 1537.0 | 1516.8 | 1507.6 |
| 42.5°  | 1512.2 | 1493.9 | 1457.8 | 1435.0 | 1421.5 |
| 45°    | 1426.1 | 1410.2 | 1376.0 | 1351.3 | 1342.1 |
| 47.5°  | 1342.1 | 1326.3 | 1290.0 | 1265.0 | 1251.4 |
| 50°    | 1253.6 | 1242.3 | 1210.6 | 1178.8 | 1167.5 |
| 52.5°  | 1167.5 | 1151.7 | 1122.3 | 1097.3 | 1081.5 |
| 55°    | 1079.2 | 1065.5 | 1038.3 | 1011.2 | 999.9  |
| 57.5°  | 990.8  | 979.5  | 949.9  | 922.7  | 913.5  |
| 60°    | 902.2  | 893.3  | 861.6  | 836.6  | 829.8  |
| 62.5°  | 816.1  | 800.2  | 777.6  | 755.0  | 745.9  |
| 65°    | 727.8  | 714.2  | 691.6  | 671.1  | 659.7  |
| 67.5°  | 637.1  | 625.6  | 605.4  | 589.6  | 580.4  |
| 70°    | 553.2  | 544.1  | 523.6  | 507.8  | 498.9  |
| 72.5°  | 467.1  | 458.0  | 446.7  | 430.8  | 424.0  |
| 75°    | 380.7  | 376.5  | 364.9  | 351.4  | 356.0  |
| 77.5°  | 303.8  | 294.7  | 290.0  | 283.4  | 276.6  |
| 80°    | 226.8  | 224.4  | 219.8  | 213.1  | 208.5  |
| 82.5°  | 154.2  | 154.2  | 152.0  | 142.9  | 142.9  |
| 85°    | 92.8   | 90.7   | 88.5   | 81.5   | 79.4   |
| 87.5°  | 40.9   | 36.4   | 31.7   | 25.0   | 22.6   |
| 90°    | 2.0    | 24.2   | 66.0   | 62.0   | 64.0   |
| 92.5°  | 41.8   | 56.7   | 58.7   | 60.7   | 60.7   |
| 95°    | 98.4   | 117.2  | 120.7  | 120.7  | 117.2  |
| 97.5°  | 163.8  | 181.3  | 188.7  | 188.7  | 188.7  |
| 100°   | 239.2  | 254.8  | 260.1  | 260.1  | 258.1  |
| 102.5° | 318.8  | 330.2  | 337.7  | 339.7  | 337.7  |
| 105°   | 405.8  | 411.1  | 415.2  | 418.6  | 418.6  |
| 107.5° | 492.0  | 500.1  | 500.1  | 501.5  | 492.0  |
| 110°   | 575.6  | 586.4  | 586.4  | 586.4  | 581.0  |

TEST NUMBER: P909910

CATALOG NUMBER: DFN2DIP-TR3F0-060D070US840-FLLFLL

**CANDELA DISTRIBUTION (continued):**

|        | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|--------|--------|--------|--------|--------|--------|
| 112.5° | 665.9  | 677.4  | 675.4  | 669.9  | 665.9  |
| 115°   | 754.9  | 765.7  | 762.3  | 760.3  | 754.9  |
| 117.5° | 843.1  | 858.0  | 848.6  | 843.1  | 837.8  |
| 120°   | 932.1  | 947.0  | 932.1  | 932.1  | 926.0  |
| 122.5° | 1013.0 | 1031.9 | 1022.5 | 1017.0 | 1013.0 |
| 125°   | 1097.9 | 1114.8 | 1109.4 | 1103.4 | 1101.4 |
| 127.5° | 1180.8 | 1201.7 | 1194.4 | 1186.3 | 1180.8 |
| 130°   | 1258.4 | 1282.6 | 1279.3 | 1275.3 | 1267.8 |
| 132.5° | 1345.3 | 1364.2 | 1365.5 | 1356.1 | 1350.7 |
| 135°   | 1420.2 | 1441.0 | 1445.1 | 1443.0 | 1437.6 |
| 137.5° | 1503.7 | 1520.6 | 1523.9 | 1522.6 | 1514.5 |
| 140°   | 1577.2 | 1594.1 | 1603.5 | 1603.5 | 1596.1 |
| 142.5° | 1652.6 | 1669.5 | 1674.9 | 1676.9 | 1669.5 |
| 145°   | 1724.1 | 1737.6 | 1748.4 | 1750.4 | 1743.0 |
| 147.5° | 1788.2 | 1805.0 | 1813.1 | 1816.4 | 1809.1 |
| 150°   | 1854.2 | 1865.6 | 1873.1 | 1879.2 | 1873.1 |
| 152.5° | 1912.8 | 1924.3 | 1933.7 | 1941.2 | 1933.7 |
| 155°   | 1971.5 | 1976.8 | 1983.0 | 1992.4 | 1986.3 |
| 157.5° | 2022.1 | 2026.1 | 2029.4 | 2043.0 | 2033.5 |
| 160°   | 2067.2 | 2071.2 | 2073.3 | 2084.7 | 2076.6 |
| 162.5° | 2109.0 | 2109.0 | 2111.0 | 2123.7 | 2114.4 |
| 165°   | 2144.7 | 2142.6 | 2142.6 | 2156.2 | 2146.7 |
| 167.5° | 2177.1 | 2171.0 | 2171.0 | 2184.4 | 2175.0 |
| 170°   | 2201.3 | 2196.0 | 2193.9 | 2207.4 | 2196.0 |
| 172.5° | 2218.2 | 2212.7 | 2210.7 | 2224.2 | 2212.7 |
| 175°   | 2231.6 | 2226.2 | 2222.2 | 2235.6 | 2224.2 |
| 177.5° | 2239.1 | 2233.6 | 2229.6 | 2241.1 | 2229.6 |
| 180°   | 2235.6 | 2235.6 | 2235.6 | 2235.6 | 2235.6 |

TEST NUMBER: P909910

CATALOG NUMBER: DFN2DIP-TR3F0-060D070US840-FLLFLL

**CIE UGR TABLE:**

| Reflectances:   |      |                  |       |       |       |       |                |       |       |       |       |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|-------|-------|-------|-------|
| Ceiling         |      | 0.7              | 0.7   | 0.5   | 0.5   | 0.3   | 0.7            | 0.7   | 0.5   | 0.5   | 0.3   |
| Wall            |      | 0.5              | 0.3   | 0.5   | 0.3   | 0.3   | 0.5            | 0.3   | 0.5   | 0.3   | 0.3   |
| Reference plane |      | 0.2              | 0.2   | 0.2   | 0.2   | 0.2   | 0.2            | 0.2   | 0.2   | 0.2   | 0.2   |
| Room dimensions |      | Viewed crosswise |       |       |       |       | Viewed endwise |       |       |       |       |
| X=2H            | Y=2H | 10.87            | 11.72 | 11.84 | 12.70 | 13.99 | 10.44          | 11.29 | 11.41 | 12.27 | 13.56 |
|                 | 3H   | 12.52            | 13.28 | 13.50 | 14.27 | 15.58 | 12.05          | 12.82 | 13.03 | 13.81 | 15.11 |
|                 | 4H   | 13.10            | 13.82 | 14.09 | 14.82 | 16.13 | 12.63          | 13.36 | 13.62 | 14.35 | 15.67 |
|                 | 6H   | 13.49            | 14.16 | 14.49 | 15.16 | 16.49 | 13.02          | 13.69 | 14.02 | 14.69 | 16.02 |
|                 | 8H   | 13.59            | 14.23 | 14.60 | 15.24 | 16.57 | 13.13          | 13.76 | 14.13 | 14.78 | 16.10 |
|                 | 12H  | 13.64            | 14.24 | 14.65 | 15.25 | 16.60 | 13.16          | 13.77 | 14.18 | 14.78 | 16.13 |
| 4H              | 2H   | 11.33            | 12.05 | 12.32 | 13.04 | 14.36 | 10.98          | 11.71 | 11.98 | 12.70 | 14.02 |
|                 | 3H   | 13.18            | 13.79 | 14.19 | 14.81 | 16.14 | 12.79          | 13.40 | 13.80 | 14.42 | 15.75 |
|                 | 4H   | 13.89            | 14.44 | 14.90 | 15.46 | 16.81 | 13.49          | 14.04 | 14.50 | 15.05 | 16.41 |
|                 | 6H   | 14.39            | 14.87 | 15.42 | 15.91 | 17.26 | 13.99          | 14.47 | 15.01 | 15.50 | 16.85 |
|                 | 8H   | 14.54            | 14.98 | 15.56 | 16.01 | 17.38 | 14.13          | 14.58 | 15.16 | 15.61 | 16.97 |
|                 | 12H  | 14.61            | 15.01 | 15.65 | 16.05 | 17.42 | 14.19          | 14.59 | 15.24 | 15.64 | 17.01 |
| 8H              | 4H   | 14.08            | 14.52 | 15.11 | 15.56 | 16.92 | 13.72          | 14.17 | 14.75 | 15.20 | 16.56 |
|                 | 6H   | 14.70            | 15.07 | 15.75 | 16.14 | 17.50 | 14.34          | 14.71 | 15.39 | 15.78 | 17.14 |
|                 | 8H   | 14.91            | 15.24 | 15.97 | 16.30 | 17.68 | 14.55          | 14.87 | 15.61 | 15.93 | 17.31 |
|                 | 12H  | 15.04            | 15.32 | 16.10 | 16.38 | 17.80 | 14.66          | 14.95 | 15.72 | 16.00 | 17.42 |
| 12H             | 4H   | 14.06            | 14.47 | 15.11 | 15.51 | 16.88 | 13.72          | 14.12 | 14.76 | 15.16 | 16.53 |
|                 | 6H   | 14.73            | 15.05 | 15.79 | 16.11 | 17.49 | 14.38          | 14.70 | 15.44 | 15.76 | 17.14 |
|                 | 8H   | 14.96            | 15.25 | 16.02 | 16.30 | 17.72 | 14.61          | 14.89 | 15.67 | 15.95 | 17.37 |

END OF REPORT